

Digi-Key 零件编号	说明	封装	1	25	100	
MAX856CSA+ND	3.3V/5V 或可调输出升压 DC/DC 转换器*	3.3V/5V or Adj. Output, Step-Up DC/DC Converter*	8-SOIC	4.13	3.12	1.83
MAX860ISA+ND	50mA 可选频率开关电容电压转换器*	50mA, Freq. Selectable, Switched-Cap Voltage Converter*	8-SOIC	3.74	2.82	1.66
MAX865EUA+ND	紧凑型双路输出充电器*	Compact, Dual-Output Charge Pump*	8-µMAX	3.60	2.72	1.60
MAX868EUB+ND	稳压可调 -2x 反转充电器*	Regulated, Adjustable -2x Inverting Charge Pump*	10-µMAX	4.51	3.40	2.00
MAX873ACA-ND	2.5V 低功率低源精密电压基准	2.5V, Low Power, Low-Drift, Precision Voltage Reference	8-SOIC	13.86	10.46	6.15
MAX881REUB+ND	低噪声偏压电源*	Low Noise Bias Supply*	10-µMAX	5.06	3.82	2.24
MAX882CSA+ND	5V/3.3V 可调式低压降线性稳压器*	5V/3.3V Adjustable Low Dropout Linear Regulator*	8-SOIC	4.11	3.10	1.83
MAX882ESA+ND	5V/3.3V 可调式低压降线性稳压器*	5V/3.3V Adjustable Low Dropout Linear Regulator*	8-SOIC	5.22	3.94	2.53
MAX883CSA+ND	5V 或可调, 低压降 IQ 200mA 线性稳压器*	5V or Adj., LDO, Low IQ, 200mA Linear Regulator*	8-SOIC	4.11	3.10	1.83
MAX889RESA+ND	0.5MHz, 稳压, 200mA, 反转充电器*	0.5MHz, Regulated, 200mA, Inverting Charge Pump*	8-SOIC	5.86	4.42	2.60
MAX889TESA+ND	2MHz, 稳压, 200mA, 反转充电器*	2MHz, Regulated, 200mA, Inverting Charge Pump*	8-SOIC	5.86	4.42	2.60
MAX892LEUA+ND	带有热关断功能的限流高端 P 沟道开关*	Current-Limited, High-Side P-Ch. Switch with Thermal SD*	8-µMAX	3.42	2.58	1.81
MAX901BCSE+ND	四路高速低功耗电压比较器*	Quad High Speed Low Power, Voltage Comparator*	16-SOIC	12.40	9.36	6.00
MAX902CSD+ND	双路高速低功耗电压比较器*	Dual High Speed Ultra Low Power, Voltage Comparator*	14-SOIC	10.26	7.74	4.97
MAX907CPA+ND	双路高速超低功耗电压比较器 +5V TTL 比较器*	Dual High Speed Ultra Low Power, Single +5V, TTL Comp*	8-Dip	4.27	3.22	2.07
MAX907CSA+ND	双路高速超低功耗电压比较器 +5V TTL 比较器*	Dual High Speed Ultra Low Power, Single +5V, TTL Comp*	8-SOIC	4.27	3.22	2.07
MAX908CPA+ND	四路高速超低功耗电压比较器*	Quad High Speed Ultra LP, Single +5V, TTL Comparator*	14-Dip	7.42	5.60	3.60
MAX913CPA+ND	单路超快低功耗精密 TTL 比较器*	Single, Ultra-Fast, Low Power Precision TTL Comparator*	8-Dip	6.39	4.82	2.83
MAX913CSA+ND	单路超快低功耗精密 TTL 比较器*	Single, Ultra-Fast, Low Power Precision TTL Comparator*	8-SOIC	6.36	4.80	2.83
MAX913ESA+ND	单路超快低功耗精密 TTL 比较器*	Single, Ultra-Fast, Low Power Precision TTL Comparator*	8-SOIC	8.29	6.26	4.97
MAX921CSA+ND	带基准的低功耗比较器*	Low Power Comparator with Reference*	8-SOIC	3.98	3.00	1.92
MAX922CSA+ND	超低功耗单/双源比较器*	Ultra Low Power, Single/Dual Supply Comparator*	8-SOIC	3.76	2.84	1.67
MAX923CSA+ND	带 1% 精密基准的双路超低功耗电压比较器*	Dual Ultra Low Power, Single Supply Comparator with 1% Precision with Reference*	8-SOIC	4.88	3.68	2.37
MAX924CSE-ND	带 1% 精密基准的四路超低功耗电压比较器*	Quad Ultra Low Power, Single Supply Comparator with 1% Precision with Reference	16-SOIC	5.64	4.26	2.74
MAX924CSE+ND	带 1% 精密基准的四路超低功耗电压比较器*	Quad Ultra Low Power, Single Supply Comparator with 1% Precision with Reference*	16-SOIC	5.64	4.26	2.74
MAX931CPA+ND	超低功耗比较器*	Ultra Low Power Comparator*	8-Dip	2.46	1.86	1.20
MAX932CSA+ND	带 2% 精密基准的双路超低功耗电压比较器*	Dual Ultra LP Single Supply Comparator with 2% Precision with Reference*	8-SOIC	3.15	2.38	1.53
MAX933CPA+ND	带 2% 精密基准的双路超低功耗电压比较器*	Dual Ultra LP Single Supply Comparator with 2% Precision with Reference*	8-Dip	3.15	2.38	1.40
MAX934CSE+ND	带 2% 精密基准的四路超低功耗电压比较器*	Quad Ultra LP Single Supply Comparator with 2% Precision with Reference*	16-SOIC	2.99	2.26	1.45
MAX941CSA+ND	单路 3V/5V 单电源 75ns 清摆幅输入比较器*	Single, 3V/5V, Single Supply, 75ns, Rail-to-Rail Input Comparator*	8-SOIC	3.45	2.60	1.68
MAX941EUA+ND	单路 3V/5V 单电源 75ns 清摆幅输入比较器*	Single, 3V/5V, Single Supply, 75ns, Rail-to-Rail Input Comparator*	8-µMAX	4.29	3.24	2.30
MAX942CSA+ND	双路 3V/5V 单电源 75ns 清摆幅输入比较器*	Dual, 3V/5V, Single Supply, 75ns, Rail-to-Rail Input Comparator*	8-SOIC	3.71	2.80	1.80
MAX942ESA+ND	双路 3V/5V 单电源 75ns 清摆幅输入比较器*	Dual, 3V/5V, Single Supply, 75ns, Rail-to-Rail Input Comparator*	8-SOIC	4.61	3.48	2.46
MAX944CSD+ND	四路 3V/5V 单电源 75ns 清摆幅输入比较器*	Quad, 3V/5V, Single Supply, 75ns, Rail-to-Rail Input Comparator*	14-SOIC	6.15	4.64	2.98
MAX961ESA+ND	+3V/+5V 超摆幅比较器*	+3V/+5V, Beyond-the-Rails Comparator*	8-SOIC	6.63	5.00	2.94
MAX964EEE+ND	四路超高速 +3V/+5V 超摆幅比较器*	Quad, Ultra HS, +3V/+5V, Beyond-the-Rails Comparator*	16-GSQP	15.13	11.42	6.72
MAX966EEE+ND	四路超高速 +3V/+5V 超摆幅比较器*	Quad, Micropower, Ultra Low Voltage, Rail-to-Rail, In/Out Comparator*	16-GSQP	5.09	3.84	2.70
MAX971CSA-ND	1% 精度单路超低功耗电压比较器*	Single, Ultra Low Power, Open-Output Comparator with 1% Accuracy	8-SOIC	3.95	2.98	1.91
MAX971CSA+ND	1% 精度单路超低功耗电压比较器*	Single, Ultra Low Power, Open-Output Comparator with 1% Accuracy*	8-SOIC	3.95	2.98	1.91
MAX975EUA+ND	带自动待机模式的 +3V/+5V 双速比较器*	+3V/+5V Dual Speed Comparator with Auto Standby*	8-µMAX	5.17	3.90	2.50
MAX987EUK-TCT-ND	高速低功耗电压清摆幅输入/输出比较器*	High Speed, Micropower, Low Voltage Rail-to-Rail In/Out Comparator	SOT-23-5	2.52	1.90	1.67
MAX987EUK-TTR-ND	高速低功耗电压清摆幅输入/输出比较器*	High Speed, Micropower, Low Voltage Rail-to-Rail In/Out Comparator	SOT-23-5	3800.00/2,500		
MAX987EUK+TCT-ND	高速低功耗电压清摆幅输入/输出比较器*	High Speed, Micropower, Low Voltage Rail-to-Rail In/Out Comparator*	SOT-23-5	2.52	1.90	1.67
MAX987EUK+TTR-ND	高速低功耗电压清摆幅输入/输出比较器*	High Speed, Micropower, Low Voltage Rail-to-Rail In/Out Comparator*	SOT-23-5	3800.00/2,500		
MAX998EUT+TCT-ND	单电源高速低功耗电压比较器*	Single Supply, High Speed, Low Power Comparator*	SOT-23-6	6.44	4.86	4.26
MAX998EUT+TTR-ND	单电源高速低功耗电压比较器*	Single Supply, High Speed, Low Power Comparator*	SOT-23-6	9720.00/2,500		
MAX999EUA+TCT-ND	单路超高速 +3V/+5V 超摆幅比较器*	Single, Ultra High Speed, +3V/+5V, Beyond-the-Rails Comparator*	SOT-23-5	7.47	5.64	4.94
MAX999EUA+TTR-ND	单路超高速 +3V/+5V 超摆幅比较器*	Single, Ultra High Speed, +3V/+5V, Beyond-the-Rails Comparator*	SOT-23-5	11280.00/2,500		
MAX1232CPA+ND	微处理器监控器*	Microprocessor Monitor*	8-Dip	3.52	2.66	1.82
MAX1232CSA+ND	微处理器监控器*	Microprocessor Monitor*	8-SOIC	3.52	2.66	1.82
MAX1232EPA+ND	高温微处理器监控器*	Microprocessor Monitor High Temperature*	8-Dip	4.40	3.32	2.28
MAX1232ESA+ND	高温微处理器监控器*	Microprocessor Monitor High Temperature*	8-SOIC	4.58	3.46	2.37
MAX1406CPE+ND	230kbps 3 个发射器/3 个接收器, ESD 保护*	230kbps, 3 Transmitters/3 Receivers, ESD Protected*	16-Dip	3.07	2.32	1.36
MAX1406CWE+ND	230kbps 3 个发射器/3 个接收器, ESD 保护*	230kbps, 3 Transmitters/3 Receivers, ESD Protected*	16-SOIC	3.07	2.32	1.36
MAX1472AKA+TCT-ND	300MHz/450MHz 低功耗, ASK 发射器*	300MHz/450MHz Low Power, ASK Transmitter*	SOT-23-8	3.13	2.57	2.04
MAX1472AKA+TTR-ND	300MHz/450MHz 低功耗, ASK 发射器*	300MHz/450MHz Low Power, ASK Transmitter*	SOT-23-8	4720.00/2,500		
MAX1473EUI+ND	315MHz/433MHz ASK 超差接收器*	315MHz/433MHz ASK Superheterodyne Receiver*	28-TSSOP	5.46	4.12	2.64
MAX1479ATE+ND	300MHz/450MHz 低功耗, ASK/FSK 发射器*	300MHz/450MHz Low Power, ASK/FSK Transmitter*	16-TQFN-EP	3.15	2.38	1.53
MAX1585ETJ+ND	5 通道薄型 DSC 电源*	5-Channel Slim DSC Power Supply*	32-DFN	7.08	5.34	3.15
MAX1615EUK+TCT-ND	高压低功耗线性稳压器*	High Voltage, Low Power Linear Regulator*	SOT-23-5	1.93	1.46	1.28
MAX1615EUK+TTR-ND	高压低功耗线性稳压器*	High Voltage, Low Power Linear Regulator*	SOT-23-5	2920.00/2,500		
MAX1617AME+ND	带 SMBus 串行接口的远程/本地温度传感器*	Remote/Local Temp. Sensor with SMBus Serial Interface*	16-GSQP	10.12	7.64	4.49
MAX1617MEE+ND	带 SMBus 串行接口的远程/本地温度传感器*	Remote/Local Temp. Sensor with SMBus Serial Interface*	16-GSQP	10.12	7.64	4.49
MAX1623EAP+ND	同步整流低压降稳压器*	Sync. Rectification, Low Voltage, Step-Down Regulator*	20-SSOP	11.74	8.86	5.20
MAX1628ESA+ND	3.3V/5V 高效升降 DC/DC 控制器*	3.3V/5V, High-Efficiency Step-Down DC/DC Controller*	8-SOIC	4.61	3.48	2.06
MAX1627ESA+ND	可调式高效升降 DC/DC 控制器*	Adj., High-Efficiency Step-Down DC/DC Controller*	8-SOIC	4.61	3.48	2.06
MAX1644EAE+ND	同步整流降压稳压器*	Sync. Rectification, Step-Down Regulator*	16-SSOP	10.02	7.56	4.45
MAX1644EAE-ND	同步整流降压稳压器*	Sync. Rectification, Step-Down Regulator*	16-SSOP	10.02	7.56	4.45
MAX1649CSA+ND	5V 高效降压升降 DC/DC 控制器*	5V, High-Efficiency LDO Step-Down DC/DC Controller*	8-SOIC	4.96	3.74	2.19
MAX1649ESA+ND	5V 高效降压升降 DC/DC 控制器*	5V, High-Efficiency LDO Step-Down DC/DC Controller*	8-SOIC	6.23	4.70	2.77
MAX1655EEE+ND	高效 PWM 升降 DC/DC 控制器*	High-Efficiency, PWM Step-Down DC/DC Controller*	16-GSQP	9.54	7.20	4.24
MAX1658ESA+ND	350mA 16.5V 输入/降压线性稳压器*	350mA, 16.5V Input, LDO Linear Regulator*	8-SOIC	5.06	3.82	2.24
MAX1668MEE+ND	多通道远程/本地温度传感器*	Multi Channel Remote/Local Temperature Sensor*	16-GSQP	9.86	7.44	4.37
MAX1672EEE+ND	升压/降压 DC/DC 转换器*	Step-Up/Down DC/DC Converter*	16-GSQP	6.84	5.16	3.03
MAX1673ESA+ND	可调式 125mA 输出充电器 DC/DC 反相器*	Regulator 125mA Output, Charge-Pump DC/DC Inverter*	8-SOIC	5.33	4.02	2.36
MAX1674EUA+ND	紧凑型高效升压 DC/DC 转换器*	Compact, High-Efficiency, Step-Up DC/DC Converter*	8-µMAX	5.06	3.82	2.24
MAX1675EUA+ND	升压 DC/DC 转换器*	Step-Up DC/DC Converter*	8-µMAX	5.06	3.82	2.24
MAX1676EUA+ND	紧凑型高效升压 DC/DC 转换器*	Compact, High-Efficiency, Step-Up DC/DC Converter*	10-µMAX	5.43	4.10	2.41
MAX1681ESA+ND	125mA 开关电容电压转换器*	125mA, Switched-Capacitor Voltage Converter*	8-SOIC	5.33	4.02	2.36
MAX1684EEE+ND	300kHz 14V 输入, 1A PWM 升降转换器*	300kHz, 14V Input, 1A, PWM Step-Down Converter*	16-GSQP	8.56	6.46	3.79
MAX1685EEE+ND	600kHz 14V 输入, 1A PWM 升降转换器*	600kHz, 14V Input, 1A, PWM Step-Down Converter*	16-GSQP	8.56	6.46	3.79
MAX1692EUB+ND	升降稳压器*	Step-Down Regulator*	10-µMAX	6.31	4.76	2.80
MAX1709ESE+ND	4A 低噪声高频升压 DC/DC 转换器*	4A, Low-Noise, High-Freq. Step-Up DC/DC Converter*	16-SOIC	9.73	7.34	4.32
MAX1715EEI+ND	笔记本电脑用超高效双路升降转换器*	Ultra High Efficiency, Dual Step-Down Controller for Notebook Computers*	28-GSQP	8.11	6.12	4.23
MAX1724EZK33+TCT-ND	3.3V 升压 DC/DC 转换器*	3.3V, Step-Up DC/DC Converter*	SOT-23-5	3.63	2.74	2.40
MAX1724EZK33+TTR-ND	3.3V 升压 DC/DC 转换器*	3.3V, Step-Up DC/DC Converter*	SOT-23-5	5480.00/2,500		
MAX1724EZK50+TCT-ND	5V 升压 DC/DC 转换器*	5V, Step-Up DC/DC Converter*	SOT-23-5	3.63	2.74	2.40
MAX1724EZK50+TTR-ND	5V 升压 DC/DC 转换器*	5V, Step-Up DC/DC Converter*	SOT-23-5	5480.00/2,500		
MAX1737EEI+ND	独立开关模式锂离子充电器控制器*	Stand-Alone Switch-Mode Lithium-Ion Battery Charger Controller*	28-GSQP	7.76	5.86	3.45
MAX1745EUB+ND	高压升降 DC/DC 控制器*	High Voltage, Step-Down DC/DC Controller*	10-µMAX	7.50	5.66	3.99
MAX1758EAI+ND	带内部 28V 开关的独立开关模式锂离子充电器*	Stand-Alone Switch-Mode Lithium-Ion Battery Charger with Internal 28V Switch*	28-SSOP	9.59	7.24	4.26
MAX1759EUB+ND	降压/升压稳压充电器*	Buck/Boost Regulating Charge Pump*	10-µMAX	6.33	4.78	2.81
MAX1760EUB+ND	0.8A, 低噪声, 1MHz 升压 DC/DC 转换器*	0.8A, Low-Noise, 1MHz, Step-Up DC/DC Converter*	10-µMAX	6.97	5.26	3.09
MAX1771CPA+ND	12V 或可调输出升压 DC/DC 转换器, 90% 效率*	12V or Adj. Out Step-Up DC/DC Converter 90% Efficient*	8-Dip	4.45	3.36	2.15
MAX1771CSA+ND	12V 或可调输出升压 DC/DC 转换器, 90% 效率*	12V or Adj. Out Step-Up DC/DC Converter 90% Efficient*	8-SOIC	4.88	3.68	2.16
MAX1771ESA+ND	12V 或可调输出升压 DC/DC 转换器, 90% 效率*	12V or Adj. Out Step-Up DC/DC Converter 90% Efficient*	8-SOIC	6.65	5.02	2.95
MAX1772EEI+ND	多种化学电池充电器构建块*	Multichemistry Battery-Charger Building Block*	28-GSQP	12.40	9.36	5.50

* 符合 RoHS 规范要求

(续下页)

★ 欢迎来电查询, 大批量订购, 价格优惠! ★

全部产品均以美元计价。

免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)

1244 (CN082-09)

digikey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686