



阻抗 100MHz (Ω) ±25%	最大 电流 (A)	最大 Rdc (Ω)	材质	Digi-Key 零件编号	剪切带 价格			带卷*		TDK 零件编号
					10	50	100	数量	价格	
80	0.10	1.5	D	445-3333-1-ND	1.36	5.88	10.86	15,000	63.00/M	MMZ0603D800C
10	0.20	0.8	F	445-3334-1-ND‡	1.36	5.88	10.86	15,000	63.00/M	MMZ0603F100C
10	0.50	0.15		445-2141-1-ND‡	1.40	6.05	11.16	15,000	65.12/M	MMZ0603S100C
80	0.20	0.5		445-2142-1-ND	1.40	6.05	11.16	15,000	65.12/M	MMZ0603S800C
120	0.20	0.8	S	445-2143-1-ND	1.40	6.05	11.16	15,000	65.12/M	MMZ0603S121C
240	0.10	1.0		445-2144-1-ND	1.40	6.05	11.16	15,000	65.12/M	MMZ0603S241C
470	0.05	1.8		445-2145-1-ND	1.40	6.05	11.16	15,000	65.00/M	MMZ0603S471C
600	0.05	2.0		445-2146-1-ND	1.40	6.05	11.16	15,000	65.12/M	MMZ0603S601C
120	0.20	0.8		445-2147-1-ND	1.40	6.05	11.16	15,000	65.12/M	MMZ0603Y121C
240	0.10	1.0	Y	445-2148-1-ND	1.40	6.05	11.16	15,000	65.12/M	MMZ0603Y241C
470	0.05	1.8		445-2149-1-ND	1.40	6.05	11.16	15,000	65.12/M	MMZ0603Y471C
MMZ1005 系列 - 0402 尺寸										
80	0.45	0.2	B	445-3335-1-ND	.57	2.47	4.57	10,000	27.00/M	MMZ1005B800C
120	0.40	0.25		445-3336-1-ND	.57	2.47	4.57	10,000	27.00/M	MMZ1005B121C
600	0.20	0.8		445-3343-1-ND	.57	2.47	4.57	10,000	27.00/M	MMZ1005B601C
10	0.50	0.1		445-3338-1-ND‡	.57	2.47	4.57	10,000	27.00/M	MMZ1005D100C
22	0.40	0.2		445-3339-1-ND	.57	2.47	4.57	10,000	27.00/M	MMZ1005D220C
33	0.40	0.35		445-3340-1-ND	.57	2.47	4.57	10,000	27.00/M	MMZ1005D330C
68	0.40	0.55	D	445-3341-1-ND	.57	2.47	4.57	10,000	27.00/M	MMZ1005D680C
120	0.35	0.75		445-3342-1-ND	.57	2.47	4.57	10,000	27.00/M	MMZ1005D121C
240	0.20	1.2		445-3343-1-ND	.57	2.47	4.57	10,000	27.00/M	MMZ1005D241C
33	0.20	0.6		445-3344-1-ND	.57	2.47	4.57	10,000	27.00/M	MMZ1005F330C
47	0.10	0.8	F	445-3345-1-ND	.57	2.47	4.57	10,000	27.00/M	MMZ1005F470C
56	0.10	0.8		445-3346-1-ND	.57	2.47	4.57	10,000	27.00/M	MMZ1005F560C
80	0.50	0.2		445-2159-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005S800C
120	0.50	0.25	S	445-2160-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005S121C
240	0.40	0.4		445-2161-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005S241C
600	0.30	0.6		445-2162-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005S601C
1000	0.20	1.0		445-2163-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005S102C
40	0.55	0.12		445-2150-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005Y400C
80	0.45	0.17		445-2151-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005Y800C
120	0.40	0.21		445-2152-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005Y121C
240	0.30	0.33		445-2153-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005Y241C
300	0.25	0.38	Y	445-2154-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005Y301C
470	0.25	0.5		445-2155-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005Y471C
600	0.25	0.56		445-2156-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005Y601C
1000	0.20	0.74		445-2157-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005Y102C
1500	0.10	1.15		445-2158-1-ND	.59	2.54	4.69	10,000	27.37/M	MMZ1005Y152C
MPZ1005 系列 - 0402 尺寸										
10	2.0	.045	S	445-2978-1-ND	.60	2.62	4.83	10,000	28.00/M	MPZ1005S100C
30	1.7	.050		445-2979-1-ND	.60	2.62	4.83	10,000	28.00/M	MPZ1005S300C
60	1.5	.075		445-2980-1-ND	.60	2.62	4.83	10,000	28.00/M	MPZ1005S600C
120	1.2	.090		445-2981-1-ND	.60	2.62	4.83	10,000	28.00/M	MPZ1005S121C
MMZ1608 系列 - 0603 尺寸										
15	1.5	0.05		445-2180-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608R150A
30	1.5	0.05		445-2181-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608R300A
60	0.8	0.1	R	445-2182-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608R600A
120	0.5	0.18		445-2170-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608R121A
300	0.5	0.25		445-2171-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608R301A
600	0.5	0.4		445-1547-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608R601A
1000	0.4	0.5		445-1548-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608R102A
40	0.6	0.1		445-2183-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608S400A
80	0.5	0.15		445-2172-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608S800A
120	0.5	0.2		445-2173-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608S121A
180	0.5	0.2	S	445-2174-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608S181A
300	0.5	0.3		445-2175-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608S301A
600	0.5	0.4		445-1549-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608S601A
1000	0.4	0.5		445-1550-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608S102A
15	1.5	0.05		445-2184-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608Y150B
30	1.5	0.05		445-2185-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608Y300B
60	0.5	0.15		445-2186-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608Y600B
120	0.5	0.2	Y	445-2176-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608Y121B
300	0.5	0.3		445-2177-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608Y301B
600	0.5	0.4		445-1551-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608Y601B
1000	0.4	0.5		445-1552-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608Y102B
1500	0.3	0.6		445-1553-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608Y152B
1500	0.3	1.0	A	445-2178-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608A152E
2500	0.2	0.8		445-2179-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608A252B
80	0.5	0.4		445-2167-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608D800B
120	0.4	0.5	D	445-2168-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608D121B
300	0.3	0.7		445-2169-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608D301B
MMZ1608-C 系列 - 0603 尺寸										
120	0.6	0.15		445-2164-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608B121C
300	0.5	0.25	B	445-2165-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608B301C
600	0.5	0.4		445-2166-1-ND	.53	2.28	4.21	4,000	24.56/M	MMZ1608B601C
MPZ1608 系列 - 0603 尺寸										
30	5.0	0.01	S	445-1562-1-ND	.53	2.28	4.21	4,000	24.56/M	MPZ1608S300A

阻抗 100MHz (Ω) ±25%	最大 电流 (A)	最大 Rdc (Ω)	材质	Digi-Key 零件编号	剪切带 价格			带卷*		TDK 零件编号
					10	50	100	数量	价格	
60	3.5	0.02		445-1563-1-ND	.53	2.28	4.21	4,000	24.56/M	MPZ1608S600A
100	3.0	0.03	S	445-1564-1-ND	.53	2.28	4.21	4,000	24.56/M	MPZ1608S101A
220	2.0	0.05		445-1565-1-ND	.53	2.28	4.21	4,000	24.56/M	MPZ1608S221A
600	1.0	0.15		445-2205-1-ND	.53	2.28	4.21	4,000	24.56/M	MPZ1608S601A
390	1.2	.12	R	445-2982-1-ND	.54	2.36	4.35	4,000	25.00/M	MPZ1608R391A
60	2.3	.03		445-2983-1-ND	.54	2.36	4.35	4,000	25.00/M	MPZ1608Y600B
100	2.0	.05	Y	445-2984-1-ND	.54	2.36	4.35	4,000	25.00/M	MPZ1608Y101B
150	1.8	.07		445-2985-1-ND	.54	2.36	4.35	4,000	25.00/M	MPZ1608Y151B
30	1.8	.07	D	445-2986-1-ND	.54	2.36	4.35	4,000	25.00/M	MPZ1608D300B
60	1.2	.12		445-2987-1-ND	.54	2.36	4.35	4,000	25.00/M	MPZ1608D600B
100	1.0	.15		445-2988-1-ND	.54	2.36	4.35	4,000	25.00/M	MPZ1608D101B
MMZ2012 系列 - 0805 尺寸										
15	1.5	0.05		445-2198-1-ND	.67	2.89	5.34	4,000	31.15/M	MMZ2012R150A
30	1.5	0.05		445-2199-1-ND	.67	2.89	5.34	4,000	31.15/M	MMZ2012R300A
60	1.0	0.1	R	445-2200-1-ND	.67	2.89	5.34	4,000	31.15/M	MMZ2012R600A
120	0.8	0.12		445-2190-1-ND	.67	2.89	5.34	4,000	31.15/M	MMZ2012R121A
300	0.6	0.15		445-2191-1-ND	.67	2.89	5.34	4,000	31.15/M	MMZ2012R301A
600	0.5	0.2		445-1554-1-ND	.67	2.89	5.34	4,000	31.15/M	MMZ2012R601A
1000	0.5	0.3		445-1555-1-ND	.67	2.89	5.34	4,000	31.15/M	MMZ2012R102A
40	1.0	0.1		445-2201-1-ND	.67	2.89	5.34	4,000	31.15/M	MMZ2012S400A
80	0.8	0.1		445-2192-1-ND	.67	2.89	5.34	4,000	31.15/M	MMZ2012S800A