



尺寸代码	类型	在 100MHz 时的阻抗 (Ω)	最大额定电流 (A)	最大直流电阻 (Ω)	尺寸 T (mm)	Digi-Key 零件编号			Digi-Key 零件编号			带卷		Taiyo Yuden 零件编号
						10	50	100	10	50	100	数量	价格	
0402	HM	470	0.25	0.45	0.5	587-1838-1-ND†	45	1.95	3.60	587-1838-2-ND	10,000	21.00/M	BK1005HM471-T	
	HM	600	0.25	0.5	0.5	587-1839-1-ND†	45	1.95	3.60	587-1839-2-ND	10,000	21.00/M	BK1005HM601-T	
	HS	600	0.3	0.55	0.5	587-1846-1-ND†	45	1.95	3.60	587-1846-2-ND	10,000	21.00/M	BK1005HS601-T	
	HW	600	0.3	0.6	0.5	587-1851-1-ND†	45	1.95	3.60	587-1851-2-ND	10,000	21.00/M	BK1005HW601-T	
	HM	1000	0.15	0.7	0.5	587-1835-1-ND†	45	1.95	3.60	587-1835-2-ND	10,000	21.00/M	BK1005HM102-T	
	HS	1000	0.3	0.58	0.5	587-1841-1-ND	45	1.95	3.60	587-1841-2-ND	10,000	21.00/M	BK1005HS102-T	
	LM	1800	0.12	0.9	0.5	587-1861-1-ND	45	1.95	3.60	587-1861-2-ND	10,000	21.00/M	BK1005LM182-T	
	HS	22	1.5	0.05	0.8	587-1869-1-ND	41	1.79	3.30	587-1869-2-ND	4,000	19.00/M	BK1608HS220-T	
	LL	30	0.5	0.2	0.8	587-1883-1-ND	41	1.79	3.30	587-1883-2-ND	4,000	19.00/M	BK1608LL300-T	
	HS	33	1.2	0.08	0.8	587-1871-1-ND	41	1.79	3.30	587-1871-2-ND	4,000	19.00/M	BK1608HS330-T	
HS	47	0.9	0.1	0.8	587-1872-1-ND	41	1.79	3.30	587-1872-2-ND	4,000	19.00/M	BK1608HS470-T		
LL	47	0.4	0.3	0.8	587-1886-1-ND	41	1.79	3.30	587-1886-2-ND	4,000	19.00/M	BK1608LL470-T		
HS	56	0.4	0.3	0.8	587-1888-1-ND	41	1.79	3.30	587-1888-2-ND	4,000	19.00/M	BK1608HS560-T		
HS	60	0.8	0.1	0.8	587-1873-1-ND	41	1.79	3.30	587-1873-2-ND	4,000	19.00/M	BK1608HS600-T		
LL	68	0.3	0.35	0.8	587-1889-1-ND	41	1.79	3.30	587-1889-2-ND	4,000	19.00/M	BK1608LL680-T		
HS	80	0.6	0.1	0.8	587-1875-1-ND	41	1.79	3.30	587-1875-2-ND	4,000	19.00/M	BK1608HS800-T		
HM	120	0.35	0.2	0.8	587-1863-1-ND	41	1.79	3.30	587-1863-2-ND	4,000	19.00/M	BK1608HM121-T		
HS	120	0.5	0.18	0.8	587-1868-1-ND	41	1.79	3.30	587-1868-2-ND	4,000	19.00/M	BK1608HS121-T		
HW	120	0.6	0.15	0.8	587-1876-1-ND	41	1.79	3.30	587-1876-2-ND	4,000	19.00/M	BK1608HW121-T		
LL	120	0.3	0.5	0.8	587-1880-1-ND	41	1.79	3.30	587-1880-2-ND	4,000	19.00/M	BK1608LL121-T		
LL	180	0.25	0.65	0.8	587-1881-1-ND	41	1.79	3.30	587-1881-2-ND	4,000	19.00/M	BK1608LL181-T		
HM	240	0.3	0.35	0.8	587-1864-1-ND	41	1.79	3.30	587-1864-2-ND	4,000	19.00/M	BK1608HM241-T		
HS	240	0.4	0.25	0.8	587-1870-1-ND	41	1.79	3.30	587-1870-2-ND	4,000	19.00/M	BK1608HS241-T		
HW	240	0.45	0.25	0.8	587-1877-1-ND	41	1.79	3.30	587-1877-2-ND	4,000	19.00/M	BK1608HW241-T		
LL	240	0.25	0.8	0.8	587-1882-1-ND	41	1.79	3.30	587-1882-2-ND	4,000	19.00/M	BK1608LL241-T		
LL	330	0.2	0.85	0.8	587-1884-1-ND	41	1.79	3.30	587-1884-2-ND	4,000	19.00/M	BK1608LL331-T		
HW	430	0.4	0.3	0.8	587-1878-1-ND	41	1.79	3.30	587-1878-2-ND	4,000	19.00/M	BK1608HW431-T		
LL	430	0.2	0.85	0.8	587-1885-1-ND	41	1.79	3.30	587-1885-2-ND	4,000	19.00/M	BK1608LL431-T		
TS	430	0.4	0.25	0.8	587-1896-1-ND	41	1.79	3.30	587-1896-2-ND	4,000	19.00/M	BK1608TS431-T		
HM	470	0.25	0.45	0.8	587-1865-1-ND	41	1.79	3.30	587-1865-2-ND	4,000	19.00/M	BK1608HM471-T		
LL	510	0.2	0.9	0.8	587-1887-1-ND	41	1.79	3.30	587-1887-2-ND	4,000	19.00/M	BK1608LL511-T		
HM	600	0.25	0.6	0.8	587-1866-1-ND	41	1.79	3.30	587-1866-2-ND	4,000	19.00/M	BK1608HM601-T		
HS	600	0.35	0.45	0.8	587-1874-1-ND	41	1.79	3.30	587-1874-2-ND	4,000	19.00/M	BK1608HS601-T		
HW	600	0.3	0.4	0.8	587-1879-1-ND	41	1.79	3.30	587-1879-2-ND	4,000	19.00/M	BK1608HW601-T		
TS	600	0.35	0.27	0.8	587-1897-1-ND	41	1.79	3.30	587-1897-2-ND	4,000	19.00/M	BK1608TS601-T		
LL	680	0.15	1.0	0.8	587-1890-1-ND	41	1.79	3.30	587-1890-2-ND	4,000	19.00/M	BK1608LL681-T		
LM	750	0.3	0.6	0.8	587-1894-1-ND	41	1.79	3.30	587-1894-2-ND	4,000	19.00/M	BK1608LM751-T		
HM	1000	0.2	0.7	0.8	587-1862-1-ND	41	1.79	3.30	587-1862-2-ND	4,000	19.00/M	BK1608HM102-T		
TS	1000	0.3	0.6	0.8	587-1867-1-ND	41	1.79	3.30	587-1867-2-ND	4,000	19.00/M	BK1608TS102-T		
HS	1000	0.3	0.3	0.8	587-1895-1-ND	41	1.79	3.30	587-1895-2-ND	4,000	19.00/M	BK1608HS102-T		
LM	1500	0.25	0.75	0.8	587-1891-1-ND	41	1.79	3.30	587-1891-2-ND	4,000	19.00/M	BK1608LM152-T		
LM	1800	0.2	0.85	0.8	587-1892-1-ND	41	1.79	3.30	587-1892-2-ND	4,000	19.00/M	BK1608LM182-T		
LM	2500	0.2	1.1	0.8	587-1893-1-ND	41	1.79	3.30	587-1893-2-ND	4,000	19.00/M	BK1608LM252-T		
HS	15	1.2	0.05	0.85	587-1906-1-ND	56	2.44	4.50	587-1906-2-ND	4,000	26.00/M	BK2125HS150-T		
HS	22	1.2	0.05	0.85	587-1907-1-ND	56	2.44	4.50	587-1907-2-ND	4,000	26.00/M	BK2125HS220-T		
HS	33	1.2	0.05	0.85	587-1909-1-ND	56	2.44	4.50	587-1909-2-ND	4,000	26.00/M	BK2125HS330-T		
HS	47	1.0	0.05	0.85	587-1911-1-ND	56	2.44	4.50	587-1911-2-ND	4,000	26.00/M	BK2125HS470-T		
LL	56	0.6	0.2	0.85	587-1916-1-ND	56	2.44	4.50	587-1916-2-ND	4,000	26.00/M	BK2125LL560-T		
HS	75	1.0	0.1	0.85	587-1913-1-ND	56	2.44	4.50	587-1913-2-ND	4,000	26.00/M	BK2125HS750-T		
HS	100	0.9	0.1	0.85	587-1903-1-ND	56	2.44	4.50	587-1903-2-ND	4,000	26.00/M	BK2125HS101-T		
HM	120	0.8	0.15	0.85	587-1899-1-ND	56	2.44	4.50	587-1899-2-ND	4,000	26.00/M	BK2125HM121-T		
HS	120	0.8	0.15	0.85	587-1905-1-ND	56	2.44	4.50	587-1905-2-ND	4,000	26.00/M	BK2125HS121-T		
LL	120	0.4	0.3	0.85	587-1914-1-ND	56	2.44	4.50	587-1914-2-ND	4,000	26.00/M	BK2125LL121-T		
HM	240	0.6	0.2	0.85	587-1900-1-ND	56	2.44	4.50	587-1900-2-ND	4,000	26.00/M	BK2125HM241-T		
HS	240	0.6	0.2	0.85	587-1908-1-ND	56	2.44	4.50	587-1908-2-ND	4,000	26.00/M	BK2125HS241-T		
LL	240	0.3	0.35	0.85	587-1915-1-ND	56	2.44	4.50	587-1915-2-ND	4,000	26.00/M	BK2125LL241-T		
HS	430	0.5	0.25	0.85	587-1910-1-ND	56	2.44	4.50	587-1910-2-ND	4,000	26.00/M	BK2125HS431-T		
HM	470	0.5	0.25	0.85	587-1901-1-ND	56	2.44	4.50	587-1901-2-ND	4,000	26.00/M	BK2125HM471-T		
HM	600	0.5	0.25	0.85	587-1902-1-ND	56	2.44	4.50	587-1902-2-ND	4,000	26.00/M	BK2125HM601-T		
HS	600	0.5	0.3	0.85	587-1912-1-ND	56	2.44	4.50	587-1912-2-ND	4,000	26.00/M	BK2125HS601-T		
LM	750	0.4	0.3	0.85	587-1920-1-ND	56	2.44	4.50	587-1920-2-ND	4,000	26.00/M	BK2125LM751-T		
HM	1000	0.4	0.35	0.85	587-1898-1-ND	56	2.44	4.50	587-1898-2-ND	4,000	26.00/M	BK2125HM102-T		
HS	1000	0.3	0.4	0.85	587-1904-1-ND	56	2.44	4.50	587-1904-2-ND	4,000	26.00/M	BK2125HS102-T		
LM	1500	0.4	0.35	0.85	587-1917-1-ND	56	2.44	4.50	587-1917-2-ND	4,000	26.00/M	BK2125LM152-T		
LM	1800	0.3	0.45	1.25	587-1918-1-ND	56	2.44	4.50	587-1918-2-ND	2,000	26.00/M	BK2125LM182-T		
LM	2500	0.2	0.75	1.25	587-1919-1-ND	56	2.44	4.50	587-1919-2-ND	2,000	26.00/M	BK2125LM252-T		
BKP 系列														
0402	HS	120	1.0	0.14	0.5	587-1921-1-ND	56	2.44	4.50	587-1921-2-ND	10,000	26.00/M	BKP1005HS121-T	
0603	HS	33	3.0	0.025	0.8	587-1926-1-ND	41	1.79	3.30	587-1926-2-ND	4,000	19.00/M	BKP1608HS330-T	
	HS	60	2.5	0.04	0.8	587-1928-1-ND	41	1.79	3.30	587-1928-2-ND	4,000	19.00/M	BKP1608HS600-T	
	HS	100	1.7	0.05	0.8	587-1922-1-ND	41	1.79	3.30	587-1922-2-ND	4,000	19.00/M	BKP1608HS101-T	
	HS	120	2.7	0.035	0.8	587-1923-1-ND	41	1.79	3.30	587-1923-2-ND	4,000	19.00/M	BKP1608HS121-T	
	HS	180	1.5	0.075	0.8	587-1924-1-ND	41	1.79	3.30	587-1924-2-ND	4,000	19.00/M	BKP1608HS181-T	
	HS	270	1.2	0.11	0.8	587-1925-1-ND	41	1.79	3.30	587-1925-2-ND	4,000	19.00/M	BKP1608HS271-T	
0805	HS	390	1.0	0.1	0.8	587-1927-1-ND	41	1.79	3.30	587-1927-2-ND	4,000	19.00/M	BKP1608HS391-T	
	HS	33	4.0	0.02	0.85	587-1931-1-ND	56	2.44	4.50	587-1931-2-ND	4,000	26.00/M	BKP2125HS330-T	
	HS	60	3.0	0.025	0.85	587-1932-1-ND	56	2.44	4.50	587-1932-2-ND	4,000	26.00/M	BKP2125HS600-T	
	HS	100	2.5	0.04	0.85	587-1929-1-ND	56	2.44	4.50	587-1929-2-ND	4,000	26.00/M	BKP2125HS101-T	
	HS	220	2.0	0.05	0.85	587-1930-1-ND	56							