




### DIP 连接器



引脚数	尺寸: 英寸 (mm)		
	A	B	C
14	.42(10.67)	.754(19.15)	.300(7.62)
16	.42(10.67)	.854(21.69)	.300(7.62)
24	.72(18.29)	1.264(32.21)	.600(15.24)
40	.72(18.29)	2.067(52.50)	.600(15.24)

技术规格: • 触点: 磷青铜 • 绝缘体材料: UL 94V-0 玻璃纤维填充阻燃热塑性塑料 • 应力释放带材料: 镀锡钢 • 颜色: 蓝色 • 工作温度: -55°C ~ 125°C • 额定电流: 每个接触最大 1A • 电介质耐受电压: 大于 500Vdc (海平面) • 绝缘电阻: 大 5x10<sup>10</sup>Ω • 可用于具有 0.100"x0.300" 或 0.100"x0.600" (2.54mmx7.62mm 或 2.54mmx15.24mm) 触点间距的标准 Dip 接口

触点数	触点表面处理	Digi-Key 零件编号	价格			
			1	10	100	1,000
<b>DIP 连接器 - 0.175" (4.44mm) 引脚长度</b>						
14	金	CDP14G-ND	1.77	13.40	102.60	741.00
	锡	CDP14S-ND	1.43	10.81	82.80	598.00
16	金	CDP16G-ND	1.89	14.34	109.80	793.00
	锡	CDP16S-ND	1.52	11.52	88.20	637.00
24	金	CDP24G-ND	3.10	23.50	180.00	1300.00
	锡	CDP24S-ND	2.51	19.04	145.80	1053.00
40	金	CDP40G-ND	4.46	33.84	259.20	1872.00
	锡	CDP40S-ND	3.60	27.26	208.80	1508.00
<b>DIP 连接器的应力释放带 - 符合 RoHS 规范表</b>						
14	—	CDSR14-ND	1.9	14.11	10.80	78.00
16	—	CDSR16-ND	.22	1.65	12.60	91.00
24	—	CDSR24-ND	.28	2.12	16.20	117.00
40	—	CDSR40-ND	.31	2.35	18.00	130.00

符合 RoHS 规范要求


### DIP 缆线组件



#### 单端型号 2

\* MC=多色  
GR=灰色

所示为不带应力释放的 DIP 连接器。连接器上的引脚 #1 连接到缆线上的第 2 导线芯




触点数	触点表面处理	长度: 英寸 (厘米)	带状缆线*	Digi-Key 零件编号	价格	
					1	10
14	金	6(15.24)	MC	C2PXG-1406M-ND	2.37	17.96
	锡	6(15.24)	MC	C2PXS-1406M-ND	2.03	15.37
	金	6(15.24)	GR	C2PXG-1406G-ND	1.94	14.74
	锡	6(15.24)	GR	C2PXS-1406G-ND	1.60	12.15
	金	18(45.72)	MC	C2PXG-1418M-ND	3.57	27.08
	锡	18(45.72)	MC	C2PXS-1418M-ND	3.23	24.49
	金	18(45.72)	GR	C2PXG-1418G-ND	2.30	17.42
	锡	18(45.72)	GR	C2PXS-1418G-ND	1.96	14.83
	金	36(91.44)	MC	C2PXG-1436M-ND	5.38	40.76
	锡	36(91.44)	MC	C2PXS-1436M-ND	5.04	38.17
	金	36(91.44)	GR	C2PXG-1436G-ND	2.83	21.44
	锡	36(91.44)	GR	C2PXS-1436G-ND	2.49	18.86
16	金	6(15.24)	MC	C2PXG-1606M-ND	2.53	19.20
	锡	6(15.24)	MC	C2PXS-1606M-ND	2.16	16.38
	金	6(15.24)	GR	C2PXG-1606G-ND	2.09	15.86
	锡	6(15.24)	GR	C2PXS-1606G-ND	1.72	13.04
	金	18(45.72)	MC	C2PXG-1618M-ND	3.82	28.93
	锡	18(45.72)	MC	C2PXS-1618M-ND	3.44	26.11
	金	18(45.72)	GR	C2PXG-1618G-ND	2.50	18.92
	锡	18(45.72)	GR	C2PXS-1618G-ND	2.12	16.10
	金	36(91.44)	MC	C2PXG-1636M-ND	5.74	43.52
	锡	36(91.44)	MC	C2PXS-1636M-ND	5.37	40.70
	金	36(91.44)	GR	C2PXG-1636G-ND	3.10	23.51
	锡	36(91.44)	GR	C2PXS-1636G-ND	2.73	20.69
24	金	6(15.24)	MC	C2PXG-2406M-ND	4.10	31.10
	锡	6(15.24)	MC	C2PXS-2406M-ND	3.51	26.64
	金	6(15.24)	GR	C2PXG-2406G-ND	3.37	25.54
	锡	6(15.24)	GR	C2PXS-2406G-ND	2.78	21.07
	金	18(45.72)	MC	C2PXG-2418M-ND	6.11	46.30
	锡	18(45.72)	MC	C2PXS-2418M-ND	5.52	41.84
	金	18(45.72)	GR	C2PXG-2418G-ND	3.91	29.62
	锡	18(45.72)	GR	C2PXS-2418G-ND	3.32	25.15
	金	36(91.44)	MC	C2PXG-2436M-ND	9.12	69.10
	锡	36(91.44)	MC	C2PXS-2436M-ND	8.53	64.64
	金	36(91.44)	GR	C2PXG-2436G-ND	4.71	35.74
	锡	36(91.44)	GR	C2PXS-2436G-ND	4.13	31.27
40	金	6(15.24)	MC	C2PXG-4006M-ND	6.07	46.00
	锡	6(15.24)	MC	C2PXS-4006M-ND	5.20	39.42
	金	6(15.24)	GR	C2PXG-4006G-ND	5.00	37.88
	锡	6(15.24)	GR	C2PXS-4006G-ND	4.13	31.30
	金	18(45.72)	MC	C2PXG-4018M-ND	9.28	70.32
	锡	18(45.72)	MC	C2PXS-4018M-ND	8.41	63.74
	金	18(45.72)	GR	C2PXG-4018G-ND	6.06	45.96
	锡	18(45.72)	GR	C2PXS-4018G-ND	5.19	39.38
	金	36(91.44)	MC	C2PXG-4036M-ND	14.09	106.81
	锡	36(91.44)	MC	C2PXS-4036M-ND	13.22	100.23
	金	36(91.44)	GR	C2PXG-4036G-ND	7.66	58.08
	锡	36(91.44)	GR	C2PXS-4036G-ND	6.79	51.50

也备有下列型号: C2RX□□□□□□□□-ND - 有应力释放带的 DIP 连接器 欢迎来电咨询完整的零件编号与价格!

#### 单端型号 4

\* MC=多色  
GR=灰色

所示为不带应力释放的 DIP 连接器。连接器上的引脚 #1 连接到缆线上的第 2 导线芯




触点数	触点表面处理	长度: 英寸 (厘米)	带状缆线*	Digi-Key 零件编号	价格	
					1	10
14	金	6(15.24)	MC	C4PXG-1406M-ND	2.37	17.96
	锡	6(15.24)	MC	C4PXS-1406M-ND	2.03	15.37
	金	6(15.24)	GR	C4PXG-1406G-ND	1.94	14.74
	锡	6(15.24)	GR	C4PXS-1406G-ND	1.60	12.15
	金	18(45.72)	MC	C4PXG-1418M-ND	3.57	27.08
	锡	18(45.72)	MC	C4PXS-1418M-ND	3.23	24.49
	金	18(45.72)	GR	C4PXG-1418G-ND	2.30	17.42
	锡	18(45.72)	GR	C4PXS-1418G-ND	1.96	14.83
	金	36(91.44)	MC	C4PXG-1436M-ND	5.38	40.76
	锡	36(91.44)	MC	C4PXS-1436M-ND	5.04	38.17
	金	36(91.44)	GR	C4PXG-1436G-ND	2.83	21.44
	锡	36(91.44)	GR	C4PXS-1436G-ND	2.49	18.86
16	金	6(15.24)	MC	C4PXG-1606M-ND	2.53	19.20
	锡	6(15.24)	MC	C4PXS-1606M-ND	2.16	16.38
	金	6(15.24)	GR	C4PXG-1606G-ND	2.09	15.86
	锡	6(15.24)	GR	C4PXS-1606G-ND	1.72	13.04
	金	18(45.72)	MC	C4PXG-1618M-ND	3.82	28.93
	锡	18(45.72)	MC	C4PXS-1618M-ND	3.44	26.11
	金	18(45.72)	GR	C4PXG-1618G-ND	2.50	18.92
	锡	18(45.72)	GR	C4PXS-1618G-ND	2.12	16.10
	金	36(91.44)	MC	C4PXG-1636M-ND	5.74	43.52
	锡	36(91.44)	MC	C4PXS-1636M-ND	5.37	40.70
	金	36(91.44)	GR	C4PXG-1636G-ND	3.10	23.51
	锡	36(91.44)	GR	C4PXS-1636G-ND	2.73	20.69
24	金	6(15.24)	MC	C4PXG-2406M-ND	4.10	31.10
	锡	6(15.24)	MC	C4PXS-2406M-ND	3.51	26.64
	金	6(15.24)	GR	C4PXG-2406G-ND	3.37	25.54
	锡	6(15.24)	GR	C4PXS-2406G-ND	2.78	21.07
	金	18(45.72)	MC	C4PXG-2418M-ND	6.11	46.30
	锡	18(45.72)	MC	C4PXS-2418M-ND	5.52	41.84
	金	18(45.72)	GR	C4PXG-2418G-ND	3.91	29.62
	锡	18(45.72)	GR	C4PXS-2418G-ND	3.32	25.15
	金	36(91.44)	MC	C4PXG-2436M-ND	9.12	69.10
	锡	36(91.44)	MC	C4PXS-2436M-ND	8.53	64.64
	金	36(91.44)	GR	C4PXG-2436G-ND	4.71	35.74
	锡	36(91.44)	GR	C4PXS-2436G-ND	4.13	31.27
40	金	6(15.24)	MC	C4PXG-4006M-ND	6.07	46.00
	锡	6(15.24)	MC	C4PXS-4006M-ND	5.20	39.42
	金	6(15.24)	GR	C4PXG-4006G-ND	5.00	37.88
	锡	6(15.24)	GR	C4PXS-4006G-ND	4.13	31.30
	金	18(45.72)	MC	C4PXG-4018M-ND	9.28	70.32
	锡	18(45.72)	MC	C4PXS-4018M-ND	8.41	63.74
	金	18(45.72)	GR	C4PXG-4018G-ND	6.06	45.96
	锡	18(45.72)	GR	C4PXS-4018G-ND	5.19	39.38
	金	36(91.44)	MC	C4PXG-4036M-ND	14.09	106.81
	锡	36(91.44)	MC	C4PXS-4036M-ND	13.22	100.23
	金	36(91.44)	GR	C4PXG-4036G-ND	7.66	58.08
	锡	36(91.44)	GR	C4PXS-4036G-ND	6.79	51.50

也备有下列型号: C4RX□□□□□□□□-ND - 带应力释放带的 DIP 连接器 欢迎来电咨询完整的零件编号与价格!

#### 双端型号 6

\* MC=多色  
GR=灰色

所示为不带应力释放的 DIP 连接器。连接器上的引脚 #1 连接到缆线上的第 2 导线芯



触点数	触点表面处理	长度: 英寸 (厘米)	带状缆线*	Digi-Key 零件编号	价格	
					1	10
14	金	6(15.24)	MC	C6PPG-1406M-ND	4.14	31.35
	锡	6(15.24)	MC	C6PPS-1406M-ND	3.45	26.18
	金	6(15.24)	GR	C6PPG-1406G-ND	3.71	28.13
	锡	6(15.24)	GR	C6PPS-1406G-ND	3.03	22.96
	金	18(45.72)	MC	C6PPG-1418M-ND	5.34	40.47
	锡	18(45.72)	MC	C6PPS-1418M-ND	4.66	35.30
	金	18(45.72)	GR	C6PPG-1418G-ND	4.06	30.81
	锡	18(45.72)	GR	C6PPS-1418G-ND	3.38	25.64
	金	36(91.44)	MC	C6PPG-1436M-ND	7.14	54.15
	锡	36(91.44)	MC	C6PPS-1436M-ND	6.46	48.98
	金	36(91.44)	GR	C6PPG-1436G-ND	4.60	34.84
	锡	36(91.44)	GR	C6PPS-1436G-ND	3.91	29.67
16	金	6(15.24)	MC	C6PPG-1606M-ND	4.42	33.53
	锡	6(15.24)	MC	C6PPS-1606M-ND	3.68	27.89
	金	6(15.24)	GR	C6PPG-1606G-ND	3.98	30.20
	锡	6(15.24)	GR	C6PPS-1606G-ND	3.24	24.56
	金	18(45.72)	MC	C6PPG-1618M-ND	5.71	43.26
	锡	18(45.72)	MC	C6PPS-1618M-ND	4.96	37.62
	金	18(45.72)	GR	C6PPG-1618G-ND	4.39	33.26
	锡	18(45.72)	GR	C6PPS-1618G-ND	3.64	27.62
	金	36(91.44)	MC	C6PPG-1636M-ND	7.63	57.86
	锡	36(91.44)	MC	C6PPS-1636M-ND	6.89	52.22
	金	36(91.44)	GR	C6PPG-1636G-ND	4.99	37.85
	锡	36(91.44)	GR	C6PPS-1636G-ND	4.25	32.21
24	金	6(15.24)	MC	C6PPG-2406M-ND	7.20	54.60
	锡	6(15.24)	MC	C6PPS-2406M-ND	6.02	45.67
	金	6(15.24)	GR	C6PPG-2406G-ND	6.47	49.04
	锡	6(15.24)	GR	C6PPS-2406G-ND	5.29	40.11
	金	18(45.72)				