



端子跳接器

插口连接器 - 单端 (接上页)



触点数	触点表面材料	长度: 英寸 (厘米)	带状 线缆*	Digi-Key 零件编号	单价	
					1	10
14	金	36(91.44)	MC	C1AXG-1436M-ND	5.35	4.06
	锡	36(91.44)	MC	C1AXS-1436M-ND	5.10	3.87
	金	36(91.44)	GR	C1AXG-1436G-ND	2.80	2.13
	锡	36(91.44)	GR	C1AXS-1436G-ND	2.55	1.94
16	金	36(91.44)	MC	C1AXG-1636M-ND	5.87	4.45
	锡	36(91.44)	MC	C1AXS-1636M-ND	5.56	4.22
	金	36(91.44)	GR	C1AXG-1636G-ND	3.23	2.45
	锡	36(91.44)	GR	C1AXS-1636G-ND	2.92	2.21
20	金	36(91.44)	MC	C1AXG-2036M-ND	6.92	5.25
	锡	36(91.44)	MC	C1AXS-2036M-ND	6.61	5.02
	金	36(91.44)	GR	C1AXG-2036G-ND	3.82	2.90
	锡	36(91.44)	GR	C1AXS-2036G-ND	3.51	2.67
26	金	36(91.44)	MC	C1AXG-2636M-ND	8.77	6.65
	锡	36(91.44)	MC	C1AXS-2636M-ND	8.40	6.37
	金	36(91.44)	GR	C1AXG-2636G-ND	4.63	3.51
	锡	36(91.44)	GR	C1AXS-2636G-ND	4.26	3.23
34	金	36(91.44)	MC	C1AXG-3436M-ND	11.28	8.56
	锡	36(91.44)	MC	C1AXS-3436M-ND	10.82	8.20
	金	36(91.44)	GR	C1AXG-3436G-ND	5.39	4.09
	锡	36(91.44)	GR	C1AXS-3436G-ND	4.92	3.74
40	金	36(91.44)	MC	C1AXG-4036M-ND	13.04	9.89
	锡	36(91.44)	MC	C1AXS-4036M-ND	12.51	9.49
	金	36(91.44)	GR	C1AXG-4036G-ND	6.61	5.01
	锡	36(91.44)	GR	C1AXS-4036G-ND	6.08	4.61
50	金	36(91.44)	MC	C1AXG-5036M-ND	16.12	12.23
	锡	36(91.44)	MC	C1AXS-5036M-ND	15.50	11.76
	金	36(91.44)	GR	C1AXG-5036G-ND	7.45	5.66
	锡	36(91.44)	GR	C1AXS-5036G-ND	6.83	5.19
60	金	36(91.44)	MC	C1AXG-6036M-ND	19.43	14.73
	锡	36(91.44)	MC	C1AXS-6036M-ND	18.68	14.17
	金	36(91.44)	GR	C1AXG-6036G-ND	9.54	7.24
	锡	36(91.44)	GR	C1AXS-6036G-ND	8.80	6.68


也备有下列型号:

- C1BX□□□□□□-ND 带应力释放的插口连接器。
- C1CX□□□□□□-ND 带中心电极标记的插口连接器。
- C1DX□□□□□□-ND 带应力释放与中心电极标记的插口连接器。

欢迎来电咨询完整的零件编号与价格!

PCB 连接器 - 单端

* MC=多色
GR=灰色



所示为不带应力释放的 PCB 连接器。

触点数	触点表面材料	长度: 英寸 (厘米)	带状 线缆*	Digi-Key 零件编号	单价	
					1	10
10	锡	36(91.44)	MC	C1PXS-1036M-ND	3.77	2.86
	锡	36(91.44)	GR	C1PXS-1036G-ND	2.12	1.61
20	锡	36(91.44)	MC	C1PXS-2036M-ND	6.39	4.85
	锡	36(91.44)	GR	C1PXS-2036G-ND	3.30	2.50
26	锡	36(91.44)	MC	C1PXS-2636M-ND	8.30	6.30
	锡	36(91.44)	GR	C1PXS-2636G-ND	4.16	3.16
34	锡	36(91.44)	MC	C1PXS-3436M-ND	10.69	8.11
	锡	36(91.44)	GR	C1PXS-3436G-ND	4.80	3.64
40	锡	36(91.44)	MC	C1PXS-4036M-ND	12.48	9.46
	锡	36(91.44)	GR	C1PXS-4036G-ND	6.05	4.59
50	锡	36(91.44)	MC	C1PXS-5036M-ND	15.60	11.83
	锡	36(91.44)	GR	C1PXS-5036G-ND	6.93	5.26
60	锡	36(91.44)	MC	C1PXS-6036M-ND	18.53	14.05
	锡	36(91.44)	GR	C1PXS-6036G-ND	8.64	6.56

卡边连接器 - 单端

* MC=多色
GR=灰色




所示为不带应力释放的卡边连接器。

触点数	触点表面材料	长度: 英寸 (厘米)	带状 线缆*	Digi-Key 零件编号	单价	
					1	10
10	金	36(91.44)	MC	C1EXG-1036M-ND	5.07	3.85
	锡	36(91.44)	MC	C1EXS-1036M-ND	4.67	3.54
	金	36(91.44)	GR	C1EXG-1036G-ND	3.42	2.60
	锡	36(91.44)	GR	C1EXS-1036G-ND	3.02	2.29
20	金	36(91.44)	MC	C1EXG-2036M-ND	8.38	6.36
	锡	36(91.44)	MC	C1EXS-2036M-ND	7.85	5.96
	金	36(91.44)	GR	C1EXG-2036G-ND	5.28	4.01
	锡	36(91.44)	GR	C1EXS-2036G-ND	4.75	3.61
26	金	36(91.44)	MC	C1EXG-2636M-ND	10.50	7.97
	锡	36(91.44)	MC	C1EXS-2636M-ND	9.85	7.47
	金	36(91.44)	GR	C1EXG-2636G-ND	6.36	4.83
	锡	36(91.44)	GR	C1EXS-2636G-ND	5.71	4.34
34	金	36(91.44)	MC	C1EXG-3436M-ND	13.45	10.20
	锡	36(91.44)	MC	C1EXS-3436M-ND	12.68	9.61
	金	36(91.44)	GR	C1EXG-3436G-ND	7.56	5.73
	锡	36(91.44)	GR	C1EXS-3436G-ND	6.78	5.15

触点数	触点表面材料	长度: 英寸 (厘米)	带状 线缆*	Digi-Key 零件编号	单价	
					1	10
40	金	36(91.44)	MC	C1EXG-4036M-ND	15.79	11.98
	锡	36(91.44)	MC	C1EXS-4036M-ND	14.86	11.27
	金	36(91.44)	GR	C1EXG-4036G-ND	9.37	7.11
50	金	36(91.44)	MC	C1EXG-5036M-ND	18.98	14.39
	锡	36(91.44)	MC	C1EXS-5036M-ND	17.92	13.59
	金	36(91.44)	GR	C1EXG-5036G-ND	10.31	7.82
	锡	36(91.44)	GR	C1EXS-5036G-ND	9.25	7.02

插口连接器至插口连接器

* MC=多色
GR=灰色



所示为不带应力释放的插口连接器。

触点数	触点表面材料	长度: 英寸 (厘米)	带状 线缆*	Digi-Key 零件编号	单价	
					1	10
10	金	6(15.24)	MC	C3AAG-1006M-ND	2.88	2.19
	锡	6(15.24)	MC	C3AAS-1006M-ND	2.51	1.91
	金	6(15.24)	GR	C3AAG-1006G-ND	2.61	1.98
	锡	6(15.24)	GR	C3AAS-1006G-ND	2.23	1.70
14	金	18(45.72)	MC	C3AAG-1018M-ND	3.68	2.80
	锡	18(45.72)	MC	C3AAS-1018M-ND	3.31	2.51
	金	18(45.72)	GR	C3AAG-1018G-ND	2.86	2.17
	锡	18(45.72)	GR	C3AAS-1018G-ND	2.49	1.89
16	金	36(91.44)	MC	C3AAG-1036M-ND	4.89	3.71
	锡	36(91.44)	MC	C3AAS-1036M-ND	4.51	3.43
	金	36(91.44)	GR	C3AAG-1036G-ND	3.24	2.46
	锡	36(91.44)	GR	C3AAS-1036G-ND	2.87	2.18
14	金	6(15.24)	MC	C3AAG-1406M-ND	4.07	3.09
	锡	6(15.24)	MC	C3AAS-1406M-ND	3.58	2.72
	金	6(15.24)	GR	C3AAG-1406G-ND	3.65	2.77
	锡	6(15.24)	GR	C3AAS-1406G-ND	3.15	2.39
	金	18(45.72)	MC	C3AAG-1418M-ND	5.28	4.00
	锡	18(45.72)	MC	C3AAS-1418M-ND	4.78	3.63
	金	18(45.72)	GR	C3AAG-1418G-ND	4.00	3.04
	锡	18(45.72)	GR	C3AAS-1418G-ND	3.51	2.66
	金	36(91.44)	MC	C3AAG-1436M-ND	7.08	5.37
	锡	36(91.44)	MC	C3AAS-1436M-ND	6.59	5.00
	金	36(91.44)	GR	C3AAG-1436G-ND	4.53	3.44
	锡	36(91.44)	GR	C3AAS-1436G-ND	4.04	3.07
16	金	6(15.24)	MC	C3AAG-1606M-ND	4.67	3.55
	锡	6(15.24)	MC	C3AAS-1606M-ND	4.05	3.08
	金	6(15.24)	GR	C3AAG-1606G-ND	4.23	3.21
	锡	6(15.24)	GR	C3AAS-1606G-ND	3.61	2.74
	金	18(45.72)	MC	C3AAG-1618M-ND	5.96	4.52
	锡	18(45.72)	MC	C3AAS-1618M-ND	5.34	4.05
	金	18(45.72)	GR	C3AAG-1618G-ND	4.64	3.52
	锡	18(45.72)	GR	C3AAS-1618G-ND	4.02	3.05
	金	36(91.44)	MC	C3AAG-1636M-ND	7.88	5.98
	锡	36(91.44)	MC	C3AAS-1636M-ND	7.26	5.51
	金	36(91.44)	GR	C3AAG-1636G-ND	5.24	3.98
	锡	36(91.44)	GR	C3AAS-1636G-ND	4.62	3.51
20	金	6(15.24)	MC	C3AAG-2006M-ND	5.02	3.81
	锡	6(15.24)	MC	C3AAS-2006M-ND	4.40	3.34
	金	6(15.24)	GR	C3AAG-2006G-ND	4.50	3.42
	锡	6(15.24)	GR	C3AAS-2006G-ND	3.88	2.95
	金	18(45.72)	MC	C3AAG-2018M-ND	6.62	5.02
	锡	18(45.72)	MC	C3AAS-2018M-ND	6.00	4.55
	金	18(45.72)	GR	C3AAG-2018G-ND	5.07	3.85
	锡	18(45.72)	GR	C3AAS-2018G-ND	4.45	3.38
	金	36(91.44)	MC	C3AAG-2036M-ND	9.03	6.85
	锡	36(91.44)	MC	C3AAS-2036M-ND	8.41	6.38
	金	36(91.44)	GR	C3AAG-2036G-ND	5.93	4.50
	锡	36(91.44)	GR	C3AAS-2036G-ND	5.31	4.03
26	金	6(15.24)	MC	C3AAG-2606M-ND	6.06	4.60
	锡	6(15.24)	MC	C3AAS-2606M-ND	5.32	4.04
	金	6(15.24)	GR	C3AAG-2606G-ND	5.37	4.08
	锡	6(15.24)	GR	C3AAS-2606G-ND	4.63	3.51
	金	18(45.72)	MC	C3AAG-2618M-ND	8.15	6.18
	锡	18(45.72)	MC	C3AAS-2618M-ND	7.41	5.62
	金	18(45.72)	GR	C3AAG-2618G-ND	6.08	4.61
	锡	18(45.72)	GR	C3AAS-2618G-ND	5.34	4.05
	金	36(91.44)	MC	C3AAG-2636M-ND	11.28	8.55
	锡	36(91.44)	MC	C3AAS-2636M-ND	10.53	7.99
	金	36(91.44)	GR	C3AAG-2636G-ND	7.14	5.42
	锡	36(91.44)	GR	C3AAS-2636G-ND	6.39	4.85
34	金	6(15.24)	MC	C3AAG-3406M-ND	7.56	5.74
	锡	6(15.24)	MC	C3AAS-3406M-ND	6.63	5.03
	金	6(15.24)	GR	C3AAG-3406G-ND	6.58	4.99
	锡	6(15.24)	GR	C3AAS-3406G-ND	5.65	4.29
	金	18(45.72)	MC	C3AAG-3418M-ND	10.29	7.81
	锡	18(45.72)	MC	C3AAS-3418M-ND	9.36	7.10
	金	18(45.72)	GR	C3AAG-3418G-ND	9.34	5.57
	锡	18(45.72)	GR	C3AAS-3418G-ND	6.41	4.87
	金	36(91.44)	MC	C3AAG-3436M-ND	14.38	10.91
	锡	36(91.44)	MC	C3AAS-3436M-ND	13.45	10.20
	金	36(91.44)	GR	C3AAG-3436G-ND	8.49	6.44
	锡	36(91.44)	GR	C3AAS-3436G-ND	7.56	5.73
40	金	6(15.24)	MC	C3AAG-4006M-ND	8.42	6.39
	锡	6(15.24)	MC	C3AAS-4006M-ND	7.37	5.59
	金	6(15.24)	GR	C3AAG-4006G-ND	7.35	5.58
	锡	6(15.24)	GR	C3AAS-4006G-ND	6.30	4.78
	金	18(45.72)	MC	C3AAG-4018M-ND	11.63	8.82
	锡	18(45.72)	MC	C3AAS-4018M-ND	10.58	8.02
40	金	18(45.72)	GR	C3AAG-4018G-ND	8.42	6.39
	锡	18(45.72)	GR	C3AAS-4018G-ND	7.36	5.59

触点数	触点表面材料	长度: 英寸 (厘米)	带状 线缆*	Digi-Key 零件编号	单价	
					1	10
40	金	36(91.44)	MC	C3AAG-4036M-ND	16.45	12.47
	锡	36(91.44)	MC	C3AAS-4036M-ND	15.39	11.67
	金	36(91.44)	GR	C3AAG-4036G-ND	10.02	7.60
	锡	36(91.44)	GR	C3AAS-4036G-ND	8.96	6.80
50	金	6(15.24)	MC	C3AAG-5006M-ND	10.19	7.73
	锡	6(15.24)	MC	C3AAS-5006M-ND	8.95	6.79
	金	6(15.24)	GR	C3AAG-5006G-ND	8.74	6.63
	锡	6(15.24)	GR	C3AAS-5006G-ND	7.50	5.69
	金	18(45.72)	MC	C3AAG-5018M-ND	14.20	10.77
	锡	18(45				