



0.5mm 与 1.0mm 柔性连接器 (接上页)

A

图号	位置数量	尺寸 (mm)		Digi-Key 零件编号	剪切带单价				Digi-Key 零件编号	带卷		Hirose 零件编号
		A	B		1	25	100	250		数量	价格	
1	13	7.07	10.6	HFJ13CT-ND	1.89	1.46	1.17	.97	—	—	—	FH12-13S-0.5SH
	14	7.57	11.1	HFJ14CT-ND	1.93	1.49	1.19	.99	HFJ14TR-ND	2,000	759.00/M	FH12-14S-0.5SH
	15	8.07	11.6	HFJ15CT-ND	1.98	1.53	1.22	1.02	—	—	—	FH12-15S-0.5SH
	16	8.57	12.1	HFJ16CT-ND	1.98	1.53	1.22	1.02	HFJ16TR-ND	2,000	778.00/M	FH12-16S-0.5SH
	17	9.07	12.6	HFJ17CT-ND	2.08	1.60	1.28	1.07	HFJ17TR-ND	2,000	815.00/M	FH12-17S-0.5SH
	19	10.07	13.6	HFJ19CT-ND	2.12	1.64	1.31	1.09	HFJ19TR-ND	2,000	833.00/M	FH12-19S-0.5SH
	20	10.57	14.1	HFJ20CT-ND	2.17	1.67	1.34	1.11	HFJ20TR-ND	2,000	852.00/M	FH12-20S-0.5SH
	22	11.57	15.1	HFJ22CT-ND	2.27	1.75	1.40	1.16	HFJ22TR-ND	2,000	889.00/M	FH12-22S-0.5SH
	26	13.57	17.1	HFJ26CT-ND	2.41	1.86	1.49	1.23	—	—	—	FH12-26S-0.5SH
	34	17.57	21.1	HFJ34CT-ND	2.74	2.11	1.69	1.40	—	—	—	FH12-34S-0.5SH
	45	23.07	26.6	HFJ45CT-ND	2.99	2.32	1.86	1.50	HFJ45TR-ND	2,000	1313.00/M	FH12-45S-0.5SH
	53	27.07	30.6	HFJ53CT-ND	3.28	2.55	2.04	1.64	HFJ53TR-ND	2,000	1441.00/M	FH12-53S-0.5SH
	0.5mm 水平安装 - 底部触点式 - 符合 RoHS 规范要求											
1	6	3.57	7.1	HFJ106CT-ND	1.79	1.38	1.10	.92	—	—	—	FH12-6S-0.5SH(55)
	10	5.57	9.1	HFJ110CT-ND	1.98	1.53	1.22	1.02	HFJ110TR-ND	2,000	778.00/M	FH12-10S-0.5SH(55)
	11	6.07	9.6	HFJ111CT-ND	2.02	1.55	1.24	1.03	HFJ111TR-ND	2,000	791.00/M	FH12-11S-0.5SH(55)
	12	6.57	10.1	HFJ112CT-ND	2.08	1.60	1.28	1.07	HFJ112TR-ND	2,000	816.00/M	FH12-12S-0.5SH(55)
	14	7.07	11.1	HFJ114CT-ND	2.18	1.68	1.34	1.12	HFJ114TR-ND	2,000	854.00/M	FH12-14S-0.5SH(55)
	15	8.07	11.6	HFJ115CT-ND	2.28	1.75	1.40	1.17	HFJ115TR-ND	2,000	893.00/M	FH12-15S-0.5SH(55)
	16	8.57	12.1	HFJ116CT-ND	2.31	1.78	1.42	1.18	HFJ116TR-ND	2,000	905.00/M	FH12-16S-0.5SH(55)
	18	9.57	13.1	HFJ118CT-ND	2.47	1.90	1.52	1.27	HFJ118TR-ND	2,000	969.00/M	FH12-18S-0.5SH(55)
	20	10.57	14.1	HFJ120CT-ND	2.57	1.98	1.58	1.32	HFJ120TR-ND	2,000	1007.00/M	FH12-20S-0.5SH(55)
	22	11.57	15.1	HFJ122CT-ND	2.67	2.05	1.64	1.37	HFJ122TR-ND	2,000	1046.00/M	FH12-22S-0.5SH(55)
	24	12.57	16.1	HFJ124CT-ND	2.80	2.15	1.72	1.43	HFJ124TR-ND	2,000	1097.00/M	FH12-24S-0.5SH(55)
	26	13.57	17.1	HFJ126CT-ND	2.96	2.28	1.82	1.52	HFJ126TR-ND	2,000	1160.00/M	FH12-26S-0.5SH(55)
	30	15.57	19.1	HFJ130CT-ND	3.09	2.38	1.90	1.58	HFJ130TR-ND	2,000	1211.00/M	FH12-30S-0.5SH(55)
	32	16.57	20.1	HFJ132CT-ND	2.99	2.32	1.86	1.50	HFJ132TR-ND	2,000	1313.00/M	FH12-32S-0.5SH(55)
	33	17.07	20.6	HFJ133CT-ND	3.07	2.39	1.91	1.54	HFJ133TR-ND	2,000	1352.00/M	FH12-33S-0.5SH(55)
	34	17.57	21.1	HFJ134CT-ND	3.07	2.39	1.91	1.54	HFJ134TR-ND	2,000	1352.00/M	FH12-34S-0.5SH(55)
	36	18.57	22.1	HFJ136CT-ND	3.16	2.46	1.97	1.59	HFJ136TR-ND	2,000	1390.00/M	FH12-36S-0.5SH(55)
	40	20.57	24.1	HFJ140CT-ND	3.48	2.70	2.16	1.74	—	—	—	FH12-40S-0.5SH(55)
	45	23.07	26.6	HFJ145CT-ND	3.86	3.00	2.40	1.93	HFJ145TR-ND	2,000	1696.00/M	FH12-45S-0.5SH(55)
	50	25.57	29.1	HFJ150CT-ND	4.18	3.24	2.60	2.09	HFJ150TR-ND	2,000	1836.00/M	FH12-50S-0.5SH(55)
	0.5mm 水平安装 - 顶部触点型											
2	12	6.57	10.5	HFJ12CT-ND	1.66	1.20	.99	.83	—	—	—	FH12A-12S-0.5SH
	15	8.07	12.0	HFJ15CT-ND	1.82	1.32	1.08	.92	—	—	—	FH12A-15S-0.5SH
	16	8.57	12.5	HFJ16CT-ND	1.88	1.36	1.12	.94	—	—	—	FH12A-16S-0.5SH
	22	11.57	15.5	HFJ22CT-ND	1.89	1.46	1.17	.97	—	—	—	FH12A-22S-0.5SH
	29	15.07	19.0	HFJ29CT-ND	2.17	1.67	1.34	1.11	HFJ29TR-ND	2,000	852.00/M	FH12A-29S-0.5SH
	32	16.57	20.5	HFJ32CT-ND	2.27	1.75	1.40	1.16	HFJ32TR-ND	2,000	889.00/M	FH12A-32S-0.5SH
	34	17.57	21.5	HFJ34CT-ND	2.41	1.86	1.49	1.23	HFJ34TR-ND	2,000	945.00/M	FH12A-34S-0.5SH
	36	18.57	22.5	HFJ36CT-ND	2.45	1.89	1.51	1.26	HFJ36TR-ND	2,000	963.00/M	FH12A-36S-0.5SH
	42	21.57	25.5	HFJ42CT-ND	2.79	2.15	1.72	1.43	HFJ42TR-ND	2,000	1093.00/M	FH12A-42S-0.5SH
	45	23.07	27.0	HFJ45CT-ND	2.93	2.25	1.80	1.50	HFJ45TR-ND	2,000	1148.00/M	FH12A-45S-0.5SH
	0.5mm 水平安装 - 顶部触点式 - 符合 RoHS 规范要求											
2	10	5.57	9.5	HFJ110CT-ND	1.86	1.35	1.11	.94	HFJ110TR-ND	2,000	637.00/M	FH12A-10S-0.5SH(55)
	12	6.57	10.5	HFJ112CT-ND	1.69	1.30	1.04	.87	HFJ112TR-ND	2,000	663.00/M	FH12A-12S-0.5SH(55)
	16	8.57	12.5	HFJ116CT-ND	1.92	1.48	1.18	.98	HFJ116TR-ND	2,000	752.00/M	FH12A-16S-0.5SH(55)
	18	9.57	13.5	HFJ118CT-ND	2.02	1.55	1.24	1.03	HFJ118TR-ND	2,000	791.00/M	FH12A-18S-0.5SH(55)
	20	10.57	14.5	HFJ120CT-ND	1.98	1.53	1.22	1.02	HFJ120TR-ND	2,000	778.00/M	FH12A-20S-0.5SH(55)
	24	12.57	16.5	HFJ124CT-ND	2.31	1.78	1.42	1.18	HFJ124TR-ND	2,000	905.00/M	FH12A-24S-0.5SH(55)
	30	15.57	19.5	HFJ130CT-ND	2.76	2.13	1.70	1.42	HFJ130TR-ND	2,000	1084.00/M	FH12A-30S-0.5SH(55)
	32	16.57	20.5	HFJ132CT-ND	2.86	2.20	1.76	1.47	HFJ132TR-ND	2,000	1122.00/M	FH12A-32S-0.5SH(55)
	33	17.07	21.0	HFJ133CT-ND	2.96	2.28	1.82	1.52	—	—	—	FH12A-33S-0.5SH(55)
	36	18.57	22.5	HFJ136CT-ND	3.15	2.43	1.94	1.62	HFJ136TR-ND	2,000	1237.00/M	FH12A-36S-0.5SH(55)
	40	20.57	24.5	HFJ140CT-ND	3.07	2.39	1.91	1.54	HFJ140TR-ND	2,000	1352.00/M	FH12A-40S-0.5SH(55)
50	25.57	29.5	HFJ150CT-ND	3.80	2.95	2.36	1.90	HFJ150TR-ND	2,000	1670.00/M	FH12A-50S-0.5SH(55)	
0.5mm 垂直安装												
3	12	7.5	9.4	HFL12CT-ND	1.66	1.20	.99	.83	—	—	—	FH12-12S-0.5SV
	13	8.0	9.9	HFL13CT-ND	1.77	1.28	1.05	.89	—	—	—	FH12-13S-0.5SV
	18	10.5	12.4	HFL18CT-ND	1.70	1.31	1.05	.87	HFL18TR-ND	1,000	696.00	FH12-18S-0.5SV
	20	11.5	13.4	HFL20CT-ND	1.84	1.42	1.14	.94	—	—	—	FH12-20S-0.5SV
	24	13.5	15.4	HFL24CT-ND	1.98	1.53	1.22	1.02	—	—	—	FH12-24S-0.5SV
	26	14.5	16.4	HFL26CT-ND	2.10	1.62	1.29	1.08	—	—	—	FH12-26S-0.5SV
	33	18.0	19.9	HFL33CT-ND	2.45	1.89	1.51	1.26	HFL33TR-ND	1,000	1004.00	FH12-33S-0.5SV
	45	24.0	25.9	HFL45CT-ND	3.02	2.33	1.86	1.55	—	—	—	FH12-45S-0.5SV
	49	26.0	27.9	HFL49CT-ND	3.21	2.47	1.98	1.64	HFL49TR-ND	1,000	1313.00	FH12-49S-0.5SV
0.5mm 垂直安装 - 符合 RoHS 规范要求												
3	10	6.5	8.4	HFL110CT-ND	1.72	1.33	1.06	.88	HFL110TR-ND	1,000	705.00	FH12-10S-0.5SV(55)
	12	7.5	9.4	HFL112CT-ND	1.92	1.48	1.18	.98	HFL112TR-ND	1,000	785.00	FH12-12S-0.5SV(55)
	15	9.0	10.9	HFL115CT-ND	2.18	1.68	1.34	1.12	HFL115TR-ND	1,000	891.00	FH12-15S-0.5SV(55)
	16	9.5	11.4	HFL116CT-ND	2.21	1.70	1.36	1.13	HFL116TR-ND	1,000	904.00	FH12-16S-0.5SV(55)
	18	10.5	12.4	HFL118CT-ND	2.37	1.83	1.46	1.22	HFL118TR-ND	1,000	971.00	FH12-18S-0.5SV(55)
	20	11.5	13.4	HFL120CT-ND	2.50	1.93	1.54	1.28	HFL120TR-ND	1,000	1024.00	FH12-20S-0.5SV(55)
	22	12.5	14.4	HFL122CT-ND	2.67	2.05	1.64	1.37	HFL122TR-ND	1,000	1091.00	FH12-22S-0.5SV(55)
	24	13.5	15.4	HFL124CT-ND	2.86	2.20	1.76	1.47	HFL124TR-ND	1,000	1170.00	FH12-24S-0.5SV(55)
	26	14.5	16.4	HFL126CT-ND	2.96	2.28	1.82	1.52	HFL126TR-ND	1,000	1210.00	FH12-26S-0.5SV(55)
	30	16.5	18.4	HFL130CT-ND	2.90	2.25	1.80	1.45	—	—	—	FH12-30S-0.5SV(55)
	33	18.0	19.9	HFL133CT-ND	3.16	2.46	1.97	1.59	HFL133TR-ND	1,000	1417.00	FH12-33S-0.5SV(55)
	36	19.5	21.4	HFL136CT-ND	3.51	2.73	2.18	1.76	HFL136TR-ND	1,000	1573.00	FH12-36S-0.5SV(55)
	40	21.5	23.4	HFL140CT-ND	3.80	2.95	2.36	1.90	HFL140TR-ND	1,000	1703.00	FH12-40S-0.5SV(55)
	45	24.0	25.9	HFL145CT-ND	4.06	3.15	2.52	2.03	HFL145TR-ND	1,000	1820.00	FH12-45S-0.5SV(55)
50	26.5	28.4	HFL150CT-ND	4.35	3.38	2.70	2.18	HFL150TR-ND	1,000	1950.00	FH12-50S-0.5SV(55)	
0.5mm 水平安装 - 底部触点型, FPC 终端厚度为 0.18mm												
1	6	3.57	7.1	HFR06CT-ND	1.88	1.36	1.12	.94	—	—	—	FH12F-6S-0.5SH
	10	5.57	9.1	HFR10CT-ND	1.70	1.31	1.05	.87	HFR10TR-ND	2,000	667.00/M	FH12F-10S-0.5SH
	12	6.57	10.1	HFR12CT-ND	1.84	1.42	1.14	.94	HFR12TR-ND	2,000	722.00/M	FH12F-12S-0.5SH
	13	7.07	10.6	HFR13CT-ND	1.89	1.46	1.17	.97	HFR13TR-ND	2,000	741.00/M	FH12F-13S-0.5SH
	14	7.57	11.1	HFR14CT-ND	1.93	1.49	1.19	.99				