



1.00 mm (0.039") FFC-FPC 连接器 (接上页)



A

图	位置数量	尺寸: 英寸 (mm)		Digi-Key 零件编号	剪切带价格			Digi-Key 零件编号	带卷		FCI 零件编号	
		A	B		1	25	100		数量	价格		
1	12	0.717 (18.20)	0.520 (13.20)	609-1939-ND†	1.19	16.34	54.95	—	—	—	SLW12S-1C7LF	
	14	0.795 (20.20)	0.598 (15.20)	609-1941-ND†	.72	8.77	29.24	—	—	—	SLW14S-1C7LF	
	15	0.835 (21.20)	0.638 (16.20)	609-1943-ND†	1.35	18.13	62.15	—	—	—	SLW15S-1C7LF	
	16	0.874 (22.20)	0.677 (17.20)	609-1945-ND†	1.33	17.87	61.25	—	—	—	SLW16S-1C7LF	
	18	0.953 (24.20)	0.756 (19.20)	609-1947-ND†	1.01	10.38	35.20	—	—	—	SLW18S-1C7LF	
	20	1.031 (26.20)	0.835 (21.20)	609-1949-ND†	1.02	13.38	45.18	—	—	—	SLW20S-1C7LF	
	22	1.110 (28.20)	0.913 (23.20)	609-1951-ND†	.78	9.78	31.79	—	—	—	SLW22S-1C7LF	
	24	1.189 (30.20)	0.992 (25.20)	609-1953-ND†	2.16	21.58	73.98	—	—	—	SLW24S-1C7LF	
	26	1.268 (32.20)	1.071 (27.20)	609-1955-ND†	.87	10.21	33.19	—	—	—	SLW26S-1C7LF	
	28	1.346 (34.20)	1.150 (29.20)	609-1957-ND†	.64	7.97	25.50	—	—	—	SLW28S-1C7LF	
30	1.425 (36.20)	1.228 (31.20)	609-1959-ND†	1.10	15.16	51.00	—	—	—	SLW30S-1C7LF		
HLW 系列 - 顶端插入 PC 安装 LIF												
2	4	0.260 (6.60)	0.118 (3.00)	609-1815-ND†	.23	2.54	7.83	—	—	—	HLW4S-2C7LF	
	5	0.300 (7.60)	0.157 (4.00)	609-1817-ND†	.25	2.71	8.40	—	—	—	HLW5S-2C7LF	
	6	0.339 (8.60)	0.197 (5.00)	609-1819-ND†	.26	2.81	8.71	—	—	—	HLW6S-2C7LF	
	8	0.417 (10.60)	0.276 (7.00)	609-1821-ND†	.30	3.29	10.07	—	—	—	HLW8S-2C7LF	
	10	0.496 (12.60)	0.354 (9.00)	609-1823-ND†	.27	2.91	9.00	—	—	—	HLW10S-2C7LF	
	12	0.575 (14.60)	0.433 (11.00)	609-1825-ND†	.46	5.49	17.89	—	—	—	HLW12S-2C7LF	
	14	0.654 (16.60)	0.512 (13.00)	609-1827-ND†	.29	3.38	10.35	—	—	—	HLW14S-2C7LF	
	15	0.693 (17.60)	0.551 (14.00)	609-1829-ND†	.34	3.94	12.67	—	—	—	HLW15S-2C7LF	
	16	0.732 (18.60)	0.591 (15.00)	609-1831-ND†	.35	4.03	12.94	—	—	—	HLW16S-2C7LF	
	18	0.811 (20.60)	0.670 (17.00)	609-1833-ND†	.37	4.29	13.49	—	—	—	HLW18S-2C7LF	
	20	0.890 (22.60)	0.748 (19.00)	609-1835-ND†	.38	4.38	13.75	—	—	—	HLW20S-2C7LF	
	22	0.969 (24.60)	0.827 (21.00)	609-1837-ND†	.38	4.55	14.30	—	—	—	HLW22S-2C7LF	
	24	1.047 (26.60)	0.906 (23.00)	609-1839-ND†	.39	4.64	14.59	—	—	—	HLW24S-2C7LF	
	26	1.126 (28.60)	0.984 (25.00)	609-1841-ND†	.41	4.90	15.69	—	—	—	HLW26S-2C7LF	
	28	1.205 (30.60)	1.063 (27.00)	609-1843-ND†	.42	5.07	16.24	—	—	—	HLW28S-2C7LF	
	30	1.283 (32.60)	1.142 (29.00)	609-1845-ND†	.42	5.07	16.24	—	—	—	HLW30S-2C7LF	
	SLW 系列 - 侧面插入 PC 安装 LIF											
	3	4	0.402 (10.20)	0.205 (5.20)	609-1928-ND†	.52	6.10	19.70	—	—	—	SLW4R-1C7LF
5		0.441 (11.20)	0.244 (6.20)	609-1930-ND†	.41	4.90	15.69	—	—	—	SLW5R-1C7LF	
6		0.480 (12.20)	0.283 (7.20)	609-1932-ND†	.41	4.90	15.69	—	—	—	SLW6R-1C7LF	
8		0.559 (14.20)	0.362 (9.20)	609-1934-ND†	.55	6.72	21.50	—	—	—	SLW8R-1C7LF	
10		0.638 (16.20)	0.441 (11.20)	609-1936-ND†	.61	7.45	23.84	—	—	—	SLW10R-1C7LF	
12		0.717 (18.20)	0.520 (13.20)	609-1938-ND†	1.20	16.46	55.35	—	—	—	SLW12R-1C7LF	
14		0.795 (20.20)	0.598 (15.20)	609-1940-ND†	.82	10.07	34.16	—	—	—	SLW14R-1C7LF	
15		0.835 (21.20)	0.638 (16.20)	609-1942-ND†	.71	8.52	28.40	—	—	—	SLW15R-1C7LF	
16		0.874 (22.20)	0.677 (17.20)	609-1944-ND†	.74	9.02	30.06	—	—	—	SLW16R-1C7LF	
18		0.953 (24.20)	0.756 (19.20)	609-1946-ND†	.83	10.18	34.53	—	—	—	SLW18R-1C7LF	
20		1.031 (26.20)	0.835 (21.20)	609-1948-ND†	.78	9.78	31.73	—	—	—	SLW20R-1C7LF	
22		1.110 (28.20)	0.913 (23.20)	609-1950-ND†	.84	10.64	34.57	—	—	—	SLW22R-1C7LF	
24		1.189 (30.20)	0.992 (25.20)	609-1952-ND†	.85	10.43	35.37	—	—	—	SLW24R-1C7LF	
26		1.268 (32.20)	1.071 (27.20)	609-1954-ND†	.87	10.93	37.07	—	—	—	SLW26R-1C7LF	
28		1.346 (34.20)	1.150 (29.20)	609-1956-ND†	.69	8.25	27.50	—	—	—	SLW28R-1C7LF	
30		1.425 (36.20)	1.228 (31.20)	609-1958-ND†	1.05	13.69	47.29	—	—	—	SLW30R-1C7LF	
HLW 系列 - 侧面插入 PC 安装 LIF												
4		4	0.260 (6.60)	0.118 (3.00)	609-1814-ND†	.20	2.27	6.88	—	—	—	HLW4R-2C7LF
	5	0.300 (7.60)	0.157 (4.00)	609-1816-ND†	.25	2.70	8.11	—	—	—	HLW5R-2C7LF	
	6	0.339 (8.60)	0.197 (5.00)	609-1818-ND†	.25	2.71	8.40	—	—	—	HLW6R-2C7LF	
	8	0.417 (10.60)	0.276 (7.00)	609-1820-ND†	.27	3.00	9.60	—	—	—	HLW8R-2C7LF	
	10	0.496 (12.60)	0.354 (9.00)	609-1822-ND†	.27	2.91	9.00	—	—	—	HLW10R-2C7LF	
	12	0.575 (14.60)	0.433 (11.00)	609-1824-ND†	.30	3.24	10.65	—	—	—	HLW12R-2C7LF	
	14	0.654 (16.60)	0.512 (13.00)	609-1826-ND†	.31	3.50	11.25	—	—	—	HLW14R-2C7LF	
	15	0.693 (17.60)	0.551 (14.00)	609-1828-ND†	.57	7.01	22.42	—	—	—	HLW15R-2C7LF	
	16	0.732 (18.60)	0.591 (15.00)	609-1830-ND†	.34	3.85	12.38	—	—	—	HLW16R-2C7LF	
	18	0.811 (20.60)	0.670 (17.00)	609-1832-ND†	.35	4.03	12.94	—	—	—	HLW18R-2C7LF	
	20	0.890 (22.60)	0.748 (19.00)	609-1834-ND†	.37	4.29	13.49	—	—	—	HLW20R-2C7LF	
	22	0.969 (24.60)	0.827 (21.00)	609-1836-ND†	.38	4.47	14.04	—	—	—	HLW22R-2C7LF	
	24	1.047 (26.60)	0.906 (23.00)	609-1838-ND†	.38	4.55	14.30	—	—	—	HLW24R-2C7LF	
	26	1.126 (28.60)	0.984 (25.00)	609-1840-ND†	.41	4.82	15.14	—	—	—	HLW26R-2C7LF	
	28	1.205 (30.60)	1.063 (27.00)	609-1842-ND†	.41	4.90	15.69	—	—	—	HLW28R-2C7LF	
	30	1.283 (32.60)	1.142 (29.00)	609-1844-ND†	.42	4.98	15.95	—	—	—	HLW30R-2C7LF	
	HFW 系列 - 顶端插入 SMT 非 ZIF											
	5	4	0.276 (7.00)	0.118 (3.00)	609-1105-1-ND	.42	5.25	16.97	609-1105-2-ND	1,000	133.32	HFW4S-2STE1LF
5		0.315 (8.00)	0.157 (4.00)	609-1106-1-ND	.70	8.80	28.16	609-1106-2-ND	1,000	232.32	HFW5S-2STE1LF	
6		0.354 (9.00)	0.197 (5.00)	609-1107-1-ND	.42	5.25	16.97	609-1107-2-ND	1,000	169.68	HFW6S-2STE1LF	
7		0.394 (10.00)	0.236 (6.00)	609-1108-1-ND	.58	7.07	22.62	609-1108-2-ND	1,000	184.35	HFW7S-2STE1LF	
8		0.433 (11.00)	0.276 (7.00)	609-1109-1-ND	.75	9.37	30.46	609-1109-2-ND	1,000	249.92	HFW8S-2STE1LF	
9		0.472 (12.00)	0.315 (8.00)	609-1110-1-ND	.38	4.71	15.08	609-1110-2-ND	1,000	122.90	HFW9S-2STE1LF	
10		0.512 (13.00)	0.354 (9.00)	609-1111-1-ND	.79	9.99	32.47	609-1111-2-ND	1,000	266.40	HFW10S-2STE1LF	
11		0.551 (14.00)	0.394 (10.00)	609-1112-1-ND	.68	8.33	26.64	609-1112-2-ND	1,000	187.94	HFW11S-2STE1LF	
12		0.591 (15.00)	0.433 (11.00)	609-1113-1-ND	.83	10.15	34.46	609-1113-2-ND	1,000	282.72	HFW12S-2STE1LF	
13		0.630 (16.00)	0.472 (12.00)	609-1114-1-ND	.60	7.41	23.70	609-1114-2-ND	1,000	193.16	HFW13S-2STE1LF	
14		0.670 (17.00)	0.512 (13.00)	609-1115-1-ND	.86	10.75	34.40	609-1115-2-ND	1,000	280.36	HFW14S-2STE1LF	
15		0.709 (18.00)	0.551 (14.00)	609-1116-1-ND	.81	10.13	32.40	—	—	—	HFW15S-2STE1LF	
16		0.748 (19.00)	0.591 (15.00)	609-1117-1-ND	1.01	12.07	40.24	609-1117-2-ND	2,000	327.96/M	HFW16S-2STE1LF	
17		0.787 (20.00)	0.630 (16.00)	609-1118-1-ND	.66	7.89	26.30	609-1118-2-ND	1,000	214.35	HFW17S-2STE1LF	
18		0.827 (21.00)	0.670 (17.00)	609-1119-1-ND	.89	11.11	37.69	609-1119-2-ND	1,000	309.28	HFW18S-2STE1LF	
19		0.866 (22.00)	0.709 (18.00)	609-1120-1-ND	.69	8.41	28.02	609-1120-2-ND	1,000	228.36	HFW19S-2STE1LF	
20		0.906 (23.00)	0.748 (19.00)	609-1121-1-ND	1.21	14.48	48.26	609-1121-2-ND	1,000	393.16	HFW20S-2STE1LF	
21		0.945 (24.00)	0.787 (20.00)	609-1122-1-ND	.73	8.99	29.96	609-1122-2-ND	1,000	244.17	HFW21S-2STE1LF	
22		0.984 (25.00)	0.827 (21.00)	609-1123-1-ND	.74	9.05	30.18	609-1123-2-ND	1,000	245.97	HFW22S-2STE1LF	
23		1.024 (26.00)	0.866 (22.00)	609-1124-1-ND	.84	10.54	33.74	609-1124-2-ND	1,000	254.77	HFW23S-2STE1LF	
24		1.063 (27.00)	0.906 (23.00)	609-1125-1-ND	.79	9.70	32.32	609-1125-2-ND	2,000	258.56/M	HFW24S-2STE1LF	
25		1.102 (28.00)	0.945 (24.00)	609-1126-1-ND	.83	10.34	33.62	609-1126-2-ND	1,000	275.84	HFW25S-2STE1LF	
26		1.142 (29.00)	0.984 (25.00)	609-1127-1-ND	.95	11.86	38.55	609-1127-2-ND	1,000	316.32	HFW26S-2STE1LF	
27		1.181 (30.00)	1.024 (26.00)	609-1128-1-ND	.89	11.12	36.13	609-1128-2-ND	1,000	296.48	HFW27S-2STE1LF	
28		1.220 (31.00)	1.063 (27.00)	609-1129-1-ND	1.04	14.26	47.95	609-1129-2-ND	1,000	414.72	HFW28S-2STE1LF	
29		1.260 (32.00)	1.102 (28.00)	609-1130-1-ND	.98	12.41	40.35	609-1130-2-ND	1,000	319.04	HFW29S-2STE1LF	
32		1.378 (35.00)	1.220 (