



1.00 mm (0.039") FFC-FPC 连接器 (接上页)



A

图	位置数量	尺寸: 英寸 (mm)		Digi-Key 零件编号	剪切带价格			Digi-Key 零件编号	带卷		FCI 零件编号	
		A	B		1	25	100		数量	价格		
6	26	1.276 (32.40)	0.984 (25.00)	609-1164-1-ND	1.19	15.53	52.44	609-1164-2-ND	1,000	427.80	SWF26S-2STE1LF	
	28	1.354 (34.40)	1.063 (27.00)	609-1166-1-ND	1.40	19.78	64.73	609-1166-2-ND	1,000	539.40	SWF28S-2STE1LF	
	30	1.433 (36.40)	1.142 (29.00)	609-1168-1-ND	1.29	16.85	58.22	609-1168-2-ND	1,000	474.92	SWF30S-2STE1LF	
SFV 系列 - 顶端插入 SMT ZIF (有安装板)												
6	4	0.409 (10.40)	0.118 (3.00)	609-1133-1-ND	.92	11.52	39.08	609-1133-2-ND	1,000	320.64	SWF4S-2STME1LF	
	5	0.449 (11.40)	0.157 (4.00)	609-1135-1-ND	.93	11.42	38.73	609-1135-2-ND	1,000	317.76	SWF5S-2STME1LF	
	6	0.488 (12.40)	0.197 (5.00)	609-1137-1-ND	.97	12.10	41.03	609-1137-2-ND	1,000	336.64	SWF6S-2STME1LF	
	8	0.567 (14.40)	0.276 (7.00)	609-1138-1-ND	1.07	13.14	44.58	609-1138-2-ND	1,000	365.76	SWF8S-2STME1LF	
	10	0.646 (16.40)	0.354 (9.00)	609-1141-1-ND	.85	10.34	35.08	609-1141-2-ND	1,000	377.76	SWF10S-2STME1LF	
	11	0.685 (17.40)	0.394 (10.00)	609-1143-1-ND	.90	11.22	37.89	609-1143-2-ND	1,000	309.07	SWF11S-2STME1LF	
	12	0.724 (18.40)	0.433 (11.00)	609-1145-1-ND	.87	11.15	37.68	609-1145-2-ND	1,000	307.37	SWF12S-2STME1LF	
	14	0.803 (20.40)	0.512 (13.00)	609-1147-1-ND	1.18	14.80	50.19	609-1147-2-ND	1,000	411.84	SWF14S-2STME1LF	
	15	0.843 (21.40)	0.551 (14.00)	609-1149-1-ND	.95	11.82	39.92	609-1149-2-ND	1,000	325.66	SWF15S-2STME1LF	
	16	0.882 (22.40)	0.591 (15.00)	609-1151-1-ND	1.10	14.43	48.75	609-1151-2-ND	1,000	397.73	SWF16S-2STME1LF	
	17	0.921 (23.40)	0.630 (16.00)	609-1153-1-ND	.93	12.12	40.95	609-1153-2-ND	1,000	334.03	SWF17S-2STME1LF	
	18	0.961 (24.40)	0.670 (17.00)	609-1155-1-ND	.97	12.43	41.97	609-1155-2-ND	1,000	342.40	SWF18S-2STME1LF	
	20	1.040 (26.40)	0.748 (19.00)	609-1157-1-ND	1.26	16.46	55.59	609-1157-2-ND	1,000	453.53	SWF20S-2STME1LF	
	22	1.118 (28.40)	0.827 (21.00)	609-1159-1-ND	.70	9.24	31.22	—	—	—	—	
	23	1.157 (29.40)	0.866 (22.00)	609-1161-1-ND	1.00	13.04	45.05	609-1161-2-ND	1,000	367.51	SWF23S-2STME1LF	
	24	1.197 (30.40)	0.906 (23.00)	609-1163-1-ND	.92	12.12	40.95	609-1163-2-ND	1,000	334.03	SWF24S-2STME1LF	
	26	1.276 (32.40)	0.984 (25.00)	609-1165-1-ND	1.44	18.88	65.23	609-1165-2-ND	1,000	532.12	SWF26S-2STME1LF	
	28	1.354 (34.40)	1.063 (27.00)	609-1167-1-ND	1.40	18.38	63.48	609-1167-2-ND	1,000	517.86	SWF28S-2STME1LF	
30	1.433 (36.40)	1.142 (29.00)	609-1169-1-ND	1.48	20.36	68.47	609-1169-2-ND	1,000	566.25	SWF30S-2STME1LF		
HFV 系列 - 侧面插入 SMT ZIF, 下部触点型												
7	4	0.260 (6.60)	0.118 (3.00)	609-1782-1-ND	.68	8.48	27.12	609-1782-2-ND	2,000	207.47/M	HFW4R-1STE1LF	
	5	0.300 (7.60)	0.157 (4.00)	609-1784-1-ND	.50	5.85	18.90	609-1784-2-ND	2,000	144.00/M	HFW5R-1STE1LF	
	6	0.339 (8.60)	0.197 (5.00)	609-1786-1-ND	.35	4.23	13.65	609-1786-2-ND	2,000	104.00/M	HFW6R-1STE1LF	
	8	0.417 (10.60)	0.276 (7.00)	609-1788-1-ND	.78	9.91	32.19	609-1788-2-ND	2,000	252.60/M	HFW8R-1STE1LF	
	10	0.496 (12.60)	0.354 (9.00)	609-1790-1-ND	.79	9.99	32.47	609-1790-2-ND	2,000	249.75/M	HFW10R-1STE1LF	
	12	0.575 (14.60)	0.433 (11.00)	609-1792-1-ND	.50	6.18	19.76	609-1792-2-ND	2,000	153.14/M	HFW12R-1STE1LF	
	14	0.654 (16.60)	0.512 (13.00)	609-1794-1-ND	.89	11.41	38.69	609-1794-2-ND	2,000	297.60/M	HFW14R-1STE1LF	
	15	0.693 (17.60)	0.551 (14.00)	609-1796-1-ND	.93	11.67	39.43	609-1796-2-ND	2,000	311.25/M	HFW15R-1STE1LF	
	16	0.732 (18.60)	0.591 (15.00)	609-1798-1-ND	.82	9.88	33.52	—	—	—	—	
	18	0.811 (20.60)	0.670 (17.00)	609-1800-1-ND	.89	11.11	37.69	609-1800-2-ND	2,000	289.95/M	HFW18R-1STE1LF	
	20	0.890 (22.60)	0.748 (19.00)	609-1802-1-ND	.58	6.94	23.12	609-1802-2-ND	2,000	176.87/M	HFW20R-1STE1LF	
	22	0.969 (24.60)	0.827 (21.00)	609-1804-1-ND	.64	8.01	25.62	609-1804-2-ND	2,000	196.00/M	HFW22R-1STE1LF	
	24	1.047 (26.60)	0.906 (23.00)	609-1806-1-ND	.71	8.72	29.08	609-1806-2-ND	2,000	205.63/M	HFW24R-1STE1LF	
	26	1.126 (28.60)	0.984 (25.00)	609-1808-1-ND	.69	8.66	28.16	609-1808-2-ND	2,000	216.60/M	HFW26R-1STE1LF	
	28	1.205 (30.60)	1.063 (27.00)	609-1810-1-ND	.75	9.38	30.48	609-1810-2-ND	2,000	234.45/M	HFW28R-1STE1LF	
	30	1.283 (32.60)	1.142 (29.00)	609-1812-1-ND	1.11	15.22	51.19	609-1812-2-ND	2,000	401.22/M	HFW30R-1STE1LF	
	HFV 系列 - 侧面插入 SMT ZIF, 上部触点型											
	7	4	0.260 (6.60)	0.118 (3.00)	609-1783-1-ND	.77	9.61	31.22	609-1783-2-ND	2,000	240.15/M	HFW4R-2STE1LF
5		0.300 (7.60)	0.157 (4.00)	609-1785-1-ND	.51	6.14	19.85	609-1785-2-ND	2,000	151.20/M	HFW5R-2STE1LF	
6		0.339 (8.60)	0.197 (5.00)	609-1787-1-ND	.35	4.23	13.65	609-1787-2-ND	2,000	104.00/M	HFW6R-2STE1LF	
8		0.417 (10.60)	0.276 (7.00)	609-1789-1-ND	.99	12.22	39.48	609-1789-2-ND	2,000	300.80/M	HFW8R-2STE1LF	
10		0.496 (12.60)	0.354 (9.00)	609-1791-1-ND	.73	9.19	29.85	609-1791-2-ND	2,000	229.65/M	HFW10R-2STE1LF	
12		0.575 (14.60)	0.433 (11.00)	609-1793-1-ND	.92	11.26	36.02	609-1793-2-ND	2,000	279.18/M	HFW12R-2STE1LF	
14		0.654 (16.60)	0.512 (13.00)	609-1795-1-ND	.80	10.09	32.80	—	—	—	—	
15		0.693 (17.60)	0.551 (14.00)	609-1797-1-ND	.51	6.25	20.00	609-1797-2-ND	2,000	155.00/M	HFW15R-2STE1LF	
16		0.732 (18.60)	0.591 (15.00)	609-1799-1-ND	.53	6.44	20.62	609-1799-2-ND	2,000	159.81/M	HFW16R-2STE1LF	
18		0.811 (20.60)	0.670 (17.00)	609-1801-1-ND	.65	7.84	26.12	609-1801-2-ND	2,000	166.47/M	HFW18R-2STE1LF	
20		0.890 (22.60)	0.748 (19.00)	609-1803-1-ND	1.31	15.76	52.52	609-1803-2-ND	2,000	401.78/M	HFW20R-2STE1LF	
22		0.969 (24.60)	0.827 (21.00)	609-1805-1-ND	.68	8.53	27.28	609-1805-2-ND	2,000	208.69/M	HFW22R-2STE1LF	
24		1.047 (26.60)	0.906 (23.00)	609-1807-1-ND	1.19	14.60	48.66	609-1807-2-ND	2,000	372.25/M	HFW24R-2STE1LF	
26		1.126 (28.60)	0.984 (25.00)	609-1809-1-ND	.69	8.66	28.16	609-1809-2-ND	2,000	216.60/M	HFW26R-2STE1LF	
28		1.205 (30.60)	1.063 (27.00)	609-1811-1-ND	.77	9.77	31.75	609-1811-2-ND	2,000	234.45/M	HFW28R-2STE1LF	
30		1.283 (32.60)	1.142 (29.00)	609-1813-1-ND	1.29	15.81	53.61	609-1813-2-ND	2,000	412.35/M	HFW30R-2STE1LF	
SFV 系列 - 侧面插入 SMT ZIF, 下部触点型												
8		4	0.386 (9.80)	0.118 (3.00)	609-1883-1-ND	.91	11.36	38.53	609-1883-2-ND	2,000	296.40/M	SWF4R-1STE1LF
	5	0.425 (10.80)	0.157 (4.00)	609-1887-1-ND	.91	11.59	39.31	609-1887-2-ND	2,000	302.40/M	SWF5R-1STE1LF	
	6	0.465 (11.80)	0.197 (5.00)	609-1889-1-ND	1.24	15.26	48.82	609-1889-2-ND	2,000	378.36/M	SWF6R-1STE1LF	
	8	0.543 (13.80)	0.276 (7.00)	609-1893-1-ND	.79	9.97	32.41	609-1893-2-ND	2,000	249.30/M	SWF8R-1STE1LF	
	10	0.622 (15.80)	0.354 (9.00)	609-1897-1-ND	1.00	13.13	44.35	609-1897-2-ND	2,000	350.10/M	SWF10R-1STE1LF	
	12	0.701 (17.80)	0.433 (11.00)	609-1900-1-ND	.89	11.11	37.67	609-1900-2-ND	2,000	289.80/M	SWF12R-1STE1LF	
	14	0.780 (19.80)	0.512 (13.00)	609-1902-1-ND	.90	11.52	39.08	609-1902-2-ND	2,000	300.60/M	SWF14R-1STE1LF	
	15	0.819 (20.80)	0.551 (14.00)	609-1905-1-ND	.97	12.35	41.71	609-1905-2-ND	2,000	329.25/M	SWF15R-1STE1LF	
	16	0.858 (21.80)	0.591 (15.00)	609-1907-1-ND	1.15	15.75	52.98	609-1907-2-ND	2,000	415.28/M	SWF16R-1STE1LF	
	18	0.937 (23.80)	0.670 (17.00)	609-1911-1-ND	.97	12.71	42.92	609-1911-2-ND	2,000	338.85/M	SWF18R-1STE1LF	
	20	1.016 (25.80)	0.748 (19.00)	609-1913-1-ND	1.41	19.46	66.73	609-1913-2-ND	2,000	537.52/M	SWF20R-1STE1LF	
	22	1.094 (27.80)	0.827 (21.00)	609-1916-1-ND	1.03	13.48	46.55	609-1916-2-ND	2,000	367.50/M	SWF22R-1STE1LF	
	24	1.173 (29.80)	0.906 (23.00)	609-1919-1-ND	1.03	14.14	47.56	609-1919-2-ND	2,000	372.80/M	SWF24R-1STE1LF	
	26	1.252 (31.80)	0.984 (25.00)	609-1921-1-ND	1.54	20.82	72.85	609-1921-2-ND	2,000	593.23/M	SWF26R-1STE1LF	
	28	1.331 (33.80)	1.063 (27.00)	609-1924-1-ND	.90	11.25	38.00	609-1924-2-ND	2,000	420.00/M	SWF28R-1STE1LF	
	30	1.409 (35.80)	1.142 (29.00)	609-1926-1-ND	1.25	17.68	57.85	609-1926-2-ND	2,000	466.03/M	SWF30R-1STE1LF	
	SFV 系列 - 侧面插入 SMT ZIF, 上部触点型											
	8	4	0.386 (9.80)	0.118 (3.00)	609-1884-1-ND	.88	10.98	37.23	609-1884-2-ND	2,000	286.35/M	SWF4R-2STE1LF
5		0.425 (10.80)	0.157 (4.00)	609-1888-1-ND	.88	10.98	37.23	609-1888-2-ND	2,000	286.35/M	SWF5R-2STE1LF	
6		0.465 (11.80)	0.197 (5.00)	609-1890-1-ND	1.02	13.47	45.49	609-1890-2-ND	2,000	359.10/M	SWF6R-2STE1LF	
8		0.543 (13.80)	0.276 (7.00)	609-1894-1-ND	.78	9.74	31.65	609-1894-2-ND	2,000	249.45/M	SWF8R-2STE1LF	
10		0.622 (15.80)	0.354 (9.00)	609-1898-1-ND	1.19	14.88	47.60	609-1898-2-ND	2,000	364.14/M	SWF10R-2STE1LF	
12		0.701 (17.80)	0.433 (11.00)	609-1901-1-ND	1.06	14.59	49.06	609-1901-2-ND	2,000	384.54/M	SWF12R-2STE1LF	
14		0.780 (19.80)	0.512 (13.00)	609-1903-1-ND								