



Abb.	Beschreibung	Schaltkreise	Abm. „A“ Zoll (mm)	Digi-Key Teile-Nr.	Preisangaben		AMP Teile-Nr.		
					1	25			
Kodierstecker mit Trägerband									
5	10 Stecker pro Streifen	—	—	A19310-ND	.58	12.97	641994-1		
Zubehör, 0,100									
6	Geschlossenes Ende, Zugentlastungsabdeckungen, weiß	2	.200 (5.08)	A19230-ND	.24	5.37	643075-2		
		3	.300 (7.62)	A19231-ND	.54	12.11	643075-3		
		4	.400 (10.16)	A19232-ND	.26	5.84	643075-4		
		5	.500 (12.70)	A19233-ND	.54	12.19	643075-5		
		6	.600 (15.24)	A19234-ND	.28	6.25	643075-6		
		7	.700 (17.78)	A19235-ND	.56	12.67	643075-7		
		8	.800 (20.32)	A19236-ND	.57	12.71	643075-8		
		9	.900 (22.86)	A19237-ND	.59	13.37	643075-9		
		10	1.000 (25.40)	A19238-ND	.57	12.79	1-643075-0		
		11	1.100 (27.94)	A19239-ND	.60	13.45	1-643075-1		
		12	1.200 (30.48)	A19240-ND	.60	13.49	1-643075-2		
		13	1.300 (33.02)	A19241-ND	.60	13.53	1-643075-3		
		14	1.400 (35.56)	A19242-ND	.60	13.57	1-643075-4		
		15	1.500 (38.10)	A23892-ND	.61	13.61	1-643075-5		
		7	Geschlossenes Ende, Staubschutz, natur	2	—	A19250-ND	.06	1.52	640550-2
3	—			A19251-ND	.25	1.88	640550-3		
4	—			A19252-ND	.15	2.43	640550-4		
5	—			A19253-ND	.26	2.82	640550-5		
6	—			A19254-ND	.17	3.42	640550-6		
7	—			A19255-ND	.17	3.82	640550-7		
8	—			A19256-ND	.19	4.27	640550-8		
9	—			A19257-ND	.18	4.11	640550-9		
10	—			A19258-ND	.22	5.01	1-640550-0		
11	—			A19259-ND	.24	5.37	1-640550-1		
12	—			A19260-ND	.26	5.97	1-640550-2		
13	—			A19261-ND	.28	6.28	1-640550-3		
14	—			A19262-ND	.30	6.74	1-640550-4		
15	—			A23893-ND	.32	7.13	1-640550-5		
8	Durchführung, Zugentlastungsabdeckungen, weiß			2	.200 (5.08)	A19270-ND	.22	5.13	643077-2
		3	.300 (7.62)	A19271-ND	.30	6.61	643077-3		
		4	.400 (10.16)	A19272-ND	.39	8.81	643077-4		
		5	.500 (12.70)	A19273-ND	.49	11.01	643077-5		
		6	.600 (15.24)	A19274-ND	.52	11.72	643077-6		
		7	.700 (17.78)	A19275-ND	.54	12.06	643077-7		
		8	.800 (20.32)	A19276-ND	.57	12.71	643077-8		
		9	.900 (22.86)	A19277-ND	.57	12.75	643077-9		
		10	1.000 (25.40)	A19278-ND	.59	13.41	1-643077-0		
		11	1.100 (27.94)	A19279-ND	.60	13.45	1-643077-1		
		12	1.200 (30.48)	A19280-ND	.60	13.49	1-643077-2		
		13	1.300 (33.02)	A19281-ND	.65	14.57	1-643077-3		
		14	1.400 (35.56)	A19282-ND	.65	14.57	1-643077-4		
		9	Durchführung, Staubschutz, natur	3	—	A19291-ND	.25	1.88	640642-3
4	—			A19292-ND	.26	2.43	640642-4		
5	—			A19293-ND	.25	2.68	640642-5		
6	—			A19294-ND	.17	3.42	640642-6		
7	—			A19295-ND	.17	3.82	640642-7		
8	—			A19296-ND	.19	4.27	640642-8		
9	—			A19297-ND	.18	3.97	640642-9		
10	—			A19298-ND	.22	5.01	1-640642-0		
11	—			A19299-ND	.24	5.38	1-640642-1		
13	—			A19301-ND	.28	6.28	1-640642-3		
14	—			A19302-ND	.30	6.75	1-640642-4		
15	—			A23895-ND	.32	7.13	1-640642-5		
Stiftsteckleisten, 0,100" (2,54 mm) Mitten (0,200" (5,08 mm) breiter Sockel)									
10	Gerader Stift, 0,64" (0,025 mm) quadratisch, verzinkt			2	.200 (5.08)	A1911-ND	.26	5.05	640452-2
				3	.300 (7.62)	A19330-ND	.34	5.16	640452-3
		4	.400 (10.16)	A1912-ND	.30	6.88	640452-4		
		5	.500 (12.70)	A19331-ND	.43	9.71	640452-5		
		6	.600 (15.24)	A1913-ND	.47	10.59	640452-6		
		7	.700 (17.78)	A19332-ND	.55	12.36	640452-7		
		8	.800 (20.32)	A1914-ND	.62	14.12	640452-8		
		9	.900 (22.86)	A19333-ND	.70	15.88	640452-9		
		10	1.000 (25.40)	A1915-ND	.78	17.65	1-640452-0		
		15	1.500 (38.10)	A24931-ND	1.47	33.09	1-640452-5		
		11	Rechtwinkliger Stift, 0,64" (0,025 mm) quadratisch, verzinkt	2	.200 (5.08)	A1916-ND	.26	3.58	640453-2
				3	.300 (7.62)	A19340-ND	.28	5.37	640453-3
				4	.400 (10.16)	A1917-ND	.32	7.15	640453-4
				5	.500 (12.70)	A19341-ND	.45	10.09	640453-5
				6	.600 (15.24)	A1918-ND	.49	11.01	640453-6
7	.700 (17.78)			A19342-ND	.57	12.84	640453-7		
8	.800 (20.32)			A1919-ND	.65	14.68	640453-8		
9	.900 (22.86)			A19343-ND	.65	14.63	640453-9		
10	1.000 (25.40)			A1920-ND	.82	18.35	1-640453-0		
12	1.200 (30.48)			A23927-ND	.98	22.02	1-640453-2		
15	1.500 (38.10)			A23896-ND	1.53	34.41	1-640453-5		

Abb.	Beschreibung	Schaltkreise	Abm. „A“ Zoll (mm)	Digi-Key Teile-Nr.	Preisangaben		AMP Teile-Nr.				
					1	25					
Stiftsteckleisten m. schmaler Basis, 0,100" (2,54 mm) Mitten (2,34-mm-breiter Sockel)											
10	Gerader Stift, 0,64" (0,025 mm) quadratisch, ohne Halteanschlüsse, verzinkt	2	.188 (4.78)	A31112-ND	.16	2.31	3-644456-2				
		3	.288 (7.32)	A31113-ND	.17	2.88	3-644456-3				
		4	.388 (9.86)	A31114-ND	.16	3.57	3-644456-4				
		5	.488 (12.40)	A31115-ND	.21	4.76	3-644456-5				
		6	.588 (14.94)	A31116-ND	.23	5.19	3-644456-6				
		7	.688 (17.48)	A31117-ND	.29	6.55	3-644456-7				
		8	.788 (20.02)	A31118-ND	.30	6.92	3-644456-8				
		9	.888 (22.56)	A31119-ND	.33	7.50	3-644456-9				
		10	.988 (25.10)	A30844-ND	.43	9.73	4-644456-0				
		11	1.088 (27.64)	A30845-ND	.50	11.24	4-644456-1				
		13	1.288 (32.72)	A30847-ND	.59	13.35	4-644456-3				
		14	1.388 (35.26)	A30848-ND	.70	15.90	4-644456-4				
		10	Gerader Stift, 0,64" (0,025 mm) quadratisch, mit Halteanschlüssen, verzinkt	2	.188 (4.78)	A30916-ND	.20	4.45	3-644695-2		
				3	.288 (7.32)	A30917-ND	.26	5.95	3-644695-3		
4	.388 (9.86)			A30918-ND	.38	8.54	3-644695-4				
5	.488 (12.40)			A30919-ND	.47	10.67	3-644695-5				
6	.588 (14.94)			A30920-ND	.52	11.64	3-644695-6				
8	.788 (20.02)			A30922-ND	.69	15.53	3-644695-8				
9	.888 (22.56)			A30923-ND	.78	17.47	3-644695-9				
10	.988 (25.10)			A30869-ND	.86	19.41	4-644695-0				
11	1.088 (27.64)			A30870-ND	.88	19.83	4-644695-1				
12	1.188 (30.18)			A30871-ND	.92	20.63	4-644695-2				
14	1.388 (35.26)			A30873-ND	1.12	25.23	4-644695-4				
11	Rechtwinkliger Stift, 0,64" (0,025 mm) quadratisch, ohne Halteanschlüsse, verzinkt			2	.188 (4.78)	A30884-ND	.16	3.58	3-644457-2		
				3	.288 (7.32)	A30885-ND	.25	5.62	3-644457-3		
				4	.388 (9.86)	A30886-ND	.30	6.92	3-644457-4		
		8	.788 (20.02)	A30890-ND	.56	12.58	3-644457-8				
		10	.988 (25.10)	A30849-ND	.82	18.35	4-644457-0				
		11	1.088 (27.64)	A30850-ND	.83	18.75	4-644457-1				
		12	1.188 (30.18)	A30851-ND	.90	20.45	4-644457-2				
		14	1.388 (35.26)	A30853-ND	1.06	23.86	4-644457-4				
		11	Rechtwinkliger Stift, 0,64" (0,025 mm) quadratisch, mit Halteanschlüssen, verzinkt	10	.988 (25.10)	A30864-ND	.90	20.19	4-644694-0		
				12	1.188 (30.18)	A30866-ND	1.00	22.49	4-644694-2		
				13	1.288 (32.72)	A30867-ND	1.08	24.37	4-644694-3		
				14	1.388 (35.26)	A30868-ND	1.11	25.03	4-644694-4		
				Verpolungsgeschützte Steckleisten, 0,100" (2,54 mm) Mitten							
				12A	Gerader Stift, 0,64" (0,025 mm) quadratisch, verzinkt	2	.200 (5.08)	A19423-ND	.25	1.64	640454-2
3	.300 (7.62)	A19430-ND	.23			2.11	640454-3				
4	.400 (10.16)	A19431-ND	.23			2.69	640454-4				
5	.500 (12.70)	A19432-ND	.26			3.60	640454-5				
6	.600 (15.24)	A19433-ND	.26			4.12	640454-6				
7	.700 (17.78)	A19434-ND	.27			4.88	640454-7				
8	.800 (20.32)	A19435-ND	.27			5.25	640454-8				
9	.900 (22.86)	A19436-ND	.34			7.78	640454-9				
10	1.000 (25.40)	A19437-ND	.34			7.79	1-640454-0				
11	1.100 (27.94)	A19438-ND	.48			10.79	1-640454-1				
12	1.200 (30.48)	A19439-ND	.50			11.43	1-640454-2				
13	1.300 (33.02)	A19440-ND	.51			11.47	1-640454-3				
14	1.400 (35.56)	A19441-ND	.51			11.50	1-640454-4				
15	1.500 (38.10)	A23929-ND	.51			11.54	1-640454-5				
12A	Gerader Stift, 0,64" (0,025 mm) quadratisch, 30-µ-vergoldet	2	.200 (5.08)			A30770-ND	.39	8.78	3-641213-2		
		3	.300 (7.62)	A30771-ND	.62	14.06	3-641213-3				
		4	.400 (10.16)	A30772-ND	.78	17.58	3-641213-4				
		5	.500 (12.70)	A30773-ND	1.03	23.31	3-641213-5				
		6	.600 (15.24)	A30774-ND	1.18	26.46	3-641213-6				
		7	.700 (17.78)	A30775-ND	1.31	29.61	3-641213-7				
		8	.800 (20.32)	A30776-ND	1.15	26.00	3-641213-8				
		9	.900 (22.86)	A30777-ND	1.71	38.37	3-641213-9				
		10	1.000 (25.40)	A30747-ND	1.79	40.35	4-641213-0				
		11	1.100 (27.94)	A30748-ND	2.00	44.98	4-641213-1				
		12	1.200 (30.48)	A30749-ND	2.11	47.62	4-641213-2				
		13	1.300 (33.02)	A30750-ND	2.35	52.92	4-641213-3				
		14	1.400 (35.56)	A30751-ND	2.50	56.22	4-641213-4				
		15	1.500 (38.10)	A30752-ND	4.14	93.10	4-641213-5				

A

† Schwarzes Gehäuse, gemäß UL 94V-0

(Forts.)

Kostenloser Versand für Bestellungen über 65 €!
Alle Preise verstehen sich in Euro und enthalten Zollgebühren.