

Catalyst Semiconductor Inc. Digi-Reel® (Forts.)		SPEICHER – RoHS-konform				
Digi-Key Teile-Nr.	Beschreibung	Gehäuse	Stückpreis ★			
			1	25	100	
CAT24C16YI-GT3CT-ND	16-Kb serieller CMOS EEPROM	16-Kb CMOS Serial EEPROM	8-TSSOP	.52	.34	.28
CAT24C16YI-GT3TR-ND	16-Kb serieller CMOS EEPROM	16-Kb CMOS Serial EEPROM	8-TSSOP	355.56/3,000		
CAT24C32LI-G-ND	32-Kb serieller I ² C CMOS EEPROM	32-Kb I ² C CMOS Serial EEPROM	8-DIP	.88	.71	.62
CAT24C32WI-G-ND	32-Kb serieller I ² C CMOS EEPROM	32-Kb I ² C CMOS Serial EEPROM	8-SOIC	.60	.47	.41
CAT24C32WI-GT3CT-ND	32-Kb serieller I ² C CMOS EEPROM	32-Kb I ² C CMOS Serial EEPROM	8-SOIC	.50	.36	.31
CAT24C32WI-GT3TR-ND	32-Kb serieller I ² C CMOS EEPROM	32-Kb I ² C CMOS Serial EEPROM	8-SOIC	425.22/3,000		
CAT24C32YI-GT3CT-ND	32-Kb serieller I ² C CMOS EEPROM	32-Kb I ² C CMOS Serial EEPROM	8-TSSOP	.50	.36	.31
CAT24C32YI-GT3TR-ND	32-Kb serieller I ² C CMOS EEPROM	32-Kb I ² C CMOS Serial EEPROM	8-TSSOP	425.22/3,000		
CAT24C44LI-ND	256-Kb serieller CMOS EEPROM	256-Kb CMOS Serial EEPROM	8-DIP	2.63	2.12	1.93
CAT24C44LI-G-ND	64-Kb serieller I ² C CMOS EEPROM	64-Kb I ² C CMOS Serial EEPROM	8-DIP	1.11	.89	.78
CAT24C64WI-G-ND	64-Kb serieller I ² C CMOS EEPROM	64-Kb I ² C CMOS Serial EEPROM	8-SOIC	.72	.57	.49
CAT24C64WI-GT3CT-ND	64-Kb serieller I ² C CMOS EEPROM	64-Kb I ² C CMOS Serial EEPROM	8-SOIC	.63	.45	.38
CAT24C64WI-GT3TR-ND	64-Kb serieller I ² C CMOS EEPROM	64-Kb I ² C CMOS Serial EEPROM	8-SOIC	530.93/3,000		
CAT24C64YI-GT3CT-ND	64-Kb serieller I ² C CMOS EEPROM	64-Kb I ² C CMOS Serial EEPROM	8-TSSOP	.39	.31	.28
CAT24C128LI-G-ND	128-Kb serieller I ² C CMOS EEPROM	128-Kb I ² C CMOS Serial EEPROM	8-DIP	1.28	1.04	.93
CAT24C128WI-G-ND	128-Kb serieller I ² C CMOS EEPROM	128-Kb I ² C CMOS Serial EEPROM	8-SOIC	.88	.71	.62
CAT24C128WI-GT3CT-ND	128-Kb serieller I ² C CMOS EEPROM	128-Kb I ² C CMOS Serial EEPROM	8-SOIC	.62	.48	.42
CAT24C128WI-GT3TR-ND	128-Kb serieller I ² C CMOS EEPROM	128-Kb I ² C CMOS Serial EEPROM	8-SOIC	605.40/3,000		
CAT24C164WI-G-ND	16-Kb serieller CMOS EEPROM	16-Kb CMOS Serial EEPROM	8-SOIC	1.23	.98	.86
CAT24C208WI-G-ND	8-Kb serieller CMOS EEPROM, zwei Ports	8-Kb Dual Port CMOS Serial EEPROM	8-SOIC	2.32	1.87	1.70
CAT24C256LI-G-ND	256-Kb serieller I ² C CMOS EEPROM	256-Kb I ² C CMOS Serial EEPROM	8-DIP	1.78	1.44	1.29
CAT24C256WI-G-ND	256-Kb serieller I ² C CMOS EEPROM	256-Kb I ² C CMOS Serial EEPROM	8-SOIC	1.07	.86	.75
CAT34C02VP2I-GT4CT-ND	2-Kb I ² C EEPROM für serielle Präsenzerkennung, DDR2 DIMMs	2-Kb I ² C EEPROM for DDR2 DIMM Serial Presence Detect	8-TDFN	.49	.35	.30
CAT34C02VP2I-GT4TR-ND	2-Kb I ² C EEPROM für serielle Präsenzerkennung, DDR2 DIMMs	2-Kb I ² C EEPROM for DDR2 DIMM Serial Presence Detect	8-TDFN	554.15/4,000		
CAT34C02YI-G-ND	2-Kb I ² C EEPROM für serielle Präsenzerkennung, DDR2 DIMMs	2-Kb I ² C EEPROM for DDR2 DIMM Serial Presence Detect	8-TSSOP	.58	.45	.39
CAT93C46LI-G-ND	1-Kb serieller Microwire-EEPROM	1-Kb Microwire Serial EEPROM	8-DIP	.50	.39	.34
CAT93C46LI-G-ND	1-Kb serieller Microwire-EEPROM	1-Kb Microwire Serial EEPROM	8-SOIC	.35	.27	.23
CAT93C46VI-GT3CT-ND	1-Kb serieller Microwire-EEPROM	1-Kb Microwire Serial EEPROM	8-SOIC	.47	.31	.26
CAT93C46VI-GT3TR-ND	1-Kb serieller Microwire-EEPROM	1-Kb Microwire Serial EEPROM	8-SOIC	319.52/3,000		
CAT93C46WI-G-ND	1-Kb serieller Microwire-EEPROM	1-Kb Microwire Serial EEPROM	8-SOIC	.35	.27	.23
CAT93C46WI-GT3CT-ND	1-Kb serieller Microwire-EEPROM	1-Kb Microwire Serial EEPROM	8-SOIC	.47	.31	.26
CAT93C46WI-GT3TR-ND	1-Kb serieller Microwire-EEPROM	1-Kb Microwire Serial EEPROM	8-SOIC	319.52/3,000		
CAT93C46YI-G-ND	1-Kb serieller Microwire-EEPROM	1-Kb Microwire Serial EEPROM	8-TSSOP	.35	.27	.23
CAT93C56LI-G-ND	2-Kb serieller Microwire-EEPROM	2-Kb Microwire Serial EEPROM	8-DIP	.53	.41	.36
CAT93C66LI-G-ND	4-Kb Microwire serieller CMOS EEPROM	4-Kb Microwire Serial CMOS EEPROM	8-DIP	.56	.44	.38
CAT93C66VI-G-ND	4-Kb Microwire serieller CMOS EEPROM	4-Kb Microwire Serial CMOS EEPROM	8-SOIC	.52	.39	.33
CAT93C66VI-GT3CT-ND	4-Kb Microwire serieller CMOS EEPROM	4-Kb Microwire Serial CMOS EEPROM	8-SOIC	.46	.33	.28
CAT93C66VI-GT3TR-ND	4-Kb Microwire serieller CMOS EEPROM	4-Kb Microwire Serial CMOS EEPROM	8-SOIC	393.99/3,000		
CAT93C86LI-G-ND	16-Kb serieller Microwire-EEPROM	16-Kb Microwire Serial EEPROM	8-DIP	.72	.56	.49
CAT93C86LI-G-ND	16-Kb serieller Microwire-EEPROM	16-Kb Microwire Serial EEPROM	8-SOIC	.65	.51	.44
CAT93C86VI-GT3CT-ND	16-Kb serieller Microwire-EEPROM	16-Kb Microwire Serial EEPROM	8-SOIC	.54	.43	.38
CAT93C86VI-GT3TR-ND	16-Kb serieller Microwire-EEPROM	16-Kb Microwire Serial EEPROM	8-SOIC	540.54/3,000		
CAT25010LI-G-ND	1-Kb SPI serieller CMOS EEPROM	1-Kb SPI Serial CMOS EEPROM	8-DIP	.56	.44	.38
CAT25010VI-G-ND	1-Kb SPI serieller CMOS EEPROM	1-Kb SPI Serial CMOS EEPROM	8-SOIC	.46	.34	.29
CAT25010VI-GT3CT-ND	1-Kb SPI serieller CMOS EEPROM	1-Kb SPI Serial CMOS EEPROM	8-SOIC	.48	.34	.29
CAT25010VI-GT3TR-ND	1-Kb SPI serieller CMOS EEPROM	1-Kb SPI Serial CMOS EEPROM	8-SOIC	406.01/3,000		
CAT25010YI-G-ND	1-Kb SPI serieller CMOS EEPROM	1-Kb SPI Serial CMOS EEPROM	8-TSSOP	.46	.34	.29
CAT25010YI-GT3CT-ND	1-Kb SPI serieller CMOS EEPROM	1-Kb SPI Serial CMOS EEPROM	8-TSSOP	.42	.29	.25
CAT25010YI-GT3TR-ND	1-Kb SPI serieller CMOS EEPROM	1-Kb SPI Serial CMOS EEPROM	8-TSSOP	406.01/3,000		
CAT25020LI-G-ND	2-Kb SPI serieller CMOS EEPROM	2-Kb SPI Serial CMOS EEPROM	8-DIP	.59	.46	.40
CAT25020VI-G-ND	2-Kb SPI serieller CMOS EEPROM	2-Kb SPI Serial CMOS EEPROM	8-SOIC	.50	.39	.34
CAT25020VI-GT3CT-ND	2-Kb SPI serieller CMOS EEPROM	2-Kb SPI Serial CMOS EEPROM	8-SOIC	.44	.31	.27
CAT25020VI-GT3TR-ND	2-Kb SPI serieller CMOS EEPROM	2-Kb SPI Serial CMOS EEPROM	8-SOIC	430.03/3,000		
CAT25040VI-G-ND	4-Kb SPI serieller CMOS EEPROM	4-Kb SPI Serial CMOS EEPROM	8-SOIC	.53	.42	.36
CAT25040VI-GT3CT-ND	4-Kb SPI serieller CMOS EEPROM	4-Kb SPI Serial CMOS EEPROM	8-SOIC	.54	.39	.33
CAT25040VI-GT3TR-ND	4-Kb SPI serieller CMOS EEPROM	4-Kb SPI Serial CMOS EEPROM	8-SOIC	463.66/3,000		
CAT25040YI-G-ND	4-Kb SPI serieller CMOS EEPROM	4-Kb SPI Serial CMOS EEPROM	8-TSSOP	.47	.33	.29
CAT25080VI-G-ND	8-Kb SPI serieller CMOS EEPROM	8-Kb SPI Serial CMOS EEPROM	8-SOIC	.61	.48	.42
CAT25080VI-GT3CT-ND	8-Kb SPI serieller CMOS EEPROM	8-Kb SPI Serial CMOS EEPROM	8-SOIC	.54	.38	.33
CAT25080VI-GT3TR-ND	8-Kb SPI serieller CMOS EEPROM	8-Kb SPI Serial CMOS EEPROM	8-TSSOP	.63	.45	.38
CAT25080YI-GT3TR-ND	8-Kb SPI serieller CMOS EEPROM	8-Kb SPI Serial CMOS EEPROM	8-TSSOP	530.93/3,000		
CAT25128VI-G-ND	128-Kb SPI serieller CMOS EEPROM	128-Kb SPI Serial CMOS EEPROM	8-SOIC	1.21	.97	.85
CAT25160LI-G-ND	16-Kb SPI serieller CMOS EEPROM	16-Kb SPI Serial CMOS EEPROM	8-DIP	.68	.53	.45
CAT25160VI-G-ND	16-Kb SPI serieller CMOS EEPROM	16-Kb SPI Serial CMOS EEPROM	8-SOIC	.66	.52	.45
CAT25160VI-GT3CT-ND	16-Kb SPI serieller CMOS EEPROM	16-Kb SPI Serial CMOS EEPROM	8-SOIC	.54	.43	.38
CAT25160VI-GT3TR-ND	16-Kb SPI serieller CMOS EEPROM	16-Kb SPI Serial CMOS EEPROM	8-SOIC	540.54/3,000		
CAT25160YI-G-ND	16-Kb SPI serieller CMOS EEPROM	16-Kb SPI Serial CMOS EEPROM	8-TSSOP	.72	.57	.49
CAT25160YI-GT3CT-ND	16-Kb SPI serieller CMOS EEPROM	16-Kb SPI Serial CMOS EEPROM	8-TSSOP	.54	.43	.38
CAT25160YI-GT3TR-ND	16-Kb SPI serieller CMOS EEPROM	16-Kb SPI Serial CMOS EEPROM	8-TSSOP	540.54/3,000		
CAT25256LI-G-ND	256-Kb SPI serieller CMOS EEPROM	256-Kb SPI Serial CMOS EEPROM	8-DIP	1.78	1.44	1.29
CAT25256VI-G-ND	256-Kb SPI serieller CMOS EEPROM	256-Kb SPI Serial CMOS EEPROM	8-SOIC	1.44	1.17	1.05
CAT25256YI-G-ND	256-Kb SPI serieller CMOS EEPROM	256-Kb SPI Serial CMOS EEPROM	8-TSSOP	1.44	1.17	1.05
CAT25320LI-G-ND	32-Kb SPI serieller CMOS EEPROM	32-Kb SPI Serial CMOS EEPROM	8-DIP	.92	.83	.71
CAT25320VI-G-ND	32-Kb SPI serieller CMOS EEPROM	32-Kb SPI Serial CMOS EEPROM	8-SOIC	.77	.62	.54
CAT25320VI-GT3CT-ND	32-Kb SPI serieller CMOS EEPROM	32-Kb SPI Serial CMOS EEPROM	8-SOIC	.66	.51	.45
CAT25320VI-GT3TR-ND	32-Kb SPI serieller CMOS EEPROM	32-Kb SPI Serial CMOS EEPROM	8-SOIC	648.65/3,000		
CAT25320YI-GT3CT-ND	32-Kb SPI serieller CMOS EEPROM	32-Kb SPI Serial CMOS EEPROM	8-TSSOP	.56	.44	.39
CAT25640VI-G-ND	64-Kb SPI serieller CMOS EEPROM	64-Kb SPI Serial CMOS EEPROM	8-SOIC	.90	.73	.64
Parallele EEPROMs						
CAT28C16AL190-ND	16-Kb, 90 ns, paralleler CMOS EEPROM	16-Kb, 90ns, CMOS Parallel EEPROM	24-DIP	7.36	6.04	5.45
CAT28C16AWI-90TCT-ND	16-Kb, 90 ns, paralleler CMOS EEPROM	16-Kb, 90ns, CMOS Parallel EEPROM	24-SOIC	2.99	2.44	2.20
CAT28C64BL112-ND	64-Kb, 120 ns, paralleler CMOS EEPROM	64-Kb, 120ns, CMOS Parallel EEPROM	8-DIP	3.91	3.14	2.87
CAT28C64BWI-12TCT-ND	64-Kb, 120 ns, paralleler CMOS EEPROM	64-Kb, 120ns, CMOS Parallel EEPROM	28-SOIC	5.88	4.80	4.31
CAT28C64BWI-12TTR-ND	64-Kb, 120 ns, paralleler CMOS EEPROM	64-Kb, 120ns, CMOS Parallel EEPROM	28-SOIC	1625.22/500		
CAT28C256HI-12TCT-ND	256-Kb, 120 ns, paralleler CMOS EEPROM	256-Kb, 120ns, Parallel EEPROM	28-TSOP	7.29	5.61	5.05
CAT28C256HI-12TTR-ND	256-Kb, 120 ns, paralleler CMOS EEPROM	256-Kb, 120ns, Parallel EEPROM	28-TSOP	1587.59/500		
Flash-Speicher						
CAT28F020G-12T-ND	2-MB, 120 ns, CMOS Flash-Speicher	2-MB, 120ns, CMOS Flash Memory	32-PLCC	11.34	9.54	8.77
CAT28F020G-90TTR-ND	2-MB, 90 ns, CMOS Flash-Speicher	2-MB, 90ns, CMOS Flash Memory	32-PLCC	4607.00/500		
CAT28F020LI112-ND	2-MB, 120 ns, CMOS Flash-Speicher	2-MB, 120ns, CMOS Flash Memory	32-DIP	7.52	6.33	5.81



freescale Semiconductor Digi-Reel®		ERWEITERTE TAKTGEBER				
Digi-Key Teile-Nr.	Beschreibung	Gehäuse	Stückpreis ★			
			1	10	25	
Taktgeber						
MC88LV926DWR2CT-ND	Low-Skew CMOS PLL 68060 Taktreiber	Low Skew CMOS PLL 68060 Clock Driver	20-SOIC	7.43	6.73	6.17
ANALOG						
MC3PHACVDWE-ND	Motor-Controller, mono-intelligent, hochleistungsfähig	High Performance Mono Intelligent Motor Controller	28-SOIC	7.71	7.29	6.86
MC3PHACVPE-ND	Motor-Controller, mono-intelligent, hochleistungsfähig	High Performance Mono Intelligent Motor Controller	28-DIP	7.71	7.29	6.86
MC3PHACVFAE-ND	Motor-Controller, mono-intelligent, hochleistungsfähig*	High Performance Mono Intelligent Motor Controller*	32-DFN	8.13	7.32	6.67
MC13820FCR2CT-ND	Rauschcharmer Verst. mit Bypass-Schalter	Low Noise Amp with Bypass Switch	12-DFN	1.11	1.00	.88
MC33186VW1-ND	20 kHz Automobil-H-Brückentreiber*	20kHz Automotive H-Bridge Driver*	20-HSOP	9.45	8.51	7.75
MC33287DWR2CT-ND	Kontaktüberwachungs- und zweif. Low-Side-Schalter	Contact Monitoring and Dual Low Side Switch	20-SOIC	2.27	1.95	1.75
MC33287DWR2TR-ND	Kontaktüberwachungs- und zweif. Low-Side-Schalter	Contact Monitoring and Dual Low Side Switch	20-SOIC	1058.66/1,000		
MC33389DDWR2CT-ND	System-Basis-Chip mit CAN	System Base Chip with CAN	28-SOIC	7.46	6.77	6.20
MC33389DDWR2TR-ND	System-Basis-Chip mit CAN	System Base Chip with CAN	28-SOIC	4638.23/1,000		
MC33886VW-ND	Ausgangs-H-Brücke, 5.2 A*	5.2A Output H-Bridge*	20-HSOP	6.23	5.61	5.11
MC33887PNB-ND	H-Brücke mit Laststromrückkopplung, 5.0 A*	5.0A H-Bridge with Load Current Feedback*	36-PQFN	6.35	5.72	5.21
MC33888FB-ND	Vierf. Highside- und acht. Lowside-Schalter	Quad High Side and Octal Low Side Switch	64-GFP	8.67	7.89	7.30
MC33981BPWA-ND	Einf. High-Side-Schalter, 4 mOhm	4m-Ohm Single High Side Switch	16-PQFN	4.84	4.36	3.98
MC34873AFPR2CT-ND	Li-Ion/Li-Pol-Batterieladegerät, 1.2 A*	1.2A Li-Ion/Li-Pol Battery Charger*	8-UDFN	.78	.71	.66
MC34873AFPR2TR-ND	Li-Ion/Li-Pol-Batterieladegerät, 1.2 A*	1.2A Li-Ion/Li-Pol Battery Charger*	8-UDFN	1219.46/3,000		
MC34713EP-ND	Vollintegrierte Stromversorgung, Schaltmodus, 5 A, 1 MHz*	5A, 1MHz Fully Integrated Switch-Mode Power Supply*	24-DFN	2.08	1.97	1.86
MC34716EP-ND	Zweif. DDR-Stromversorgung, Schaltmodus, 1 MHz*	1MHz Dual Switch-Mode DDR Power Supply*	26-DFN	2.85	2.70	2.54
MC34717EP-ND	Vollintegrierte zweif. Stromversorgung, Schaltmodus, 5 A, 1 MHz*	5A, 1MHz Fully Integrated Dual Switch-Mode Power Supply*	26-DFN	2.85	2.70	2.54
MC34923EGR2CT-ND	Vollbrücken-PWM-Motortreiber*	Full-Bridge PWM Motor Driver*	24-SOIC	6.37	5.69	5.35
MC34923EGR2TR-ND	Vollbrücken-PWM-Motortreiber*	Full-Bridge PWM Motor Driver*	24-SOIC	4086.48/1,000		
MC233285EF-ND	Zweif. Highside TMOS-Treiber*	Dual High-Side TMOS Driver*	8-SOIC	1.70	1.54	1.38
MC233287EG-ND	Kontaktüberwachung/zweif. Lowside-Schalter, geschützt*	Contact Monitoring/Dual Low-Side Protected Driver*	20-SOIC	2.07	1.86	1.67
MC233399EF-ND	Local Interconnect Network (LIN), physische Schnittstelle*	Local Interconnect Network Physical Interface (LIN)*	8-SOIC	1.07	.97	.87
MC233689DEW-ND	System-Basis-Chip mit LIN-Transceiver*	System Basis Chip with LIN Transceiver*	32-SOIC	3.23	2.89	2.60
MC233742EG-ND	System-Basis-Chip erweitertem HS-CAN-Transceiver*	System Basis Chip w/ Enhanced High Speed CAN Xcvr*	28-SOIC	4.17	3.73	3.36

* RoHS-konform ★ NIEDRIGERE PREISE FÜR HÖHERE QUANTITÄTEN AUF ANFRAGE! ★ (Forts.)

Kostenloser Versand für Bestellungen über 65 €!
Alle Preise verstehen sich in Euro und enthalten Zollgebühren.