

Infineon Digi-Key Reel (Forts.)		INTEGRIERTE SCHALTKREISE			
Digi-Key Teile-Nr.	Beschreibung	Gehäuse	Stückpreis ★		
			1	10	100
BTS6143DINCT-ND	Smart High-Side-Leistungsschalter PROFET®, 1-Kan.*	TO-252-5	3.23	2.57	2.24
BTS6143DINTR-ND	Smart High-Side-Leistungsschalter PROFET®, 1-Kan.*	TO-252-5	2752.75/2.500		
BTS6163DINCT-ND	Smart High-Side-Leistungsschalter PROFET®, 1-Kan.*	TO-252-5	5.13	4.08	3.56
BTS6163DINTR-ND	Smart High-Side-Leistungsschalter PROFET®, 1-Kan.*	TO-252-5	4374.37/2.500		
BTS50055-1TMACT-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	TO-220-7	5.42	4.88	3.98
BTS50055-1TMATR-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	TO-220-7	2528.13/1.000		
BTS50055-1TMB-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	TO-220-7	5.05	4.52	3.71
BTS50080-1TEBCT-ND	Smart Leistungs-High-Side-Schalter PROFET®, 1-Kan.*	TO-252-5	3.14	2.83	2.31
BTS50080-1TEBTR-ND	Smart Leistungs-High-Side-Schalter PROFET®, 1-Kan.*	TO-252-5	3479.48/2.500		
BTS50080-1TMACT-ND	Smart Leistungs-High-Side-Schalter PROFET®, 1-Kan.*	TO-220-7	4.16	3.75	3.06
BTS50080-1TMATR-ND	Smart Leistungs-High-Side-Schalter PROFET®, 1-Kan.*	TO-220-7	1942.74/1.000		
BTS50080-1TMB-ND	Smart Leistungs-High-Side-Schalter PROFET®, 1-Kan.*	TO-220-7	3.88	3.47	2.85
BTS50085-1TMACT-ND	Smart Leistungs-High-Side-Schalter PROFET®, 1-Kan.*	TO-220-7	5.96	5.37	4.38
BTS50085-1TMATR-ND	Smart Leistungs-High-Side-Schalter PROFET®, 1-Kan.*	TO-220-7	2781.18/1.000		
BTS50085-1TMB-ND	Smart Leistungs-High-Side-Schalter PROFET®, 1-Kan.*	TO-220-7	5.57	4.97	4.08
IFX1177GSVINCT-ND	Mono-integrierter Festspannungsregler, Typ NPN*	SOT-223	1.03	.92	.73
IFX1177GSVINTR-ND	Mono-integrierter Festspannungsregler, Typ NPN*	SOT-223	1505.50/4.000		
ISP452CT-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	SOT-223-4	1.51	1.30	1.06
ISP452TR-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	SOT-223-4	2331.93/4000		
ISP742R1CT-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	DSO-8	1.42	1.28	1.01
ISP742R1TR-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	DSO-8	1309.31/2.500		
ISP752R1CT-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	DSO-8	1.55	1.33	1.09
ISP752R1TR-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	DSO-8	1487.49/2.500		
ISP752TCT-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	DSO-8	1.48	1.27	1.04
ISP752TTR-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	DSO-8	1427.43/2.500		
ISP762TCT-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	DSO-8	1.73	1.49	1.22
ISP762TTR-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	DSO-8	1669.67/2.500		
ISP772TCT-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	DSO-8	1.93	1.66	1.36
ISP772TTR-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	DSO-8	1863.86/2.500		
ITS410E2-ND	Smart Leistungs-High-Side-Schalter PROFET®, 1-Kan.*	TO-220-5	2.76	2.47	2.03
ITS428L2CT-ND	Smart Leistungs-High-Side-Schalter PROFET®, 1-Kan.*	TO-252-5	2.44	2.10	1.71
ITS428L2TR-ND	Smart Leistungs-High-Side-Schalter PROFET®, 1-Kan.*	TO-252-5	2352.35/2.500		
ITS436L2-ND	Smart Leistungs-High-Side-Schalter PROFET®, 1-Kan.*	TO-220-5	2.82	2.52	2.07
ITS436L2S-ND	Smart Leistungs-High-Side-Schalter PROFET®, 1-Kan.*	TO-220-5	2.92	2.52	2.07
ITS612N1-ND	Smart Leistungs-High-Side-Schalter PROFET®, 2-Kan.*	TO-220AB/7	2.36	2.11	1.73
ITS621L1-ND	Smart Leistungs-High-Side-Schalter PROFET®, 2-Kan.*	TO-220AB/7	3.15	2.82	2.31
ITS716GCT-ND	Smart Leistungs-High-Side-Schalter PROFET®, 4-Kan.*	DSO-20	3.26	2.94	2.39
ITS716GTR-ND	Smart Leistungs-High-Side-Schalter PROFET®, 4-Kan.*	DSO-20	1519.92/1.000		
ITS724GCT-ND	Smart Leistungs-High-Side-Schalter PROFET®, 4-Kan.*	DSO-20	3.59	3.23	2.63
ITS724GTR-ND	Smart Leistungs-High-Side-Schalter PROFET®, 4-Kan.*	DSO-20	1672.87/1.000		
ITS4140NCT-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	SOT-223-4	1.04	.94	.75
ITS4140NTR-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	SOT-223-4	1540.74/4.000		
ITS4141DCT-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	TO-252-5	1.62	1.39	1.14
ITS4141DTR-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	TO-252-5	1559.56/2.500		
ITS4141NCT-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	SOT-223-4	1.49	1.28	1.05
ITS4141NTR-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	SOT-223-4	2303.10/4.000		
ITS4142NCT-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	SOT-223-4	1.54	1.32	1.08
ITS4142NTR-ND	Smart Leistungs-High-Side-Schalter, 1-Kan.*	SOT-223-4	2370.37/4.000		
ITS488R1CT-ND	Smart Leistungs-High-Side-Schalter, 8-Kan.*	DSO-36	6.97	6.31	5.26
ITS488R1TR-ND	Smart Leistungs-High-Side-Schalter, 8-Kan.*	DSO-36	13671.26/4000		
ITS5215LCT-ND	Smart High-Side-Leistungsschalter, 2-Kan.*	DSO-12-9	2.59	2.23	1.82
ITS5215LTR-ND	Smart High-Side-Leistungsschalter, 2-Kan.*	DSO-12-9	1298.40/1.000		
TCA505BGEGINCT-ND	Schalter für Induktivitäts-Proxi*	16-DSO	3.80	3.43	2.79
TCA505BGEGINTR-ND	Schalter für Induktivitäts-Proxi*	16-DSO	4358.35/2.500		
TCA3727IN-ND	2-Phasen-Schrittmotortreiber*	20-DIP	6.14	5.53	4.55
TLE4207GINCT-ND	Zweif. Halbbrückentreiber, 1 A*	DSO-14	2.40	2.07	1.69
TLE4209A-ND	H-Brücken DC-Motortreiber*	8-DIP	1.91	1.73	1.39
TLE4226GCT-ND	Low-Side-Schalter, 6-Kan.*	DSO-24	2.95	2.66	2.17
TLE4226GTR-ND	Low-Side-Schalter, 6-Kan.*	DSO-24	1376.58/1.000		
TLE4250-2GCT-ND	LDO-Spannungsverfolgung*	SCT595-5	.99	.89	.71
TLE4250-2GTR-ND	LDO-Spannungsverfolgung*	SCT595-5	1093.09/3.000		
TLE4251DINCT-ND	LDO-Spannungsverfolgung*	Low Dropout Voltage Tracker*	2.56	1.98	1.80
TLE4251DINTR-ND	LDO-Spannungsverfolgung*	Low Dropout Voltage Tracker*	2474.47/2.500		
TLE4251GCT-ND	LDO-Spannungsverfolgung*	Low Dropout Voltage Tracker*	2.69	2.31	1.89
TLE4251GTR-ND	LDO-Spannungsverfolgung*	Low Dropout Voltage Tracker*	1137.94/1.000		
TLE4252DCT-ND	LDO-Spannungsverfolgungsregler*	Low Dropout Voltage Tracking Regulator*	2.44	2.10	1.72
TLE4252DTR-ND	LDO-Spannungsverfolgungsregler*	Low Dropout Voltage Tracking Regulator*	2538.36/2.500		
TLE4252GCT-ND	LDO-Spannungsverfolgungsregler*	Low Dropout Voltage Tracking Regulator*	2.63	2.25	1.84
TLE4252GTR-ND	LDO-Spannungsverfolgungsregler*	Low Dropout Voltage Tracking Regulator*	1087.49/1.000		
TLE4253GCT-ND	LDO-Spannungsverfolgungsregler*	Low Dropout Voltage Tracking Regulator*	1.52	1.31	1.07
TLE4253GSTR-ND	LDO-Spannungsverfolgungsregler*	Low Dropout Voltage Tracking Regulator*	DSO-8	1469.47/2.500	
TLE4254GACT-ND	LDO-Spannungsverfolgungsregler*	Low Dropout Voltage Tracking Regulator*	DSO-8	1.43	1.28
TLE4254GATR-ND	LDO-Spannungsverfolgungsregler*	Low Dropout Voltage Tracking Regulator*	DSO-8	1309.31/2.500	
TLE4254GACT-ND	LDO-Spannungsverfolgungsregler*	Low Dropout Voltage Tracking Regulator*	DSO-8	1.43	1.28
TLE4254GSTR-ND	LDO-Spannungsverfolgungsregler*	Low Dropout Voltage Tracking Regulator*	DSO-8	1309.31/2.500	
TLE4262GCT-ND	5 V Low-Drop-Spannungsregler*	5V Low Drop Voltage Regulator*	DSO-20	2.64	2.27
TLE4262GTR-ND	5 V Low-Drop-Spannungsregler*	5V Low Drop Voltage Regulator*	DSO-20	1095.49/1.000	
TLE4262GMCT-ND	5 V Low-Drop-Spannungsregler*	5V Low Drop Voltage Regulator*	DSO-14	2.35	2.01
TLE4262GTR-ND	5 V Low-Drop-Spannungsregler*	5V Low Drop Voltage Regulator*	DSO-14	2260.26/2.500	
TLE4263-2ESCT-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	DSO-8	2.19	1.88
TLE4263-2ESTR-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	DSO-8	2104.10/2.500	
TLE4263GCT-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	DSO-20	2.92	2.51
TLE4263GTR-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	DSO-20	1017.02/1.000	
TLE4263GMCT-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	DSO-14	2.29	1.97
TLE4263GTR-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	DSO-14	2210.21/2.500	
TLE4263GCT-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	DSO-8	2.07	1.78
TLE4263GSTR-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	DSO-8	2000.00/2.500	
TLE4264GCT-ND	5 V LDO-Festspannungsregler*	5V Low Dropout Fixed Voltage Regulator*	SOT-223-4	1.35	1.21
TLE4264GTR-ND	5 V LDO-Festspannungsregler*	5V Low Dropout Fixed Voltage Regulator*	SOT-223-4	534.13/1.000	
TLE4266-2GCT-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	SOT-223-4	1.53	1.31
TLE4266-2GTR-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	SOT-223-4	2354.35/4.000	
TLE4266-2GS V33CT-ND	3.3 V LDO-Spannungsregler*	3.3V Low Dropout Voltage Regulator*	SOT-223-4	1.53	1.31
TLE4266-2GS V33TR-ND	3.3 V LDO-Spannungsregler*	3.3V Low Dropout Voltage Regulator*	SOT-223-4	2354.35/4.000	
TLE4267GINCT-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	TO-263-7	2.54	2.29
TLE4267GINTR-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	TO-263-7	1183.58/1.000	
TLE4267GMCT-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	DSO-14	2.41	2.07
TLE4267GTR-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	DSO-14	2320.32/2.500	
TLE4267SIN-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	P-TO-220-7	2.39	1.92
TLE4268GCT-ND	5 V LDO-Festspannungsregler*	5V Low Dropout Fixed Voltage Regulator*	DSO-20	2.50	2.26
TLE4268GTR-ND	5 V LDO-Festspannungsregler*	5V Low Dropout Fixed Voltage Regulator*	DSO-20	1167.57/1.000	
TLE4268GCT-ND	5 V LDO-Festspannungsregler*	5V Low Dropout Fixed Voltage Regulator*	DSO-8	2.27	1.95
TLE4268GSTR-ND	5 V LDO-Festspannungsregler*	5V Low Dropout Fixed Voltage Regulator*	DSO-8	2184.18/2.500	
TLE4270-2-ND	5 V LDO-Festspannungsregler*	5V Low Dropout Fixed Voltage Regulator*	TO-220-5	2.41	2.15
TLE4270-2DCT-ND	5 V LDO-Festspannungsregler*	5V Low Dropout Fixed Voltage Regulator*	TO-252-5	2.58	2.33
TLE4270-2DTR-ND	5 V LDO-Festspannungsregler*	5V Low Dropout Fixed Voltage Regulator*	TO-252-5	2856.85/2.500	
TLE4270-2GCT-ND	5 V LDO-Festspannungsregler*	5V Low Dropout Fixed Voltage Regulator*	TO-263-5	2.69	2.43
TLE4270-2GTR-ND	5 V LDO-Festspannungsregler*	5V Low Dropout Fixed Voltage Regulator*	TO-263-5	1256.46/1.000	
TLE4270GINCT-ND	5 V Low-Drop-Festspannungsregler	5V Low-Drop Fixed Voltage Regulator	P-TO-263-5	2.75	2.48
TLE4270GINTR-ND	5 V Low-Drop-Festspannungsregler	5V Low-Drop Fixed Voltage Regulator	P-TO-263-5	1282.08/1.000	
TLE4271-2-ND	5 V LDO-Festspannungsregler*	5V Low Dropout Fixed Voltage Regulator*	TO-220-7	2.64	2.37
TLE4271-2S-ND	5 V LDO-Festspannungsregler*	5V Low Dropout Fixed Voltage Regulator*	TO-220-7	2.64	2.37
TLE4274D V33CT-ND	3.3 V LDO-Spannungsregler*	3.3V Low Dropout Voltage Regulator*	TO-252-3	1.53	1.32
TLE4274D V33TR-ND	3.3 V LDO-Spannungsregler*	3.3V Low Dropout Voltage Regulator*	TO-252-3	1445.44/2.500	
TLE4274D V50CT-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	TO-252-3	1.56	1.34
TLE4274D V50TR-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	TO-252-3	1505.50/2.500	
TLE4274G V10CT-ND	10 V LDO-Spannungsregler*	10V Low Dropout Voltage Regulator*	TO-263-3	1.83	1.57
TLE4274G V10TR-ND	10 V LDO-Spannungsregler*	10V Low Dropout Voltage Regulator*	TO-263-3	757.56/1.000	
TLE4274G V50CT-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	TO-263-3	1.79	1.54
TLE4274G V50TR-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	TO-263-3	742.34/1.000	
TLE4274GS V25CT-ND	2.5 V LDO-Spannungsregler*	2.5V Low Dropout Voltage Regulator*	SOT-223-4	1.42	1.22
TLE4274GS V25TR-ND	2.5 V LDO-Spannungsregler*	2.5V Low Dropout Voltage Regulator*	SOT-223-4	586.19/1.000	
TLE4274GS V33CT-ND	3.3 V LDO-Spannungsregler*	3.3V Low Dropout Voltage Regulator*	SOT-223-4	1.42	1.22
TLE4274GS V33TR-ND	3.3 V LDO-Spannungsregler*	3.3V Low Dropout Voltage Regulator*	SOT-223-4	586.19/1.000	
TLE4274V50IN-ND	Low-Drop-Spannungsregler	Low-Drop Voltage Regulator	P-TO-220-3-1	1.59	1.28
TLE4276DVCT-ND	Einstellbarer Low-Dropout-Spannungsregler*	Adjustable Low Dropout Voltage Regulator*	TO-252-5	2.16	1.86
TLE4276DVTR-ND	Einstellbarer Low-Dropout-Spannungsregler*	Adjustable Low Dropout Voltage Regulator*	TO-252-5	2088.09/2.500	
TLE4276SVCT-ND	Einstellbarer Low-Dropout-Spannungsregler*	Adjustable Low Dropout Voltage Regulator*	TO-220-5	2.35	2.02
TLE4276SVTR-ND	Einstellbarer Low-Dropout-Spannungsregler*	Adjustable Low Dropout Voltage Regulator*	TO-220-5	973.77/1.000	
TLE4276S V50CT-ND	5 V LDO-Spannungsregler*	5V Low Dropout Voltage Regulator*	TO-220-5	2.40	2.06

* RoHS-konform

★ NIEDRIGERE PREISE FÜR HÖHERE QUANTITÄTEN AUF ANFRAGE! ★

(Forts.)

Kostenloser Versand für Bestellungen über 65 €!

Alle Preise verstehen sich in Euro und enthalten Zollgebühren.