

TEXAS INSTRUMENTS Digi-Key (Forts.)			DIGITALLOGIK RoHS-konforme Teile sind erhältlich			
TI Teile-Nr.	Digi-Key Teile-Nr.	Beschreibung	Gehäuse	Stückpreis ★		
				1	25	100
SN74LVTH241DBR	296-12742-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-SSOP	.85	.66	.59
SN74LVTH241DBR	296-12742-2-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-SSOP	562.16/2,000		
SN74LVTH241DWR	296-1715-5-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-SOIC	.74	.60	.52
SN74LVTH241PWREP	296-22388-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	1.51	1.17	1.06
SN74LVTH241PWREP	296-22388-2-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	1167.57/2,000		
SN74LVTH241PWR	296-8709-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	.78	.60	.53
SN74LVTH244ADBR	296-1269-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-SSOP	510.91/2,000		
SN74LVTH244ADBR	296-1269-2-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-SSOP	.70	.55	.49
SN74LVTH244ADWR	296-1270-5-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-SOIC	.74	.60	.52
SN74LVTH244ADWR	296-1270-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-SOIC	.78	.60	.53
SN74LVTH244AGQNR	296-12107-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-SOIC	510.91/2,000		
SN74LVTH244AGQNR	296-12107-2-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-BGA	1.00	.80	.72
SN74LVTH244APWR	296-1271-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	396.40/1,000		
SN74LVTH244APWR	296-1271-2-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	.78	.60	.53
SN74LVTH244AODBR	296-22389-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	510.91/2,000		
SN74LVTH244AODBR	296-22389-2-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	1.68	1.30	1.18
SN74LVTH244AOPWR	296-18128-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	1.68	1.30	1.18
SN74LVTH244AOPWR	296-18128-2-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	1297.30/2,000		
SN74LVTH244ARGYR	296-13986-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-DFN	.85	.66	.59
SN74LVTH244ARGYR	296-13986-2-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-DFN	843.24/3,000		
SN74LVTH245ADBR	296-8710-1-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-SSOP	.85	.66	.59
SN74LVTH245ADBR	296-8710-2-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-SSOP	562.16/2,000		
SN74LVTH245ADWR	296-8711-5-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-SOIC	.74	.60	.52
SN74LVTH245ADWR	296-8711-1-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-SOIC	.78	.60	.53
SN74LVTH245AGQNR	296-8711-2-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-SOIC	510.91/2,000		
SN74LVTH245AGQNR	296-12108-1-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-BGA	1.00	.80	.72
SN74LVTH245AGQNR	296-12108-2-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-BGA	396.40/1,000		
SN74LVTH245AIPWR	296-22390-1-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-TSSOP	1.37	1.09	.98
SN74LVTH245AIPWR	296-22390-2-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-TSSOP	1009.01/2,000		
SN74LVTH245AODBR	296-22391-1-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-TSSOP	2.69	2.20	1.98
SN74LVTH245AODBR	296-22391-2-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-TSSOP	2385.74/2,000		
SN74LVTH245APWR	296-1272-1-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-TSSOP	.78	.60	.53
SN74LVTH245APWR	296-1272-2-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-TSSOP	510.91/2,000		
SN74LVTH273DWR	296-8713-5-ND	Achft. ABT-D-Flip-Flop m. Löschen*	20-SOIC	.74	.60	.52
SN74LVTH273DWR	296-14934-1-ND	Achft. ABT-D-Flip-Flop m. Löschen	20-SOIC	.78	.60	.53
SN74LVTH273DWR	296-14934-2-ND	Achft. ABT-D-Flip-Flop m. Löschen	20-SOIC	510.91/2,000		
SN74LVTH273IPWR	296-22392-1-ND	Achft. ABT-D-Flip-Flop m. Löschen	20-TSSOP	1.37	1.09	.98
SN74LVTH273IPWR	296-22392-2-ND	Achft. ABT-D-Flip-Flop m. Löschen	20-TSSOP	1009.01/2,000		
SN74LVTH273MNSREP	296-22393-1-ND	Achft. ABT-D-Flip-Flop m. Löschen	20-SOP	2.69	2.20	1.98
SN74LVTH273MNSREP	296-22393-2-ND	Achft. ABT-D-Flip-Flop m. Löschen	20-SOP	2385.74/2,000		
SN74LVTH273PWR	296-1273-1-ND	Achft. ABT-D-Flip-Flop m. Löschen	20-TSSOP	.78	.60	.53
SN74LVTH273PWR	296-1273-2-ND	Achft. ABT-D-Flip-Flop m. Löschen	20-TSSOP	510.91/2,000		
SN74LVTH373DBR	296-8718-1-ND	Achft. Tri-State-ABT-D-Latch	20-SSOP	.70	.55	.49
SN74LVTH373DBR	296-8718-2-ND	Achft. Tri-State-ABT-D-Latch	20-SSOP	464.46/2,000		
SN74LVTH373DWR	296-8719-5-ND	Achft. Tri-State-ABT-D-Latch	20-SOIC	.77	.60	.52
SN74LVTH373IPWR	296-22394-1-ND	Achft. Tri-State-ABT-D-Latch	20-TSSOP	1.37	1.09	.98
SN74LVTH373IPWR	296-22394-2-ND	Achft. Tri-State-ABT-D-Latch	20-TSSOP	1009.01/2,000		
SN74LVTH373IPWR	296-26644-5-ND	Achft. Tri-State-ABT-D-Latch*	20-TSSOP	.77	.60	.52
SN74LVTH373PWR	296-8720-1-ND	Achft. Tri-State-ABT-D-Latch	20-TSSOP	.70	.55	.49
SN74LVTH373PWR	296-8720-2-ND	Achft. Tri-State-ABT-D-Latch	20-TSSOP	464.46/2,000		
SN74LVTH374DBR	296-8721-1-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-SSOP	.85	.66	.59
SN74LVTH374DBR	296-8721-2-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-SSOP	562.16/2,000		
SN74LVTH374DWR	296-8722-5-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-SOIC	.74	.60	.52
SN74LVTH374DWR	296-8722-1-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-SOIC	.78	.60	.53
SN74LVTH374DWR	296-8722-2-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-SOIC	510.91/2,000		
SN74LVTH374IPWR	296-22395-1-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-TSSOP	1.37	1.09	.98
SN74LVTH374IPWR	296-22395-2-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-TSSOP	1009.01/2,000		
SN74LVTH374PWR	296-8723-1-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-TSSOP	.78	.60	.53
SN74LVTH540DBR	296-8724-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	1.67	1.31	1.18
SN74LVTH540DBR	296-8724-2-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	1222.47/2,000		
SN74LVTH540DWR	296-8725-5-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-SOIC	1.53	1.23	1.07
SN74LVTH540PWR	296-8726-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	1.67	1.31	1.18
SN74LVTH540PWR	296-8726-2-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	1222.47/2,000		
SN74LVTH541DBR	296-8727-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-SSOP	1.95	1.51	1.37
SN74LVTH541DBR	296-8727-2-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-SSOP	1504.86/2,000		
SN74LVTH541DWR	296-8728-5-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-SOIC	1.87	1.51	1.36
SN74LVTH541PWR	296-8729-1-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	1.79	1.38	1.26
SN74LVTH541PWR	296-8729-2-ND	Achft. Tri-State-ABT-Puffer/Treiber	20-TSSOP	1380.39/2,000		
SN74LVTH543DGVR	296-8731-1-ND	Achft. Tri-State-ABT-Busempfänger/Register	24-TVSOIP	1.67	1.29	1.17
SN74LVTH543DWR	296-1717-5-ND	Achft. Tri-State-ABT-Busempfänger/Register	24-SOIC	1.00	.80	.60
SN74LVTH543IPWR	296-22396-1-ND	Achft. Tri-State-ABT-Busempfänger/Register	24-TSSOP	2.43	1.99	1.78
SN74LVTH543IPWR	296-22396-2-ND	Achft. Tri-State-ABT-Busempfänger/Register	24-TSSOP	2151.43/2,000		
SN74LVTH543PWR	296-8732-1-ND	Achft. Tri-State-ABT-Busempfänger/Register	20-TSSOP	1.67	1.29	1.17
SN74LVTH543PWR	296-8732-2-ND	Achft. Tri-State-ABT-Busempfänger/Register	24-TSSOP	1286.49/2,000		
SN74LVTH573DWR	296-1718-5-ND	Achft. transparentes Tri-State-ABT-D-Latch	20-SOIC	.82	.66	.57
SN74LVTH573DWR	296-14935-1-ND	Achft. transparentes Tri-State-ABT-D-Latch	20-SOIC	.85	.66	.59
SN74LVTH573DWR	296-14935-2-ND	Achft. transparentes Tri-State-ABT-D-Latch	20-SOIC	562.16/2,000		
SN74LVTH573IPWR	296-22397-1-ND	Achft. transparentes Tri-State-ABT-D-Latch	20-TSSOP	1.37	1.09	.98
SN74LVTH573IPWR	296-22397-2-ND	Achft. transparentes Tri-State-ABT-D-Latch	20-TSSOP	1009.01/2,000		
SN74LVTH573NSR	296-13300-1-ND	Achft. transparentes Tri-State-ABT-D-Latch	20-SOP	.81	.64	.58
SN74LVTH573NSR	296-13300-2-ND	Achft. transparentes Tri-State-ABT-D-Latch	20-SOP	595.80/2,000		
SN74LVTH573PWR	296-26645-5-ND	Achft. transparentes Tri-State-ABT-D-Latch*	20-TSSOP	.82	.66	.57
SN74LVTH573PWR	296-8734-1-ND	Achft. transparentes Tri-State-ABT-D-Latch	20-TSSOP	.85	.66	.59
SN74LVTH573PWR	296-8734-2-ND	Achft. transparentes Tri-State-ABT-D-Latch	20-TSSOP	562.16/2,000		
SN74LVTH573RGYR	296-13988-1-ND	Achft. transparentes Tri-State-ABT-D-Latch	20-VQFN	.81	.64	.58
SN74LVTH573RGYR	296-13988-2-ND	Achft. transparentes Tri-State-ABT-D-Latch	20-VQFN	893.69/3,000		
SN74LVTH574DBR	296-8735-1-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-SSOP	.85	.66	.59
SN74LVTH574DBR	296-8735-2-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-SSOP	562.16/2,000		
SN74LVTH574DWR	296-1719-5-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-SOIC	.74	.60	.52
SN74LVTH574DWR	296-1719-1-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-SOIC	.78	.60	.53
SN74LVTH574DWR	296-1719-2-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-SOIC	510.91/2,000		
SN74LVTH574IPWR	296-22398-1-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-TSSOP	1.37	1.09	.98
SN74LVTH574IPWR	296-22398-2-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-TSSOP	1009.01/2,000		
SN74LVTH574PWR	296-8736-1-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-TSSOP	.78	.60	.53
SN74LVTH574PWR	296-8736-2-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-TSSOP	510.91/2,000		
SN74LVTH574RGYR	296-13989-1-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-VQFN	.85	.66	.59
SN74LVTH574RGYR	296-13989-2-ND	Achft. Tri-State-ABT-D-Flip-Flop	20-VQFN	843.24/3,000		
SN74LVTH646DBR	296-8737-1-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-SSOP	2.34	1.85	1.67
SN74LVTH646DBR	296-8737-2-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-SSOP	1722.99/2,000		
SN74LVTH646DWR	296-1720-5-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-SOIC	2.35	1.88	1.65
SN74LVTH646IPWR	296-22399-1-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-TSSOP	2.22	1.71	1.55
SN74LVTH646IPWR	296-22399-2-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-TSSOP	1708.11/2,000		
SN74LVTH646PWR	296-8738-1-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-TSSOP	2.12	1.68	1.51
SN74LVTH646PWR	296-8738-2-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-TSSOP	1565.31/2,000		
SN74LVTH652DBR	296-8739-1-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-SSOP	2.39	1.84	1.67
SN74LVTH652DBR	296-8739-2-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-SSOP	1838.64/2,000		
SN74LVTH652DGVR	296-12925-1-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-TVSOIP	2.11	1.63	1.48
SN74LVTH652DGVR	296-12925-2-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-TVSOIP	1621.62/2,000		
SN74LVTH652DWR	296-1721-5-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-SOIC	2.23	1.81	1.63
SN74LVTH652PWR	296-8740-1-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-TSSOP	2.11	1.63	1.48
SN74LVTH652PWR	296-8740-2-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-TSSOP	1622.42/2,000		
SN74LVTH2245DBR	296-8704-1-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-SSOP	.85	.66	.59
SN74LVTH2245DBR	296-8704-2-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-SSOP	562.16/2,000		
SN74LVTH2245DGVR	296-12921-1-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-TVSOIP	.78	.60	.53
SN74LVTH2245DWR	296-1714-5-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-SOIC	.74	.60	.52
SN74LVTH2245PWR	296-8705-1-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-TSSOP	.78	.60	.53
SN74LVTH2245PWR	296-8705-2-ND	Achft. Tri-State-ABT-Bus-Transceiver	20-TSSOP	510.91/2,000		
SN74LVTH2952DWR	296-1716-5-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-SOIC	1.06	.88	.71
SN74LVTH2952PWR	296-8715-1-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-TSSOP	1.98	1.57	1.41
SN74LVTH2952PWR	296-8715-2-ND	Achft. Tri-State-ABT-Bus-Transceiver/Register	24-TSSOP	1460.15/2,000		
SN74LVTH16240DGG	296-8674-1-ND	16-Bit-Tri-State-ABT-Puffer/Treiber	48-TSSOP	1.22	.97	.87
SN74LVTH16240DL	296-8675-5-ND	16-Bit-Tri-State-ABT-Puffer/Treiber	48-SSOP	1.37	1.11	1.00
SN74LVTH16241DGG	296-8676-1-ND	16-Bit-Tri-State-AB				