

Panasonic Serie ECQ-E(F) Mini-Metall-Polyester-Schichtkondensatoren (Forts.)

Betriebsspannung (V DC)	Kapazität (µF)	Abmessungen (mm)						Digi-Key Teile-Nr.	Preisangaben					Panasonic Teile-Nr.
		L	T	H	F	G	ød		1	50	100	500	1.000	
250	.15	10.3	6.0	10.8	7.5	1.0	0.6	EF2154-ND	.34	8.09	13.86	51.98	87.79	ECOQ-E2154KF
	.18	12.0	5.0	10.3	10.0	1.0	0.6	EF2184-ND	.34	8.94	15.57	57.66	98.02	ECOQ-E2184KF
	.22	12.0	5.5	10.5	10.0	1.0	0.6	EF2224-ND	.34	9.28	16.18	59.90	101.83	ECOQ-E2224KF
	.27	12.0	6.0	11.5	10.0	1.0	0.6	EF2274-ND	.38	10.09	17.58	65.11	110.68	ECOQ-E2274KF
	.33	12.0	6.5	12.0	10.0	1.0	0.6	EF2334-ND	.39	10.45	18.20	67.43	114.63	ECOQ-E2334KF
	.39	18.5	4.9	12.0	15.0	1.0	0.6	EF2394-ND	.50	13.34	23.25	86.09	146.35	ECOQ-E2394KF
	.47	18.5	5.3	12.5	15.0	1.0	0.6	EF2474-ND	.48	12.82	22.33	82.72	140.63	ECOQ-E2474KF
	.56	18.5	5.5	13.0	15.0	1.0	0.6	EF2564-ND	.51	13.69	23.85	88.33	150.16	ECOQ-E2564KF
	.68	18.5	6.0	13.5	15.0	1.0	0.8	EF2684-ND	.52	13.93	24.26	89.85	152.74	ECOQ-E2684KF
	.82	18.5	6.5	14.5	15.0	1.0	0.8	EF2824-ND	.54	14.51	25.27	93.61	159.14	ECOQ-E2824KF
	1.0	18.5	7.4	15.0	15.0	1.0	0.8	EF2105-ND	.54	14.47	25.21	93.37	158.73	ECOQ-E2105KF
	1.2	18.5	8.0	15.9	15.0	1.0	0.8	EF2125-ND	.57	16.77	28.75	113.81	191.68	ECOQ-E2125KF
	1.5	18.5	9.0	16.8	15.0	1.0	0.8	EF2155-ND	.62	18.17	31.15	123.32	207.70	ECOQ-E2155KF
	1.8	26.0	7.5	15.5	22.5	1.0	0.8	EF2185-ND	.74	23.26	40.05	155.03	266.99	ECOQ-E2185KF
	2.2	26.0	8.5	16.3	22.5	1.0	0.8	EF2225-ND	.68	21.48	37.00	143.21	246.64	ECOQ-E2225KF
	2.7	26.0	9.4	17.0	22.5	1.0	0.8	EF2275-ND	.80	27.45	47.51	179.50	316.76	ECOQ-E2275KF
	3.3	26.0	10.3	18.0	22.5	1.5	0.8	EF2335-ND	.78	26.82	46.41	175.34	309.43	ECOQ-E2335KF
	3.9	26.0	11.0	20.5	22.5	1.5	0.8	EF2395-ND	.89	30.37	52.56	198.56	350.39	ECOQ-E2395KF
	4.7	26.0	12.0	21.5	22.5	1.5	0.8	EF2475-ND	.94	32.37	56.02	211.63	374.45	ECOQ-E2475KF
	5.6	31.0	11.8	21.0	27.5	1.5	0.8	EF2565-ND	1.52	53.82	94.19	358.82	627.94	ECOQ-E2565KF
6.8	31.0	13.0	22.4	27.5	1.5	0.8	EF2685-ND	1.63	57.23	100.16	381.57	667.74	ECOQ-E2685KF	
8.2	31.0	14.3	23.5	27.5	1.5	0.8	EF2825-ND	1.75	61.82	108.18	412.12	721.22	ECOQ-E2825KF	
10.0	31.0	15.9	25.8	27.5	1.5	0.8	EF2106-ND	2.75	95.39	173.04	643.34	1197.95	ECOQ-E2106KF	
400	.01	10.3	4.3	7.4	7.5	1.0	0.6	EF4103-ND	.29	6.93	11.87	44.51	75.16	ECOQ-E4103KF
	.012	10.3	4.4	7.5	7.5	1.0	0.6	EF4123-ND	.29	6.93	11.87	44.51	75.16	ECOQ-E4123KF
	.015	10.3	4.4	7.5	7.5	1.0	0.6	EF4153-ND	.29	6.93	11.87	44.51	75.16	ECOQ-E4153KF
	.018	10.3	4.4	7.5	7.5	1.0	0.6	EF4183-ND	.29	6.93	11.87	44.51	75.16	ECOQ-E4183KF
	.022	10.3	4.8	7.9	7.5	1.0	0.6	EF4223-ND	.29	6.93	11.87	44.51	75.16	ECOQ-E4223KF
	.027	10.3	5.5	8.0	7.5	1.0	0.6	EF4273-ND	.29	6.93	11.87	44.51	75.16	ECOQ-E4273KF
	.033	10.3	6.0	9.0	7.5	1.0	0.6	EF4333-ND	.29	6.93	11.87	44.51	75.16	ECOQ-E4333KF
	.039	12.0	4.9	8.0	10.0	1.0	0.6	EF4393-ND	.29	6.93	11.87	44.51	75.16	ECOQ-E4393KF
	.047	12.0	5.0	8.3	10.0	1.0	0.6	EF4473-ND	.29	6.93	11.87	44.51	75.16	ECOQ-E4473KF
	.056	12.0	5.0	10.0	10.0	1.0	0.6	EF4563-ND	.42	11.24	19.59	72.55	123.34	ECOQ-E4563KF
	.068	12.0	5.4	10.5	10.0	1.0	0.6	EF4683-ND	.47	12.72	22.17	82.08	139.54	ECOQ-E4683KF
	.082	12.0	5.8	11.0	10.0	1.0	0.6	EF4823-ND	.44	11.71	20.39	75.52	128.38	ECOQ-E4823KF
	.1	12.0	6.3	12.0	10.0	1.0	0.6	EF4104-ND	.30	7.19	12.32	46.21	78.05	ECOQ-E4104KF
	.12	18.5	5.0	10.0	15.0	1.0	0.6	EF4124-ND	.52	13.86	24.15	89.45	152.06	ECOQ-E4124KF
	.15	18.5	5.0	12.4	15.0	1.0	0.6	EF4154-ND	.51	13.77	23.98	88.81	150.97	ECOQ-E4154KF
	.18	18.5	5.4	12.5	15.0	1.0	0.6	EF4184-ND	.57	15.23	26.53	98.26	167.04	ECOQ-E4184KF
	.22	18.5	5.9	13.0	15.0	1.0	0.6	EF4224-ND	.53	15.47	26.52	104.98	176.82	ECOQ-E4224KF
	.27	18.5	6.5	14.3	15.0	1.0	0.8	EF4274-ND	.55	16.21	27.79	110.01	185.27	ECOQ-E4274KF
	.33	18.5	7.0	14.9	15.0	1.0	0.8	EF4334-ND	.57	16.82	28.83	114.11	192.19	ECOQ-E4334KF
	.39	18.5	7.5	15.4	15.0	1.0	0.8	EF4394-ND	.64	18.98	32.54	128.80	216.92	ECOQ-E4394KF
.47	18.5	7.8	17.0	15.0	1.0	0.8	EF4474-ND	.63	19.98	34.41	133.19	229.38	ECOQ-E4474KF	
.56	26.0	6.5	16.0	22.5	1.0	0.8	EF4564-ND	.72	22.76	39.19	151.71	261.29	ECOQ-E4564KF	
.68	26.0	7.0	16.5	22.5	1.0	0.8	EF4684-ND	.62	18.27	31.33	124.00	208.85	ECOQ-E4684KF	
.82	26.0	7.9	17.3	22.5	1.0	0.8	EF4824-ND	.83	26.23	45.17	174.85	301.12	ECOQ-E4824KF	
1.0	26.0	8.5	18.9	22.5	1.0	0.8	EF4105-ND	.76	26.03	45.05	170.17	300.30	ECOQ-E4105KF	
1.2	26.0	9.5	18.9	22.5	1.0	0.8	EF4125-ND	1.15	39.07	67.62	255.46	450.81	ECOQ-E4125KF	
1.5	31.0	9.5	19.0	27.5	1.0	0.8	EF4155-ND	1.28	43.93	76.04	287.25	506.91	ECOQ-E4155KF	
1.8	31.0	11.0	20.5	27.5	1.5	0.8	EF4185-ND	.87	29.73	51.46	194.40	343.06	ECOQ-E4185KF	
2.2	31.0	11.0	22.0	27.5	1.5	0.8	EF4225-ND	1.39	48.82	85.43	325.45	569.53	ECOQ-E4225KF	
630	.01	12.0	4.5	7.5	10.0	1.0	0.6	EF6103-ND	.33	7.92	13.57	50.90	85.97	ECOQ-E6103KF
	.012	12.0	4.5	7.8	10.0	1.0	0.6	EF6123-ND	.33	8.74	15.22	56.38	95.84	ECOQ-E6123KF
	.015	12.0	5.0	8.2	10.0	1.0	0.6	EF6153-ND	.34	9.23	16.06	59.50	101.15	ECOQ-E6153KF
	.018	12.0	4.9	10.0	10.0	1.0	0.6	EF6183-ND	.37	9.93	17.30	64.06	108.91	ECOQ-E6183KF
	.022	12.0	5.3	10.5	10.0	1.0	0.6	EF6223-ND	.36	9.61	16.74	61.98	105.37	ECOQ-E6223KF
	.027	12.0	5.5	10.9	10.0	1.0	0.6	EF6273-ND	.38	10.25	17.86	66.15	112.45	ECOQ-E6273KF
	.033	12.0	6.0	11.9	10.0	1.0	0.6	EF6333-ND	.38	10.25	17.86	66.15	112.45	ECOQ-E6333KF
	.039	12.0	6.0	13.4	10.0	1.0	0.6	EF6393-ND	.39	10.47	18.23	67.51	114.76	ECOQ-E6393KF
	.047	12.0	6.5	13.5	10.0	1.0	0.6	EF6473-ND	.37	9.91	17.27	63.98	108.77	ECOQ-E6473KF
	.056	18.5	5.4	10.5	15.0	1.0	0.6	EF6563-ND	.43	11.65	20.30	75.20	127.83	ECOQ-E6563KF
	.068	18.5	5.8	11.0	15.0	1.0	0.6	EF6683-ND	.46	12.18	21.21	78.56	133.55	ECOQ-E6683KF
	.082	18.5	6.5	12.0	15.0	1.0	0.6	EF6823-ND	.46	12.41	21.62	80.08	136.14	ECOQ-E6823KF
	.1	18.5	6.3	14.0	15.0	1.0	0.6	EF6104-ND	.50	13.38	23.31	86.33	146.75	ECOQ-E6104KF
	.12	18.5	6.3	14.5	15.0	1.0	0.8	EF6124-ND	.52	13.93	24.26	89.85	152.74	ECOQ-E6124KF
	.15	18.5	7.5	15.4	15.0	1.0	0.8	EF6154-ND	.53	14.10	24.56	90.97	154.65	ECOQ-E6154KF
	.18	18.5	8.0	16.0	15.0	1.0	0.8	EF6184-ND	.62	18.23	31.25	123.70	208.34	ECOQ-E6184KF
	.22	18.5	9.0	16.5	15.0	1.0	0.8	EF6224-ND	.63	18.75	32.15	127.28	214.36	ECOQ-E6224KF
	.27	26.0	7.0	16.5	22.5	1.0	0.8	EF6274-ND	.68	19.99	34.27	135.65	228.45	ECOQ-E6274KF
	.33	26.0	7.8	17.0	22.5	1.0	0.8	EF6334-ND	.67	19.80	33.94	134.35	226.27	ECOQ-E6334KF
	.39	26.0	8.5	17.9	22.5	1.0	0.8	EF6394-ND	.78	24.62	42.41	164.18	282.75	ECOQ-E6394KF
.47	26.0	9.3	18.5	22.5	1.0	0.8	EF6474-ND	.83	26.35	45.39	175.71	302.61	ECOQ-E6474KF	
.56	26.0	10.0	20.0	22.5	1.5	0.8	EF6564-ND	.82	28.07	48.58	183.51	323.84	ECOQ-E6564KF	
.68	26.0	11.5	21.0	22.5	1.5	0.8	EF6684-ND	.84	28.80	49.86	188.35	332.37	ECOQ-E6684KF	
.82	31.0	11.3	20.5	27.5	1.5	0.8	EF6824-ND	1.27	43.18	74.74	282.35	498.26	ECOQ-E6824KF	
1.0	31.0	12.5	21.9	27.5	1.5	0.8	EF6105-ND	1.26	42.89	74.23	280.44	494.89	ECOQ-E6105KF	
1.2	31.0	13.5	23.0	27.5	1.5	0.8	EF6125-ND	1.34	45.71	79.12	298.89	527.45	ECOQ-E6125KF	
1.5	31.0	15.3	24.7	27.5										