

STATIC PROTECTION

Protection of static sensitive parts is a MUST in today's semiconductor market. To ensure the quality that Digi-Key customers have come to expect, the Digi-Key static control program includes proper static safety protection in the following areas:

- **Receiving, Incoming Inspection, and QC**
- **Order Picking**
- **Final Inspection**
- **Packaging and Shipping**

Shielded metallized bags are used in order picking, and 100% recyclable paper packaging is used in packaging and shipping.

As our program is continuously updated with the latest static control technology, you can be reassured that Digi-Key's static sensitive parts are quality safe, *all the way to your door step!*

• Please Note: SO-x packages are the same as x-SOIC packages •

Digi-Reel® Most SMT outdow parts are available on a Digi-Reel®. For Digi-Reel part number, change 1-ND to 6-ND or CT-ND to DKR-ND. See Digi-Key® Services on page 2 for additional information.

ANALOG DEVICES Digi-Reel®		AMPLIFIERS			
Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25	100
Audio/Video					
AD813ARZ-14-ND	Triple Video Amp Single Low Power*	14-SOIC	7.73	6.19	5.22
AD828ARZ-ND	Op Amp Video Dual Low Power*	8-Dip	4.63	3.71	2.88
AD830ANZ-ND	Video Differential Amp High Speed*	8-SOIC	4.63	3.71	2.88
AD830ARZ-ND	Video Differential Amp High Speed*	8-SOIC	5.02	4.02	3.40
AD830JAZ-R7CT-ND	Video Differential Amp High Speed*	8-SOIC	5.02	4.02	3.40
AD830JAZ-R7TR-ND	Video Differential Amp High Speed*	8-SOIC	2392.06/750		
AD8013ARZ-14-ND	Triple Video Amp*	14-SOIC	8.06	6.45	5.45
AD8023ARZ-ND	Triple Video Amp, High Current Output*	14-SOIC	7.15	6.45	5.72
AD8073JAZ-ND	Triple Video Amp*	14-SOIC	4.13	3.31	2.57
AD8074ARUZ-ND	High Speed Triple Video Buffer*	16-TSSOP	4.20	3.37	2.62
AD8074Z-EVAL-ND	Evaluation Board for AD8074*		70.54	—	—
AD8075ARUZ-ND	Triple Video Buffer High Speed*	16-TSSOP	4.20	3.37	2.62
AD8075Z-EVAL-ND	Evaluation Board for AD8075*		70.54	—	—
AD8079ARZ-ND	Dual 260MHz Buffer*	8-SOIC	7.25	5.81	4.90
AD8079BZ-ND	Dual 260MHz Buffer*	8-SOIC	7.25	5.81	4.90
OP275SPZ-ND	Op Amp Bipolar/JFET Audio*	8-Dip	2.01	1.61	1.21
OP275GSZ-ND	Op Amp Bipolar/JFET Audio*	8-SOIC	1.90	1.52	1.14
SSM2211CP-REEL7CT-ND	Audio Amp Low Distortion 1W	8-LFCSP	84	71	57
SSM2211SZ-ND	Audio Amp Low Distortion 1W*	8-SOIC	1.04	87	70
SSM2301CPZ-REEL7CT-ND	Audio Amp Class-D 1.52W*	8-LFCSP	1.69	1.41	1.13
SSM2301CPZ-REEL7TR-ND	Audio Amp Class-D 1.52W*	8-LFCSP	1120.69/1,500		
SSM2301RMZ-REEL7CT-ND	Audio Amp Class-D Mono, 1.52W*	8-MSOP	1.12	.93	.75
SSM2301RMZ-REEL7TR-ND	Audio Amp Class-D Mono, 1.52W*	8-MSOP	494.42/1,000		
SSM2301-MINI-EVALZ-ND	Evaluation Board for SSM2301-Mini*		44.84	—	—
SSM2302CPZ-REEL7CT-ND	Audio Amp Class-D Stereo*	16-LFCSP	1.90	1.52	1.14
SSM2302Z-EVAL-ND	Evaluation Board for SSM2302*		44.84	—	—
SSM2305CPZ-REEL7CT-ND	Audio Amp Class-D Mono, 2.8W*	8-LFCSP	1.51	1.21	.91
SSM2305RMZ-REEL7CT-ND	Audio Amp Class-D Mono, 2.8W*	8-MSOP	1.24	1.00	.75
SSM2305RMZ-REEL7TR-ND	Audio Amp Class-D Mono, 2.8W*	8-MSOP	644.36/1,000		
SSM2305-EVALZ-ND	Evaluation Board for SSM2305*		44.84	—	—
SSM2306CPZ-REEL7CT-ND	Audio Amp Class-D Stereo, 2W*	16-LFCSP	1.65	1.64	1.23
SSM2311CBZ-REEL7CT-ND	Audio Amp Class-D Mono, 3.3W*	9-WLSCP	1.51	1.21	.91
SSM2311-EVALZ-ND	Evaluation Board for SSM2311*		44.84	—	—
SSM2315-EVALZ-ND	Evaluation Board for SSM2315*		44.84	—	—
SSM2315CBZ-REEL7CT-ND	Audio Amp Class-D Mono, 3W*	9-WLSCP	1.69	1.36	1.02
SSM2315CBZ-REEL7TR-ND	Audio Amp Class-D Mono, 3W*	9-WLSCP	2601.22/3,000		
SSM2317-EVALZ-ND	Evaluation Board for SSM2317*		44.84	—	—
SSM2317-MINI-EVALZ-ND	Evaluation Board for SSM2317-Mini*		44.84	—	—
SSM2317CBZ-REEL7CT-ND	Audio Amp Class-D Mono, 3W*	9-WLSCP	1.88	1.51	1.13
Comparator					
AD790AQ-ND	Precision Comparator High Speed	8-Dip	10.46	9.42	8.36
AD790JNZ-ND	Precision Comparator High Speed*	8-Dip	6.13	4.91	4.14
AD8210WVYZ-ND	Precision Comparator High Speed*	8-SOIC	6.13	4.91	4.14
AD8210VYZ-ND	High Voltage, Bidirectional Current Shunt Monitor*	8-SOIC	3.70	2.96	2.31
AD8210VYZ-ND	High Voltage, Bidirectional Current Shunt Monitor*	8-SOIC	3.38	2.70	2.10
AD8211VYZ-RL7CT-ND	High Voltage Current Shunt Monitor*	SOT-23-5	1.45	1.16	.87
AD8211VYZ-RL7TR-ND	High Voltage Current Shunt Monitor*	SOT-23-5	2220.56/3,000		
AD8212YRZ-RL7CT-ND	High Voltage Current Shunt Monitor*	8-MSOP	1.92	1.54	1.16
AD8212YRZ-R7TR-ND	High Voltage Current Shunt Monitor*	8-MSOP	998.75/1,000		
AD8213YRZ-RL7CT-ND	Dual High Voltage Current Shunt Monitor*	10-MSOP	3.36	2.70	2.10
AD8213YRZ-R7TR-ND	Dual High Voltage Current Shunt Monitor*	10-MSOP	1906.43/1,000		
AD8215YRZ-ND	High Voltage, Current Shunt Monitor*	8-SOIC	2.25	1.80	1.40
AD8465WBPCZ-WP-ND	Comparator R-R, Fast 2.5V-5.5V, LVDS*	12-LFCSP	4.92	3.94	3.33
AD8561ANZ-ND	Comparator Single 7nS*	8-Dip	3.31	2.65	2.06
AD8561ARUZ-ND	Comparator Single 7nS*	8-TSSOP	3.31	2.65	2.06
AD8561ARZ-ND	Comparator Single 7nS*	8-SOIC	3.31	2.65	2.06
AD8561ARZ-REEL7CT-ND	Comparator Single 7nS*	8-SOIC	3.31	2.65	2.06
AD8561ARZ-REEL7TR-ND	Comparator Single 7nS*	8-SOIC	1874.83/1,000		
AD8564ARZ-ND	Comparator Quad 7nS*	16-SOIC	6.16	4.93	4.16
AD8564ARUZ-REELCT-ND	Comparator Quad 7nS*	16-TSSOP	6.16	4.93	4.16
AD8564ARUZ-REELTR-ND	Comparator Quad 7nS*	16-TSSOP	9552.19/2,500		
AD8611ARZ-ND	Comparator Single 4nS High Speed*	8-SOIC	3.91	3.13	2.43
AD8611ARMZ-R2CT-ND	Comparator Single 4nS High Speed*	8-MSOP	4.33	3.47	2.70
AD8611ARMZ-R2TR-ND	Comparator Single 4nS High Speed*	8-MSOP	640.00/250		
AD8612ARUZ-ND	Comparator Dual 4nS Fast*	14-TSSOP	5.82	4.66	3.93
AD96687BPZ-ND	Comparator Dual 2.5nS*	20-PLCC	5.40	4.33	3.65
AD96687BQ-ND	Comparator Dual 2.5nS*	16-Dip	8.31	7.49	6.64
AD96687BRZ-ND	Comparator Dual 2.5nS*	16-SOIC	4.92	3.94	3.33
ADCMP341YRZ-REEL7CT-ND	Dual Comparator/Reference*	SOT-23-8	1.88	1.51	1.13
ADCMP341YRZ-REEL7TR-ND	Dual Comparator/Reference*	SOT-23-8	2886.72/3,000		
ADCMP354YKZS-REEL7CT-ND	Comparator, Open-Drain, High Voltage*	SC70-4	.67	.56	.45
ADCMP354YKZS-REEL7TR-ND	Comparator, Open-Drain, High Voltage*	SC70-4	869.88/3,000		
ADCMP361YRZ-REEL7CT-ND	Comparator/Reference*	SOT-23-5	1.26	1.01	.76
ADCMP361YRZ-REEL7TR-ND	Comparator/Reference*	SOT-23-5	1935.06/3,000		
ADCMP370AKSREELTR-ND	Comparator, Open-Drain, High Voltage*	SC70-5	934.32/3,000		
ADCMP370AKSZ-REEL7CT-ND	Comparator, Open-Drain, High Voltage*	SC70-5	.59	.50	.40
ADCMP370AKSZ-REEL7TR-ND	Comparator, Open-Drain, High Voltage*	SC70-5	773.23/3,000		
ADCMP371AKSZ-REEL7CT-ND	Comparator, Push-Pull*	SC70-5	.59	.50	.40
ADCMP371AKSZ-REEL7TR-ND	Comparator, Push-Pull*	SC70-5	773.23/3,000		
ADCMP551BR0Z-ND	Comparator, Single Supply, HS PECL/LVPECL*	16-SOQP	4.52	3.62	2.82
ADCMP552BR0Z-ND	Comparator, Single Supply, HS PECL/LVPECL*	20-SOQP	5.02	4.02	3.40
ADCMP553BRMZ-ND	Comparator, Single Supply, HS PECL/LVPECL*	8-MSOP	3.39	2.71	2.11
ADCMP562BR0Z-ND	Comparator Dual High Speed PECL*	20-SOQP	4.52	3.62	2.82

* RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

(Continued)

Free shipping on orders over €65! All prices in euro and include duties. (EU2011-EN) 797