

ANALOG DEVICES		POWER MANAGEMENT			
Digi-Key Part No.		Description	Pkg.	Price Each*	
				1	25 100
ADR443BRZ-ND	3V, LDO XFET® Voltage Reference*	8-SOIC	5.78	4.63	3.91
ADR444ARMZ-ND	4.096V, LDO XFET® Voltage Reference*	8-MSOP	4.43	3.55	2.99
ADR444ARZ-ND	4.096V, LDO XFET® Reference*	8-SOIC	4.18	3.35	2.83
ADR444BRZ-ND	4.096V, LDO XFET® Voltage Reference*	8-SOIC	5.78	4.63	3.91
ADR445ARMZ-ND	5V, LDO XFET® Voltage Reference*	8-MSOP	4.43	3.55	2.99
ADR445ARZ-ND	5V, LDO XFET® Voltage Reference*	8-SOIC	4.18	3.35	2.83
ADR445BRZ-ND	5V, LDO XFET® Voltage Reference*	8-SOIC	5.78	4.63	3.91
ADR5044ARTZ-REEL7CT-ND	4.096V Precision Reference Shunt*	SOT-23-3	.64	.54	.43
ADR5044ARTZ-REEL7TR-ND	4.096V Precision Reference Shunt*	SOT-23-3	837.67/3,000		
ADR510ARTZ-REEL7CT-ND	1V, Precision Reference Shunt*	SOT-23-3	1.10	.88	.66
ADR510ARTZ-REEL7TR-ND	1V, Precision Reference Shunt*	SOT-23-3	1681.28/3,000		
ADR512ARTZ-REEL7CT-ND	1.2V, Precision Reference Shunt*	SOT-23-3	1.10	.88	.66
ADR512ARTZ-REEL7TR-ND	1.2V, Precision Reference Shunt*	SOT-23-3	1681.28/3,000		
ADR520ARTZ-REEL7CT-ND	Voltage Reference Shunt 2.048V*	SOT-23	1.04	.87	.70
ADR520ARTZ-REEL7TR-ND	Voltage Reference Shunt 2.048V*	SOT-23	1353.15/3,000		
ADR525ART-R2CT-ND	Voltage Reference Shunt 2.5V	SOT-23	1.64	1.31	.98
ADR525ART-REEL7CT-ND	Voltage Reference Shunt 2.5V*	SOT-23	1.19	.90	.80
ADR525ARTZ-REEL7CT-ND	Voltage Reference Shunt 2.5V*	SOT-23-3	1.07	.89	.72
ADR525ARTZ-REEL7TR-ND	Voltage Reference Shunt 2.5V*	SOT-23-3	1385.37/3,000		
ADR525BK5Z-REEL7CT-ND	Voltage Reference Shunt 2.5V*	SC-70-3	1.82	1.46	1.10
ADR525BK5Z-REEL7TR-ND	Voltage Reference Shunt 2.5V*	SC-70-3	1385.37/3,000		
ADR525BRZ-REEL7CT-ND	Voltage Reference Shunt 2.5V*	SOT-23	1.68	1.34	1.01
ADR525BRZ-REEL7TR-ND	Voltage Reference Shunt 2.5V*	SOT-23	2569.50/3,000		
ADR530BK5Z-REEL7CT-ND	Voltage Reference Shunt 3.0V*	SC-70-3	1.82	1.46	1.10
ADR530BK5Z-REEL7TR-ND	Voltage Reference Shunt 3.0V*	SC-70-3	2791.56/3,000		
ADR530BRZ-REEL7CT-ND	Voltage Reference Shunt 3.0V*	SOT-23	1.68	1.34	1.01
ADR530BRZ-REEL7TR-ND	Voltage Reference Shunt 3.0V*	SOT-23	2569.50/3,000		
ADR550BRZ-REEL7CT-ND	Voltage Reference Shunt 5.0V*	SOT-23	1.68	1.34	1.01
ADR550BRZ-REEL7TR-ND	Voltage Reference Shunt 5.0V*	SOT-23	2569.50/3,000		
ADR821ARMZ-REEL7CT-ND	2.5V, LP, Precision Reference and Op Amp*	10-MSOP	2.01	1.61	1.21
ADR821BRMZ-REEL7CT-ND	2.5V, LP, Precision Reference and Op Amp*	10-MSOP	2.35	1.88	1.46
ADR827ARMZ-REEL7CT-ND	1.25V, LP, Precision Reference and Op Amp*	10-MSOP	2.01	1.61	1.21
ADR827BRMZ-REEL7CT-ND	1.25V, LP, Precision Reference and Op Amp*	10-MSOP	2.35	1.88	1.46
ADR1581ARTZ-REEL7CT-ND	Voltage Reference Shunt 1.25V*	SOT-23-3	1.10	.88	.66
ADR1581ARTZ-REEL7TR-ND	Voltage Reference Shunt 1.25V*	SOT-23-3	1681.28/3,000		
ADR5040ARTZ-REEL7CT-ND	Voltage Reference Shunt 2.048V*	SOT-23	.64	.54	.43
ADR5040ARTZ-REEL7TR-ND	Voltage Reference Shunt 2.048V*	SOT-23	837.67/3,000		
ADR5041ARTZ-REEL7CT-ND	Voltage Reference Shunt 2.5V*	SOT-23	.64	.54	.43
ADR5041ARTZ-REEL7TR-ND	Voltage Reference Shunt 2.5V*	SOT-23	837.67/3,000		
ADR5041BK5Z-REEL7CT-ND	Voltage Reference Shunt 2.5V*	SC70	1.04	.87	.70
ADR5041BK5Z-REEL7TR-ND	Voltage Reference Shunt 2.5V*	SC70	1353.15/3,000		
REF01CPZ-ND	Precision Voltage Reference 10V*	8-Dip	2.08	1.67	1.30
REF01CSZ-ND	Precision Voltage Reference 10V*	8-SOIC	2.01	1.61	1.25
REF01EZ-ND	Precision Voltage Reference 10V*	8-CDIP	8.30	7.48	6.63
REF01HFZ-ND	Precision Voltage Reference 10V*	8-Dip	3.18	2.55	1.98
REF02AZ-ND	Prec. Voltage Reference/Temp. 5V Transducer*	8-CDIP	28.17	24.43	22.69
REF02CPZ-ND	Precision Voltage Reference 5V*	8-Dip	2.08	1.67	1.30
REF02CSZ-ND	Precision Voltage Reference 5V*	8-SOIC	2.01	1.61	1.25
REF02EZADI-ND	Precision Voltage Reference 5V*	8-CDIP	8.30	7.48	6.63
REF02HFZ-ND	Precision Voltage Reference 5V*	8-Dip	3.18	2.55	1.98
REF02HSZ-ND	Precision Voltage Reference 5V*	8-SOIC	3.54	2.83	2.20
REF03GPZ-ND	Precision Voltage Reference 2.5V*	8-Dip	2.14	1.71	1.33
REF03GSZ-ND	Precision Voltage Reference 2.5V*	8-SOIC	2.01	1.61	1.25
REF43GPZ-ND	Precision Voltage Reference Low Power 2.5V*	8-Dip	6.36	5.09	4.30
REF43GSZ-ND	Precision Voltage Reference Low Power 2.5V*	8-SOIC	6.36	5.09	4.30
REF191ESZ-ND	Voltage Reference LDO 2.048V*	8-SOIC	4.15	3.32	2.58
REF191GSZ-ND	Voltage Reference LDO 2.048V*	8-SOIC	2.30	1.85	1.44
REF192ESZ-ND	Voltage Reference LDO 2.5V*	8-SOIC	4.15	3.32	2.58
REF192FSZ-ND	Voltage Reference LDO 2.5V*	8-SOIC	3.21	2.58	2.01
REF192GSZ-ND	Voltage Reference LDO 2.5V*	8-Dip	2.30	1.85	1.44
REF192GRUZ-ND	Voltage Reference LDO 2.5V*	8-TSSOP	3.64	2.92	2.27
REF192GRUZREEL7CT-ND	Voltage Reference LDO 2.5V*	8-TSSOP	3.64	2.92	2.27
REF192GSZ-ND	Voltage Reference LDO 2.5V*	8-SOIC	2.30	1.85	1.44
REF193GSZ-ND	Voltage Reference LDO 3V*	8-SOIC	2.30	1.85	1.44
REF194ESZ-ND	Voltage Reference LDO 4.5V*	8-SOIC	3.78	3.02	2.35
REF194GSZ-ND	Voltage Reference LDO 4.5V*	8-SOIC	2.30	1.85	1.44
REF195ESZ-ND	Voltage Reference LDO 5V*	8-SOIC	3.78	3.02	2.35
REF195FSZ-ND	Voltage Reference LDO 5V*	8-SOIC	2.92	2.34	1.82
REF195FS-REELCT-ND	Voltage Reference LDO 5V*	8-SOIC	3.48	2.79	2.17
REF195GPZ-ND	Voltage Reference LDO 5V*	8-Dip	2.10	1.69	1.31
REF195GSZ-ND	Voltage Reference LDO 5V*	8-SOIC	2.30	1.85	1.44
REF196GSZ-ND	Voltage Reference LDO 3.3V*	8-SOIC	2.30	1.85	1.44
REF198ESZ-ND	Voltage Reference LDO 4.096V*	8-SOIC	4.15	3.32	2.58
REF198FSZ-ND	Voltage Reference LDO 4.096V*	8-SOIC	3.21	2.58	2.01
REF198GRUZ-ND	Voltage Reference LDO 4.096V*	8-TSSOP	3.64	2.92	2.27
REF198GSZ-ND	Voltage Reference LDO 4.096V*	8-SOIC	2.30	1.85	1.44
REF198SZ-ND	Voltage Reference LDO 4.096V*	8-SOIC	2.30	1.85	1.44

ANALOG DEVICES		SENSOR/SIGNAL CONDITIONING			
Digi-Key Part No.		Description	Pkg.	Price Each*	
				1	25 100
ADE7758ARWZ-ND	Energy Metering*	24-SOIC	9.87	8.89	7.88
ADE7759ARSZ-ND	Energy Meter with Sensor Interface*	20-SSOP	3.72	2.98	2.32
ADE7763ARSZ-ND	Energy Meter Single Phase Active and Apparent*	20-SSOP	2.99	2.40	1.87
ADE7763ARSZRLCT-ND	Energy Meter Single Phase Active and Apparent*	20-SSOP	2.99	2.40	1.87
ADE7763ARSZRLCT-ND	Energy Meter Single Phase Active and Apparent*	20-SSOP	2543.67/1,500		
Temperature					
AD590UF-ND	Temperature Transducer 2-Terminal*	2-COFF	12.76	11.92	11.07
AD590JH-ND	Temperature Transducer 2-Terminal*	TO-52-3	7.01	5.61	4.73
AD590JURZ-ND	Temperature Transducer 2-Terminal*	8-SOIC	4.51	3.61	3.05
AD590KF-ND	Temperature Transducer 2-Terminal*	2-COFF	13.95	13.03	12.10
AD590KH-ND	Temperature Transducer 2-Terminal*	TO-52-3	8.81	7.94	7.04
AD590KRZ-ND	Temperature Transducer 2-Terminal*	8-SOIC	7.47	5.98	5.05
AD590LF-ND	Temperature Transducer 2-Terminal*	2-COFF	34.71	32.40	30.09
AD590LH-ND	Temperature Transducer 2-Terminal*	TO-52-3	17.67	16.50	15.32
AD590MF-ND	Temperature Transducer 2-Terminal*	2-COFF	63.76	59.51	55.26
AD590MH-ND	Temperature Transducer 2-Terminal*	TO-52-3	42.07	39.27	36.46
AD592ANZ-ND	Temperature Transducer 2-Terminal*	TO-92	3.98	3.19	2.48
AD592BZ-ND	Temperature Transducer 2-Terminal*	TO-92	9.17	8.26	7.32
AD592CNZ-ND	Temperature Transducer 2-Terminal*	TO-92	12.21	11.00	9.75
AD594AQ-ND	Thermocouple Amp with Compensator	14-Dip	10.20	9.19	8.15
AD594CQ-ND	Thermocouple Amp with Compensator	14-Dip	16.58	15.48	14.37
AD595AQ-ND	Thermocouple Amp with Compensator	14-Dip	10.20	9.19	8.15
AD595CQ-ND	Thermocouple Amp with Compensator	14-Dip	16.58	15.48	14.37
AD596AHZ-ND	Thermocouple Conditioning*	TO-100	11.01	9.92	8.79
AD597AHZ-ND	Thermocouple Conditioning*	TO-100	11.86	10.69	9.48
AD597ARZ-ND	Thermocouple Conditioning*	8-SOIC	4.91	3.93	3.32
AD22100ARZ-ND	Temperature Sensor Voltage Out*	8-SOIC	4.63	3.71	3.13
AD22100ATZ-ND	Temperature Sensor Voltage Out*	TO-92-3	4.20	3.36	2.84
AD22100KTZ-ND	Temperature Sensor Voltage Out*	TO-92-3	2.81	2.25	1.75
AD22100SRZ-ND	Temperature Sensor Voltage Out*	8-SOIC	5.09	4.08	3.44
AD22100STZ-ND	Temperature Sensor Voltage Out*	TO-92-3	4.63	3.71	3.13
AD22103KRZ-ND	Temperature Sensor Voltage Out*	8-SOIC	2.81	2.25	1.75
AD22105ARZ-ND	Thermostatic Switch Solid State*	8-SOIC	2.47	1.98	1.54
AD7314ARMZ-ND	Temperature Sensor 10-Bit Digital*	8-MSOP	1.36	1.10	.82
AD714ARMOREEL7CT-ND	Temperature Sensor 10-Bit Digital*	8-MSOP	2.47	1.98	1.54
AD714ARMZ-ND	Temperature Sensor 10-Bit Digital*	8-MSOP	2.08	1.67	1.30
AD714AARTZ0500RCT-ND	Temperature Sensor 10-Bit*	SOT-23-6	1.93	1.55	1.21
AD714AARTZ0500RTR-ND	Temperature Sensor 10-Bit*	SOT-23-6	558.44/500		
AD714AARTZ-1REEL7CT-ND	Temperature Sensor 10-Bit*	SOT-23-6	2.15	1.72	1.29
AD714AARTZ-1REEL7TR-ND	Temperature Sensor 10-Bit*	SOT-23-6	3247.56/3,000		
AD714AARTZ-2REEL7CT-ND	Temperature Sensor 10-Bit*	SOT-23-6	1.93	1.55	1.21
AD714SARTZ-0500RL7TR-ND	Temperature Sensor 10-Bit*	SOT-23-5	558.44/500		
AD714SARTZ-1500RL7CT-ND	Temperature Sensor 10-Bit*	SOT-23-5	1.93	1.55	1.21
AD714SARTZ-1500RL7TR-ND	Temperature Sensor 10-Bit*	SOT-23-5	558.44/500		
AD714SARTZ-2REEL7TR-ND	Temperature Sensor 10-Bit*	8-MSOP	2.07	1.66	1.24
AD714SARTZ-2REEL7TR-ND	Temperature Sensor 10-Bit*	16-SOIC	5.04	4.04	3.41
AD714SARTZ-2REEL7TR-ND	Temperature Sensor 10-Bit/Four 1-Channel ADCs*	16-TSSOP	5.04	4.04	3.41
AD714SARTZ-2REEL7TR-ND	Temperature Sensor 10-Bit/Four 1-Channel ADCs*	8-MSOP	4.26	3.41	2.88
AD714SARTZ-2REEL7TR-ND	Temperature Sensor 10-Bit/Four 1-Channel ADCs*	8-SOIC	4.26	3.41	2.88
AD714SARTZ-2REEL7TR-ND	Digital Temperature Sensor 10-Bit*	8-SOIC	2.05	1.64	1.28
AD714SARTZ-2REEL7TR-ND	Digital Temperature Sensor 10-Bit*	SOT-23-6	2.07	1.66	1.24
AD714SARTZ-2REEL7TR-ND	Digital Temperature Sensor 10-Bit*	SOT-23-6	3172.22/3,000		
AD22103KTZ-ND	Temperature Sensor 3.3V Signal Condition*	TO-92	2.68	2.15	1.67
AD22151VYZ-ND	Magnetic Field Sensor Linear*	8-SOIC	4.55	3.65	2.84
ADT17310TRZ-ND	Digital SPI Temperature Sensor 16-Bit*	8-SOIC	2.60	2.09	1.62
ADT17410TRZ-ND	PC Temperature Sensor	8-SOIC	2.60	2.09	1.62
EVAL-AD77410EBZ-ND	Evaluation Board for AD77410*	—	123.92		
AD775ARZ-ND	Digital Temperature Sensor 12-Bit*	8-MSOP	1.43	1.14	.86
AD775ARZ-ND	Digital Temperature Sensor 12-Bit*	8-SOIC	1.43	1.14	.86
AD775BRMZ-ND	Digital Temperature Sensor 12-Bit*	8-MSOP	2.01	1.61	1.21
ADT6401SRJZ-RL7CT-ND	Temperature Switch 2.7V-5.5V*	SOT-23-6	1.24	1.00	.75
ADT6401SRJZ-RL7TR-ND	Temperature Switch 2.7V-5.5V*	SOT-23-6	1903.33/3,000		
ADT6402SRJZ-RL7CT-ND	Temperature Switch 2.7V-5.5V*	SOT-23-6	1.24	1.00	.75
ADT6402SRJZ-RL7TR-ND	Temperature Switch 2.7V-5.5V*	SOT-23-6	1903.33/3,000		
ADT6501SRJZP06RL7CT-ND	Temperature Switch 2.7V-5.5V*	SOT-23-5	1.03	.83	.62
ADT6501SRJZP06RL7CT-ND	Temperature Switch 2.7V-5.5V*	SOT-23-5	1.03	.83	.62
ADT6503SRJZ02SR7CT-ND	Temperature Switch 2.7V-5.5V*	SOT-23-5	1.03	.83	.62
ADT6504SRJZ01SR7CT-ND	Temperature Switch 2.7V-5.5V*	SOT-23-5	1.03	.83	.62
ADT7301ARMZ-ND	Digital Temperature Sensor 13-Bit*	8-MSOP	2.27	1.82	1.42
ADT7301ARTZ-REEL7CT-ND	Digital Temperature Sensor 13-Bit*	SOT-23-6	2.25	1.80	1.40
ADT7301ARTZ-REEL7TR-ND	Digital Temperature Sensor 13-Bit*	SOT-23-6	3778.42/3,000		
ADT7302ARMZ-ND	Micropower Digital Temperature Sensor 13-Bit*	8-Dip	1.61	1.29	.97
ADT7302ARTZ-REEL7CT-ND	Micropower Digital Temperature Sensor 13-Bit*	SOT-23-6	1.61	1.29	.97
ADT7302ARTZ-REEL7TR-ND	Micropower Digital Temperature Sensor 13-Bit*	SOT-23-6	2474.33/3,000		
EVAL-AD77411EBZ-ND	Evaluation Board for AD77411*	—	135.53		
ADT7470ARZ-ND	Temperature Sensor Hub/Fan Controller*	16-QSOP	4.06	3.25	2.53
ADT7517ARZ-ND	SPI				