

TEXAS INSTRUMENTS		Digi+Reel® (Cont.)		AMPLIFIERS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
LM358DR	296-1014-1-ND	Dual Op Amp	8-SOIC	.49	.29	.24			
LM358DR	296-1014-2-ND	Dual Op Amp	8-SOIC	208.59/2,500					
LM358P	296-1395-5-ND	8-Dip	8-SOP	.39	.26	.21			
LM358PSR	296-1396-1-ND	Dual Op Amp	8-SOP	.37	.25	.20			
LM358PSR	296-1396-2-ND	Dual Op Amp	8-SOP	168.52/2,000					
LM358PWR	296-9555-1-ND	Dual Op Amp	8-TSSOP	.38	.26	.21			
LM358PWR	296-9555-2-ND	Dual Op Amp	8-TSSOP	175.13/2,000					
LM392D	296-26105-5-ND	LP Op Amp and Voltage Comparator*	8-SOIC	1.32	1.06	.93			
LM392DR	296-20853-1-ND	LP Op Amp and Voltage Comparator	8-SOIC	1.19	.95	.85			
LM392P	296-20854-5-ND	LP Op Amp and Voltage Comparator	8-Dip	1.10	.88	.77			
LM393PW	296-26106-5-ND	Dual Differential Comparator*	8-TSSOP	.40	.27	.22			
LM2900N	296-9526-5-ND	Quad Op Amp	14-Dip	.45	.30	.25			
LM2901PW	296-26088-5-ND	Quad Differential Comparator*	14-TSSOP	.44	.30	.24			
LM2902D	296-6598-5-ND	Quad Op Amp	14-SOIC	.44	.30	.24			
LM2902DR	296-14594-1-ND	Quad Op Amp	14-SOIC	.40	.27	.22			
LM2902DR	296-14594-2-ND	Quad Op Amp	14-SOIC	231.31/2,500					
LM2902KAVQDR	296-17253-1-ND	Quad Op Amp	14-SOIC	.57	.45	.39			
LM2902KAVQDRQ1	296-23358-1-ND	Quad Op Amp	14-TSSOP	.59	.46	.40			
LM2902KAVQDRQ1	296-23358-2-ND	Quad Op Amp	14-TSSOP	384.96/2,000					
LM2902KDR	296-18440-5-ND	Quad Op Amp	14-SOIC	.39	.26	.22			
LM2902KN	296-18441-5-ND	Quad Op Amp	14-Dip	.43	.29	.24			
LM2902KNSR	296-18442-1-ND	Quad Op Amp	14-SOP	.48	.32	.26			
LM2902N	296-6599-5-ND	Quad Op Amp	14-Dip	.45	.30	.24			
LM2902PWR	296-6600-1-ND	Quad Op Amp	14-TSSOP	.40	.27	.22			
LM2902PWR	296-6600-2-ND	Quad Op Amp	14-TSSOP	185.05/2,000					
LM2902QDRG4Q1	296-24705-1-ND	Quad Op Amp*	14-SOIC	.50	.36	.31			
LM2902QDRG4Q1	296-24705-2-ND	Quad Op Amp*	14-SOIC	355.22/2,500					
LM2904AVQDRG4Q1	296-24707-1-ND	Dual Gen. Purp. Op Amp*	8-SOIC	.59	.46	.40			
LM2904AVQDRG4Q1	296-24707-2-ND	Dual Gen. Purp. Op Amp*	8-SOIC	481.20/2,500					
LM2904AVQDRG4Q1	296-22007-1-ND	Dual General Purpose Op Amp	8-TSSOP	.57	.45	.39			
LM2904AVQDRQ1	296-17791-1-ND	Dual General Purpose Op Amp	8-TSSOP	.59	.46	.40			
LM2904AVQDRQ1	296-17791-2-ND	Dual General Purpose Op Amp	8-TSSOP	384.96/2,000					
LM2904D	296-9527-5-ND	Dual General Purpose Op Amp	8-SOIC	.42	.28	.23			
LM2904DGKR	296-17931-1-ND	Dual General Purpose Op Amp	8-MSOP	.39	.26	.21			
LM2904DGKR	296-17931-2-ND	Dual General Purpose Op Amp	8-MSOP	220.98/2,500					
LM2904DR	296-14596-1-ND	Dual General Purpose Op Amp	8-SOIC	.39	.26	.21			
LM2904P	296-9528-5-ND	Dual General Purpose Op Amp	8-Dip	.43	.29	.24			
LM2904PW	296-26089-5-ND	Dual Op Amp*	8-TSSOP	.42	.28	.23			
LM2904PWR	296-9529-1-ND	Dual General Purpose Op Amp	8-TSSOP	.39	.26	.21			
LM2904PWR	296-9529-2-ND	Dual General Purpose Op Amp	8-TSSOP	176.79/2,000					
LM2904QDRG4Q1	296-24708-1-ND	Dual Gen. Purp. Op Amp*	8-SOIC	.50	.36	.31			
LM2904QDRG4Q1	296-24708-2-ND	Dual Gen. Purp. Op Amp*	8-SOIC	355.22/2,500					
LM2904QDRQ1	296-15184-1-ND	Dual General Purpose Op Amp	8-SOIC	.50	.36	.31			
LM2904QDRQ1	296-15184-2-ND	Dual General Purpose Op Amp	8-SOIC	355.22/2,500					
LM2904QDRQ1	296-17099-1-ND	Dual General Purpose Op Amp	8-SOIC	.59	.42	.36			
LM2904QDRQ1	296-17099-2-ND	Dual General Purpose Op Amp	8-SOIC	419.25/2,500					
LM3900D	296-9564-5-ND	Quad Op Amp	14-SOIC	.45	.30	.25			
LM3900DR	296-14604-1-ND	Quad Op Amp	14-SOIC	.42	.28	.23			
LM3900DR	296-14604-2-ND	Quad Op Amp	14-SOIC	239.57/2,500					
LM3900N	296-9565-5-ND	Quad Op Amp	14-Dip	.41	.28	.23			
LMV321DBVR	296-9567-1-ND	Low Voltage R/R Op Amp	SOT-23-5	.62	.48	.43			
LMV321DBVR	296-9567-2-ND	Low Voltage R/R Op Amp	SOT-23-5	612.14/3,000					
LMV321DBVRQ1	296-20922-1-ND	Low Voltage R/R Op Amp	SOT-23-5	.68	.53	.47			
LMV321DBVRQ1	296-20922-2-ND	Low Voltage R/R Op Amp	SOT-23-5	617.62/3,000					
LMV321DCKR	296-9568-1-ND	Low Voltage R/R Op Amp	SC70-5	.62	.48	.43			
LMV321DCKR	296-9568-2-ND	Low Voltage R/R Op Amp	SC70-5	612.14/3,000					
LMV324ID	296-9569-5-ND	Quad Low Voltage R/R Op Amp	14-SOIC	.79	.62	.54			
LMV324IDR	296-9569-1-ND	Quad Low Voltage R/R Op Amp	14-SOIC	.73	.57	.50			
LMV324IDR	296-9569-2-ND	Quad Low Voltage R/R Op Amp	14-SOIC	598.92/2,500					
LMV324IDPWR	296-9570-1-ND	Quad Low Voltage R/R Op Amp	14-TSSOP	.73	.57	.50			
LMV324IDPWR	296-9570-2-ND	Quad Low Voltage R/R Op Amp	14-TSSOP	479.14/2,000					
LMV324QDR	296-17467-1-ND	Quad Low Voltage R/R Op Amp	14-SOIC	.80	.62	.55			
LMV324QDR	296-17467-2-ND	Quad Low Voltage R/R Op Amp	14-SOIC	658.81/2,500					
LMV324QDWR	296-17468-1-ND	Quad Low Voltage R/R Op Amp	14-TSSOP	.80	.62	.55			
LMV324QDWR	296-17468-2-ND	Quad Low Voltage R/R Op Amp	14-TSSOP	527.05/2,000					
LMV324QDWRG4Q1	296-24417-1-ND	Quad Low Volt. R/R Op Amp*	14-TSSOP	.82	.65	.58			
LMV324QDWRG4Q1	296-24417-2-ND	Quad Low Volt. R/R Op Amp*	14-TSSOP	601.40/2,000					
LMV324SIDR	296-15361-1-ND	Quad Low Voltage R/R Op Amp	16-SOIC	.88	.68	.60			
LMV324SIDR	296-15361-2-ND	Quad Low Voltage R/R Op Amp	16-SOIC	718.71/2,500					
LMV339IPW	296-26114-5-ND	Quad Low Voltage Comparator*	14-TSSOP	.90	.73	.64			
LMV341IDBVR	296-17843-1-ND	Single R/R Out CMOS Op Amp	SOT-23-6	.73	.57	.50			
LMV341IDBVR	296-17843-2-ND	Single R/R Out CMOS Op Amp	SOT-23-6	718.71/3,000					
LMV341IDBVRQ1	296-17359-1-ND	Single R/R Out CMOS Op Amp	SC70-6	.73	.57	.50			
LMV341IDBVRQ1	296-17359-2-ND	Single R/R Out CMOS Op Amp	SC70-6	718.71/3,000					
LMV341QDWRQ1	296-24890-1-ND	Single R/R Out CMOS Op Amp*	SOT-23-6	.83	.65	.57			
LMV341QDWRQ1	296-24890-2-ND	Single R/R Out CMOS Op Amp*	SOT-23-6	826.51/3,000					
LMV341QDCKRQ1	296-24893-1-ND	Single R/R Out CMOS Op Amp*	SC70-6	.83	.65	.57			
LMV341QDCKRQ1	296-24893-2-ND	Single R/R Out CMOS Op Amp*	SC70-6	826.51/3,000					
LMV342IDGKR	296-22012-1-ND	Dual R/R Out CMOS Op Amp	8-MSOP	.78	.62	.56			
LMV344IDR	296-20925-1-ND	Quad R/R Out CMOS Op Amp	14-SOIC	.78	.62	.56			
LMV344IDR	296-20925-2-ND	Quad R/R Out CMOS Op Amp	14-SOIC	722.84/2,500					
LMV344IPWR	296-18596-1-ND	Quad R/R Out CMOS Op Amp	14-TSSOP	.78	.62	.56			
LMV344IPWR	296-18596-2-ND	Quad R/R Out CMOS Op Amp	14-TSSOP	578.27/2,000					
LMV358IDR	296-9571-1-ND	Dual Low Voltage R/R Op Amp	8-SOIC	.73	.57	.50			
LMV358IDR	296-9571-2-ND	Dual Low Voltage R/R Op Amp	8-SOIC	598.92/2,500					
LMV358IPWR	296-9572-1-ND	Dual Low Voltage R/R Op Amp	8-TSSOP	.73	.57	.50			
LMV358IPWR	296-9572-2-ND	Dual Low Voltage R/R Op Amp	8-TSSOP	479.14/2,000					
LMV358ODR	296-17471-1-ND	Dual Low Voltage R/R Op Amp	8-SOIC	.80	.62	.55			
LMV393ID	296-26115-5-ND	Dual Low Voltage Comparator*	8-SOIC	.79	.62	.54			
LMV710IDBVR	296-17853-1-ND	Low Power R/R I/O Op Amp	SOT-23-5	1.03	.82	.74			
LMV710IDBVR	296-17853-2-ND	Low Power R/R I/O Op Amp	SOT-23-5	1144.97/3,000					
LMV710IDCKR	296-17854-1-ND	Low Power R/R I/O Op Amp	SC70-5	1.03	.82	.74			
LMV710IDCKR	296-17854-2-ND	Low Power R/R I/O Op Amp	SC70-5	1144.97/3,000					
LMV711IDBVR	296-18000-1-ND	Single, Low Power, R/R I/O Op Amp	SOT-23-5	1.03	.82	.74			
LMV712IDGSR	296-20926-1-ND	Dual, Low Power, R/R In/Out Op Amp	10-MSOP	1.41	1.12	1.01			
LMV715IDBVR	296-20927-1-ND	Single Low Power, R/R In/Out Op Amp	SOT-23-6	1.13	.90	.81			
LMV715IDBVR	296-20927-2-ND	Single Low Power, R/R In/Out Op Amp	SOT-23-6	1144.97/3,000					
LMV715IDCKR	296-20928-1-ND	Single Low Power, R/R In/Out Op Amp	SC70-6	1.13	.90	.81			
LMV821DBVR	296-18459-1-ND	Single, Low Voltage, R/R Op Amp	SOT-23-5	1.48	1.17	1.05			
LMV821DCKR	296-18460-1-ND	Single, Low Voltage, R/R Op Amp	SC70-5	1.48	1.17	1.05			

TEXAS INSTRUMENTS		Digi+Reel® (Cont.)		AMPLIFIERS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
LMV821DCKR	296-18460-2-ND	Single, Low Voltage, R/R Op Amp	SC70-5	1630.72/3,000					
LMV821DBVR	296-18461-1-ND	Single, Low Voltage, R/R Op Amp	SOT-23-5	1.48	1.17	1.05			
LMV821DBVR	296-18461-2-ND	Single, Low Voltage, R/R Op Amp	SOT-23-5	1630.72/3,000					
LMV821DCKR	296-18462-1-ND	Single, Low Voltage, R/R Op Amp	SC70-5	1.48	1.17	1.05			
LMV822D	296-26116-5-ND	Dual, Low Voltage R/R Op Amp*	8-SOIC	.90	.73	.64			
LMV824DR	296-18465-1-ND	Quad Low Voltage R/R Op Amp	14-SOIC	.88	.70	.63			
LMV824IDGVR	296-17523-1-ND	Quad Low Voltage R/R Op Amp	14-TSSOP	.88	.70	.63			
LMV824IDR	296-18466-1-ND	Quad Low Voltage R/R Op Amp	14-SOIC	.88	.70	.63			
LMV824IDPWR	296-18467-1-ND	Quad Low Voltage R/R Op Amp	14-TSSOP	.88	.70	.63			
LMV824IPWR	296-18467-2-ND	Quad Low Voltage R/R Op Amp	14-TSSOP	647.66/2,000					
LMV824PW	296-26117-5-ND	Quad Low Voltage R/R Op Amp*	14-TSSOP	.97	.78	.68			
LMV931IDBVR	296-18469-1-ND	1.8V R/R In/Out Op Amp	SOT-23-5	.91	.72	.65			
LMV931IDBVR	296-18469-2-ND	1.8V R/R In/Out Op Amp	SOT-23-5	1006.19/3,000					
LMV931IDCKR	296-17996-1-ND	1.8V R/R In/Out Op Amp	SC70-5	.91	.72	.65			
LMV931IDR	296-26118-5-ND	1.8V R/R In/Out Op Amp*	8-SOIC	1.42	1.14	1.00			
LMV931IDGKR	296-17910-1-ND	1.8V Dual Op Amp	8-MSOP	1.29	1.02	.92			
LMV931IDGR	296-17911-1-ND	1.8V Dual Op Amp	8-SOIC	1.29	1.02	.92			
LMV931IDR	296-17911-2-ND	1.8V Dual Op Amp	8-SOIC	1185.45/2,500					
LMV931IPWR	296-20930-1-ND	1.8V Quad Op Amp	14-TSSOP	1.32	1.05	.94			
LMV931IPWR	296-20930-2-ND	1.8V Quad Op Amp	14-TSSOP	971.49/2,000					
LMV981IDGSR	296-18471-1-ND	1.8V R/R In/Out Op Amp w/Shutdown	SC70-6	1.07	.85	.76			
LMV981IDGSR	296-17949-1-ND	1.8V R/R In/Out Op Amp	10-MSOP	1.13	.90	.81			
LOG101AID	296-12850-5-ND	Precision Logarithmic/Log Ratio Amp	8-SOIC	15.18	12.77	11.73			
LOG102AID	296-12850-5-ND	Precision Logarithmic/Log Ratio Amp	14-SOIC	15.81	13.30	12.22			
LOG104AID	296-12851-5-ND	Precision Logarithmic/Log Ratio Amp	8-SOIC	15.18	12.77	11.73			
LOG112AIDW	296-13456-5-ND	Precision Logarithmic/Log Ratio Amp with On Chip 2.5 Volt. Reference	14-SOIC	17.27	14.52	13.35</			