

TEXAS INSTRUMENTS		Digi+Reel® (Cont.)		AMPLIFIERS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
TLC271CD	296-1308-5-ND	LP Programmable Op Amp	8-SOIC	.73	.59	.51			
TLC271CP	296-1820-5-ND	LP Programmable Op Amp	8-Dip	.69	.54	.47			
TLC271CPS	296-26741-5-ND	LP Programmable Op Amp*	8-SO	.73	.59	.51			
TLC271ID	296-1821-5-ND	LP Programmable Op Amp	8-SOIC	.76	.61	.54			
TLC271IP	296-1822-5-ND	LP Programmable Op Amp	8-Dip	.73	.57	.50			
TLC272ACD	296-1309-5-ND	Dual Precision Op Amp	8-SOIC	.82	.66	.58			
TLC272ACDR	296-1309-1-ND	Dual Precision Op Amp	8-SOIC	.85	.67	.59			
TLC272ACDR	296-1309-2-ND	Dual Precision Op Amp	8-SOIC	704.25/2,500					
TLC272ACP	296-7346-5-ND	Dual Precision Op Amp	8-Dip	.78	.61	.53			
TLC272AID	296-7347-5-ND	Dual Precision Op Amp	8-SOIC	.85	.68	.60			
TLC272AIP	296-7348-5-ND	Dual Precision Op Amp	8-Dip	.82	.64	.56			
TLC272BCD	296-7349-5-ND	Dual Precision Op Amp	8-SOIC	.84	.68	.60			
TLC272BCDR	296-26742-1-ND	Dual Precision Op Amp*	8-SOIC	.88	.69	.61			
TLC272BCDR	296-26742-2-ND	Dual Precision Op Amp*	8-SOIC	731.10/2,500					
TLC272BCP	296-7350-5-ND	Dual Precision Op Amp	8-Dip	.84	.68	.60			
TLC272BID	296-7351-5-ND	Dual Precision Op Amp	8-SOIC	.88	.71	.62			
TLC272BIDR	296-26743-1-ND	Dual Precision Op Amp*	8-SOIC	.80	.64	.58			
TLC272BIDR	296-26743-2-ND	Dual Precision Op Amp*	8-SOIC	739.36/2,500					
TLC272BIP	296-7352-5-ND	Dual Precision Op Amp	8-Dip	.74	.60	.52			
TLC272CD	296-1310-5-ND	Dual Precision Op Amp	8-SOIC	.77	.60	.52			
TLC272CDR	296-1310-1-ND	Dual Precision Op Amp	8-SOIC	.70	.55	.48			
TLC272CDR	296-1310-2-ND	Dual Precision Op Amp	8-SOIC	577.96/2,500					
TLC272CP	296-1824-5-ND	Dual Precision Op Amp	8-Dip	.64	.50	.44			
TLC272CPSR	296-7353-1-ND	Dual Single-Supply Op Amp	8-SOP	.70	.55	.48			
TLC272CPSR	296-7353-2-ND	Dual Single-Supply Op Amp	8-SOP	462.62/2,000					
TLC272CPW	296-7354-5-ND	Dual Single-Supply Op Amp	8-TSSOP	.77	.60	.52			
TLC272CPWR	296-7354-1-ND	Dual Single-Supply Op Amp	8-TSSOP	.70	.55	.48			
TLC272CPWR	296-7354-2-ND	Dual Single-Supply Op Amp	8-TSSOP	462.62/2,000					
TLC272ID	296-1311-5-ND	Dual Precision Single-Supply Op Amp	8-SOIC	.80	.62	.54			
TLC272IDR	296-1311-1-ND	Dual Precision Single-Supply Op Amp	8-SOIC	.74	.58	.51			
TLC272IDR	296-1311-2-ND	Dual Precision Single-Supply Op Amp	8-SOIC	607.91/2,500					
TLC272IP	296-7355-5-ND	Dual Single-Supply Op Amp	8-Dip	.67	.52	.46			
TLC274ACD	296-1825-5-ND	Quad Precision Op Amp	14-SOIC	1.05	.84	.74			
TLC274ACN	296-7356-5-ND	Quad Precision Op Amp	14-Dip	.88	.70	.62			
TLC274AID	296-7357-5-ND	Quad Precision Op Amp	14-SOIC	1.08	.84	.74			
TLC274AIDR	296-26744-1-ND	Quad Precision Op Amp*	14-SOIC	.95	.75	.68			
TLC274AIDR	296-26744-2-ND	Quad Precision Op Amp*	14-SOIC	873.60/2,500					
TLC274AIP	296-7358-5-ND	Quad Precision Op Amp	14-Dip	.88	.70	.62			
TLC274BCD	296-7359-5-ND	Quad Precision Op Amp	14-SOIC	1.16	.94	.82			
TLC274BCN	296-7360-5-ND	Quad Precision Op Amp	14-Dip	.97	.78	.68			
TLC274BID	296-1312-5-ND	Quad Precision Op Amp	14-SOIC	1.16	.94	.82			
TLC274BIDR	296-1312-1-ND	Quad Precision Op Amp	14-SOIC	1.06	.84	.75			
TLC274BIDR	296-1312-2-ND	Quad Precision Op Amp	14-SOIC	971.49/2,500					
TLC274BIN	296-7361-5-ND	Quad Precision Op Amp	14-Dip	.97	.78	.68			
TLC274CD	296-1313-5-ND	Quad Single-Supply Op Amp	14-SOIC	.97	.78	.68			
TLC274CDR	296-1313-1-ND	Quad Single-Supply Op Amp	14-SOIC	.87	.69	.62			
TLC274CDR	296-1313-2-ND	Quad Single-Supply Op Amp	14-SOIC	800.90/2,500					
TLC274CN	296-1826-5-ND	Quad Precision Op Amp	14-Dip	.80	.65	.57			
TLC274CPWR	296-26745-1-ND	Quad Precision Op Amp*	14-TSSOP	.87	.69	.62			
TLC274CPWR	296-26745-2-ND	Quad Precision Op Amp*	14-TSSOP	641.05/2,000					
TLC274ID	296-1314-5-ND	Quad Precision Op Amp	14-SOIC	.97	.78	.68			
TLC274IDR	296-1314-1-ND	Quad Precision Op Amp	14-SOIC	.87	.69	.62			
TLC274IDR	296-1314-2-ND	Quad Precision Op Amp	14-SOIC	800.90/2,500					
TLC274IN	296-7362-5-ND	Quad Single-Supply Op Amp	14-Dip	.97	.78	.68			
TLC274IPW	296-14197-5-ND	Quad Single-Supply Op Amp	14-TSSOP	.97	.78	.68			
TLC274MD	296-7363-5-ND	Quad Single-Supply Op Amp	14-SOIC	1.04	.84	.73			
TLC277CD	296-7364-5-ND	Dual Precision Single-Supply Op Amp	8-SOIC	2.21	1.78	1.60			
TLC277CDR	296-26747-1-ND	Dual Precision Op Amp*	8-SOIC	2.06	1.59	1.44			
TLC277CDR	296-26747-2-ND	Dual Precision Op Amp*	8-SOIC	1980.57/2,500					
TLC277CP	296-1828-5-ND	Dual Precision Op Amp	8-Dip	1.82	1.47	1.32			
TLC277ID	296-1829-5-ND	Dual Precision Op Amp	8-SOIC	2.30	1.86	1.68			
TLC277IP	296-7365-5-ND	Dual Precision Single-Supply Op Amp	8-Dip	1.95	1.57	1.42			
TLC279CD	296-7366-5-ND	Quad Prec. Single-Supply Op Amp	14-SOIC	2.75	2.22	2.02			
TLC279CN	296-7367-5-ND	Quad Prec. Single-Supply Op Amp	14-Dip	2.31	1.86	1.70			
TLC279ID	296-1315-5-ND	Quad Prec. Single-Supply Op Amp	14-SOIC	2.87	2.31	2.10			
TLC279IDR	296-1315-1-ND	Quad Prec. Single-Supply Op Amp	14-SOIC	2.60	2.13	1.91			
TLC279IDR	296-1315-2-ND	Quad Prec. Single-Supply Op Amp	14-SOIC	2884.12/2,500					
TLC279IN	296-7368-5-ND	Quad Prec. Single-Supply Op Amp	14-Dip	2.43	1.96	1.78			
TLC393QDR	296-15027-1-ND	Dual Micropower LinCMOS Voltage Comparator	8-SOIC	.97	.77	.70			
TLC1078CD	296-10231-5-ND	Dual Micropower Low Voltage Op Amp	8-SOIC	5.39	4.42	3.99			
TLC1078CP	296-10232-5-ND	Dual Micropower Low Voltage Op Amp	8-Dip	5.06	4.08	3.71			
TLC1078ID	296-10233-5-ND	Dual Micropower Low Voltage Op Amp	8-SOIC	5.60	4.59	4.15			
TLC1078IP	296-10234-5-ND	Dual Micropower Low Voltage Op Amp	8-Dip	5.27	4.24	3.87			
TLC1079CD	296-10235-5-ND	Quad Micropower Low Volt. Op Amp	14-SOIC	7.56	6.20	5.60			
TLC1079CN	296-10236-5-ND	Quad Micropower Low Volt. Op Amp	14-Dip	6.28	5.15	4.65			
TLC1079ID	296-10237-5-ND	Quad Micropower Low Volt. Op Amp	14-SOIC	7.85	6.44	5.81			
TLC1079IN	296-10238-5-ND	Quad Micropower Low Volt. Op Amp	14-Dip	6.57	5.39	4.86			
TLC2201ACD	296-7050-5-ND	Low Noise Precision Op Amp	8-SOIC	4.51	3.63	3.31			
TLC2201AID	296-7052-5-ND	Low Noise Precision Op Amp	8-SOIC	4.72	3.80	3.46			
TLC2201AMD	296-7054-5-ND	Low Noise Precision Op Amp	8-SOIC	4.83	3.89	3.54			
TLC2201CD	296-2425-5-ND	Low Noise Precision R/R Op Amp	8-SOIC	4.39	3.54	3.22			
TLC2201CP	296-10241-5-ND	Low Noise Precision R/R Op Amp	8-Dip	3.63	2.92	2.66			
TLC2201IDR	296-7061-1-ND	Low Noise Precision R/R Op Amp	8-SOIC	4.11	3.36	3.02			
TLC2201IDR	296-7061-2-ND	Low Noise Precision R/R Op Amp	8-SOIC	4560.07/2,500					
TLC2201ID	296-10242-5-ND	Low Noise Precision R/R Op Amp	8-SOIC	4.51	3.63	3.31			
TLC2201IP	296-7062-5-ND	Low Noise Precision R/R Op Amp	8-Dip	3.84	3.09	2.82			
TLC2202ACD	296-7063-5-ND	Dual Low Noise Precision Op Amp	14-SOIC	7.54	6.19	5.58			
TLC2202AID	296-7065-5-ND	Dual Low Noise Precision Op Amp	14-SOIC	6.61	5.42	4.90			
TLC2202CD	296-1807-5-ND	Dual Low Noise Precision Op Amp	14-SOIC	5.49	4.51	4.07			
TLC2202CP	296-7071-5-ND	Dual Low Noise Precision Op Amp	8-Dip	5.15	4.15	3.78			
TLC2202IP	296-7073-5-ND	Dual Low Noise Precision R/R Op Amp	8-Dip	5.39	4.34	3.95			
TLC2252AID	296-7074-5-ND	Dual Rail-to-Rail Op Amp	8-SOIC	1.82	1.47	1.32			
TLC2252AIDR	296-26729-1-ND	Dual Rail-to-Rail Op Amp*	8-SOIC	1.71	1.32	1.20			

TEXAS INSTRUMENTS		Digi+Reel® (Cont.)		AMPLIFIERS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
TLC2252AIDR	296-26729-2-ND	Dual Rail-to-Rail Op Amp*	8-SOIC	1646.00/2,500					
TLC2252AIP	296-7075-5-ND	Dual Rail-to-Rail Op Amp	8-Dip	1.51	1.22	1.10			
TLC2252AIPWR	296-7076-1-ND	Dual Rail-to-Rail Op Amp	8-TSSOP	1.71	1.32	1.20			
TLC2252AIPWR	296-7076-2-ND	Dual Rail-to-Rail Op Amp	8-TSSOP	1316.80/2,000					
TLC2252AQD	296-7077-5-ND	Dual Rail-to-Rail Op Amp	8-SOIC	1.72	1.39	1.25			
TLC2252AODR6401	296-24514-1-ND	Dual Rail-to-Rail Op Amp*	8-SOIC	1.83	1.41	1.28			
TLC2252AODR6401	296-24514-2-ND	Dual Rail-to-Rail Op Amp*	8-SOIC	1757.53/2,500					
TLC2252CD	296-7078-5-ND	Dual R/R Micropower Op Amp	8-SOIC	1.72	1.39	1.25			
TLC2252CDR	296-26730-1-ND	Dual R/R Micropower Op Amp*	8-SOIC	1.59	1.23	1.12			
TLC2252CDR	296-26730-2-ND	Dual R/R Micropower Op Amp*	8-SOIC	1534.48/2,500					
TLC2252CP	296-7079-5-ND	Dual R/R Micropower Op Amp	8-Dip	1.41	1.14	1.03			
TLC2252ID	296-7080-5-ND	Dual R/R Micropower Op Amp	8-SOIC	1.72	1.39	1.25			
TLC2252IP	296-7081-5-ND	Dual R/R Micropower Op Amp	8-Dip	1.51	1.22	1.10			
TLC2252QD	296-7082-5-ND	Dual R/R Micropower Op Amp	8-SOIC	1.61	1.31	1.18			
TLC2254AID	296-7083-5-ND	Quad Rail-to-Rail Op Amp	14-SOIC	2.30	1.86	1.68			
TLC2254AIDR	296-26731-1-ND	Quad Rail-to-Rail Op Amp*	14-SOIC	2.20	1.70	1.54			
TLC2254AIDR	296-26731-2-ND	Quad Rail-to-Rail Op Amp*	14-SOIC	2118.95/2,500					
TLC2254AIP	296-7084-5-ND	Quad Rail-to-Rail Op Amp	14-Dip	1.95	1.57	1.42			
TLC2254AIPWR	296-7085-1-ND	Quad Rail-to-Rail Op Amp	14-TSSOP	2.20	1.70	1.54			
TLC2254AIPWR	296-7085-2-ND	Quad Rail-to-Rail Op Amp	14-TSSOP	1695.16/2,000					
TLC2254AQD	296-7086-5-ND	Quad Rail-to-Rail Op Amp	14-SOIC	2.07	1.68	1.51			
TLC2254CD	296-1300-5-ND	Quad R/R Micropower Op Amp	14-SOIC	2.07	1.68	1.51			
TLC2254CDR	296-1300-1-ND	Quad R/R Micropower Op Amp	14-SOIC	2.06	1.59	1.44			
TLC2254CDR	296-1300-2-ND	Quad R/R Micropower Op Amp	14-SOIC	1979.54/2,500					
TLC2254CN	296-7088-5-ND	Quad R/R Micropower Op Amp	14-Dip	1.82	1.47	1.32			
TLC2254CPWR	296-7089-1-ND	Quad R/R Micropower Op Amp	14-TSSOP	2.06	1.59	1.44			
TLC2254CPWR	296-7089-2-ND	Quad R/R Micropower Op Amp	14-TSSOP	1584.48/2,000					
TLC2254ID	296-1301-5-ND	Quad Low Power Op Amp	14-SOIC	2.21	1.78	1.60			
TLC2254IDR	296-1301-1-ND	Quad Low Power Op Amp	14-SOIC	2.06	1.59	1.44			
TLC2254IDR	296-1301-2-ND	Quad Low Power Op Amp	14-SOIC	1979.54/2,500					
TLC2254IN	296-7090-5-ND	Quad R/R Micropower Op Amp	14-Dip	1.82	1.47	1.32			
TLC2254QD	296-7091-5-ND	Quad R/R Micropower Op Amp	14-SOIC	2.07	1.68	1.51			
TLC2262AID	296-7092-5-ND	Dual Rail-to-Rail Op Amp	8-SOIC	1.95	1.57	1.42			
TLC2262AIDR	296-26732-1-ND	Dual Rail-to-Rail Op Amp*	8-SOIC	1.79	1.39	1.26			
TLC2262AIDR	296-26732-2-ND	Dual Rail-to-Rail Op Amp*	8-SOIC	1728.61/2,500					
TLC2262AIP	296-7093-5-ND	Dual Rail-to-Rail Op Amp	8-Dip	1.59	1.29	1.16			
TLC2262AQD	296-7094-5-ND	Dual Rail-to-Rail Op Amp	8-SOIC	1.82	1.47	1.32			
TLC2262CD	296-1302-5-ND	Dual Rail-to-Rail Op Amp	8-SOIC	1.82	1.47	1.32			
TLC2262CDR	296-1302-1-ND	Dual Rail-to-Rail Op Amp	8-SOIC	1.65	1.28	1.16			
TLC2262CDR	296-1302-2-ND	Dual Rail-to-Rail Op Amp	8-SOIC	1589.21/2,500					
TLC2262CP	296-7095-5-ND	Dual Rail-to-Rail Op Amp	8-Dip	1.46	1.18	1.06			
TLC2262CPWR	296-7096-1-ND	Dual Rail-to-Rail Op Amp	8-TSSOP	1.65	1.28	1.16			
TLC2262CPWR	296-7096-2-ND	Dual Rail-to-Rail Op Amp	8-TSSOP	1272.19/2,000					
TLC2262ID	296-7097-5-ND	Dual Rail-to-Rail Op Amp	8-SOIC	1.82	1.47	1.32			
TLC2262IP	296-7098-5-ND	Dual Rail-to-Rail Op Amp	8-Dip	1.59	1.29	1.16			
TLC2262QD	296-7099-5-ND	Dual Rail-to-Rail Op Amp	8-SOIC	1.72	1.39	1.25			
TLC2264AID	296-7100-5-ND	Quad Rail-to-Rail Op Amp	14-SOIC	2.30	1.86	1.68			
TLC2264AIDR									