

TEXAS INSTRUMENTS		Digi+Reel® (Cont.)		AMPLIFIERS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
TLV2382IDR	296-12226-1-ND	2-Channel, Rail-to-Rail, I/O Op Amp	8-SOIC	2.20	1.70	1.54			
TLV2382IDR	296-12226-2-ND	2-Channel, Rail-to-Rail, I/O Op Amp	8-SOIC	2118.95/2,500					
TLV2401CDBVT	296-26791-1-ND	880nA/Ch., R/R, I/O Op Amp with Reverse Battery Protection*	SOT-23-5	2.06	1.59	1.44			
TLV2401CDBVT	296-26791-2-ND	880nA/Ch., R/R, I/O Op Amp with Reverse Battery Protection*	SOT-23-5	293.27/250					
TLV2401CDBVT	296-10530-1-ND	Micropower Op Amp	8-SOIC	1.79	1.39	1.26			
TLV2401IDBVT	296-10531-1-ND	Micropower Op Amp	SOT-23-5	2.20	1.70	1.54			
TLV2401IDBVT	296-10531-2-ND	Micropower Op Amp	SOT-23-5	313.92/250					
TLV2401IDR	296-10532-1-ND	Micropower Op Amp	8-SOIC	1.94	1.50	1.36			
TLV2401IP	296-10533-5-ND	Micropower Op Amp	8-Dip	1.72	1.39	1.25			
TLV2402CDR	296-10534-1-ND	Dual Micropower Rail-to-Rail Op Amp	8-SOIC	2.75	2.12	1.93			
TLV2402CDR	296-10534-2-ND	Dual Micropower Rail-to-Rail Op Amp	8-SOIC	2649.72/2,500					
TLV2402ID	296-26792-5-ND	880nA/Ch., R/R, I/O Op Amp with Reverse Battery Protection*	8-SOIC	2.75	2.22	2.02			
TLV2402IDGK	296-13799-5-ND	Dual Micropower Rail-to-Rail Op Amp	8-MSOP	2.75	2.22	2.02			
TLV2402IP	296-10536-5-ND	Dual Micropower Rail-to-Rail Op Amp	8-Dip	2.31	1.86	1.70			
TLV2404AIN	296-13363-5-ND	880nA/Ch., R/R, I/O Op Amp with Reverse Battery Protection	14-Dip	3.40	2.74	2.49			
TLV2404CD	296-2427-5-ND	880nA/Ch., R/R, I/O Op Amp with Reverse Battery Protection	14-SOIC	3.07	2.48	2.26			
TLV2404IN	296-10538-5-ND	880nA/Ch., R/R, I/O Op Amp with Reverse Battery Protection	14-Dip	3.30	2.66	2.43			
TLV2422AID	296-10540-5-ND	Dual Micropower Rail-to-Rail Op Amp	8-SOIC	2.30	1.86	1.68			
TLV2422CD	296-10541-5-ND	Dual Micropower Rail-to-Rail Op Amp	8-SOIC	2.54	2.05	1.87			
TLV2422ID	296-10543-5-ND	Dual Micropower Rail-to-Rail Op Amp	8-SOIC	2.54	2.05	1.87			
TLV2422QD	296-10544-5-ND	Dual Micropower Rail-to-Rail Op Amp	8-SOIC	2.43	1.96	1.78			
TLV2423AID	296-10545-5-ND	Dual Micropower Rail-to-Rail Op Amp	8-SOIC	2.30	1.86	1.68			
TLV2423AQD	296-10547-5-ND	Dual Micropower Rail-to-Rail Op Amp	8-SOIC	2.07	1.68	1.51			
TLV2432CD	296-10548-5-ND	Dual Micropower Rail-to-Rail Op Amp	8-SOIC	1.72	1.39	1.25			
TLV2432ID	296-10549-5-ND	Dual Micropower Rail-to-Rail Op Amp	8-SOIC	1.72	1.39	1.25			
TLV2432QD	296-10550-5-ND	Dual Micropower Rail-to-Rail Op Amp	8-SOIC	1.59	1.29	1.16			
TLV2434AIPWR	296-10551-1-ND	Quad R/R Micropower Op Amp	14-TSSOP	2.60	2.13	1.91			
TLV2434AIPWR	296-10551-2-ND	Quad R/R Micropower Op Amp	14-TSSOP	2308.12/2,000					
TLV2434CD	296-10552-5-ND	Quad R/R Micropower Op Amp	14-SOIC	2.64	2.12	1.94			
TLV2434CPW	296-10553-5-ND	Quad R/R Micropower Op Amp	14-TSSOP	2.64	2.12	1.94			
TLV2434IDR	296-10554-1-ND	Quad R/R Micropower Op Amp	14-SOIC	2.48	2.03	1.82			
TLV2434IDR	296-10554-2-ND	Quad R/R Micropower Op Amp	14-SOIC	2746.78/2,500					
TLV2442AIDR	296-10556-1-ND	Dual, Rail-to-Rail Op Amp	8-SOIC	2.06	1.59	1.44			
TLV2442AQD	296-10557-5-ND	Dual, Rail-to-Rail Op Amp	8-SOIC	1.95	1.57	1.42			
TLV2442AQPW	296-10558-5-ND	Dual, Rail-to-Rail Op Amp	8-SOP	1.95	1.57	1.42			
TLV2442CD	296-10559-5-ND	Dual, Rail-to-Rail Op Amp	8-SOIC	1.72	1.39	1.25			
TLV2442ID	296-10560-5-ND	Dual, Rail-to-Rail Op Amp	8-SOIC	1.72	1.39	1.25			
TLV2442QD	296-10561-5-ND	Dual, Rail-to-Rail Op Amp	8-SOIC	1.59	1.29	1.16			
TLV2442QDGKRQ1	296-24925-1-ND	Dual, Rail-to-Rail Op Amp*	8-MSOP	1.79	1.39	1.26			
TLV2442QDGKRQ1	296-24925-2-ND	Dual, Rail-to-Rail Op Amp*	8-MSOP	1728.61/2,500					
TLV2442QDWP	296-10562-5-ND	Dual, Rail-to-Rail Op Amp	8-TSSOP	1.59	1.29	1.16			
TLV2444CD	296-10564-5-ND	Quad, Rail-to-Rail Op Amp	14-SOIC	2.52	2.03	1.85			
TLV2444CPW	296-10565-5-ND	Quad, Rail-to-Rail Op Amp	14-TSSOP	2.52	2.03	1.85			
TLV2450AID	296-10568-5-ND	Single, Rail-to-Rail Op Amp	8-SOIC	2.31	1.86	1.70			
TLV2450AIP	296-10569-5-ND	Single, Rail-to-Rail Op Amp	8-Dip	1.18	1.76	1.58			
TLV2450CD	296-1884-5-ND	Low Power Rail-to-Rail Op Amp	8-SOIC	1.59	1.29	1.16			
TLV2450CDBVR	296-10570-1-ND	Single, Rail-to-Rail Op Amp	SOT-23-6	1.79	1.39	1.26			
TLV2450CDBVR	296-10570-2-ND	Single, Rail-to-Rail Op Amp	SOT-23-6	2074.34/3,000					
TLV2450CP	296-1885-5-ND	Low Power Rail-to-Rail Op Amp	8-Dip	1.59	1.29	1.16			
TLV2450ID	296-1886-5-ND	Low Power Rail-to-Rail Op Amp	8-SOIC	1.59	1.29	1.16			
TLV2450IP	296-1887-5-ND	Low Power Rail-to-Rail Op Amp	8-Dip	1.37	1.11	1.00			
TLV2451AID	296-10572-5-ND	Single, Rail-to-Rail Op Amp	8-SOIC	2.44	1.97	1.77			
TLV2451AIDR	296-10572-1-ND	Single, Rail-to-Rail Op Amp	8-SOIC	2.31	1.79	1.62			
TLV2451AIDR	296-10572-2-ND	Single, Rail-to-Rail Op Amp	8-SOIC	2230.47/2,500					
TLV2451AIP	296-10573-5-ND	Single, Rail-to-Rail Op Amp	8-Dip	2.05	1.66	1.49			
TLV2451CD	296-1888-5-ND	Low Power Rail-to-Rail Op Amp	8-SOIC	1.72	1.39	1.25			
TLV2451CDBVT	296-26793-1-ND	23-µA, 220kHz R/R I/O Op Amp*	SOT-23-5	1.79	1.39	1.26			
TLV2451CDBVT	296-26793-2-ND	23-µA, 220kHz R/R I/O Op Amp*	SOT-23-5	256.09/250					
TLV2451CP	296-1889-5-ND	Low Power Rail-to-Rail Op Amp	8-Dip	1.26	1.02	0.92			
TLV2451ID	296-1890-5-ND	Low Power Rail-to-Rail Op Amp	8-SOIC	1.72	1.39	1.25			
TLV2451IDBVR	296-10576-1-ND	Single, Rail-to-Rail Op Amp	SOT-23-5	1.65	1.28	1.16			
TLV2451IDBVR	296-10576-2-ND	Single, Rail-to-Rail Op Amp	SOT-23-5	1908.29/3,000					
TLV2451IP	296-1891-5-ND	Low Power Rail-to-Rail Op Amp	8-Dip	1.46	1.18	1.06			
TLV2452AIDR	296-10578-1-ND	Dual, Rail-to-Rail Op Amp	8-SOP	2.49	1.92	1.75			
TLV2452AIDR	296-10578-2-ND	Dual, Rail-to-Rail Op Amp	8-SOP	2397.76/2,500					
TLV2452AIP	296-10579-5-ND	Dual, Rail-to-Rail Op Amp	8-Dip	2.21	1.78	1.60			
TLV2452CD	296-2428-5-ND	Dual, Rail-to-Rail Op Amp	8-SOIC	2.44	1.97	1.77			
TLV2452CDR	296-2428-1-ND	Dual, Rail-to-Rail Op Amp	8-SOIC	2.20	1.70	1.54			
TLV2452CDR	296-2428-2-ND	Dual, Rail-to-Rail Op Amp	8-SOIC	2118.95/2,500					
TLV2452CDGKR	296-10580-1-ND	Dual, Rail-to-Rail Op Amp	8-MSOP	2.20	1.70	1.54			
TLV2452CDGKR	296-10580-2-ND	Dual, Rail-to-Rail Op Amp	8-MSOP	2118.95/2,500					
TLV2452IDR	296-10583-1-ND	Dual, Rail-to-Rail Op Amp	8-SOIC	2.35	1.81	1.64			
TLV2452IDR	296-10583-2-ND	Dual, Rail-to-Rail Op Amp	8-SOIC	2259.38/2,500					
TLV2452IP	296-10584-5-ND	Dual, Rail-to-Rail Op Amp	8-Dip	2.07	1.68	1.51			
TLV2453AIN	296-10586-5-ND	Dual, Rail-to-Rail Op Amp	14-Dip	2.78	2.24	2.04			
TLV2453CD	296-2429-5-ND	Dual, Rail-to-Rail Op Amp	14-SOIC	2.31	1.86	1.70			
TLV2453IN	296-10591-5-ND	Dual, Rail-to-Rail Op Amp	14-Dip	2.30	1.86	1.68			
TLV2454AID	296-10592-5-ND	Quad, Rail-to-Rail Op Amp	14-SOIC	2.96	2.38	2.17			
TLV2454AIDR	296-10592-1-ND	Quad, Rail-to-Rail Op Amp	14-SOIC	2.70	2.21	1.99			
TLV2454AIN	296-10593-5-ND	Quad, Rail-to-Rail Op Amp	14-Dip	2.52	2.03	1.85			
TLV2454AIPWR	296-10594-1-ND	Quad, Rail-to-Rail Op Amp	14-TSSOP	2.70	2.21	1.99			
TLV2454AIPWR	296-10594-2-ND	Quad, Rail-to-Rail Op Amp	14-TSSOP	2395.69/2,000					
TLV2454CD	296-2430-5-ND	Quad, Rail-to-Rail Op Amp	14-SOIC	2.31	1.86	1.70			
TLV2454CD	296-10595-5-ND	Quad, Rail-to-Rail Op Amp	14-Dip	2.31	1.86	1.70			
TLV2454ID	296-10596-5-ND	Quad, Rail-to-Rail Op Amp	14-SOIC	2.87	2.31	2.10			
TLV2454IDR	296-10597-1-ND	Quad, Rail-to-Rail Op Amp	14-SOIC	2.60	2.13	1.91			
TLV2454IDR	296-10597-2-ND	Quad, Rail-to-Rail Op Amp	14-SOIC	2885.15/2,500					
TLV2454IN	296-10598-5-ND	Quad, Rail-to-Rail Op Amp	14-Dip	2.43	1.96	1.78			
TLV2455AID	296-10600-5-ND	Quad, Rail-to-Rail Op Amp	16-SOIC	3.30	2.66	2.43			
TLV2455AIN	296-10601-5-ND	Quad, Rail-to-Rail Op Amp	16-Dip	2.75	2.22	2.02			
TLV2455AIPWR	296-10602-1-ND	Quad, Rail-to-Rail Op Amp	16-TSSOP	2.95	2.41	2.17			
TLV2455CD	296-2431-5-ND	Quad, Rail-to-Rail Op Amp	16-SOIC	3.35	2.70	2.46			
TLV2455CN	296-10603-5-ND	Quad, Rail-to-Rail Op Amp	16-Dip	3.35	2.70	2.46			
TLV2455ID	296-10605-5-ND	Quad, Rail-to-Rail Op Amp	16-SOIC	4.16	3.35	3.05			
TLV2455IN	296-10606-5-ND	Quad, Rail-to-Rail Op Amp	16-Dip	4.47	2.79	2.55			
TLV2460AIP	296-7478-5-ND	LP R/R I/O Op Amp with Shutdown	8-Dip	2.18	1.76	1.58			

TEXAS INSTRUMENTS		Digi+Reel® (Cont.)		AMPLIFIERS			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
TLV2460CD	296-2432-5-ND	LP R/R I/O Op Amp with Shutdown	8-SOIC	1.82	1.47	1.32			
TLV2460CDBVR	296-7479-1-ND	LP R/R I/O Op Amp with Shutdown	SOT-23-6	1.79	1.39	1.26			
TLV2460CDBVR	296-7479-2-ND	LP R/R I/O Op Amp with Shutdown	SOT-23-6	2074.34/3,000					
TLV2460CP	296-7480-5-ND	LP R/R I/O Op Amp with Shutdown	8-Dip	1.59	1.29	1.16			
TLV2460IDBVR	296-7481-1-ND	LP R/R I/O Op Amp with Shutdown	SOT-23-6	1.79	1.39	1.26			
TLV2460IDBVR	296-7481-2-ND	LP R/R I/O Op Amp with Shutdown	SOT-23-6	2074.34/3,000					
TLV2460IDBVT	296-26794-1-ND	LP R/R I/O Op Amp with SD*	SOT-23-6	2.06	1.59	1.44			
TLV2460IDBVT	296-26794-2-ND	LP R/R I/O Op Amp with SD*	SOT-23-6	293.27/250					
TLV2460IDR	296-7482-1-ND	LP R/R I/O Op Amp with Shutdown	8-SOIC	1.79	1.39	1.26			
TLV2460IDR	296-7482-2-ND	LP R/R I/O Op Amp with Shutdown	8-SOIC	1728.61/2,500					
TLV2460IP	296-7483-5-ND	LP R/R I/O Op Amp with Shutdown	8-Dip	1.59	1.29	1.16			
TLV2461AIDR	296-7484-1-ND	LP R/R I/O Op Amp with Shutdown	8-SOIC	2.31	1.79	1.62			
TLV2461AIDR	296-7484-2-ND	LP R/R I/O Op Amp with Shutdown	8-SOIC	2230.47/2,500					
TLV2461AIP	296-7485-5-ND</								