

TEXAS INSTRUMENTS		Digi+Reel® (Cont.)		RoHS Compliant Parts Available		CCD	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
VSP2262Y	VSP2262Y-ND	12-Bit, 20MHz, Digital Camera CCD Signal Processor	48-LQFP	17.28	14.69	13.61	
VSP2262Y2K	VSP2262YTR-ND	12-Bit, 20MHz, Digital Camera CCD Signal Processor	48-LQFP	21962.69/2,000			
VSP2270Y	296-12541-ND	28MHz CCD Signal Processor	48-LQFP	15.90	13.38	12.29	
VSP2272Y	296-12542-ND	28MHz CCD Signal Processor	48-LQFP	21.31	18.12	16.79	
VSP2560PTR	296-23846-1-ND	10-Bit CCD Analog Front End for Digital Camera	48-LQFP	8.43	7.00	6.37	
VSP2562PT	296-23847-ND	12-Bit CCD Analog Front End for Digital Camera	48-LQFP	10.27	8.64	7.94	
VSP2566PT	296-23848-ND	16-Bit CCD Analog Front End for Digital Camera	48-LQFP	18.01	15.31	14.19	
VSP2582RHN	296-23849-ND	CCD Analog Front End for Digital Camera	36-QFN	7.85	6.44	5.81	
VSP2590ZWR	296-24637-1-ND	16-Bit, 41.5MHz, Analog Front-End*	159-NFBGA	29.74	26.77	24.54	
VSP2590ZWR	296-24637-2-ND	16-Bit, 41.5MHz, Analog Front-End*	159-NFBGA	19330.74/1,000			
VSP3010Y	VSP3010Y-ND	12-Bit, CCD/CIS Controller	48-LQFP	16.72	14.07	12.93	
VSP3100Y	VSP3100Y-ND	14-Bit 10MHz CCD/CIS Signal Processor	48-LQFP	14.54	12.23	11.24	
VSP3200Y	VSP3200Y-ND	16-Bit, CCD/CIS Processor	48-LQFP	14.54	12.23	11.24	
VSP3200Y2K	VSP3200YTR-ND	16-Bit, CCD/CIS Processor	48-LQFP	12477.41/2,000			
VSP3210Y	VSP3210Y-ND	16-Bit, CCD/CIS Processor	48-LQFP	17.36	14.60	13.42	
VSP3210Y2K	VSP3210YTR-ND	16-Bit, CCD/CIS Processor	48-LQFP	15596.77/2,000			
VSP5000PM	296-14235-5-ND	12-Bit, 30MHz CCD Signal Front End	64-LQFP	19.83	16.86	15.62	
VSP5010PMR	296-24686-1-ND	12-Bit, CCD Analog Front End*	64-LQFP	19.58	17.63	16.16	
VSP5010PMR	296-24686-2-ND	12-Bit, CCD Analog Front End*	64-LQFP	12726.07/1,000			

TEXAS INSTRUMENTS		Digi+Reel®		RoHS Compliant Parts Available		COMPARATORS	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
<b>General Purpose Comparators</b>							
L293DNE	296-9518-5-ND	Quad Half-H Drivers	16-Dip	2.89	2.33	2.12	
L293DNE	296-9519-5-ND	Quad Half-H Drivers	16-Dip	2.89	2.33	2.12	
LM139DGA	296-22032-5-ND	Quad Differential Comparator	14-SOIC	1.37	1.10	97	
LM239DR	296-14590-1-ND	Quad Differential Comparator	14-SOIC	4.5	3.0	25	
LM239DR	296-14590-2-ND	Quad Differential Comparator	14-SOIC	256.16/2,500			
LM293AD	296-9530-5-ND	Dual Differential Comparator	8-SOIC	36	27	23	
LM293D	296-9531-5-ND	Dual Differential Comparator	8-SOIC	47	31	26	
LM293DR	296-12848-1-ND	Dual Differential Comparator	8-SOIC	4.5	3.0	24	
LM293DR	296-12848-2-ND	Dual Differential Comparator	8-SOIC	251.96/2,500			
LM293P	296-9532-5-ND	Dual Differential Comparator	8-Dip	42	29	23	
LM339AD	296-6604-5-ND	Quad Differential Comparator	14-SOIC	40	27	22	
LM339ADR	296-6604-1-ND	Quad Differential Comparator	14-SOIC	38	26	21	
LM339ADR	296-6604-2-ND	Quad Differential Comparator	14-SOIC	218.92/2,500			
LM339AN	296-6605-5-ND	Quad Differential Comparator	14-Dip	44	30	24	
LM339APWR	296-18454-1-ND	Quad Differential Comparator	14-TSSOP	42	28	23	
LM339APWR	296-18454-2-ND	Quad Differential Comparator	14-TSSOP	191.66/2,000			
LM339D	296-1013-5-ND	Quad Differential Comparator	14-SOIC	39	26	22	
LM339DR	296-1013-1-ND	Quad Differential Comparator	14-SOIC	36	24	20	
LM339DR	296-1013-2-ND	Quad Differential Comparator	14-SOIC	208.59/2,500			
LM339DRBR	296-6606-1-ND	Quad Differential Comparator	14-SSOP	39	26	21	
LM339DRBR	296-6606-2-ND	Quad Differential Comparator	14-SSOP	176.79/2,000			
LM339N	296-1393-5-ND	Quad Differential Comparator	14-Dip	42	29	23	
LM339PWR	296-6607-1-ND	Quad Diff. Comparator, A Grade	14-TSSOP	40	27	22	
LM339PWR	296-6607-2-ND	Quad Diff. Comparator, A Grade	14-TSSOP	183.39/2,000			
LM393AD	296-6608-5-ND	Dual Diff. Comparator, A Grade	8-SOIC	38	25	21	
LM393ADGKR	296-16807-1-ND	Dual Diff. Comparator, A Grade	8-MSSOP	52	31	25	
LM393ADGKR	296-16807-2-ND	Dual Diff. Comparator, A Grade	8-MSSOP	218.92/2,500			
LM393ADR	296-14605-1-ND	Dual Diff. Comparator, A Grade	8-SOIC	52	31	25	
LM393ADR	296-14605-2-ND	Dual Diff. Comparator, A Grade	8-SOIC	218.92/2,500			
LM393AP	296-6609-5-ND	Dual Diff. Comparator, A Grade	8-Dip	40	27	22	
LM393APWR	296-6610-1-ND	Dual Diff. Comparator, A Grade	8-TSSOP	52	31	25	
LM393APWR	296-6610-2-ND	Dual Diff. Comparator, A Grade	8-TSSOP	175.13/2,000			
LM393D	296-1015-5-ND	Dual Differential Comparator	8-SOIC	36	24	20	
LM393DGKR	296-16808-1-ND	Dual Differential Comparator	8-MSSOP	49	29	24	
LM393DGKR	296-16808-2-ND	Dual Differential Comparator	8-MSSOP	208.59/2,500			
LM393DR	296-1015-1-ND	Dual Differential Comparator	8-SOIC	49	29	24	
LM393DR	296-1015-2-ND	Dual Differential Comparator	8-SOIC	208.59/2,500			
LM393P	296-1398-5-ND	Dual Differential Comparator	8-Dip	39	26	21	
LM393PSR	296-9566-1-ND	Dual Differential Comparator	8-SOP	37	25	20	
LM393PSR	296-9566-2-ND	Dual Differential Comparator	8-SOP	168.52/2,000			
LM393PWR	296-14607-1-ND	Dual Differential Comparator	8-TSSOP	38	26	21	
LM393PWR	296-14607-2-ND	Dual Differential Comparator	8-TSSOP	175.13/2,000			
LM2901AVDRG4Q1	296-24703-1-ND	Quad Differential Comp.*	14-SOIC	59	46	40	
LM2901AVDRG4Q1	296-24703-2-ND	Quad Differential Comp.*	14-SOIC	481.20/2,500			
LM2901AVDRQ1	296-18437-1-ND	Quad Differential Comparator	14-SOIC	59	46	40	
LM2901AVDRQ1	296-18437-2-ND	Quad Differential Comparator	14-SOIC	481.20/2,500			
LM2901AVOPWR	296-21575-1-ND	Quad Differential Comparator	14-TSSOP	57	45	39	
LM2901AVOPWR	296-21575-2-ND	Quad Differential Comparator	14-TSSOP	376.70/2,000			
LM2901AVOPWRG4Q1	296-23883-1-ND	Quad Differential Comparator	14-TSSOP	59	46	40	
LM2901AVOPWRG4Q1	296-23883-2-ND	Quad Differential Comparator	14-TSSOP	384.96/2,000			
LM2901D	296-1385-5-ND	Quad Diff. Comparator, Ind. Temp.	14-SOIC	44	30	24	
LM2901DR	296-14593-1-ND	Quad Diff. Comparator, Ind. Temp.	14-SOIC	40	27	22	
LM2901DR	296-14593-2-ND	Quad Diff. Comparator, Ind. Temp.	14-SOIC	231.31/2,500			
LM2901N	296-1386-5-ND	Quad Diff. Comparator, Ind. Temp.	14-Dip	45	30	24	
LM2901PWR	296-6597-1-ND	Quad Diff. Comparator, Ind. Temp.	14-TSSOP	40	27	22	
LM2901PWR	296-6597-2-ND	Quad Diff. Comparator, Ind. Temp.	14-TSSOP	185.05/2,000			
LM2901QDRG4Q1	296-24704-1-ND	Quad Differential Comp.*	14-SOIC	50	36	31	
LM2901QDRG4Q1	296-24704-2-ND	Quad Differential Comp.*	14-SOIC	355.22/2,500			
LM2901QDRQ1	296-17157-1-ND	Quad Diff. Comparator, Ind. Temp	14-SOIC	50	36	31	
LM2901QDRQ1	296-17157-2-ND	Quad Diff. Comparator, Ind. Temp	14-SOIC	355.22/2,500			
LM2901QPWRQ1	296-18438-1-ND	Quad Differential Comparator	14-TSSOP	50	36	31	
LM2901QPWRQ1	296-18438-2-ND	Quad Differential Comparator	14-TSSOP	284.18/2,000			
LM2901VQPPWRG4	296-22033-1-ND	Quad Differential Comparator	14-TSSOP	58	41	35	
LM2901VQPPWRG4	296-22033-2-ND	Quad Differential Comparator	14-TSSOP	325.48/2,000			
LM2901VQPPWRG4Q1	296-25458-1-ND	Quad Diff. Comparator*	14-TSSOP	59	42	36	
LM2901VQPPWRG4Q1	296-25458-2-ND	Quad Diff. Comparator*	14-TSSOP	335.40/2,000			
LM2901VQPPWRQ1	296-21229-1-ND	Quad Differential Comparator	14-TSSOP	59	42	36	
LM2901VQPPWRQ1	296-21229-2-ND	Quad Differential Comparator	14-TSSOP	335.40/2,000			
LM2903AVDRQ1	296-18444-1-ND	Dual Differential Comparator	8-SOIC	37	45	39	
LM2903AVDRQ1	296-18444-2-ND	Dual Differential Comparator	8-SOIC	470.88/2,500			
LM2903AVOPWRG4Q1	296-25109-1-ND	Dual Diff. Comparator*	8-TSSOP	59	46	40	
LM2903AVOPWRG4Q1	296-25109-2-ND	Dual Diff. Comparator*	8-TSSOP	384.96/2,000			

TEXAS INSTRUMENTS		Digi+Reel® (Cont.)		RoHS Compliant Parts Available		COMPARATORS	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
LM2903D	296-1012-5-ND	Dual Diff. Comparator, Ind. Temp.	8-SOIC	42	28	23	
LM2903DGKR	296-16806-1-ND	Dual Diff. Comparator, Ind. Temp.	8-MSSOP	39.26/21			
LM2903DGKR	296-16806-2-ND	Dual Diff. Comparator, Ind. Temp.	8-MSSOP	220.98/2,500			
LM2903DR	296-1012-1-ND	Dual Diff. Comparator, Ind. Temp.	8-SOIC	39.26/21			
LM2903DR	296-1012-2-ND	Dual Diff. Comparator, Ind. Temp.	8-SOIC	220.98/2,500			
LM2903P	296-6601-5-ND	Dual Diff. Comparator, Ind. Temp.	8-Dip	43	29	24	
LM2903PSR	296-17322-1-ND	Dual Diff. Comparator, Ind. Temp.	8-SOP	43	29	24	
LM2903PSR	296-17322-2-ND	Dual Diff. Comparator, Ind. Temp.	8-SOP	196.61/2,000			
LM2903PWR	296-6602-1-ND	Dual Diff. Comparator, Ind. Temp.	8-TSSOP	39	26	21	
LM2903PWR	296-6602-2-ND	Dual Diff. Comparator, Ind. Temp.	8-TSSOP	176.79/2,000			
LM2903QDRG4	296-22034-1-ND	Dual Diff. Comparator, Ind. Temp.	8-SOIC	49	35	30	
LM2903QDRG4	296-22034-2-ND	Dual Diff. Comparator, Ind. Temp.	8-SOIC	342.83/2,500			
LM2903QDRG4Q1	296-24706-1-ND	Dual Diff. Comparator*	8-SOIC	50	36	31	
LM2903QDRG4Q1	296-24706-2-ND	Dual Diff. Comparator*	8-SOIC	355.22/2,500			
LM2903QDRQ1	296-15183-1-ND	Dual Diff. Comparator, Ind. Temp.	8-SOIC	50	36	31	
LM2903QDRQ1	296-15183-2-ND	Dual Diff. Comparator, Ind. Temp.	8-SOIC	355.22/2,500			
LM2903QDRQ1	296-19541-1-ND	Dual Differential Comparator	8-SOIC	59	42	36	
LM2903QDRQ1	296-19541-2-ND	Dual Differential Comparator	8-SOIC	419.25/2,500			
LM3302D	296-9546-5-ND	Quad Differential Comparator	14-SOIC	79	62	54	
LM3302DR	296-14598-1-ND	Quad Differential Comparator	14-SOIC	73	57	50	
LM3302N	296-17223-5-ND	Quad Differential Comparator	14-Dip	73	57	50	
LMV331QDBVRQ1	296-24709-1-ND	Single Low Voltage Comp.*	SOT-23-5	71	56	49	
LMV331QDBVRQ1	296-24709-2-ND	Single Low Voltage Comp.*	SOT-23-5	703.84/3,000			
LMV3391DR	296-6611-1-ND	Quad Low Voltage Comparator	14-SOIC	82	65	58	
LMV3391DR	296-6611-2-ND	Quad Low Voltage Comparator	14-SOIC	751.75/2,500			
LMV3391PWR	296-6612-1-ND	Quad Low Voltage Comparator	14-TSSOP	82	65	58	
LMV3391PWR	296-6612-2-ND	Quad Low Voltage Comparator	14-TSSOP	601.40/2,000			
TL3311DBVR	296-10168-1-ND	Single Differential Comparator	SOT-23-5	59	42	36	
TL3311DBVR	296-10168-2-ND	Single Differential Comparator	SOT-23-5	500.62/3,000			
TL3311KDBVR	296-23863-1-ND	Single Differential Comparator	SOT-23-5	59	42	36	
TL3311KDBVR	296-23863-2-ND	Single Differential Comparator	SOT-23-5	500.62/3,000			
TL3372CD	296-1327-5-ND	Dual Differential Comparator	8-SOIC	1.00	81	71	
TL3372CDR	296-1327-1-ND	Dual Differential Comparator	8-SOIC	90	72	65	
TL3372CDR	296-1327-2-ND	Dual Differential Comparator	8-SOIC	832.30/2,500			
TL3372CP	296-1845-5-ND	Dual Differential Comparator	8-Dip	83	67	59	
TL3372CPWR	296-10309-1-ND	Dual Differential Comparator	8-TSSOP	90	72	65	
TL3372CPWR	296-10309-2-ND	Dual Differential Comparator	8-TSSOP	665.84/2,000			
TL3372ID	296-10310-5-ND	Dual Differential Comparator	8-SOIC	108	87	76	
TL3372IP	296-1846-5-ND	Dual Differential Comparator	8-Dip	92	74	65	
TL3372MD	296-10311-5-ND	Dual Differential Comparator	8-SOIC	108	87	76	
TL3372OD	296-10312-5-ND	Dual Differential Comparator	8-SOIC	96	77	67	
TL3372ODRG4	296-22049-1-ND	Dual Differential Comparator	8-SOIC	104	83	74	
TL3372ODRG4	296-22049-2-ND	Dual Differential Comparator	8-SOIC	956.21/2,500			
TL3374CN	296-10313-5-ND	Quad Differential Comparator	14-Dip	104	84	73	
TL3374ID	296-10315-5-ND	Quad Differential Comparator	14-SOIC	128	104	93	
TL3374IN	296-10316-5-ND	Quad Differential Comparator	14-Dip	115	92	81	
TL3374MD	296-10317-5-ND	Quad Differential Comparator	14-SOIC	128	104	93	
TLV7211AIDBVR	296-21866-1						