

TEXAS INSTRUMENTS		Digi+Reel® (Cont.)		DATA CONVERSION			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
TLV5608IPW	296-3037-5-ND	10-Bit, 1/3µs, 2.7V-5.5V Octal Serial DAC	20-TSSOP	10.19	8.58	7.88			
TLV5610IDW	296-3038-5-ND	12-Bit, 1/3µs, 2.7V-5.5V Octal Serial DAC	20-SOIC	19.86	16.89	15.64			
TLV5610IPW	296-3039-5-ND	12-Bit, 1/3µs, 2.7V-5.5V Octal Serial DAC	20-TSSOP	19.86	16.89	15.64			
TLV5610IYE	296-17097-ND	12-Bit, 1/3µs, 2.7V-5.5V Octal Serial DAC	20-WCSP	19.07	16.21	15.02			
TLV5613CDW	296-2299-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-SOIC	6.48	5.32	4.80			
TLV5613CPW	296-1918-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-TSSOP	6.48	5.32	4.80			
TLV5613IDW	296-1919-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-SOIC	8.24	6.76	6.10			
TLV5613IPW	296-1920-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-TSSOP	8.24	6.76	6.10			
TLV5614CD	296-2300-5-ND	12-Bit, 3µs, 2.7V-5.5V Quad Serial DAC	16-SOIC	16.07	13.51	12.42			
TLV5614CPW	296-3040-5-ND	12-Bit, 3µs, 2.7V-5.5V Quad Serial DAC	16-TSSOP	17.74	15.09	13.98			
TLV5614ID	296-1921-5-ND	12-Bit, 3µs, 2.7V-5.5V Quad Serial DAC	16-SOIC	18.84	16.01	14.84			
TLV5614IPW	296-1922-5-ND	12-Bit, 3µs, 2.7V-5.5V Quad Serial DAC	16-TSSOP	18.84	16.01	14.84			
TLV5614IYE	296-25178-ND	12-Bit, 3µs, 2.7V-5.5V Quad Serial DAC*	16-WCSP	17.27	14.68	13.60			
TLV5616CD	296-2301-5-ND	12-Bit, 3µs, 2.7V-5.5V Quad Serial DAC	8-SOIC	7.85	6.44	5.81			
TLV5616CDR	296-2301-1-ND	12-Bit, 3µs, 2.7V-5.5V Quad Serial DAC	8-SOIC	6.87	5.71	5.19			
TLV5616CP	296-3041-5-ND	12-Bit, 3µs, 2.7V-5.5V Quad Serial DAC	8-Dip	6.48	5.32	4.80			
TLV5616ID	296-1923-5-ND	12-Bit, 3µs, 2.7V-5.5V Quad Serial DAC	8-SOIC	8.24	6.76	6.10			
TLV5616IDR	296-1923-1-ND	12-Bit, 3µs, 2.7V-5.5V Quad Serial DAC	8-SOIC	7.29	6.06	5.51			
TLV5616IDGK	296-3042-5-ND	12-Bit, 3µs, 2.7V-5.5V Quad Serial DAC	8-MSOP	8.24	6.76	6.10			
TLV5617ACD	296-2302-5-ND	10-Bit, 2.5µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	5.39	4.42	3.99			
TLV5617AID	296-3043-5-ND	10-Bit, 2.5µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	5.70	4.68	4.22			
TLV5618ACD	296-2303-5-ND	12-Bit, 2.5µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	10.62	8.93	8.21			
TLV5618AID	296-3044-5-ND	12-Bit, 2.5µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	11.30	9.51	8.74			
TLV5618AIP	296-10735-5-ND	12-Bit, 2.5µs, 2.7V-5.5V Dual Serial DAC	8-Dip	9.42	7.92	7.28			
TLV5618AMDREP	296-21259-1-ND	12-Bit, 2.5µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	14.06	11.93	11.01			
TLV5618AQD	296-2304-5-ND	12-Bit, 2.5µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	10.89	9.16	8.42			
TLV5619CDW	296-1924-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-SOIC	9.81	8.05	7.26			
TLV5619CPW	296-1925-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-TSSOP	9.81	8.05	7.26			
TLV5619IDW	296-3045-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-SOIC	9.16	7.71	7.08			
TLV5619IPW	296-2305-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-TSSOP	9.16	7.71	7.08			
TLV5620CD	296-3047-5-ND	8-Bit, 10µs, 2.7V-5.25V Quad Serial DAC	14-SOIC	2.64	2.12	1.94			
TLV5620CN	296-2306-5-ND	8-Bit, 10µs, 2.7V-5.25V Quad Serial DAC	14-Dip	2.52	2.03	1.85			
TLV5620ID	296-3048-5-ND	8-Bit, 10µs, 2.7V-5.25V Quad Serial DAC	14-SOIC	2.87	2.31	2.10			
TLV5620IN	296-3049-5-ND	8-Bit, 10µs, 2.7V-5.25V Quad Serial DAC	14-Dip	2.75	2.22	2.02			
TLV5621ID	296-2307-5-ND	8-Bit, 10µs, 2.7V-5.25V Quad Serial DAC	14-SOIC	5.50	4.43	4.04			
TLV5623CD	296-2308-5-ND	8-Bit, 3µs, 2.7V-5.5V Single Serial DAC	8-SOIC	2.64	2.12	1.94			
TLV5623CDGK	296-3051-5-ND	8-Bit, 3µs, 2.7V-5.5V Single Serial DAC	8-MSOP	2.64	2.12	1.94			
TLV5623ID	296-3052-5-ND	8-Bit, 3µs, 2.7V-5.5V Single Serial DAC	8-SOIC	2.87	2.31	2.10			
TLV5623IDGK	296-3053-5-ND	8-Bit, 3µs, 2.7V-5.5V Single Serial DAC	8-MSOP	2.87	2.31	2.10			
TLV5624CD	296-2309-5-ND	8-Bit, 1.0-3.5µs, 2.7V-5.5V Single Serial DAC	8-SOIC	3.52	2.83	2.58			
TLV5624ID	296-3054-5-ND	8-Bit, 1.0-3.5µs, 2.7V-5.5V Single Serial DAC	8-SOIC	4.51	3.63	3.31			
TLV5624IDGK	296-3055-5-ND	8-Bit, 1.0-3.5µs, 2.7V-5.5V Single Serial DAC	8-MSOP	4.51	3.63	3.31			
TLV5625CD	296-2310-5-ND	8-Bit, 3 or 10µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	4.51	3.63	3.31			
TLV5625ID	296-3056-5-ND	8-Bit, 3 or 10µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	4.83	3.89	3.54			
TLV5626CD	296-2311-5-ND	8-Bit, 1µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	5.06	4.08	3.71			
TLV5626ID	296-3057-5-ND	8-Bit, 1µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	5.27	4.24	3.87			
TLV5627CD	296-2312-5-ND	8-Bit, 3µs, 2.7V-5.5V Quad Serial DAC	16-SOIC	5.50	4.43	4.04			
TLV5627ID	296-3058-5-ND	8-Bit, 3µs, 2.7V-5.5V Quad Serial DAC	16-SOIC	4.83	3.89	3.54			
TLV5627IPW	296-3059-5-ND	8-Bit, 3µs, 2.7V-5.5V Quad Serial DAC	16-TSSOP	5.20	4.27	3.86			
TLV5628CDW	296-3060-5-ND	8-Bit, 10µs, 2.7V-5.5V Octal Serial DAC	16-SOIC	5.31	4.36	3.93			
TLV5628CN	296-2313-5-ND	8-Bit, 10µs, 2.7V-5.5V Octal Serial DAC	16-Dip	5.06	4.08	3.71			
TLV5628IDW	296-3061-5-ND	8-Bit, 10µs, 2.7V-5.5V Octal Serial DAC	16-SOIC	5.60	4.59	4.15			
TLV5628IN	296-3062-5-ND	8-Bit, 10µs, 2.7V-5.5V Octal Serial DAC	16-Dip	5.50	4.43	4.04			
TLV5629IDW	296-3063-5-ND	8-Bit, 1/3µs, 2.7V-5.5V Octal Serial DAC	20-SOIC	7.46	6.12	5.52			

TEXAS INSTRUMENTS		Digi+Reel® (Cont.)		DATA CONVERSION			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
TLV5629IPW	296-3064-5-ND	8-Bit, 1/3µs, 2.7V-5.5V Octal Serial DAC	20-TSSOP	7.46	6.12	5.52			
TLV5630IDW	296-3065-5-ND	12-Bit, 1/3µs, 2.7V-5.5V Octal Serial DAC	20-SOIC	17.43	14.82	13.73			
TLV5630IPW	296-3066-5-ND	12-Bit, 1/3µs, 2.7V-5.5V Octal Serial DAC	20-TSSOP	20.57	17.49	16.20			
TLV5631IDW	296-3067-5-ND	10-Bit, 1/3µs, 2.7V-5.5V Octal Serial DAC	20-SOIC	11.65	9.80	9.01			
TLV5631IPW	296-3068-5-ND	10-Bit, 1/3µs, 2.7V-5.5V Octal Serial DAC	20-TSSOP	11.65	9.80	9.01			
TLV5632IDW	296-3069-5-ND	8-Bit, 1/3µs, 2.7V-5.5V Octal Serial DAC	20-SOIC	9.91	8.13	7.34			
TLV5632IPW	296-3070-5-ND	8-Bit, 1/3µs, 2.7V-5.5V Octal Serial DAC	20-TSSOP	9.91	8.13	7.34			
TLV5633CDW	296-2314-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-SOIC	10.19	8.58	7.88			
TLV5633IDW	296-3071-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-SOIC	10.96	9.22	8.47			
TLV5633IPW	296-3072-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-TSSOP	10.96	9.22	8.47			
TLV5636CD	296-2315-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	8-SOIC	9.57	8.06	7.41			
TLV5636ID	296-3073-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	8-SOIC	10.19	8.58	7.88			
TLV5636IDGK	296-3074-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	8-MSOP	10.19	8.58	7.88			
TLV5637CD	296-2316-5-ND	10-Bit, 1µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	7.75	6.36	5.74			
TLV5637ID	296-3075-5-ND	10-Bit, 1µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	10.02	8.22	7.42			
TLV5638CD	296-2317-5-ND	12-Bit, 1 or 3.5µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	9.76	8.21	7.55			
TLV5638ID	296-3076-5-ND	12-Bit, 1 or 3.5µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	10.36	8.72	8.01			
TLV5638MDREP	296-18149-1-ND	12-Bit, 1 or 3.5µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	12.92	10.96	10.12			
TLV5638QD	296-3077-5-ND	12-Bit, 1 or 3.5µs, 2.7V-5.5V Dual Serial DAC	8-SOIC	9.92	8.35	7.67			
TLV5639CDW	296-2318-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-SOIC	8.53	7.00	6.32			
TLV5639IDW	296-3078-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-SOIC	9.13	7.49	6.76			
TLV5639IPW	296-3079-5-ND	12-Bit, 1µs, 2.7V-5.5V Single Parallel DAC	20-TSSOP	9.67	8.14	7.48			
P82B96DGKR	296-20941-1-ND	Dual Bidirectional Bus Buffer	8-MSOP	3.97	3.24	2.91			
P82B96DGKR	296-20941-2-ND	Dual Bidirectional Bus Buffer	8-MSOP	4394.85	2/500				
P82B96P	296-20943-5-ND	Dual Bidirectional Bus Buffer	8-Dip	3.70	2.98	2.71			
Audio Digital-to-Analog Converters									
DF1704E	DF1704E-ND	Stereo, 24-Bit, Digital Interpolation Filter for PCM1704	28-SSOP	24.78	21.07	19.52			
DSD1702E	296-13072-5-ND	Enhanced Multiformat, Delta-Sigma, Audio DAC	20-QSOP	6.10	5.00	4.51			
DSD1791DB	296-15082-5-ND	24-Bit, 192kHz Sampling, Audio Stereo DAC	28-SSOP	5.27	4.32	3.90			
DSD1792DB	296-15310-5-ND	24-Bit, 192kHz Sampling, Audio Stereo DAC	28-SSOP	19.31	16.42	15.21			
DSD1793DB	296-15083-5-ND	24-Bit, 192kHz Sampling, Audio Stereo DAC	28-SSOP	5.27	4.32	3.90			
DSD1794ADBR	296-21535-1-ND	24-Bit, 192kHz Sampling, Audio Stereo DAC	28-SSOP	18.91	16.03	14.80			
DSD1794DB	296-15311-5-ND	24-Bit, 192kHz Sampling, Audio Stereo DAC	28-SSOP	19.31	16.42	15.21			
DSD1796DB	296-18431-ND	24-Bit, 192kHz Sampling, Audio Stereo DAC	28-SSOP	7.34	6.02	5.43			
PCM56P	PCM56P-ND	Serial In 16-Bit, Mono DAC, 80dB	16-Dip	15.99	13.45	12.36			
PCM56U	PCM56U-ND	16-Bit, Audio DAC	16-SOIC	17.41	14.81	13.72			
PCM1800Y	PCM1800Y-ND	24-Bit, 96kHz, 6-Channel DAC	48-LQFP	11.43	9.62	8.84			
PCM1802KY	PCM1802KY-ND	24-Bit, 192kHz, 6-Channel DAC	48-LQFP	9.65	8.12	7.46			
PCM1802ZY	PCM1802ZY-ND	24-Bit, 192kHz, 6-Channel DAC	48-LQFP	10.19	8.58	7.54			
PCM1804Y	PCM1804Y-ND	24-Bit, 192kHz, 6-Channel DAC	48-LQFP	10.57	8.90	8.18			
PCM1806E	296-13111-5-ND	24-Bit, 6-Channel, Enhanced Multilevel Delta-Sigma DAC	20-SSOP	5.55	4.47	4.07			
PCM1808KY	PCM1808KY-ND	24-Bit, 192kHz, 8-Channel DAC	48-LQFP	10.18	8.56	7.87			
PCM1808Y	PCM1808Y-ND	24-Bit, 192kHz, 8-Channel DAC	48-LQFP	9.36	7.88	7.24			
PCM1808DBQ	296-18004-5-ND	24-Bit, 192kHz, Enhanced Multilevel, Delta-Sigma, Audio DAC	28-QSOP						