

TEXAS INSTRUMENTS Digi+Reel® (Cont.)		DATA TRANSMISSION RoHS Compliant Parts Available				
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	25	100
TRSF3223ECDBR	296-25080-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	20-SSOP	1895.90	2,000	
TRSF3223ECDWR	296-25081-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	20-SOIC	2.46	1.90	1.73
TRSF3223ECDWR	296-25081-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	20-SOIC	1895.90	2,000	
TRSF3223ECPWR	296-25082-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	20-TSSOP	2.46	1.90	1.73
TRSF3223ECPWR	296-25082-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	20-TSSOP	1895.90	2,000	
TRSF3223EIDBR	296-25083-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	20-SSOP	2.46	1.90	1.73
TRSF3223EIDBR	296-25083-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	20-SSOP	1895.90	2,000	
TRSF3223EIDWR	296-25084-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	20-SOIC	2.46	1.90	1.73
TRSF3223EIDWR	296-25084-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	20-SOIC	1895.90	2,000	
TRSF3223EIPWR	296-25085-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	20-TSSOP	2.46	1.90	1.73
TRSF3223EIPWR	296-25085-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	20-TSSOP	1895.90	2,000	
TRSF3232ECDBR	296-25086-1-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-SSOP	2.17	1.68	1.52
TRSF3232ECDBR	296-25086-2-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-SSOP	1672.85	2,000	
TRSF3232ECDR	296-25087-1-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-SOIC	2.17	1.68	1.52
TRSF3232ECDR	296-25087-2-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-SOIC	2091.07	2,500	
TRSF3232ECDWR	296-25088-1-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-SOIC	2.17	1.68	1.52
TRSF3232ECDWR	296-25088-2-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-SOIC	1672.85	2,000	
TRSF3232ECPWR	296-25089-1-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-TSSOP	2.17	1.68	1.52
TRSF3232ECPWR	296-25089-2-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-TSSOP	1672.85	2,000	
TRSF3232EIDBR	296-25090-1-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-SSOP	2.17	1.68	1.52
TRSF3232EIDBR	296-25090-2-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-SSOP	1672.85	2,000	
TRSF3232EIDR	296-25091-1-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-SOIC	2.17	1.68	1.52
TRSF3232EIDR	296-25091-2-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-SOIC	2091.07	2,500	
TRSF3232EIDWR	296-25092-1-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-SOIC	2.17	1.68	1.52
TRSF3232EIDWR	296-25092-2-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-SOIC	1672.85	2,000	
TRSF3232EIPWR	296-25093-1-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-TSSOP	2.17	1.68	1.52
TRSF3232EIPWR	296-25093-2-ND	3V to 5.5V 2-Channel RS-232 Line Driver/Receiver*	16-TSSOP	1672.85	2,000	
TRSF3238CPWR	296-25094-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-TSSOP	2.60	2.01	1.83
TRSF3238CPWR	296-25094-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-TSSOP	2007.42	2,000	
TRSF3238ECDBR	296-25095-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SSOP	2.75	2.12	1.93
TRSF3238ECDBR	296-25095-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SSOP	2118.95	2,000	
TRSF3238ECDWR	296-25096-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SOIC	2.75	2.12	1.93
TRSF3238ECDWR	296-25096-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SOIC	1137.95	1,000	
TRSF3238EIDBR	296-25097-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SSOP	2.75	2.12	1.93
TRSF3238EIDBR	296-25097-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SSOP	2118.95	2,000	
TRSF3238EIDWR	296-25098-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SOIC	2.75	2.12	1.93
TRSF3238EIDWR	296-25098-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SOIC	1137.95	1,000	
TRSF3238IPWR	296-25099-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-TSSOP	2.60	2.01	1.83
TRSF3238IPWR	296-25099-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-TSSOP	2007.42	2,000	
TRSF3243CDBR	296-25100-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SSOP	2.60	2.01	1.83
TRSF3243CDBR	296-25100-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SSOP	2007.42	2,000	
TRSF3243CDWR	296-25101-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SOIC	2.60	2.01	1.83
TRSF3243CDWR	296-25101-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SOIC	1078.06	1,000	
TRSF3243CPWR	296-25102-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-TSSOP	2.60	2.01	1.83
TRSF3243CPWR	296-25102-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-TSSOP	2007.42	2,000	
TRSF3243IDBR	296-25103-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SSOP	2.60	2.01	1.83
TRSF3243IDBR	296-25103-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SSOP	2007.42	2,000	
TRSF3243IDWR	296-25104-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SOIC	2.60	2.01	1.83
TRSF3243IDWR	296-25104-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-SOIC	1078.06	1,000	
TRSF3243IPWR	296-25105-1-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-TSSOP	2.60	2.01	1.83
TRSF3243IPWR	296-25105-2-ND	3V to 5.5V Multichannel RS-232 Line Driver/Receiver*	28-TSSOP	2007.42	2,000	
UA9636ACD	296-11147-5-ND	Dual Line Driver with Adj. Slew Rate	8-SOIC	.76	.62	.54
UA9636ACP	296-11148-5-ND	Dual Line Driver with Adj. Slew Rate	8-Dip	.83	.67	.58
UA9637ACDR	296-15056-1-ND	Dual Differential Line Receiver	8-SOIC	.88	.70	.63
UA9637ACDR	296-15056-2-ND	Dual Differential Line Receiver	8-SOIC	809.58	2,500	

TEXAS INSTRUMENTS Digi+Reel® (Cont.)		DATA TRANSMISSION RoHS Compliant Parts Available				
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	25	100
UA9637ACP	296-15057-5-ND	Dual Differential Line Receiver	8-Dip	.89	.72	.63
UA9638CDR	296-15058-1-ND	Dual High Speed Diff. Line Driver	8-SOIC	.55	.43	.38
UA9638CDR	296-15058-2-ND	Dual High Speed Diff. Line Driver	8-SOIC	450.22	2,500	
UA9638CP	296-15059-5-ND	Dual High Speed Diff. Line Driver	8-Dip	.55	.43	.37
UC5170CQ	296-11352-5-ND	Octal Line Driver with Strapped Mode Selection	28-PLCC	7.46	6.12	5.52
UC5180CQ	296-11354-5-ND	Low Speed Async. Octal Line Rcvr	28-PLCC	7.06	5.80	5.23
SCSI						
SN7597082DGG	296-9921-5-ND	SCSI Differential Converter Control	56-TSSOP	29.66	25.21	23.36
SN7597082DL	296-9922-5-ND	SCSI Differential Converter Control	56-SSOP	29.66	25.21	23.36
SN7597182DGG	296-9923-5-ND	SCSI Differential Converter - Data	56-TSSOP	27.01	22.97	21.28
SN7597182DL	296-9924-5-ND	SCSI Differential Converter - Data	56-SSOP	27.01	22.97	21.28
SN75976A1MDGGREP	296-23022-1-ND	9-Channel Differential Transceiver	56-TSSOP	33.75	29.49	27.53
SN75976A2DL	296-1278-5-ND	9-Channel Differential Transceiver	56-SSOP	27.76	23.60	21.86
SN75976A2DLR	296-1278-1-ND	9-Channel Differential Transceiver	56-SSOP	24.45	22.01	20.18
SN75976A2DLR	296-1278-2-ND	9-Channel Differential Transceiver	56-SSOP	15894.16	100	
UCC6564MWP	296-12333-5-ND	9-Line LVD Only SCSI Terminator with Regulator	36-QSOP	6.10	5.00	4.51
Switches						
MAX4594DBVR	296-17649-1-ND	5V Analog Switch	SOT-23-5	.82	.65	.58
MAX4594DCKR	296-17650-1-ND	5V Analog Switch	SC70-5	.82	.65	.58
MAX4594DCKR	296-17650-2-ND	5V Analog Switch	SC70-5	802.10	3,000	
MAX4595DBVR	296-17651-1-ND	5V Analog Switch	SOT-23-5	.82	.65	.58
MAX4597DCKR	296-17656-1-ND	5V Analog Switch	SC70-5	.82	.65	.58
MAX4597DCKR	296-17656-2-ND	5V Analog Switch	SC70-5	902.10	3,000	
TL52055PWR	296-18889-1-ND	Wide Bandwidth, 2-In, 1-Out, 3-Circuit Video Switch	16-TSSOP	.78	.62	.56
TMDS141RHAR	296-21873-1-ND	HDMI Hider	40-QFN	4.34	3.55	3.19
TMDS141RHAR	296-21873-2-ND	HDMI Hider	40-QFN	4807.90	2,500	
TMDS2618PAG	296-25277-ND	2:1 DV/HDMI Switch*	64-TQFP	3.82	3.07	2.80
TMDS2618PAG	296-24235-ND	2:1 DV/HDMI Switch*	64-TQFP	3.75	3.02	2.75
TMDS331APFCR	296-19741-1-ND	3:1 DV/HDMI Switch	80-TQFP	5.58	4.56	4.09
TMDS331APFCR	296-19741-2-ND	3:1 DV/HDMI Switch	80-TQFP	2602.22	1,000	
TMDS331PFC	296-18264-ND	3:1 DV/HDMI Switch	80-TQFP	5.58	4.58	4.13
TMDS335PAG	296-21970-ND	2.5Gbps, 3:1 DV/HDMI Switch*	64-TQFP	5.32	4.28	3.90
TMDS3618PAG	296-25278-ND	3:1 DV/HDMI Switch*	64-TQFP	4.16	3.35	3.05
TMDS361PAG	296-24028-5-ND	3:1 DV/HDMI Switch	64-TQFP	3.15	2.53	2.31
TMDS361PAGR	296-24008-1-ND	3:1 DV/HDMI Switch*	64-TQFP	2.85	2.33	2.09
TMDS44ZPNP	296-26832-5-ND	4:1 DV/HDMI Switch*	128-HTQFP	7.96	6.52	5.89
TMDS461PZT	296-24122-ND	4:1 DV/HDMI Switch*	100-TQFP	4.51	3.63	3.31
TPS22902YFPR	296-24472-1-ND	Low rON Load Switch*	4-DSBGA	1.01	.80	.72
TPS22921YFPR	296-24472-2-ND	Low rON Load Switch*	4-DSBGA	1110.28	3,000	
TPS22921YZPR	296-24473-1-ND	Low rON Load Switch*	6-DSBGA	1.35	1.07	.96
TPS22921YZPR	296-24473-2-ND	Low rON Load Switch*	6-DSBGA	1491.94	3,000	
TPS22922YZPR	296-24474-1-ND	Low rON Load Switch*	6-DSBGA	1.35	1.07	.96
TPS22922YZPR	296-24474-2-ND	Low rON Load Switch*	6-DSBGA	1491.94	3,000	
TPS22945DCKR	296-24475-1-ND	Low Input Volt. Load Switch*	SC70-5	1.13	.90	.81
TPS22945DCKR	296-24475-2-ND	Low Input Volt. Load Switch*	SC70-5	1249.06	3,000	
TPSDDR2811ZXRY	296-25542-1-ND	8-Channel 1GHz SPST Switch*	20-BGA	1.45	1.12	1.02
TPSDDR2811ZXRY	296-25542-2-ND	8-Channel 1GHz SPST Switch*	20-BGA	1394.04	2,500	
TS3A4741DCNR	296-24793-1-ND	0.9-Ohm Low Voltage Single Supply Dual SPST Analog Switch*	SOT-23-8	.94	.75	.67
TS3A4741DCNR	296-24793-2-ND	0.9-Ohm Low Voltage Single Supply Dual SPST Analog Switch*	SOT-23-8	1040.89	3,000	
TS3A4741DGKR	296-21917-1-ND	0.9-Ohm Low Voltage Single Supply Dual SPST Analog Switch	8-MSOP	.94	.75	.67
TS3A4741DGKR	296-21917-2-ND	0.9-Ohm Low Voltage Single Supply Dual SPST Analog Switch	8-MSOP	867.41	2,500	
TS3A4742DCNR	296-24794-1-ND	0.9-Ohm Low Voltage Single Supply Dual SPST Analog Switch*	SOT-23-8	.94	.75	.67
TS3A4742DCNR	296-24794-2-ND	0.9-Ohm Low Voltage Single Supply Dual SPST Analog Switch*	SOT-23-8	1040.89	3,000	
TS3A4742DGKR	296-24795-1-ND	0.9-Ohm Low Voltage Single Supply Dual SPST Analog Switch*	8-MSOP	.94	.75	.67
TS3A4742DGKR	296-24795-2-ND	0.9-Ohm Low Voltage Single Supply Dual SPST Analog Switch*	8-MSOP	867.41	2,500	
TS3A4751PWR	296-20700-1-ND	0.9-Ohm Low Voltage Single Supply Quad SPST Analog Switch	14-TSSOP	1.26	1.00	.90
TS3A4751PWR	296-20700-2-ND	0.9-Ohm Low Voltage Single Supply Quad SPST Analog Switch	14-TSSOP	925.23	2,000	
TS3A4751R6GYR	296-24477-1-ND	0.9-Ohm Low Voltage Single Supply Quad SPST Analog Switch*	14-QFN	1.28	1.02	.91
TS3A4751R6GYR	296-24477-2-ND	0.9-Ohm Low Voltage Single Supply Quad SPST Analog Switch*	14-QFN	1415.11	3,000	
TS3A4751RUCR	296-24478-1-ND	0.9-Ohm Low Voltage Single Supply Quad SPST Analog Switch*	14-QFN	1.32	1.05	.94
TS3A4751RUCR	296-24478-2-ND	0.9-Ohm Low Voltage Single Supply Quad SPST Analog Switch*	14-QFN	1457.24	3,000	
TS3A5017DR	296-17583-1-ND	14-Ohm Dual SP4T Analog Switch	16-SOIC	.88	.68	.60
TS3A5017DR	296-17583-2-ND	14-Ohm Dual SP4T Analog Switch	16-SOIC	718.71	2,500	
TS3A5017PWR	296-17584-1-ND	14-Ohm Dual SP4T Analog Switch	16-TSSOP	.88	.68	.60
TS3A5017PWR	296-17584-2-ND	14-Ohm Dual SP4T Analog Switch	16-TSSOP	574.97	2,000	
TS3A5017RSVR	296-24683-1-ND	12-Ohm Dual SP4T Analog Switch*	16-UQFN	.84	.67	.60
TS3A5017RSVR	296-					