

TEXAS INSTRUMENTS		DIGI-KEY REAL (Cont.)		DIGITAL LOGIC		RoHS Compliant Parts Available	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
SN74LVC828ADGVR	296-12741-1-ND	Tri-State 10-Bit Buffer/Driver	24-TVSOP	1.16	.92	.83	
SN74LVC828ADGVR	296-12741-2-ND	Tri-State 10-Bit Buffer/Driver	24-TVSOP	855.84/2,000			
SN74LVC828ADW	296-12913-5-ND	Tri-State 10-Bit Buffer/Driver	24-SOIC	1.28	1.03	.90	
SN74LVC828APWR	296-8549-1-ND	Tri-State 10-Bit Buffer/Driver	24-TSSOP	1.16	.92	.83	
SN74LVC828APWR	296-8549-2-ND	Tri-State 10-Bit Buffer/Driver	24-TSSOP	855.84/2,000			
SN74LVC841ADBR	296-8550-1-ND	Tri-St. 10-Bit Interface D-Type Latch	24-TSSOP	2.17	1.68	1.52	
SN74LVC841ADBR	296-8550-2-ND	Tri-St. 10-Bit Interface D-Type Latch	24-TSSOP	1673.68/2,000			
SN74LVC841ADGVR	296-8551-1-ND	Tri-St. 10-Bit Interface D-Type Latch	24-TVSOP	2.02	1.57	1.42	
SN74LVC841ADGVR	296-8551-2-ND	Tri-St. 10-Bit Interface D-Type Latch	24-TVSOP	1561.33/2,000			
SN74LVC841ADW	296-8552-5-ND	Tri-St. 10-Bit Interface D-Type Latch	24-SOIC	2.18	1.76	1.58	
SN74LVC841APWR	296-8553-1-ND	Tri-St. 10-Bit Interface D-Type Latch	24-TSSOP	2.02	1.57	1.42	
SN74LVC841APWR	296-8553-2-ND	Tri-St. 10-Bit Interface D-Type Latch	24-TSSOP	1561.33/2,000			
SN74LVC861ADBR	296-12914-1-ND	Tri-State 10-Bit Bus Transceiver	24-TSSOP	2.37	1.83	1.66	
SN74LVC861ADBR	296-12914-2-ND	Tri-State 10-Bit Bus Transceiver	24-TSSOP	1828.99/2,000			
SN74LVC861ADGVR	296-8555-1-ND	Tri-State 10-Bit Bus Transceiver	24-TVSOP	2.37	1.83	1.66	
SN74LVC861ADGVR	296-8555-2-ND	Tri-State 10-Bit Bus Transceiver	24-TVSOP	1828.99/2,000			
SN74LVC861ADW	296-8556-5-ND	Tri-State 10-Bit Bus Transceiver	24-SOIC	2.10	1.70	1.53	
SN74LVC861ADW	296-8557-1-ND	Tri-State 9-Bit Bus Transceiver	24-TSSOP	2.37	1.83	1.66	
SN74LVC863ADBR	296-8557-2-ND	Tri-State 9-Bit Bus Transceiver	24-TSSOP	1828.99/2,000			
SN74LVC863ADGVR	296-8558-1-ND	Tri-State 9-Bit Bus Transceiver	24-TVSOP	2.37	1.83	1.66	
SN74LVC863ADGVR	296-8558-2-ND	Tri-State 9-Bit Bus Transceiver	24-TVSOP	1828.99/2,000			
SN74LVC863ADW	296-8559-5-ND	Tri-State 9-Bit Bus Transceiver	24-SOIC	2.10	1.70	1.53	
SN74LVC863APWR	296-8560-1-ND	Tri-State 9-Bit Bus Transceiver	24-TSSOP	2.37	1.83	1.66	
SN74LVC1404DCTR	296-17257-1-ND	Oscillator Driver	SM8	.93	.74	.67	
SN74LVC1404DCTR	296-17257-2-ND	Oscillator Driver	SM8	1030.97/3,000			
SN74LVC1404YEPF	296-18751-1-ND	Oscillator Driver	8-DSBGA	1.41	1.12	1.01	
SN74LVC1404YEPF	296-18751-2-ND	Oscillator Driver	8-DSBGA	1561.33/3,000			
SN74LVC1404YPPR	296-18082-1-ND	Oscillator Driver	8-DSBGA	1.27	1.01	.91	
SN74LVC1404YPPR	296-18082-2-ND	Oscillator Driver	8-DSBGA	1405.20/3,000			
SN74LVC1404YZPR	296-8489-1-ND	Tri-State Octal Buffer/Driver	20-SOP	.60	.47	.41	
SN74LVC2244ADBR	296-8489-2-ND	Tri-State Octal Buffer/Driver	20-TSSOP	394.88/2,000			
SN74LVC2244ADGVR	296-23275-1-ND	Tri-State Octal Buffer/Driver	24-TSSOP	.60	.47	.41	
SN74LVC2244ADGVR	296-23275-2-ND	Tri-State Octal Buffer/Driver	24-TSSOP	495.59/2,500			
SN74LVC2244ADW	296-12901-1-ND	Tri-State Octal Buffer/Driver	20-TVSOP	.55	.43	.38	
SN74LVC2244ADW	296-12901-2-ND	Tri-State Octal Buffer/Driver	20-TVSOP	360.18/2,000			
SN74LVC2244ADWR	296-8490-5-ND	Tri-State Octal Buffer/Driver	20-SOIC	.59	.47	.41	
SN74LVC2244ADWR	296-8490-1-ND	Tri-State Octal Buffer/Driver	20-SOIC	.55	.43	.38	
SN74LVC2244ADWR	296-8490-2-ND	Tri-State Octal Buffer/Driver	20-SOIC	360.18/2,000			
SN74LVC2244ANSR	296-13256-1-ND	Tri-State Octal Buffer/Driver	20-TSSOP	.60	.47	.41	
SN74LVC2244ANSR	296-13256-2-ND	Tri-State Octal Buffer/Driver	20-TSSOP	394.88/2,000			
SN74LVC2244APWR	296-8491-1-ND	Tri-State Octal Buffer/Driver*	20-TSSOP	.59	.47	.41	
SN74LVC2244APWR	296-8491-2-ND	Tri-State Octal Buffer/Driver	20-TSSOP	.55	.43	.38	
SN74LVC2244APWR	296-8491-3-ND	Tri-State Octal Buffer/Driver	20-TSSOP	360.18/2,000			
SN74LVC2952ADBR	296-12904-1-ND	Tri-St. Octal Bus Transceiver/Register	24-TSSOP	1.10	.87	.79	
SN74LVC2952ADBR	296-12904-2-ND	Tri-St. Octal Bus Transceiver/Register	24-TSSOP	809.58/2,000			
SN74LVC2952ADW	296-8507-5-ND	Tri-St. Octal Bus Transceiver/Register	24-SOIC	1.02	.81	.71	
SN74LVC24245ADBR	296-8514-1-ND	Tri-St. Octal Bus Xcvr/3.3V-5V Shifter	24-TSSOP	1.03	.82	.74	
SN74LVC24245ADBR	296-8514-2-ND	Tri-St. Octal Bus Xcvr/3.3V-5V Shifter	24-TSSOP	763.32/2,000			
SN74LVC24245ADW	296-8515-5-ND	Tri-St. Octal Bus Xcvr/3.3V-5V Shifter	24-SOIC	1.04	.84	.73	
SN74LVC24245ADW	296-14911-1-ND	Tri-St. Octal Bus Xcvr/3.3V-5V Shifter	24-SOIC	.94	.75	.67	
SN74LVC24245ADWR	296-14911-2-ND	Tri-St. Octal Bus Xcvr/3.3V-5V Shifter	24-SOIC	693.92/2,000			
SN74LVC24245AIPWREP	296-22369-1-ND	Tri-St. Octal Bus Xcvr/3.3V-5V Shifter	24-TSSOP	1.94	1.50	1.36	
SN74LVC24245AIPWREP	296-22369-2-ND	Tri-St. Octal Bus Xcvr/3.3V-5V Shifter	24-TSSOP	1494.41/2,000			
SN74LVC24245APWR	296-12183-1-ND	Tri-State Octal Xcvr/3.3V-5V Shifter	24-TSSOP	.94	.75	.67	
SN74LVC24245APWR	296-12183-2-ND	Tri-State Octal Xcvr/3.3V-5V Shifter	24-TSSOP	693.92/2,000			
SN74LVC16244ADGGR	296-1226-1-ND	Tri-State 16-Bit Buffer/Driver	48-TSSOP	1.19	.95	.85	
SN74LVC16244ADGGR	296-1226-2-ND	Tri-State 16-Bit Buffer/Driver	48-TSSOP	878.97/2,000			
SN74LVC16244ADGVR	296-8471-1-ND	Tri-State 16-Bit Buffer/Driver	48-TSSOP	1.19	.95	.85	
SN74LVC16244ADGVR	296-8471-2-ND	Tri-State 16-Bit Buffer/Driver	48-TSSOP	878.97/2,000			
SN74LVC16244ADL	296-1227-5-ND	Tri-State 16-Bit Buffer/Driver	48-TSSOP	1.43	1.15	1.00	
SN74LVC16244ADL	296-1227-1-ND	16-Bit Buffer/Driver	48-TSSOP	1.31	1.04	.94	
SN74LVC16244ADL	296-1227-2-ND	16-Bit Buffer/Driver	48-TSSOP	517.96/1,000			
SN74LVC16244AGQLR	296-8472-1-ND	Tri-State 16-Bit Buffer/Driver	56-BGA	1.73	1.34	1.22	
SN74LVC16244AGQLR	296-8472-2-ND	Tri-State 16-Bit Buffer/Driver	56-BGA	718.71/1,000			
SN74LVC16244AZQLR	296-16642-1-ND	Tri-State 16-Bit Buffer/Driver	56-BGA	1.73	1.34	1.22	
SN74LVC16244AZQLR	296-16642-2-ND	Tri-State 16-Bit Buffer/Driver	56-BGA	718.71/1,000			
SN74LVC16244AZRDR	296-16882-1-ND	Tri-State 16-Bit Buffer/Driver	54-FBGA	1.73	1.34	1.22	
SN74LVC16244AZRDR	296-16882-2-ND	Tri-State 16-Bit Buffer/Driver	54-FBGA	718.71/1,000			
SN74LVC16245ADGGR	296-1228-1-ND	Tri-State 16-Bit Bus Transceiver	48-TSSOP	1.31	1.04	.94	
SN74LVC16245ADGGR	296-1228-2-ND	Tri-State 16-Bit Bus Transceiver	48-TSSOP	966.54/2,000			
SN74LVC16245ADGVR	296-8473-1-ND	Tri-State 16-Bit Bus Transceiver	48-TVSOP	1.31	1.04	.94	
SN74LVC16245ADGVR	296-8473-2-ND	Tri-State 16-Bit Bus Transceiver	48-TVSOP	966.54/2,000			
SN74LVC16245ADL	296-8474-5-ND	Tri-State 16-Bit Bus Transceiver	48-TSSOP	1.41	1.14	1.03	
SN74LVC16245ADL	296-8474-1-ND	Tri-State 16-Bit Bus Transceiver	48-TSSOP	1.45	1.14	1.03	
SN74LVC16245ADL	296-8474-2-ND	Tri-State 16-Bit Bus Transceiver	48-TSSOP	570.01/1,000			
SN74LVC16245AGQLR	296-9843-1-ND	Tri-State 16-Bit Bus Transceiver	56-BGA	1.88	1.45	1.32	
SN74LVC16245AGQLR	296-9843-2-ND	Tri-State 16-Bit Bus Transceiver	56-BGA	779.01/1,000			
SN74LVC16245AGRDR	296-16883-1-ND	Tri-State 16-Bit Bus Transceiver	54-BGA	1.88	1.45	1.32	
SN74LVC16245AGRDR	296-16883-2-ND	Tri-State 16-Bit Bus Transceiver	54-BGA	779.01/1,000			
SN74LVC16245AZQLR	296-23271-1-ND	Tri-State 16-Bit Bus Transceiver	56-VFBGA	1.88	1.45	1.32	
SN74LVC16245AZQLR	296-23271-2-ND	Tri-State 16-Bit Bus Transceiver	56-VFBGA	779.01/1,000			
SN74LVC16245AZRDR	296-16884-1-ND	Tri-State 16-Bit Bus Transceiver	54-BGA	1.88	1.45	1.32	
SN74LVC16245AZRDR	296-16884-2-ND	Tri-State 16-Bit Bus Transceiver	54-BGA	779.01/1,000			
SN74LVC16373ADGGR	296-13241-1-ND	Tri-State 16-Bit Transp. D-Type Latch	48-TSSOP	1.19	.95	.85	
SN74LVC16373ADGGR	296-13241-2-ND	Tri-State 16-Bit Transp. D-Type Latch	48-TSSOP	878.97/2,000			
SN74LVC16373ADGVR	296-13242-1-ND	Tri-St. 16-Bit Transp. D-Type Latch	48-TVSOP	1.19	.95	.85	
SN74LVC16373ADGVR	296-13242-2-ND	Tri-St. 16-Bit Transp. D-Type Latch	48-TVSOP	1.31	1.04	.94	
SN74LVC16373ADL	296-13243-1-ND	Tri-St. 16-Bit Transp. D-Type Latch	48-TSSOP	1.19	.95	.85	
SN74LVC16373ADL	296-13243-2-ND	Tri-St. 16-Bit Transp. D-Type Latch	48-TSSOP	517.96/1,000			
SN74LVC16373AGQLR	296-13244-1-ND	Tri-St. 16-Bit Transp. D-Type Latch	56-BGA	1.73	1.34	1.22	
SN74LVC16373AGQLR	296-13244-2-ND	Tri-St. 16-Bit Transp. D-Type Latch	56-BGA	718.71/1,000			
SN74LVC16373AZQLR	296-23272-1-ND	Tri-St. 16-Bit Transp. D-Type Latch	56-VFBGA	1.73	1.34	1.22	
SN74LVC16373AZQLR	296-23272-2-ND	Tri-St. 16-Bit Transp. D-Type Latch	56-VFBGA	718.71/1,000			
SN74LVC16373DGGGR	296-11846-1-ND	Tri-State 16-Bit Transp. D-Type Latch	48-TSSOP	1.19	.95	.85	
SN74LVC16373DGGGR	296-11846-2-ND	Tri-State 16-Bit Transp. D-Type Latch	48-TSSOP	878.97/2,000			
SN74LVC16373DL	296-11834-5-ND	Tri-St. 16-Bit Transp. D-Type Latch	48-TSSOP	1.43	1.15	1.00	
SN74LVC16373DL	296-11834-1-ND	Tri-St. 16-Bit Transp. D-Type Latch	48-TSSOP	1.31	1.04	.94	
SN74LVC16373DL	296-11834-2-ND	Tri-St. 16-Bit Transp. D-Type Latch	48-TSSOP	517.96/1,000			
SN74LVC16374ADGGR	296-13245-1-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	48-TSSOP	1.31	1.04	.94	
SN74LVC16374ADGGR	296-13245-2-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	48-TSSOP	966.54/2,000			
SN74LVC16374ADGVR	296-13246-1-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	48-TVSOP	1.31	1.04	.94	
SN74LVC16374ADGVR	296-13246-2-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	48-TVSOP	966.54/2,000			

* RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

(Continued)

TEXAS INSTRUMENTS		DIGI-KEY REAL (Cont.)		DIGITAL LOGIC		RoHS Compliant Parts Available	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
SN74LVC16374ADL	296-13247-1-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	48-TSSOP	1.45	1.14	1.03	
SN74LVC16374ADL	296-13247-2-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	48-TSSOP	570.01/1,000			
SN74LVC16374AGQLR	296-13248-1-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	56-BGA	1.88	1.45	1.32	
SN74LVC16374AGQLR	296-13248-2-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	56-BGA	779.01/1,000			
SN74LVC16374AGRDR	296-16885-1-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	54-BGA	1.88	1.45	1.32	
SN74LVC16374AGRDR	296-16885-2-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	54-BGA	779.01/1,000			
SN74LVC16374AZRDR	296-16886-1-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	103-BGA	1.88	1.45	1.32	
SN74LVC16374AZRDR	296-16886-2-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	103-BGA	779.01/1,000			
SN74LVC16374DGGGR	296-11833-1-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	48-TSSOP	1.19	.95	.85	
SN74LVC16374DGGGR	296-11833-2-ND	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	48-TSSOP	878.97/2,000			