

POWER CONTROL/ MANAGEMENT PRODUCTS					
TEXAS INSTRUMENTS		Digi-Reel® (Cont.)		RoHS Compliant Parts Available	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	
			1	25	100
TPS2398DGK	296-15731-5-ND	Neg. 48V Hot-Swap Power Manager Evaluation Module for TPS2398	8-MSOP	2.78	2.24 2.04
TPS2398EVM	296-18944-ND			41.31	—
TPS2399DGK	296-15732-5-ND	Neg. 48V Hot-Swap Power Manager Evaluation Module for TPS2399	8-MSOP	2.78	2.24 2.04
TPS2399EVM	296-18945-ND			41.31	—
TPS2410PW	296-21612-5-ND	Full Featured N+1 and OR-Ing Power Rail Controller	14-TSSOP	4.74	3.82 3.48
TPS2411PW	296-21613-5-ND	Full Featured N+1 and OR-Ing Power Rail Controller	14-TSSOP	4.74	3.82 3.48
TPS2412D	296-23785-5-ND	N+1 and OR-Ing Power Rail Controller	8-SOIC	3.35	2.70 2.46
TPS2412PW	296-21614-5-ND	N+1 and OR-Ing Power Rail Controller	8-TSSOP	3.35	2.70 2.46
TPS2413D	296-23786-5-ND	N+1 and OR-Ing Power Rail Controller	8-SOIC	3.35	2.70 2.46
TPS2413PW	296-21615-5-ND	N+1 and OR-Ing Power Rail Controller	8-TSSOP	3.35	2.70 2.46
TPS2420RSAR	296-24162-1-ND	3V to 20V Hot-Swap Controller* 3V to 20V Hot-Swap Power Manager	16-QFN	4.83	3.95 3.55
TPS2420RSAR	296-24162-2-ND	3V to 20V Hot-Swap Controller* 3V to 20V Hot-Swap Power Manager	16-QFN	6427.47	3,000
TPS2420RSAT	296-24175-1-ND	3V to 20V Hot-Swap Controller* 3V to 20V Hot-Swap Power Manager	16-QFN	5.45	4.46 4.00
TPS2420RSAT	296-24175-2-ND	3V to 20V Hot-Swap Controller* 3V to 20V Hot-Swap Power Manager	16-QFN	840.56	250
TPS2421-1DDAR	296-24238-1-ND	3V to 20V Hot-Swap Controller* 3V to 20V Hot-Swap Power Manager	8-SOIC	3.97	3.24 2.91
TPS2421-1DDAR	296-24238-2-ND	3V to 20V Hot-Swap Controller* 3V to 20V Hot-Swap Power Manager	8-SOIC	4394.85	2,500
TPS2421-2DDAR	296-24239-1-ND	3V to 20V Hot-Swap Controller* 3V to 20V Hot-Swap Power Manager	8-SOIC	3.97	3.24 2.91
TPS2421-2DDAR	296-24239-2-ND	3V to 20V Hot-Swap Controller* 3V to 20V Hot-Swap Power Manager	8-SOIC	4394.85	2,500
TPS2458RHBT	296-24210-1-ND	3.3V Hot-Swap Controller*	32-QFN	5.70	4.66 4.19
TPS2458RHBT	296-24210-2-ND	3.3V Hot-Swap Controller*	32-QFN	878.76	250
TPS2459RHBT	296-24211-1-ND	3.3V Hot-Swap Controller w/PC*	32-QFN	6.13	5.09 4.63
TPS2459RHBT	296-24211-2-ND	3.3V Hot-Swap Controller w/PC*	32-QFN	983.06	250
TPS2490DGS	296-17085-ND	Positive High-Voltage Power-Limiting Hot-Swap Controller	10-MSOP	3.93	3.16 2.88
TPS2490DGS	296-26924-1-ND	Positive High-Voltage Power-Limiting Hot-Swap Controller*	10-MSOP	3.47	2.84 2.55
TPS2490DGS	296-26924-2-ND	Positive High-Voltage Power-Limiting Hot-Swap Controller*	10-MSOP	3845.50	2,500
TPS2490EVM-001	296-18946-ND	Evaluation Module for TPS2490-001		41.31	—
TPS2491DGS	296-16906-ND	Positive High-Voltage Power-Limiting Hot-Swap Controller	10-MSOP	3.93	3.16 2.88
TPS2491DGS	296-26925-1-ND	Positive High-Voltage Power-Limiting Hot-Swap Controller*	10-MSOP	3.47	2.84 2.55
TPS2491DGS	296-26925-2-ND	Positive High-Voltage Power-Limiting Hot-Swap Controller*	10-MSOP	3845.50	2,500
TPS2491EVM-002	296-18947-ND	Evaluation Module for TPS2491-002		41.31	—
TPS2590RSAT	296-24879-1-ND	3V to 20V Hot-Swap Power Manager* DC Controller*	16-QFN	3.10	2.53 2.28
TPS2590RSAT	296-24879-2-ND	3V to 20V Hot-Swap Power Manager* DC Controller*	16-QFN	477.69	250
TPS27553APW	296-24928-5-ND	PoE Power Device/Current-Mode DC/DC Controller*	14-TSSOP	4.05	3.26 2.97
TPS2756PWP	296-24573-5-ND	PoE Power Device/Current-Mode DC/DC Controller*	20-HTSSOP	5.32	4.28 3.90
TPS23757EVM	296-25232-ND	Evaluation Module for TPS23757		41.31	—
TPS23757PW	296-24949-5-ND	PoE Power Device/Current-Mode DC/DC Controller*	20-TSSOP	4.63	3.72 3.39
TPS54232EVM-415	296-24176-ND	Evaluation Module for TPS54232		21.07	—
UCC2914D	296-12245-5-ND	5V to 35V Hot-Swap Power Manager	18-SOIC	10.90	9.17 8.43
UCC2914N	296-2502-5-ND	5V to 35V Hot-Swap Power Manager	18-Dip	9.36	7.88 7.24
UCC3914D	296-11347-5-ND	5V to 35V Hot-Swap Power Manager	18-SOIC	9.36	7.88 7.24
UCC3914N	296-2327-5-ND	5V to 35V Hot-Swap Power Manager	18-Dip	8.88	7.29 6.58
UCC2912DP	296-16715-5-ND	Prog. Hot-Swap Power Manager	16-SOIC	6.72	5.51 4.97
UCC2912PWP	296-16716-ND	Prog. Hot-Swap Power Manager	24-TSSOP	6.72	5.51 4.97
UCC2913D	296-2328-5-ND	Neg. Voltage Hot-Swap Power Manager	8-SOIC	4.51	3.63 3.31
UCC2913N	296-12247-5-ND	Neg. Voltage Hot-Swap Power Manager	8-Dip	3.82	3.07 2.80
UCC2915DP	296-2329-5-ND	15V Hot-Swap Prog. Power Manager	16-SOIC	9.09	7.65 7.03
UCC2917D	296-2330-5-ND	Pos. Floating Hot-Swap Power Manager	16-SOIC	5.37	4.41 3.98
UCC2917N	296-12249-5-ND	Pos. Floating Hot-Swap Power Manager	16-Dip	5.20	4.19 3.82
UCC2919D	296-2331-5-ND	3V to 8V Hot-Swap Power Manager	16-SOIC	5.81	4.77 4.30
UCC2919PW	296-12251-5-ND	3V to 8V Hot-Swap Power Manager	16-TSSOP	6.72	5.51 4.97
UCC2921D	296-2332-5-ND	Latching Negative Floating Hot-Swap Power Manager	8-SOIC	4.97	4.00 3.65
UCC3912DP	296-2333-5-ND	Prog. Hot-Swap Power Manager	16-SOIC	5.68	4.66 4.21
UCC3912PWP	296-12031-5-ND	Prog. Hot-Swap Power Manager	24-TSSOP	5.68	4.66 4.21
UCC3913D	296-2335-5-ND	Negative Volt. Hot-Swap Power Manager	8-SOIC	4.16	3.35 3.05
UCC3913N	296-6770-5-ND	Negative Volt. Hot-Swap Power Manager	8-Dip	3.47	2.79 2.55
UCC3915DP	296-2336-5-ND	15V Prog. Hot-Swap Power Manager	16-SOIC	6.30	5.17 4.67
UCC3915N	296-6771-5-ND	7-15V Prog. Hot-Swap Power Manager	16-Dip	5.27	4.32 3.90
UCC3915PWP	296-6772-5-ND	7-15V Prog. Hot-Swap Power Manager	24-HTSSOP	6.30	5.17 4.67
UCC3917D	296-2337-5-ND	Positive Floating Hot-Swap Pwr Manager	16-SOIC	5.20	4.19 3.82
UCC3917EVM	296-13599-ND	Evaluation Module for UCC3917		41.31	—
UCC3917N	296-6774-5-ND	Positive Floating Hot-Swap Pwr Manager	16-Dip	4.28	3.44 3.14
UCC3918DP	296-2338-5-ND	Low On-Res. Hot-Swap Power Manager	16-SOIC	5.78	4.75 4.28
UCC3918EVM	296-13600-ND	Evaluation Module for UCC3918		41.31	—
UCC3919D	296-2339-5-ND	3V to 8V Hot-Swap Power Manager	16-SOIC	5.01	4.11 3.71
UCC3919PW	296-6777-5-ND	Single Hot-Swap Power Controller	16-TSSOP	5.78	4.75 4.28
UCC3921D	296-2340-5-ND	Neg. Floating Hot-Swap Power Manager	8-SOIC	4.51	3.63 3.31
UCC3921N	296-6779-5-ND	Negative Latchable Floating Hot-Swap Power Manager	8-Dip	3.70	2.98 2.71
Lighting and Display					
TPS60230EVM-047	296-18968-ND	Evaluation Module for TPS60230-047		41.31	—
TPS60230RGT	296-27003-1-ND	White LED Backlight Driver*	16-QFN	1.45	1.12 1.02
TPS60230RGT	296-27003-2-ND	White LED Backlight Driver*	16-QFN	1672.85	3,000
TPS60230RGT	296-17136-1-ND	White LED Backlight Driver	16-QFN	1.71	1.32 1.20
TPS60230RGT	296-17136-2-ND	White LED Backlight Driver	16-QFN	243.70	250
TPS60231EVM-047	296-17608-ND	Evaluation Module for TPS60231		41.31	—
TPS60231RGT	296-17490-1-ND	White LED Backlight Driver	16-QFN	1.13	90 .81
TPS60231RGT	296-17490-2-ND	White LED Backlight Driver	16-QFN	1249.06	3,000
TPS60250RTER	296-21893-1-ND	White LED Backlight Driver	16-QFN	3.00	2.70 2.42
TPS60250RTER	296-21893-2-ND	White LED Backlight Driver	16-QFN	4383.86	3,000
TPS60251RTWT	296-21894-1-ND	White LED Backlight Driver	24-QFN	2.60	2.13 1.91
TPS60251RTWT	296-21894-2-ND	White LED Backlight Driver	24-QFN	401.28	250
TPS60252RTET	296-23407-1-ND	White LED Backlight Driver	16-QFN	2.60	2.13 1.91
TPS60252RTET	296-23407-2-ND	White LED Backlight Driver	16-QFN	401.28	250
TPS61040DBVR	296-12685-1-ND	White LED Backlight Driver	SOT23-5	1.83	1.41 1.28
TPS61040DBVR	296-12685-2-ND	White LED Backlight Driver	SOT23-5	2109.03	3,000
TPS61040DBVR	296-22980-1-ND	White LED Backlight Driver	6-SOIC	1.83	1.41 1.28
TPS61040DBVR	296-22980-2-ND	White LED Backlight Driver	6-SOIC	2109.03	3,000
TPS61040EVM-001	296-13585-ND	Evaluation Module for TPS61040		41.31	—
TPS61040EVM-002	296-20609-ND	Evaluation Module for TPS61040		41.31	—

* RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

(Continued)

POWER CONTROL/ MANAGEMENT PRODUCTS					
TEXAS INSTRUMENTS		Digi-Reel® (Cont.)		RoHS Compliant Parts Available	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	
			1	25	100
TPS61040DBVR01	296-23425-1-ND	White LED Backlight Driver	SOT23-5	2.20	1.70 1.54
TPS61040DBVR01	296-23425-2-ND	White LED Backlight Driver	SOT23-5	2542.74	3,000
TPS61041DBVR	296-12686-1-ND	White LED Backlight Driver	SOT23-5	1.71	1.32 1.20
TPS61041DBVR	296-12686-2-ND	White LED Backlight Driver	SOT23-5	1975.21	3,000
TPS61041DBVR	296-22981-1-ND	White LED Backlight Driver	6-SOIC	1.71	1.32 1.20
TPS61041DBVR	296-22981-2-ND	White LED Backlight Driver	6-SOIC	1975.21	3,000
TPS61041QDBVR01	296-21895-1-ND	White LED Backlight Driver	SOT23-5	2.06	1.59 1.44
TPS61041QDBVR01	296-21895-2-ND	White LED Backlight Driver	SOT23-5	2376.69	3,000
TPS61042DBRR	296-14449-1-ND	White LED Backlight Driver	8-SOIC	2.06	1.59 1.44
TPS61042DBRR	296-14449-2-ND	White LED Backlight Driver	8-SOIC	2376.69	3,000
TPS61042EVM-226	296-20610-ND	Evaluation Module for TPS61042		41.31	—
TPS61043DBRR	296-16675-1-ND	White LED Backlight Driver	8-SOIC	2.06	1.59 1.44
TPS61043DBRR	296-16675-2-ND	White LED Backlight Driver	8-SOIC	2.31	1.79 1.62
TPS61043RBT	296-27009-1-ND	White LED Backlight Driver*	8-SOIC	—	—
TPS61043RBT	296-27009-2-ND	White LED Backlight Driver*	8-SOIC	330.44	250
TPS61043RBR	296-16675-2-ND	White LED Backlight Driver	8-SOIC	2376.69	3,000
TPS61050DRCT	296-21681-1-ND	Photo Flash LED Driver	10-SOIC	2.85	2.33 2.09
TPS61050DRCT	296-21681-2-ND	Photo Flash LED Driver	10-SOIC	—	—
TPS61050VZGT	296-21682-1-ND	Photo Flash LED Driver	12-DSBGA	2.97	2.43 2.19
TPS61050VZGT	296-21682-2-ND	Photo Flash LED Driver	12-DSBGA	458.49	250
TPS61052DRCT	296-23720-1-ND	Photo Flash LED Driver	10-SOIC	2.85	2.33 2.09
TPS61052DRCT	296-23720-2-ND	Photo Flash LED Driver	10-SOIC	—	—
TPS61052ZGR	296-21896-1-ND	Photo Flash LED Driver	12-DSBGA	2.60	2.13 1.91
TPS61052ZGR	296-21896-2-ND	Photo Flash LED Driver	12-DSBGA	3462.19	3,000
TPS61052VZGT	296-21897-1-ND	Photo Flash LED Driver	12-DSBGA	2.97	2.43 2.19
TPS61052VZGT	296-21897-2-ND	Photo Flash LED Driver	12-DSBGA	458.49	250
TPS61054DRCT	296-23434-1-ND	White LED Backlight Driver	10-SOIC	2.60	2.13 1.91
TPS61054DRCT	296-23434-2-ND	White LED Backlight Driver	10-SOIC	401.28	250
TPS61055DRCT	296-23435-1-ND	White LED Backlight Driver	10-SOIC	2.48	2.03 1.82
TPS61055DRCT	296-23435-2-ND	White LED Backlight Driver	10-SOIC	382.07	250
TPS61058DRCR	296-18728-1-ND	Photo Flash LED Driver	10-SOIC	2.31	1.79 1.62
TPS61058DRCR	296-18728-2-ND	Photo Flash LED Driver	10-SOIC	2676.56	3,000
TPS61059DRCT	296-19426-1-ND	Photo Flash LED Driver	10-SOIC	2.48	2.03 1.82
TPS61059DRCT	296-19426-2-ND	Photo Flash LED Driver	10-SOIC	382.07	250
TPS61059EVM-141	296-19609-ND	Evaluation Module for TPS61059		41.31	—
TPS61060DBRR	296-17500-1-ND	White LED Backlight Driver	8-SOIC	2.46	1.90 1.73
TPS61060DBRR	296-17500-2-ND	White LED Backlight Driver	8-SOIC	2845.09	3,000
TPS61060YZR	296-19296-1-ND	White LED Backlight Driver	8-DSBGA	2.75	2.12 1.93
TPS61060YZR	296-19296-2-ND	White LED Backlight Driver	8-DSBGA	3178.66	3,000
TPS61060YZF	296-17745-1-ND	White LED Backlight Driver	8-DSBGA	2.60	2.13 1.91
TPS61060YZF	296-17745-2-ND	White LED Backlight Driver	8-DSBGA	401.28	250
TPS61061DBRR	296-17499-1-ND	White LED Backlight Driver	8-SOIC	2.60	2.01 1.83
TPS61061DBRR	296-17499-2-ND	White LED Backlight Driver	8-SOIC	3011.13	3,000
TPS61061EVM-091	296-17517-ND	Evaluation Module for TPS61061-091		41.31	—
TPS61061YZF	296-17746-1-ND	White LED Backlight Driver	8-DSBGA	2.85	2.33 2.09
TPS61061YZF	296-17746-2-ND	White LED Backlight Driver	8-DSBGA	439.49	250