

TEXAS INSTRUMENTS <b>Digi+Reel</b> (Cont.)		POWER SUPPLY PRODUCTS			
		RoHS Compliant Parts Available			
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	
				1	25 100
TPS3809K330DBVRQ1	296-15644-1-ND	2.93V Supply Voltage Supervisor	SOT-23-3	.82	.64 .57
TPS3809K330DBVRQ1	296-15644-2-ND	2.93V Supply Voltage Supervisor	SOT-23-3	812.88/3,000	
TPS3809K330MDBVREP	296-22439-1-ND	3.3V Supply Voltage Supervisor	SOT-23-3	1.85	1.43 1.30
TPS3809K330MDBVREP	296-22439-2-ND	3.3V Supply Voltage Supervisor	SOT-23-3	2141.25/3,000	
TPS3809L330DBVR	296-10917-1-ND	2.64V Supply Voltage Supervisor	SOT-23-3	.85	.67 .59
TPS3809L330DBVR	296-10917-2-ND	2.64V Supply Voltage Supervisor	SOT-23-3	845.10/3,000	
TPS3809L330DBVT	296-2632-1-ND	2.64V Supply Voltage Supervisor	SOT-23-3	.85	.67 .61
TPS3809L330DBVT	296-2632-2-ND	2.64V Supply Voltage Supervisor	SOT-23-3	119.99/250	
TPS3809L30MDBVREP	296-22440-1-ND	3V Supply Voltage Supervisor	SOT-23-3	1.85	1.43 1.30
TPS3809L30MDBVREP	296-22440-2-ND	3V Supply Voltage Supervisor	SOT-23-3	2141.25/3,000	
TPS3809L300DBVRQ1	296-15645-1-ND	2.64V Supply Voltage Supervisor	SOT-23-3	.87	.69 .62
TPS38131500DBVRQ1	296-24776-1-ND	4.55V Supervisor with Programmable Watchdog Window*	SOT-23-6	2.60	2.13 1.91
TPS38131500DBVRQ1	296-24776-2-ND	4.55V Supervisor with Programmable Watchdog Window*	SOT-23-6	3460.95/3,000	
TPS3813K33MDBVREP	296-22441-1-ND	3.3V Processor Supervisory Circuit	SOT-23-6	5.70	4.66 4.19
TPS3813K33MDBVREP	296-22441-2-ND	3.3V Processor Supervisory Circuit	SOT-23-6	7581.12/3,000	
TPS3820-33DBVT	296-2633-1-ND	2.93V Supply Monitor	SOT-23-5	1.59	1.23 1.12
TPS3820-33DBVT	296-2633-2-ND	2.93V Supply Monitor	SOT-23-5	227.18/250	
TPS3820-330DBVRQ1	296-15646-1-ND	2.93V Supply Monitor	SOT-23-5	1.59	1.23 1.12
TPS3820-330DBVRQ1	296-15646-2-ND	2.93V Supply Monitor	SOT-23-5	1841.38/3,000	
TPS3820-50DBVT	296-2635-1-ND	4.55V Supply Monitor	SOT-23-5	1.59	1.23 1.12
TPS3820-50DBVT	296-2635-2-ND	4.55V Supply Monitor	SOT-23-5	227.18/250	
TPS3823-25DBVR	296-3333-1-ND	2.25V Supply Monitor	SOT-23-5	1.71	1.32 1.20
TPS3823-25DBVR	296-3333-2-ND	2.25V Supply Monitor	SOT-23-5	1975.21/3,000	
TPS3823-250DBVRQ1	296-15648-1-ND	2.25V Supply Monitor	SOT-23-5	1.94	1.50 1.36
TPS3823-300DBVR	296-3334-1-ND	2.63V Supply Monitor	SOT-23-5	1.45	1.15 1.04
TPS3823-300DBVR	296-3334-2-ND	2.63V Supply Monitor	SOT-23-5	1603.46/3,000	
TPS3823-300DBVRQ1	296-15649-1-ND	2.63V Supply Monitor	SOT-23-5	1.59	1.23 1.12
TPS3823-330DBVR	296-1357-1-ND	2.93V Supply Monitor	SOT-23-5	1.32	1.05 .94
TPS3823-330DBVR	296-1357-2-ND	2.93V Supply Monitor	SOT-23-5	1457.24/3,000	
TPS3823-50DBVR	296-3335-1-ND	4.55V Supply Monitor	SOT-23-5	1.45	1.15 1.04
TPS3823-50DBVR	296-3335-2-ND	4.55V Supply Monitor	SOT-23-5	1603.46/3,000	
TPS3823-50DBVT	296-10922-1-ND	4.55V Supply Monitor	SOT-23-5	1.59	1.23 1.12
TPS3823-50DBVT	296-10922-2-ND	4.55V Supply Monitor	SOT-23-5	227.18/250	
TPS3824-300DBVR	296-3337-1-ND	2.63V Supply Monitor	SOT-23-5	1.45	1.12 1.02
TPS3824-300DBVR	296-3337-2-ND	2.63V Supply Monitor	SOT-23-5	1672.85/3,000	
TPS3824-330DBVR	296-3338-1-ND	2.93V Supply Monitor	SOT-23-5	1.45	1.15 1.04
TPS3824-330DBVR	296-3338-2-ND	2.93V Supply Monitor	SOT-23-5	1603.46/3,000	
TPS3824-330DBVT	296-2695-1-ND	2.93V Supply Monitor*	SOT-23-5	1.59	1.23 1.12
TPS3824-330DBVT	296-2695-2-ND	2.93V Supply Monitor*	SOT-23-5	227.18/250	
TPS3824-50DBVR	296-1358-1-ND	4.55V Supply Monitor	SOT-23-5	1.45	1.12 1.02
TPS3824-50DBVR	296-1358-2-ND	4.55V Supply Monitor	SOT-23-5	1672.85/3,000	
TPS3825-330DBVT	296-2636-1-ND	2.93V Supply Monitor	SOT-23-5	1.71	1.32 1.20
TPS3825-330DBVT	296-2636-2-ND	2.93V Supply Monitor	SOT-23-5	243.70/250	
TPS3825-50DBVT	296-2637-1-ND	4.55V Supply Monitor	SOT-23-5	1.45	1.12 1.02
TPS3825-50DBVT	296-2637-2-ND	4.55V Supply Monitor	SOT-23-5	206.53/250	
TPS3825-500DBVRQ1	296-15657-1-ND	4.55V Supply Monitor	SOT-23-5	1.45	1.12 1.02
TPS3828-330DBVT	296-2638-1-ND	2.93V Supply Monitor	SOT-23-5	1.59	1.23 1.12
TPS3828-330DBVT	296-2638-2-ND	2.93V Supply Monitor	SOT-23-5	227.18/250	
TPS3828-500DBVT	296-2639-1-ND	4.55V Supply Monitor	SOT-23-5	1.71	1.32 1.20
TPS3828-500DBVT	296-2639-2-ND	4.55V Supply Monitor	SOT-23-5	243.70/250	
TPS3828-500DBVRG40	296-24436-1-ND	5V Supply Monitor*	SOT-23-5	1.83	1.41 1.28
TPS3828-500DBVRG40	296-24436-2-ND	5V Supply Monitor*	SOT-23-5	2107.79/3,000	
TPS3828-500DBVRQ1	296-15659-1-ND	4.55V Supply Monitor*	SOT-23-5	1.83	1.41 1.28
TPS3836E180DBVRQ1	296-15660-1-ND	1.71V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3836E180DBVRQ1	296-15660-2-ND	1.71V Low Current Monitor	SOT-23-5	3296.14/3,000	
TPS3836H300DBVRQ1	296-15661-1-ND	2.79V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3836J25DBVT	296-3340-1-ND	2.25V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3836J25DBVT	296-3340-2-ND	2.25V Low Current Monitor	SOT-23-5	382.07/250	
TPS3836J250DBVRQ1	296-15662-1-ND	2.25V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3836K33DBVT	296-3341-1-ND	2.93V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3836K33DBVT	296-3341-2-ND	2.93V Low Current Monitor	SOT-23-5	382.07/250	
TPS3836K330DBVRQ1	296-15663-1-ND	2.93V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3836K330DBVRQ1	296-15663-2-ND	2.93V Low Current Monitor	SOT-23-5	3296.14/3,000	
TPS3836L300DBVRQ1	296-15664-1-ND	2.64V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3836L300DBVRQ1	296-15664-2-ND	2.64V Low Current Monitor	SOT-23-5	3296.14/3,000	
TPS3837E180DBVT	296-3343-1-ND	1.71V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3837E180DBVRQ1	296-15665-1-ND	1.71V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3837E180DBVRQ1	296-15665-2-ND	1.71V Low Current Monitor	SOT-23-5	3296.14/3,000	
TPS3837J25DBVT	296-3344-1-ND	2.25V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3837K33DBVT	296-3345-1-ND	2.93V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3837K33DBVT	296-3345-2-ND	2.93V Low Current Monitor	SOT-23-5	382.07/250	
TPS3837K330DBVREP	296-20786-1-ND	2.93V Low Current Monitor	SOT-23-5	2.87	2.35 2.11
TPS3838E180MDBVREP	296-22442-1-ND	1.8V Nanopower Supervisory Circuit	SOT-23-5	2.48	2.03 1.82
TPS3838E180MDBVREP	296-22442-2-ND	1.8V Nanopower Supervisory Circuit	SOT-23-5	3296.14/3,000	
TPS3838E180DBVRQ1	296-15669-1-ND	1.71V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3838E180DBVRQ1	296-15669-2-ND	1.71V Low Current Monitor	SOT-23-5	3296.14/3,000	
TPS3838K33DBVT	296-3349-1-ND	2.93V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3838K33DBVT	296-3349-2-ND	2.93V Low Current Monitor	SOT-23-5	382.07/250	
TPS3838K33DRVR	296-22631-1-ND	2.93V Low Current Monitor	6-SOIC	2.75	2.12 1.93
TPS3838K33DRVR	296-22631-2-ND	2.93V Low Current Monitor	6-SOIC	3179.66/3,000	
TPS3838K33MDBVREP	296-22444-1-ND	3.3V Nanopower Supervisory Circuit	SOT-23-5	2.48	2.03 1.82
TPS3838K33MDBVREP	296-22444-2-ND	3.3V Nanopower Supervisory Circuit	SOT-23-5	3296.14/3,000	
TPS3838K330DBVRQ1	296-15670-1-ND	2.93V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3838K330DBVRQ1	296-15670-2-ND	2.93V Low Current Monitor	SOT-23-5	3296.14/3,000	
TPS3838L30DBVT	296-3350-1-ND	2.64V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS3838L30DBVT	296-3350-2-ND	2.64V Low Current Monitor	SOT-23-5	382.07/250	
TPS3838L300DBVRQ1	296-15671-1-ND	2.64V Low Current Monitor	SOT-23-5	2.48	2.03 1.82
TPS38600RGPT	296-25181-1-ND	Programmable Quad Supply Voltage Monitor*	20-QFN	2.73	2.23 2.00
TPS38600RGPT	296-25181-2-ND	Programmable Quad Supply Voltage Monitor*	20-QFN	420.28/250	
TPS386040RGPT	296-25182-1-ND	Programmable Quad Supply Voltage Monitor*	20-QFN	2.73	2.23 2.00
TPS386040RGPT	296-25182-2-ND	Programmable Quad Supply Voltage Monitor*	20-QFN	420.28/250	

TEXAS INSTRUMENTS <b>Digi+Reel</b> (Cont.)		POWER SUPPLY PRODUCTS			
		RoHS Compliant Parts Available			
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	
				1	25 100
TPS65191RHBR	296-24956-1-ND	Triple High-Voltage Scan Driver*	32-QFN	2.49	1.92 1.75
TPS65191RHBR	296-24956-2-ND	Triple High-Voltage Scan Driver*	32-QFN	2877.31/3,000	
TPS65193RGER	296-24943-1-ND	5-Ch. Level Shifter for LCD Displays*	24-VQFN	1.97	1.52 1.38
TPS65193RGER	296-24943-2-ND	5-Ch. Level Shifter for LCD Displays*	24-VQFN	2275.08/3,000	
TWL1200ZOCR	296-24629-1-ND	19-Bit Voltage Transceiver*	48-BGA	3.72	3.04 2.73
TWL1200ZOCR	296-24629-2-ND	19-Bit Voltage Transceiver*	48-BGA	4120.17/2,500	
TXB0101DBVR	296-21664-1-ND	1-Bit Bidirectional Voltage Level Translator	SOT-23-6	.73	.57 .50
TXB0101DBVR	296-21664-2-ND	1-Bit Bidirectional Voltage Level Translator	SOT-23-6	718.71/3,000	
TXB0101DCKR	296-22861-1-ND	1-Bit Bidirectional Voltage Level Translator	SC70-6	.73	.57 .50
TXB0101DCKR	296-22861-2-ND	1-Bit Bidirectional Voltage Level Translator	SC70-6	718.71/3,000	
TXB0101DLRL	296-24665-1-ND	1-Bit Bidirectional Voltage Level Translator*	6-SOT	.73	.57 .50
TXB0101DLRL	296-24665-2-ND	1-Bit Bidirectional Voltage Level Translator*	6-SOT	958.28/4,000	
TXB0102DCKR	296-22862-1-ND	2-Bit Bidirectional Voltage Level Translator	8-US8	1.22	.97 .87
TXB0102DCKR	296-22862-2-ND	2-Bit Bidirectional Voltage Level Translator	8-US8	1353.15/3,000	
TXB0102YZPR	296-21961-1-ND	2-Bit Bidirectional Voltage Level Translator	8-DSBGA	1.30	1.03 .93
TXB0104DR	296-21928-1-ND	4-Bit Bidirectional Voltage Level Translator	14-SOIC	1.59	1.23 1.12
TXB0104PWR	296-21929-1-ND	4-Bit Bidirectional Voltage Level Translator	14-TSSOP	1.59	1.23 1.12
TXB0104PWR	296-21929-2-ND	4-Bit Bidirectional Voltage Level Translator	14-TSSOP	1227.58/2,000	
TXB0104RGYR	296-21930-1-ND	4-Bit Bidirectional Voltage Level Translator	14-QFN	1.59	1.23 1.12
TXB0104YZTR	296-24804-1-ND	4-Bit Bidirectional Voltage Level Translator*	12-DSBGA	1.73	1.34 1.22
TXB0104YZTR	296-24804-2-ND	4-Bit Bidirectional Voltage Level Translator*	12-DSBGA	2007.42/3,000	
TXB0104ZXUR	296-20795-1-ND	4-Bit Bidirectional Voltage Level Translator	12-BGA	1.59	1.23 1.12
TXB0104ZXUR	296-20795-2-ND	4-Bit Bidirectional Voltage Level Translator	12-BGA	1534.48/2,500	
TXB01061PWRQ1	296-24960-1-ND	6-Bit Bidirectional Voltage Level Translator*	16-TSSOP	2.17	1.68 1.52
TXB01061PWRQ1	296-24960-2-ND	6-Bit Bidirectional Voltage Level Translator*	16-TSSOP	1673.68/2,000	
TXB0106PWR	296-23759-1-ND	6-Bit Bidirectional Voltage Level Translator	16-TSSOP	2.02	1.57 1.42
TXB0108XYR	296-22000-1-ND	8-Bit Bidirectional Voltage Level Translator	20-BGA	2.31	1.79 1.62
TXB0108XYR	296-22000-2-ND	8-Bit Bidirectional Voltage Level Translator	20-BGA	2230.47/2,500	
TXS0101DBVR	296-22863-1-ND	1-Bit Bidirectional Voltage Level Translator	SOT-23-6	.73	.57 .50
TXS0101DBVR	296-22863-2-ND	1-Bit Bidirectional Voltage Level Translator	SOT-23-6	718.71/3,000	
TXS0101DCKR	296-22864-1-ND	1-Bit Bidirectional Voltage Level Translator	SC70-6	.73	.57 .50
TXS0101DCKR	296-22864-2-ND	1-Bit Bidirectional Voltage Level Translator	SC70-6	718.71/3,000	
TXS0101YZPR	296-24805-1-ND	1-Bit Bidirectional Voltage Level Translator*	6-DSBGA	.88	.68 .60
TXS0101YZPR	296-24805-2-ND	1-Bit Bidirectional Voltage Level Translator*	6-DSBGA	862.45/3,000	
TXS0102DCKR	296-21978-1-ND	2-Bit Bidirectional Voltage Level Translator	SM8	1.03	.82 .74
TXS0102DCKR	296-21978-2-ND	2-Bit Bidirectional Voltage Level Translator	SM8	1144.97/3,000	
TXS0102DCUR	296-21931-1-ND	2-Bit Bidirectional Voltage Level Translator	8-US8	1.03	.82 .74
TXS0102DCUR	296-21931-2-ND	2-Bit Bidirectional Voltage Level Translator	8-US8	1144.97/3,000	
TXS0102YZPR	296-21932-1-ND	2-Bit Bidirectional Voltage Level Translator	8-DSBGA	1.10	