
 POWER SUPPLY PRODUCTS RoHS Compliant Parts Available					
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each**	
				1	25 100
TL4050C10IDCKR	296-22812-1-ND	10V Precision Micropower Shunt Voltage Reference	SC70-5	1.13	90 81
TL4050C10IDCKR	296-22812-2-ND	10V Precision Micropower Shunt Voltage Reference	SC70-5	1249.06/3,000	
TL4050C100DBZR	296-22813-1-ND	10V Precision Micropower Shunt Voltage Reference	SOT-23-3	1.38	1.10 .99
TL4050C100DBZR	296-22813-2-ND	10V Precision Micropower Shunt Voltage Reference	SOT-23-3	1526.63/3,000	
TL4050C100DCKR	296-22814-1-ND	10V Precision Micropower Shunt Voltage Reference	SC70-5	1.50	1.19 1.08
TL4050C100DCKR	296-22814-2-ND	10V Precision Micropower Shunt Voltage Reference	SC70-5	1665.42/3,000	
TL4050C200DBZRQ1	296-24672-1-ND	2.048V Precision Micropower Shunt Voltage Reference*	SOT-23-3	1.54	1.22 1.10
TL4050C200DBZRQ1	296-24672-2-ND	2.048V Precision Micropower Shunt Voltage Reference*	SOT-23-3	1700.11/3,000	
TL4050C500DBZRQ1	296-24862-1-ND	5.0V Precision Micropower Shunt Voltage Reference*	SOT-23-3	1.19	.95 .85
TL4050C500DBZRQ1	296-24862-2-ND	5.0V Precision Micropower Shunt Voltage Reference*	SOT-23-3	1318.46/3,000	
TL4051B12IDBZR	296-22832-1-ND	1.2V Precision Micropower Shunt Voltage Reference	SOT-23-3	1.26	1.00 .90
TL4050C25IDBZR	296-22815-1-ND	2.5V Precision Micropower Shunt Voltage Reference	SOT-23-3	1.03	.82 .74
TL4050C25IDBZR	296-22815-2-ND	2.5V Precision Micropower Shunt Voltage Reference	SOT-23-3	1144.97/3,000	
TL4050C25IDCKR	296-22816-1-ND	2.5V Precision Micropower Shunt Voltage Reference	SC70-5	1.13	.90 .81
TL4050C25IDCKR	296-22816-2-ND	2.5V Precision Micropower Shunt Voltage Reference	SC70-5	1249.06/3,000	
TL4050C25DDBZR	296-22817-1-ND	2.5V Precision Micropower Shunt Voltage Reference	SOT-23-3	1.38	1.10 .99
TL4050C25DDBZR	296-22817-2-ND	2.5V Precision Micropower Shunt Voltage Reference	SOT-23-3	1526.63/3,000	
TL4050C25DQCKR	296-22818-1-ND	2.5V Precision Micropower Shunt Voltage Reference	SC70-5	1.50	1.19 1.08
TL4050C25DQCKR	296-22818-2-ND	2.5V Precision Micropower Shunt Voltage Reference	SC70-5	1665.42/3,000	
TL4050C411DCKR	296-22820-1-ND	4.096V Precision Micropower Shunt Voltage Reference	SC70-5	1.13	.90 .81
TL4050C411DCKR	296-22820-2-ND	4.096V Precision Micropower Shunt Voltage Reference	SC70-5	1249.06/3,000	
TL4050C410DCKR	296-22822-1-ND	4.096V Precision Micropower Shunt Voltage Reference	SC70-5	1.50	1.19 1.08
TL4050C410DCKR	296-22822-2-ND	4.096V Precision Micropower Shunt Voltage Reference	SC70-5	1665.42/3,000	
TL4050C50IDBZR	296-22823-1-ND	5V Precision Micropower Shunt Voltage Reference	SOT-23-3	1.03	.82 .74
TL4050C50IDBZR	296-22823-2-ND	5V Precision Micropower Shunt Voltage Reference	SOT-23-3	1144.97/3,000	
TL4050C50IDCKR	296-22824-1-ND	5V Precision Micropower Shunt Voltage Reference	SC70-5	1.13	.90 .81
TL4050C50IDCKR	296-22824-2-ND	5V Precision Micropower Shunt Voltage Reference	SC70-5	1249.06/3,000	
TL4050C500DBZR	296-22825-1-ND	5V Precision Micropower Shunt Voltage Reference	SOT-23-3	1.38	1.10 .99
TL4050C500DBZR	296-22825-2-ND	5V Precision Micropower Shunt Voltage Reference	SOT-23-3	1526.63/3,000	
TL4050C500DCKR	296-22826-1-ND	5V Precision Micropower Shunt Voltage Reference	SC70-5	1.50	1.19 1.08
TL4050C500DCKR	296-22826-2-ND	5V Precision Micropower Shunt Voltage Reference	SC70-5	1665.42/3,000	
TL4051A12IDBZR	296-22827-1-ND	1.2V Precision Micropower Shunt Voltage Reference	SOT-23-3	1.68	1.45 1.32
TL4051A12IDBZR	296-22827-2-ND	1.2V Precision Micropower Shunt Voltage Reference	SOT-23-3	2174.71/3,000	
TL4051A12IDCKR	296-22828-1-ND	1.2V Precision Micropower Shunt Voltage Reference	SC70-5	2.02	1.57 1.42
TL4051A12IDCKR	296-22828-2-ND	1.2V Precision Micropower Shunt Voltage Reference	SC70-5	2341.99/3,000	
TL4051A12QDBZR	296-22829-1-ND	1.2V Precision Micropower Shunt Voltage Reference	SOT-23-3	2.02	1.57 1.42
TL4051A12QDBZR	296-22829-2-ND	1.2V Precision Micropower Shunt Voltage Reference	SOT-23-3	2341.99/3,000	
TL4051A12QDCKR	296-22830-1-ND	1.2V Precision Micropower Shunt Voltage Reference	SC70-5	2.31	1.79 1.62
TL4051A12QDCKR	296-22830-2-ND	1.2V Precision Micropower Shunt Voltage Reference	SC70-5	2676.56/3,000	
TL4051AIDBZR	296-22719-1-ND	Adj., Precision Micropower Shunt Voltage Reference	SOT-23-3	1.88	1.45 1.32
TL4051AIDBZR	296-22719-2-ND	Adj., Precision Micropower Shunt Voltage Reference	SOT-23-3	2174.71/3,000	
TL4051AIDCKR	296-22720-1-ND	Adj., Precision Micropower Shunt Voltage Reference	SC70-5	2.02	1.57 1.42
TL4051AIDCKR	296-22720-2-ND	Adj., Precision Micropower Shunt Voltage Reference	SC70-5	2341.99/3,000	
TL4051A0QBZR	296-22721-1-ND	Adj., Precision Micropower Shunt Voltage Reference	SOT-23-3	2.02	1.57 1.42
TL4051A0QBZR	296-22721-2-ND	Adj., Precision Micropower Shunt Voltage Reference	SOT-23-3	2341.99/3,000	
TL4051A0QCKR	296-22831-1-ND	Adjustable Precision Micropower Shunt Voltage Reference	SC70-5	2.31	1.79 1.62
TL4051A0QCKR	296-22831-2-ND	Adjustable Precision Micropower Shunt Voltage Reference	SC70-5	2676.56/3,000	
TL4051B12IDBZR	296-22832-2-ND	1.2V Precision Micropower Shunt Voltage Reference	SOT-23-3	1387.85/3,000	
TL4051B12IDCKR	296-22833-1-ND	1.2V Precision Micropower Shunt Voltage Reference	SC70-5	1.38	1.10 .99
TL4051B12IDCKR	296-22833-2-ND	1.2V Precision Micropower Shunt Voltage Reference	SC70-5	1526.63/3,000	
TL4051B12QDBZR	296-22834-1-ND	1.2V Precision Micropower Shunt Voltage Reference	SOT-23-3	1.54	1.22 1.10
TL4051B12QDBZR	296-22834-2-ND	1.2V Precision Micropower Shunt Voltage Reference	SOT-23-3	1700.11/3,000	
TL4051B12QDCKR	296-22835-1-ND	1.2V Precision Micropower Shunt Voltage Reference	SC70-5	1.59	1.23 1.12

 POWER SUPPLY PRODUCTS RoHS Compliant Parts Available					
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each**	
				1	25 100
TL4051B120DCKR	296-22835-2-ND	1.2V Precision Micropower Shunt Voltage Reference	SC70-5	1840.14/3,000	
TL4051BIDBZR	296-22722-1-ND	Adj., Precision Micropower Shunt Voltage Reference	SOT-23-3	1.26	1.00 .90
TL4051BIDBZR	296-22722-2-ND	Adj., Precision Micropower Shunt Voltage Reference	SOT-23-3	1387.85/3,000	
TL4051BIDCKR	296-22723-1-ND	Adj., Precision Micropower Shunt Voltage Reference	SC70-5	1.38	1.10 .99
TL4051BIDCKR	296-22723-2-ND	Adj., Precision Micropower Shunt Voltage Reference	SC70-5	1526.63/3,000	
TL4051B0QDBZR	296-22724-1-ND	Adj., Precision Micropower Shunt Voltage Reference	SOT-23-3	1.54	1.22 1.10
TL4051B0QDBZR	296-22724-2-ND	Adj., Precision Micropower Shunt Voltage Reference	SOT-23-3	1700.11/3,000	
TL4051B0QCKR	296-22725-1-ND	Adj., Precision Micropower Shunt Voltage Reference	SC70-5	1.59	1.23 1.12
TL4051B0QCKR	296-22725-2-ND	Adj., Precision Micropower Shunt Voltage Reference	SC70-5	1840.14/3,000	
TL4051C120DBZR	296-22838-1-ND	1.2V Precision Micropower Shunt Voltage Reference	SOT-23-3	1.38	1.10 .99
TL4051C120DBZR	296-22838-2-ND	1.2V Precision Micropower Shunt Voltage Reference	SOT-23-3	1526.63/3,000	
TL4051C120DCKR	296-22839-1-ND	1.2V Precision Micropower Shunt Voltage Reference	SC70-5	1.50	1.19 1.08
TL4051C120DCKR	296-22839-2-ND	1.2V Precision Micropower Shunt Voltage Reference	SC70-5	1665.42/3,000	
TL4051CIDBZR	296-22726-1-ND	Adj., Precision Micropower Shunt Reference	SOT-23-3	1.16	.92 .83
TL4051CIDBZR	296-22726-2-ND	Adj., Precision Micropower Shunt Reference	SOT-23-3	1283.76/3,000	
TL4051C0DBZR	296-22728-1-ND	Adj., Precision Micropower Shunt Reference	SOT-23-3	1.38	1.10 .99
TL4051C0DBZR	296-22728-2-ND	Adj., Precision Micropower Shunt Reference	SOT-23-3	1526.63/3,000	
Low Dropout Voltage Regulators					
DEM-SOT223LDO	296-20842-ND	Demo Module for SOT-223 LDOs	—	4.21	— —
DEM-SOT23LDO	296-20843-ND	Demo Module for SOT23-5 and SOT23-6 LDOs	—	4.21	— —
DEM-TO263LDO	296-20844-ND	Demo Module for TO220 and TO263 LDOs	—	4.21	— —
LP2950-33LPE3	296-26120-ND	Adj. Micropower Volt. Reg.*	TO-92	47	35 .30
LP2950-50LPRE3	296-20933-1-ND	5V, Adjustable Micropower Volt. Reg.	TO-92	.45	.32 .28
LP2950-50LPRE3	296-20933-2-ND	5V, Adjustable Micropower Volt. Reg.	TO-92	256.09/2,000	
LP2951-33D	296-26121-5-ND	Adj. Micropower Volt. Reg.*	8-SOIC	.61	.48 .42
LP2951-33DR	296-26122-1-ND	Adj. Micropower Volt. Reg.*	8-SOIC	.55	.43 .38
LP2951-33DR	296-26122-2-ND	Adj. Micropower Volt. Reg.*	8-SOIC	450.22/2,500	
LP2951-50D	296-26123-5-ND	Adj. Micropower Volt. Reg.*	8-SOIC	.61	.48 .42
LP2951DR	296-22748-1-ND	Adj. Micropower Voltage Regulator	8-SOIC	.55	.43 .38
LP2951DR	296-22748-2-ND	Adj. Micropower Voltage Regulator	8-SOIC	450.22/2,500	
LP2981-28DBVR	296-18472-1-ND	2.8V, 100mA LDO Regulator	SOT-23-5	.73	.57 .50
LP2981-28DBVR	296-18472-2-ND	2.8V, 100mA LDO Regulator	SOT-23-5	718.71/3,000	
LP2981-29DBVR	296-22749-1-ND	2.9V, 100mA LDO Regulator	SOT-23-5	.73	.57 .50
LP2981-29DBVR	296-22749-2-ND	2.9V, 100mA LDO Regulator	SOT-23-5	718.71/3,000	
LP2981-30DBVR	296-17546-1-ND	3V, 100mA LDO Regulator	SOT-23-5	.73	.57 .50
LP2981-30DBVR	296-17546-2-ND	3V, 100mA LDO Regulator	SOT-23-5	718.71/3,000	
LP2981-33DBVR	296-17360-1-ND	3.3V, 100mA LDO Regulator	SOT-23-5	.73	.57 .50
LP2981-33DBVR	296-17360-2-ND	3.3V, 100mA LDO Regulator	SOT-23-5	718.71/3,000	
LP2981-33MDBVREP	296-22177-1-ND	3.3V, 100mA LDO Regulator	SOT-23-5	2.48	2.03 1.82
LP2981-33MDBVREP	296-22177-2-ND	3.3V, 100mA LDO Regulator	SOT-23-5	3296.14/3,000	
LP2981-50DBVR	296-22750-1-ND	5V, 100mA LDO Regulator	SOT-23-5	.73	.57 .50
LP2981-50DBVR	296-22750-2-ND	5V, 100mA LDO Regulator	SOT-23-5	718.71/3,000	
LP2981A-28DBVR	296-18473-1-ND	2.8V, 100mA LDO Regulator	SOT-23-5	.80	.62 .55
LP2981A-28DBVR	296-18473-2-ND	2.8V, 100mA LDO Regulator	SOT-23-5	790.58/3,000	
LP2981A-29DBVR	296-22751-1-ND	2.9V, 100mA LDO Regulator	SOT-23-5	.80	.62 .55
LP2981A-29DBVR	296-22751-2-ND	2.9V, 100mA LDO Regulator	SOT-23-5	718.71/3,000	
LP2981A-30DBVR	296-17545-1-ND	3V, 100mA LDO Regulator	SOT-23-5	.80	.62 .55
LP2981A-30DBVR	296-17545-2-ND	3V, 100mA LDO Regulator	SOT-23-5	790.58/3,000	
LP2981A-33DBVR	296-17361-1-ND	3.3V, 100mA LDO Regulator	SOT-23-5	.80	.62 .55
LP2981A-33DBVR	296-17361-2-ND	3.3V, 100mA LDO Regulator	SOT-23-5	790.58/3,000	
LP2985-10DBVR	296-24263-1-ND	10V, 150mA LDO Regulator*	SOT-23-5	.65	.51 .45
LP2985-10DBVR	296-24263-2-ND	10V, 150mA LDO Regulator*	SOT-23-5	646.84/3,000	
LP2985-18DBVR	296-18474-1-ND	1.8V, 150mA LDO Regulator	SOT-23-5	.65	.51 .45
LP2985-18DBVR	296-18474-2-ND	1.8V, 150mA LDO Regulator	SOT-23-5	646.84/3,000	
LP2985-28DBVR	296-18475-1-ND	2.8V, 150mA LDO Regulator	SOT-23-5	.65	.51 .45
LP2985-28DBVR	296-18475-2-ND	2.8V, 150mA LDO Regulator	SOT-23-5	646.84/3,000	
LP2985-33DBVR	296-18476-1-ND	3.3V, 150mA LDO Regulator	SOT-23-5	.65	.51 .45
LP2985-33DBVR	296-18476-2-ND	3.3V, 150mA LDO Regulator	SOT-23-5	646.84/3,000	
LP2985-50DBVR	296-20717-1-ND	5V, 150mA LDO Regulator	SOT-23-5	.65	.51 .45
LP2985-50DBVR	296-20717-2-ND	5V, 150mA LDO Regulator	SOT-23-5	646.84/3,000	
LP2985A-10DBVR	296-24264-1-ND	10V, 150mA LDO Regulator*	SOT-23-5	.69	.54 .48
LP2985A-10DBVR	296-24264-2-ND	10V, 150mA LDO Regulator*	SOT-23-5	684.01/3,000	
LP2985A-18DBVR	296-18477-1-ND	1.8V, 150mA LDO Regulator	SOT-23-5	.69	.54 .48
LP2985A-18DBVR	296-18477-2-ND	1.8V, 150mA LDO Regulator	SOT-23-5	684.01/3,000	
LP2985A-28DBVR	296-18478-1-ND	2.8V, 150mA LDO Regulator	SOT-23-5	.69	.54 .48
LP2985A-28DBVR	296-18478-2-ND	2.8V, 150mA LDO Regulator	SOT-23-5	684.01/3,000	
LP2985A-33DBVR	296-18479-1-ND	3.3V, 150mA LDO Regulator	SOT-23-5	.69	.54 .48
LP2985A-33DBVR	296-18479-2-ND	3.3V, 150mA LDO Regulator	SOT-23-5	684.01/3,000	
LP2985A-50DBVR	296-26128-1-ND	5V, 150mA LDO Regulator*	SOT-23-5	.69	.54 .48
LP2985A-50DBVR	296-26128-2-ND	5V, 150mA LDO Regulator*	SOT-23-5	684.01/3,000	
REG101NA-A/250	296-9653-1-ND	Adj., DMOS 100mA LDO Regulator	SOT-23-5	2.60	2.13 1.91
REG101NA-A/250	296-9653-2-ND	Adj., DMOS 100mA LDO Regulator	SOT-23-5	401.28/250	
REG101NA-2.5/250	REG101NA-2.5CT-ND	2.5V DMOS 100mA LDO Regulator	SOT-23-5	3.35	2.74 2.46
REG101NA-2.5/250	REG101NA-2.5TR-ND	2.5V DMOS 100mA LDO Regulator	SOT-23-5	515.90/250	
REG101NA-2.8/250	REG101NA-2.8CT-ND	2.8V DMOS 100mA LDO Regulator	SOT-23-5	3.35	2.74 2.46
REG101NA-2.8/250	REG101NA-2.8TR-ND	2.8V DMOS 100mA LDO Regulator	SOT-23-5	515.90/250	
REG101NA-2.85/250	REG101NA-2.85CT-ND	2.85V DMOS 100mA LDO Regulator	SOT-23-5	3.35	2.74 2.46
REG101NA-2.85/250	REG101NA-2.85TR-ND	2.85V DMOS 100mA LDO Regulator	SOT-23-5	515.90/250	
REG101NA-3/250	REG101NA-3CT-ND	3V DMOS 100mA LDO Regulator	SOT-23-5	2.60	2.13 1.91
REG101NA-3/250	REG101NA-3TR-ND	3V DMOS 100mA LDO Regulator	SOT-23-5	401.28/250	
REG101NA-3.3/250	REG101NA-3.3CT-ND	3.3V DMOS 100mA LDO Regulator	SOT-23-5	2.60	2.13 1.91
REG101NA-3.3/250	REG101NA-3.3TR-ND	3.3V DMOS 100mA LDO Regulator	SOT-23-5	401.28/250	
REG101NA-5/250	REG101NA-5CT-ND	5V DMOS 100mA LDO Regulator	SOT-23-5	2.60	2.13 1.91
REG101NA-5/250	REG101NA-5TR-ND	5V DMOS 100mA LDO Regulator	SOT-23-5	401.28/250	
REG101UA-A	REG101UA-A-ND	Adj., 100mA LDO Regulator	8-SOIC	2	