

TEXAS INSTRUMENTS		Digi-Reel (Cont.)	POWER SUPPLY PRODUCTS RoHS Compliant Parts Available			
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	25	100
TPS715A33DRBT	296-17615-2-ND	3.3V, 80mA LDO Linear Regulator	8-SO8	227.18/250		
TPS715A33DRVR	296-22584-1-ND	3.3V, 80mA LDO Linear Regulator	6-SO6	1.54 1.22 1.10		
TPS715A33DRVTR	296-22584-2-ND	3.3V, 80mA LDO Linear Regulator	6-SO6	1700.11/3,000		
TPS758A01KTRTR	296-21900-1-ND	Adjustable, 3A LDO Regulator	5-DDPAK	5.91 4.91 4.47		
TPS769A01KTRTR	296-21901-1-ND	Adjustable, 3A LDO Regulator	5-DDPAK	1728.61/500		
TPS7670301MPWPREF	296-21351-1-ND	Dual Adj. 1.8V/3.3V LDO Regulator	28-HTSSOP	7.44 6.18 5.62		
TPS7670301MPWPREF	296-21351-2-ND	Dual Adj. 1.8V/3.3V LDO Regulator	28-HTSSOP	7302.72/2,000		
TPS7670301PWP	296-2740-5-ND	Dual Adj. 1.8V/3.3V LDO Regulator	28-HTSSOP	5.44 4.37 3.98		
TPS7670301PWPDP	296-19002-1-ND	Dual Adj. 1.8V/3.3V LDO Regulator	28-HTSSOP	5.70 4.66 4.19		
TPS7670301PWPDP	296-19002-2-ND	Dual Adj. 1.8V/3.3V LDO Regulator	28-HTSSOP	5054.08/2,000		
TPS76703180PWPDP	296-19003-1-ND	Dual 1.8V/3.3V LDO Regulator	28-HTSSOP	5.70 4.66 4.19		
TPS76703180PWPDP	296-19003-2-ND	Dual 1.8V/3.3V LDO Regulator	28-HTSSOP	5054.08/2,000		
TPS76703180PWPDP	296-2741-5-ND	Dual 1.8V/3.3V LDO Regulator	28-HTSSOP	5.44 4.37 3.98		
TPS7670325PWPREF	296-2742-5-ND	Dual 2.5V/3.3V LDO Regulator	28-HTSSOP	5.44 4.37 3.98		
TPS7670325PWPREF	296-22515-1-ND	Dual 2.5V/3.3V LDO Regulator	28-HTSSOP	2.48 2.03 1.82		
TPS7670325PWPREF	296-22515-2-ND	Dual 2.5V/3.3V LDO Regulator	28-HTSSOP	2197.43/2,000		
TPS7670325PWPDP	296-17532-1-ND	Dual 2.5V/3.3V LDO Regulator	28-HTSSOP	5.70 4.66 4.19		
TPS7670325PWPDP	296-17532-2-ND	Dual 2.5V/3.3V LDO Regulator	28-HTSSOP	5054.08/2,000		
TPS799XKVM-105	296-21172-ND	Evaluation Module for TPS799XX		8.43		
TPS21401PWP	296-12564-5-ND	Adj. LDO, 3.3V Switch, Dual Current Limit	14-HTSSOP	3.93 3.16 2.88		
TPS21501PWP	296-12566-5-ND	Adj. LDO, 5V Switch, Dual Curr. Limit	14-HTSSOP	3.93 3.16 2.88		
TPS2151PWP	296-12567-5-ND	Adj. LDO, 5V Switch, Dual Curr. Limit	14-HTSSOP	3.93 3.16 2.88		
TPS71010DR	296-1359-1-ND	Adj. 1.2V-9.75V, 500mA LDO Reg.	8-SOIC	3.22 2.64 2.37		
TPS71010DR	296-1359-2-ND	Adj. 1.2V-9.75V, 500mA LDO Reg.	8-SOIC	3570.82/2,500		
TPS71010P	296-8041-5-ND	Adj. 1.2V-9.75V, 500mA LDO Reg.	8-Dip	3.01 2.42 2.21		
TPS71010PWR	296-8042-1-ND	Adj. 1.2V-9.75V, 500mA LDO Reg.	20-TSSOP	3.22 2.64 2.37		
TPS71010PWR	296-8042-2-ND	Adj. 1.2V-9.75V, 500mA LDO Reg.	20-TSSOP	2866.65/2,000		
TPS71330D	296-8046-5-ND	3.3V, 500mA PMOS LDO Regulator	8-SOIC	2.70 2.98 2.71		
TPS71330P	296-8046-6-ND	3.3V, 500mA PMOS LDO Regulator	8-Dip	3.01 2.42 2.21		
TPS71330PWR	296-8047-1-ND	3.3V, 500mA PMOS LDO Regulator	20-TSSOP	3.22 2.64 2.37		
TPS71330PWR	296-8047-2-ND	3.3V, 500mA PMOS LDO Regulator	20-TSSOP	2866.65/2,000		
TPS71480D	296-1961-5-ND	4.8V, 500mA LDO Regulator	8-SOIC	3.01 2.42 2.21		
TPS71480P	296-1961-6-ND	4.8V, 500mA LDO Regulator	8-Dip	3.01 2.42 2.21		
TPS71500D	296-8049-5-ND	5V, 500mA LDO Regulator	8-SOIC	2.70 2.98 2.71		
TPS71500P	296-8050-5-ND	5V, 500mA LDO Regulator	8-Dip	2.59 2.09 1.91		
TPS72010D	296-1360-5-ND	Adjustable 250mA LDO Regulator	8-SOIC	2.05 1.66 1.49		
TPS72010DR	296-1360-1-ND	Adjustable 250mA LDO Regulator	8-SOIC	1.88 1.45 1.32		
TPS72010DR	296-1360-2-ND	Adjustable 250mA LDO Regulator	8-SOIC	1813.29/2,500		
TPS72010P	296-8052-5-ND	Adjustable 250mA LDO Regulator	8-Dip	1.44 1.16 1.05		
TPS72010PWR	296-8053-1-ND	Adjustable 250mA LDO Regulator	8-TSSOP	1.88 1.45 1.32		
TPS72010PWR	296-8053-2-ND	Adjustable 250mA LDO Regulator	8-TSSOP	1449.81/2,000		
TPS72250D	296-1962-5-ND	2.5V, 250mA LDO Regulator	8-SOIC	2.05 1.66 1.49		
TPS72250P	296-1963-5-ND	2.5V, 250mA LDO Regulator	8-Dip	1.67 1.35 1.21		
TPS72300D	296-1964-5-ND	3.0V, 250mA LDO Regulator	8-SOIC	1.67 1.35 1.21		
TPS72300PWR	296-8055-1-ND	3.0V, 250mA LDO Regulator	8-TSSOP	1.88 1.45 1.32		
TPS72300PWR	296-8055-2-ND	3.0V, 250mA LDO Regulator	8-TSSOP	1449.81/2,000		
TPS72330D	296-8056-5-ND	3.3V, 250mA LDO Regulator	8-SOIC	2.05 1.66 1.49		
TPS72330P	296-8056-6-ND	3.3V, 250mA LDO Regulator	8-Dip	1.67 1.35 1.21		
TPS72330PWR	296-8057-1-ND	3.3V, 250mA LDO Regulator	8-TSSOP	1.88 1.45 1.32		
TPS72330PWR	296-8057-2-ND	3.3V, 250mA LDO Regulator	8-TSSOP	1449.81/2,000		
TPS72480D	296-8058-5-ND	4.85V, 250mA PMOS LDO Regulator	8-SOIC	2.05 1.66 1.49		
TPS72480P	296-2659-5-ND	4.85V, 250mA PMOS LDO Regulator	8-Dip	1.67 1.35 1.21		
TPS72500D	296-1361-5-ND	5.0V, 250mA LDO Regulator	8-SOIC	2.05 1.66 1.49		
TPS72500DR	296-1361-1-ND	5.0V, 250mA LDO Regulator	8-SOIC	1.88 1.45 1.32		
TPS72500DR	296-1361-2-ND	5.0V, 250mA LDO Regulator	8-SOIC	1812.26/2,500		
TPS72500P	296-8059-5-ND	5.0V, 250mA LDO Regulator	8-Dip	1.67 1.35 1.21		
TPS72500PWR	296-8060-1-ND	5.0V, 250mA LDO Regulator	8-TSSOP	1.88 1.45 1.32		
TPS72500PWR	296-8060-2-ND	5.0V, 250mA LDO Regulator	8-TSSOP	1449.81/2,000		
TPS73010D	296-1362-5-ND	Adjustable 500mA LDO Regulator	8-SOIC	3.12 2.51 2.29		
TPS73010DR	296-1362-1-ND	Adjustable 500mA LDO Regulator	8-SOIC	2.73 2.23 2.00		
TPS73010P	296-1362-2-ND	Adjustable 500mA LDO Regulator	8-SOIC	3021.46/2,500		
TPS73010P	296-2660-5-ND	Adjustable 500mA LDO Regulator	8-Dip	2.54 2.05 1.87		
TPS73230D	296-8061-5-ND	Adjustable 500mA LDO Regulator	20-TSSOP	3.12 2.51 2.29		
TPS73250D	296-2661-5-ND	2.5V, 500mA LDO Reg., Delay Reset	8-SOIC	2.54 2.05 1.87		
TPS73250P	296-8062-5-ND	2.5V, 500mA LDO Reg., Delay Reset	8-Dip	2.54 2.05 1.87		
TPS73250PWR	296-8063-1-ND	2.5V, 500mA LDO Reg., Delay Reset	20-TSSOP	2.73 2.23 2.00		
TPS73250PWR	296-8063-2-ND	2.5V, 500mA LDO Reg., Delay Reset	20-TSSOP	2417.17/2,000		
TPS73300D	296-2662-5-ND	3.0V, 500mA LDO Reg., Delay Reset	8-SOIC	3.12 2.51 2.29		
TPS73300DR	296-2662-1-ND	3.0V, 500mA LDO Reg., Delay Reset	8-SOIC	2.73 2.23 2.00		
TPS73300DR	296-2662-2-ND	3.0V, 500mA LDO Reg., Delay Reset	8-SOIC	3021.46/2,500		
TPS73300P	296-8064-5-ND	3.0V, 500mA LDO Reg., Delay Reset	8-Dip	2.54 2.05 1.87		
TPS73330D	296-8066-5-ND	3.3V, 500mA LDO Reg., Delay Reset	8-SOIC	3.12 2.51 2.29		
TPS73330DR	296-8066-1-ND	3.3V, 500mA LDO Reg., Delay Reset	8-SOIC	2.73 2.23 2.00		
TPS73330DR	296-8066-2-ND	3.3V, 500mA LDO Reg., Delay Reset	8-SOIC	3021.46/2,500		
TPS73330P	296-2663-5-ND	3.3V, 500mA LDO Reg., Delay Reset	8-Dip	2.54 2.05 1.87		
TPS73330PWR	296-8067-1-ND	3.3V, 500mA LDO Reg., Delay Reset	20-TSSOP	2.73 2.23 2.00		
TPS73330PWR	296-8067-2-ND	3.3V, 500mA LDO Reg., Delay Reset	20-TSSOP	2417.17/2,000		
TPS73480D	296-8068-5-ND	4.85V, 500mA LDO Reg., Delay Reset	8-SOIC	3.12 2.51 2.29		
TPS73480DR	296-8068-1-ND	4.85V, 500mA LDO Reg., Delay Reset	8-SOIC	2.73 2.23 2.00		
TPS73480DR	296-8068-2-ND	4.85V, 500mA LDO Reg., Delay Reset	8-SOIC	3021.46/2,500		
TPS73480P	296-2664-5-ND	4.85V, 500mA LDO Reg., Delay Reset	8-Dip	2.20 1.77 1.61		
TPS73500D	296-8069-5-ND	5.0V, 500mA LDO Reg., Delay Reset	8-SOIC	3.12 2.51 2.29		
TPS73500P	296-2665-5-ND	5.0V, 500mA LDO Reg., Delay Reset	8-Dip	2.20 1.77 1.61		
TPS73500PWR	296-8070-1-ND	5.0V, 500mA LDO Reg., Delay Reset	20-TSSOP	2.73 2.23 2.00		
TPS73500PWR	296-8070-2-ND	5.0V, 500mA LDO Reg., Delay Reset	20-TSSOP	2417.17/2,000		
TPS7418D	296-2668-5-ND	1.5V, 200mA LDO Regulator	8-SOIC	1.92 1.55 1.40		
TPS7418D	296-2669-5-ND	1.8V, 200mA LDO Regulator	8-SOIC	1.92 1.55 1.40		
TPS7425D	296-2670-5-ND	2.5V, 200mA LDO Regulator	8-SOIC	2.30 1.86 1.68		
TPS7430D	296-2671-5-ND	3.0V, 200mA LDO Regulator	8-SOIC	1.92 1.55 1.40		
TPS7433D	296-2672-5-ND	3.3V, 200mA LDO Regulator	8-SOIC	2.30 1.86 1.68		
TPS51103DRCR	296-23707-1-ND	Integ. LDO, Switchover Circuit	10-SOON	2.48 2.03 1.82		
TPS51103DRCR	296-23707-2-ND	Integ. LDO, Switchover Circuit	10-SOON	3296.14/3,000		
TPS70102PWP	296-2652-5-ND	Dual, 3.3V/1.2V, 500mA LDO Reg.	20-TSSOP	4.14 3.35 3.05		
TPS70148PWP	296-2654-5-ND	Dual, 3.3V/1.5V, 500mA LDO Reg.	20-TSSOP	5.20 4.19 3.82		
TPS70151EVM-152	296-10986-ND	Evaluation Module for TPS7015	—	83.44		
TPS70151PWP	296-2655-5-ND	Dual, 3.3V/1.8V, 500mA LDO Reg.	20-TSSOP	4.16 3.35 3.05		
TPS70158PWP	296-2656-5-ND	Dual, 3.3V/2.5V, 500mA LDO Reg.	20-TSSOP	5.20 4.19 3.82		
TPS70202PWP	296-8016-5-ND	Dual, Adj., 500mA LDO Regulator	20-TSSOP	5.20 4.19 3.82		
TPS70204PWP	296-8017-5-ND	Dual, 3.3V/1.2V, 500mA/250mA LDO Regulator	20-TSSOP	5.20 4.19 3.82		
TPS70248PWP	296-8018-5-ND	Dual, 3.3V/1.5V, 500mA/250mA LDO Regulator	20-TSSOP	5.20 4.19 3.82		

TEXAS INSTRUMENTS		Digi-Reel (Cont.)	POWER SUPPLY PRODUCTS RoHS Compliant Parts Available			
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	25	100
TPS70251PWP	296-8019-5-ND	Dual, 3.3V/1.8V, 500mA/250mA LDO Regulator	20-HTSSOP	5.20 4.19 3.82		
TPS70258PWP	296-8020-5-ND	Dual, 3.3V/2.5V, 500mA/250mA LDO Regulator	20-HTSSOP	5.20 4.19 3.82		
TPS70302PWP	296-8021-5-ND	Dual, 3.3V, 1A/2A LDO Regulator	24-HTSSOP	5.78 4.75 4.28		
TPS70345MPWPREF	296-21274-1-ND	Dual, 3.3V/1.2V, 1A/2A LDO Regulator	24-HTSSOP	8.76 7.27 6.61		
TPS70345MPWPREF	296-21274-2-ND	Dual, 3.3V/1.2V, 1A/2A LDO Regulator	24-HTSSOP	8691.44/2,000		
TPS70345PWP	296-8022-5-ND	Dual, 3.3V/1.2V, 1A/2A LDO Regulator	24-HTSSOP	5.78 4.75 4.28		
TPS70348PWP	296-8023-5-ND	Dual, 3.3V/1.5V, 1A/2A LDO Regulator	—	5.78 4.75 4.28		
TPS70351EVM-165	296-10987-ND	Evaluation Module for TPS70351	—	83.44		
TPS70351PWP	296-8024-5-ND	Dual, 3.3V/1.8V, 1A/2A LDO Regulator	24-HTSSOP	5.78 4.75 4.28		
TPS70358PWP	296-8025-5-ND	Dual, 3.3V/2.5V, 1A/2A LDO Regulator	24-HTSSOP	5.78 4.75 4.28		
TPS70402PWP	296-8026-5-ND	Dual, Adj., 1A/2A LDO Regulator	24-HTSSOP	5.78 4.75 4.28		
TPS70445PWP	296-8027-5-ND	Dual, 3.3V/1.2V, 1A/2A LDO Regulator	24-HTSSOP	5.78 4.75 4.28		
TPS70448PWP	296-8028-5-ND	Dual, 3.3V/1.5V, 1A/2A LDO Regulator	24-HTSSOP	5.78 4.75 4.28		
TPS70451PWP	296-8029-5-ND	Dual, 3.3V/1.8V, 1A/2A LDO Regulator	24-HTSSOP	5.78 4.75 4.28		
TPS70458PWP	296-8030-5-ND	Dual, 3.3V/2.5V, 1A/2A LDO Regulator	24-HTSSOP	5.78 4.75 4.28		
TPS70702PWP	296-8031-5-ND	Dual, Adj., 1A/2A LDO Regulator	20-HTSSOP	3.24 2.61 2.38		
TPS70745PWP	296-8032-5-ND	Dual, 3.3V/1.2V, 250mA/125mA LDO Regulator	20-HTSSOP			