

TEXAS INSTRUMENTS		DigiKey		POWER SUPPLY PRODUCTS		RoHS Compliant Parts Available	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	1	25	100
TPS736125DRBT	296-18252-1-ND	1.25V, 400mA LDO Regulator	8-SOIC	2.48	2.03	1.82	
TPS736125DRBT	296-18252-2-ND	1.25V, 400mA LDO Regulator	8-SOIC	382.07/250			
TPS793285DBVR	296-12157-1-ND	2.85V, 200mA, High PSRR, RF LDO Regulator	SOT-23-5	.79	.62	.55	
TPS793285DBVR	296-12157-2-ND	2.85V, 200mA, High PSRR, RF LDO Regulator	SOT-23-5	786.98/3,000			
TPS793285DBVT	296-27100-1-ND	2.85V, 200mA, High PSRR, RF LDO Regulator*	SOT-23-5	.78	.63	.56	
TPS793285DBVT	296-27100-2-ND	2.85V, 200mA, High PSRR, RF LDO Regulator*	SOT-23-5	111.52/250			
TPS793285YEOVM	296-19007-ND	Evaluation Module for TPS793285YEQ	—	8.43	—	—	
TPS793475DBVR	296-12160-1-ND	4.75V, 200mA, High PSRR, RF LDO Regulator	SOT-23-5	.79	.62	.55	
TPS793475DBVR	296-12160-2-ND	4.75V, 200mA, High PSRR, RF LDO Regulator	SOT-23-5	788.10/3,000			
TPS797285DCR	296-25465-1-ND	2.85V, 50mA LDO Regulator*	SC70-5	1.07	.85	.76	
TPS797285DCR	296-25465-2-ND	2.85V, 50mA LDO Regulator*	SC70-5	1179.67/3,000			
TPS799285DRVR	296-19747-1-ND	2.85V, 200mA LDO Regulator	6-SOIC	1.16	.92	.83	
TPS799285DRVR	296-19747-2-ND	2.85V, 200mA LDO Regulator	6-SOIC	1286.24/3,000			
TPS728120150DRVT	296-25585-1-ND	1.2V/1.5V, 200mA LDO Reg.*	6-SOIC	1.41	1.12	1.01	
TPS728120150DRVT	296-25585-2-ND	1.2V/1.5V, 200mA LDO Reg.*	6-SOIC	199.30/250			
TPS780230300DRVT	296-24206-1-ND	150mA, Ultralow Power, LDO Regulator*	6-SOIC	1.37	1.09	.98	
TPS780230300DRVT	296-24206-2-ND	150mA, Ultralow Power, LDO Regulator*	6-SOIC	194.13/250			
TPS780300250DRVR	296-24057-1-ND	2.5V or 3V Dual Level Output, 150mA LDO Regulator	6-SOIC	1.21	.96	.86	
TPS780300250DRVR	296-24057-2-ND	2.5V or 3V Dual Level Output, 150mA LDO Regulator	6-SOIC	1335.80/3,000			
TPS780330220DCR	296-23332-1-ND	3.3V or 2.2V Dual Level Output, 150mA LDO Regulator	TSOT-23	1.08	.86	.77	
TPS780330220DCR	296-23332-2-ND	3.3V or 2.2V Dual Level Output, 150mA LDO Regulator	TSOT-23	1197.02/3,000			
TPS780330220DRVR	296-23439-1-ND	3.3V or 2.2V Dual Level Output, 150mA LDO Regulator	6-SOIC	1.21	.96	.86	
TPS780330220DRVR	296-23439-2-ND	3.3V or 2.2V Dual Level Output, 150mA LDO Regulator	6-SOIC	1335.80/3,000			
UA781L5ACDR	296-27137-1-ND	15V, 100mA, Pos. Volt. Reg.*	8-SOIC	48	32	26	
UA781L5ACDR	296-27137-2-ND	15V, 100mA, Pos. Volt. Reg.*	8-SOIC	272.61/2,500			
UC282T-1	296-15146-5-ND	1.5V, Fast LDO Regulator	TO-220-5	7.75	6.36	5.74	
UC282T-2	296-15147-5-ND	2.1V, Fast LDO Regulator	TO-220-5	7.75	6.36	5.74	
UC282T-3	296-15148-5-ND	2.5V, Fast LDO Regulator	TO-220-5	7.75	6.36	5.74	
UC282T-ADJ	296-15149-5-ND	Adj., Fast LDO Regulator	TO-220-5	7.75	6.36	5.74	
UC282TD-3	296-2795-5-ND	2.5V, Fast LDO Regulator	TO-263-5	5.01	4.11	3.71	
UC282TDKTT-3	296-16013-5-ND	2.5V, Fast LDO Regulator	TO-263-5	6.40	5.25	4.74	
UC282TDKTTT-ADJ	296-16014-1-ND	1.2V/Adj., Fast LDO Regulator	TO-263-5	6.79	5.64	—	
UC282TDTR-ADJ	296-18067-1-ND	1.2V/Adj., Fast LDO Regulator	TO-263-5	6.79	5.64	5.13	
UC282TDTR-3	296-19031-1-ND	2.5V, Fast LDO Regulator	TO-263-5	6.79	5.64	5.13	
UC285T-1	296-15153-5-ND	1.5V, Fast LDO Regulator	TO-220-5	8.99	7.37	6.65	
UC285T-2	296-15154-5-ND	2.1V, Fast LDO Regulator	TO-220-5	7.54	6.19	5.58	
UC285T-3	296-15155-5-ND	2.5V, Fast LDO Regulator	TO-220-5	8.99	7.37	6.65	
UC285T-ADJ	296-15156-5-ND	1.2V/Adj., Fast LDO Regulator	TO-220-5	8.99	7.37	6.65	
UC285TDKTTT-1	296-16015-1-ND	1.5V, Fast LDO Regulator	TO-263-5	7.99	6.64	—	
UC285TDKTTT-1	296-16015-2-ND	1.5V, Fast LDO Regulator	TO-263-5	309.09/50			
UC285TDKTTT-ADJ	296-16018-1-ND	1.2V/Adj., Fast LDO Regulator	TO-263-5	309.09/50			
UC285TDKTTT-ADJ	296-16018-2-ND	1.2V/Adj., Fast LDO Regulator	TO-263-5	309.09/50			
UC382T-1	296-2801-5-ND	1.5V, Fast Transient Response LDO Regulator	TO-220-5	6.72	5.51	4.97	
UC382T-2	296-2802-5-ND	2.1V, Fast Transient Response LDO Regulator	TO-220-5	5.81	4.77	4.30	
UC382T-3	296-2803-5-ND	2.5V, Fast Transient Response LDO Regulator	TO-220-5	6.72	5.51	4.97	
UC382T-ADJ	296-2804-5-ND	Adjustable Fast Transient Response LDO Regulator	TO-220-5	6.72	5.51	4.97	
UC385EVM-207	296-20626-ND	Evaluation Module for UC385	—	41.31	—	—	
UC385T-1	296-2809-5-ND	1.5V, 5A LDO Regulator	TO-220-5	7.85	6.44	5.81	
UC385T-2	296-2810-5-ND	2.1V, 5A LDO Regulator	TO-220-5	7.85	6.44	5.81	
UC385T-3	296-2811-5-ND	2.5V, 5A LDO Regulator	TO-220-5	7.85	6.44	5.81	
UC385T-ADJ	296-2812-5-ND	1.2V/Adj., 5A LDO Regulator	TO-220-5	7.85	6.44	5.81	
UC385TD-2	296-2814-5-ND	2.1V, 5A LDO Regulator	TO-263-5	5.09	4.18	3.77	
UC2573D	296-2793-5-ND	Buck Pulse PWM Voltage Regulator	16-SOIC	3.24	2.61	2.38	
UC2578DP	296-19029-5-ND	Buck PWM Step-Down Voltage Reg.	16-SOIC	8.37	6.86	6.19	
UC2832TDWEP	296-18185-5-ND	2V Precision LDO Linear Controller	16-SOIC	8.99	7.37	6.65	
UC2834DWD	296-2797-5-ND	High-Efficiency Linear Regulator	16-SOIC	14.99	12.61	11.59	
UC2835D	296-2798-5-ND	High-Efficiency Regulator Controller	8-SOIC	8.88	7.29	6.58	
UC2836D	296-2799-5-ND	High-Efficiency Regulator Controller	8-SOIC	9.81	8.26	7.59	
UC3832N	296-11273-5-ND	Adjustable, 100mA LDO Regulator	14-Dip	6.40	5.25	4.74	
UC3833N	296-11274-5-ND	Adjustable, 100mA LDO Regulator	8-Dip	5.55	4.47	4.07	
UC3834DWD	296-2808-5-ND	High-Efficiency Linear Regulator	16-SOIC	10.22	8.64	7.94	
UCC281DP-5	296-2817-5-ND	5V, 1A LDO Regulator	8-SOIC	5.37	4.41	3.98	
UCC281DP-ADJ	296-2818-5-ND	Adjustable, 1A LDO Regulator	8-SOIC	5.37	4.41	3.98	
UCC283T-3	296-11413-5-ND	3.3V, 3A LDO Regulator	TO-220-3	7.75	6.36	5.74	
UCC283T-5	296-11414-5-ND	5V, 3A LDO Regulator	TO-220-3	7.75	6.36	5.74	
UCC283T-ADJ	296-15163-5-ND	Adjustable, 3A LDO Regulator	TO-220	7.75	6.36	5.74	
UCC283TKITTT-5	296-19039-1-ND	5V, 3A LDO Regulator	3-D2PAK	6.79	5.64	—	
UCC283TKITTT-5	296-19039-2-ND	5V, 3A LDO Regulator	3-D2PAK	262.49/50			
UCC284DP-12	296-11415-5-ND	12V, 500mA Negative LDO Regulator	8-SOIC	5.78	4.75	4.28	
UCC284DP-5	296-11416-5-ND	5V, 500mA Negative LDO Regulator	8-SOIC	6.61	5.42	4.90	
UCC284DP-ADJ	296-11417-5-ND	Adj., 500mA Negative LDO Regulator	8-SOIC	6.61	5.42	4.90	
UCC381DP-3	296-2819-5-ND	3.3V, 1A LDO Regulator	8-SOIC	5.32	4.28	3.90	
UCC381DP-5	296-2820-5-ND	5V, 1A LDO Regulator	8-SOIC	5.32	4.28	3.90	
UCC381DP-ADJ	296-2821-5-ND	Adjustable, 1A LDO Regulator	8-SOIC	5.32	4.28	3.90	
UCC383T-3	296-8156-5-ND	3.3V, 3A LDO Linear Regulator	TO-220-3	6.72	5.51	4.97	
UCC383T-5	296-8157-5-ND	5V, 3A LDO Linear Regulator	TO-220-3	6.72	5.51	4.97	
UCC383T-ADJ	296-8158-5-ND	Adjustable, 3A LDO Linear Regulator	TO-220	6.72	5.51	4.97	
UCC383TD-ADJ	296-8161-5-ND	Adjustable, 3A LDO Linear Regulator	TO-263-4	4.87	3.92	3.57	
UCC383TKITTT-3	296-16028-1-ND	3.3V, 3A LDO Linear Regulator	3-D2PAK	5.91	4.91	—	
UCC383TKITTT-3	296-16028-2-ND	3.3V, 3A LDO Linear Regulator	3-D2PAK	228.62/50			
UCC383TKITTT-5	296-16029-1-ND	5V, 3A LDO Linear Regulator	3-D2PAK	5.91	4.91	—	
UCC383TKITTT-5	296-16029-2-ND	5V, 3A LDO Linear Regulator	3-D2PAK	228.62/50			
UCC384DP-12	296-8162-5-ND	-12V, 0.5A LDO Linear Regulator	8-SOIC	5.44	4.37	3.98	
UCC384DP-5	296-8163-5-ND	-5V, 0.5A LDO Linear Regulator	8-SOIC	5.44	4.37	3.98	
UCC384DP-ADJ	296-8164-5-ND	Neg. Adj. 0.5A LDO Linear Regulator	8-SOIC	5.44	4.37	3.98	
UCC383DWR	296-13767-1-ND	Precision LDO Linear Controller	16-SOIC	5.95	4.86	4.37	

* RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

(Continued)

Free shipping on orders over €65! All prices in euro and include duties.

(EU2011-EN) 985

C

TEXAS INSTRUMENTS		DigiKey		POWER SUPPLY PRODUCTS		RoHS Compliant Parts Available	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*	1	25	100
Voltage Regulators							
LMF789D25CPWR	296-17215-1-ND	Dual Linear FET Controller	8-TSSOP	91	.72	.65	
LM237KCE3	296-21574-5-ND	Adj., 1.5A 3-Terminal Regulator	TO-220-3	.73	.57	.50	
LM317DCY	296-23224-5-ND	3-Terminal Adjustable Regulator	SOT-223	.79	.62	.54	
LM317DCYR	296-12602-1-ND	3-Terminal Adjustable Regulator	SOT-223	.73	.57	.50	
LM317DCYR	296-12602-2-ND	3-Terminal Adjustable Regulator	SOT-223	598.92/2,500			
LM317KCE3	296-13869-5-ND	3-Terminal Adjustable Regulator	TO-220	.66	.52	.45	
LM317KCE3	296-21576-5-ND	3-Terminal Adjustable Regulator	TO-220	.66	.52	.45	
LM317KTR	296-21390-1-ND	3-Terminal Adjustable Regulator	D2PAK-3	.88	.68	.60	
LM317KTR	296-21390-2-ND	3-Terminal Adjustable Regulator	D2PAK-3	198.26/500			
LM317LCLDR	296-17220-1-ND	3-Terminal Adjustable Regulator	8-SOIC	48	.32	.26	
LM317LCLDR	296-17220-2-ND	3-Terminal Adjustable Regulator	8-SOIC	272.61/2,500			
LM317LCPK	296-26093-1-ND	100mA Adjustable Pos. Reg.*	SOT-89-3	.64	.50	.44	
LM317LCPK	296-26093-2-ND	100mA Adjustable Pos. Reg.*	SOT-89-3	232.96/1,000			
LM317LCPWR	296-17222-1-ND	3-Terminal Adjustable Regulator	8-TSSOP	48	.32	.26	
LM317LCPWR	296-17222-2-ND	3-Terminal Adjustable Regulator	8-TSSOP	218.09/2,000			
LM317LDR	296-20678-1-ND	3-Terminal Adjustable Regulator	8-SOIC	.53	.35	.29	
LM317LDR	296-20678-2-ND	3-Terminal Adjustable Regulator	8-SOIC	299.46/2,500			
LM317LILPR	296-20679-1-ND	3-Terminal Adjustable Regulator	TO-92	.53	.35	.29	
LM317LILPR	296-20679-2-ND	3-Terminal Adjustable Regulator	TO-92	239.90/2,000			
LM317LILPK	296-21742-1-ND	3-Terminal Adjustable Regulator	SOT-89	.67	.52	.46	
LM317LILPK	296-21742-2-ND	3-Terminal Adjustable Regulator	SOT-89	242.87/1,000			
LM317LIPWR	296-20680-1-ND	3-Terminal Adjustable Regulator	8-TSSOP	.53	.35	.29	
LM317LIPWR	296-20680-2-ND	3-Terminal Adjustable Regulator	8-TSSOP	239.90/2,000			
LM317MDCY	296-26095-5-ND	3-Terminal Adjustable Reg.*	SOT-223-4	.76	.62	.54	
LM317MODCYRG4	296-23127-1-ND	3-Terminal Adjustable Regulator	SOT-223-4	.88	.68	.60	
LM317MODCYRG4	296-23127-2-ND	3-Terminal Adjustable Regulator	SOT-223-4	724.90/2,500			
LM337KC	296-9550-5-ND	Adj., 1.5A Negative Voltage Regulator	TO-220-3	.77	.62	.54	
LM337KCE3	296-21577-5-ND	Adj., 1.5A Negative Voltage Regulator	TO-220-3	.73			