

| TEXAS INSTRUMENTS | | Digi+Reel® (Cont.) | | POWER SUPPLY PRODUCTS | | | |
|-------------------|-------------------|---|----------|--------------------------------|------|------|--|
| | | | | RoHS Compliant Parts Available | | | |
| T.I. Part No. | Digi-Key Part No. | Description | Pkg. | Price Each* | | | |
| | | | | 1 | 25 | 100 | |
| TL431BIP | 296-18874-5-ND | Adjustable Precision Shunt Regulator | 8-Dip | .55 | .43 | .38 | |
| TL431BIPK | 296-18060-1-ND | Adjustable Precision Shunt Regulator | SOT-89 | .64 | .50 | .45 | |
| TL431BODR | 296-17886-1-ND | Adjustable Precision Shunt Regulator | 8-SOIC | .59 | .46 | .41 | |
| TL431BODR | 296-17886-2-ND | Adjustable Precision Shunt Regulator | 8-SOIC | 487.40/2,500 | | | |
| TL431BOLPME3 | 296-19380-ND | Adjustable Precision Shunt Regulator | TO-92 | .62 | .48 | .42 | |
| TL431BIDCKR | 296-17867-1-ND | Adjustable Precision Shunt Regulator | SC70-6 | .64 | .46 | .39 | |
| TL431BIDCKR | 296-17867-2-ND | Adjustable Precision Shunt Regulator | SC70-6 | 545.23/3,000 | | | |
| TL431BILPR | 296-17375-1-ND | Adjustable Precision Shunt Regulator | TO-92 | .64 | .46 | .39 | |
| TL431BILPR | 296-17375-2-ND | Adjustable Precision Shunt Regulator | TO-92 | 363.48/2,000 | | | |
| TL431BODBVR | 296-17311-1-ND | Adjustable Precision Shunt Regulator | SOT-23-5 | .59 | .46 | .41 | |
| TL431BODBVR | 296-17311-2-ND | Adjustable Precision Shunt Regulator | SOT-23-5 | 584.88/3,000 | | | |
| TL431BODBZR | 296-17623-1-ND | Adjustable Precision Shunt Regulator | SOT-23 | .64 | .50 | .44 | |
| TL431BODBZR | 296-17623-2-ND | Adjustable Precision Shunt Regulator | SOT-23 | 629.49/3,000 | | | |
| TL431BODBZRQ1 | 296-20654-1-ND | Adjustable Precision Shunt Regulator | SOT-23 | .70 | .55 | .48 | |
| TL431BODBZRQ1 | 296-20654-2-ND | Adjustable Precision Shunt Regulator | SOT-23 | 693.92/3,000 | | | |
| TL431BODCKR | 296-17868-1-ND | Adjustable Precision Shunt Regulator | SC70-6 | .64 | .50 | .44 | |
| TL431BOLPR | 296-17376-1-ND | Adjustable Precision Shunt Regulator | TO-92 | .64 | .50 | .44 | |
| TL431BOLPR | 296-17376-2-ND | Adjustable Precision Shunt Regulator | TO-92 | 419.66/2,000 | | | |
| TL431CD | 296-1289-5-ND | Adjustable Precision Shunt Regulator | 8-SOIC | .39 | .26 | .21 | |
| TL431CDBVR | 296-10185-1-ND | Adjustable Precision Shunt Regulator | SOT-23-5 | .36 | .24 | .20 | |
| TL431CDBVR | 296-10185-2-ND | Adjustable Precision Shunt Regulator | SOT-23-5 | 245.35/3,000 | | | |
| TL431CDBZR | 296-17331-1-ND | Adjustable Precision Shunt Regulator | SOT-23 | .40 | .26 | .22 | |
| TL431CDBZR | 296-17331-2-ND | Adjustable Precision Shunt Regulator | SOT-23 | 270.13/3,000 | | | |
| TL431CDR | 296-1289-1-ND | Adjustable Precision Shunt Regulator | 8-SOIC | .70 | .41 | .34 | |
| TL431CDR | 296-1289-2-ND | Adjustable Precision Shunt Regulator | 8-SOIC | 272.61/2,500 | | | |
| TL431CLP | 296-1290-ND | Adjustable Precision Shunt Regulator | TO-92 | .42 | .28 | .23 | |
| TL431CLPM | 296-26717-1-ND | Adjustable Prec. Shunt Reg.* | TO-92-3 | .36 | .24 | .20 | |
| TL431CLPM | 296-26717-3-ND | Adjustable Prec. Shunt Reg.* | TO-92-3 | 163.57/2,000 | | | |
| TL431CLPR | 296-1290-1-ND | Adjustable Precision Shunt Regulator | TO-92 | .40 | .26 | .22 | |
| TL431CLPR | 296-1290-2-ND | Adjustable Precision Shunt Regulator | TO-92 | 180.09/2,000 | | | |
| TL431CP | 296-1798-5-ND | Adjustable Precision Shunt Regulator | 8-Dip | .36 | .24 | .20 | |
| TL431CPK | 296-1991-1-ND | Adjustable Precision Shunt Regulator | SOT-89 | .27 | .20 | .17 | |
| TL431CPSR | 296-26718-1-ND | Adjustable Prec. Shunt Reg.* | 8-SOP | .36 | .24 | .20 | |
| TL431CPSR | 296-26718-2-ND | Adjustable Prec. Shunt Reg.* | 8-SOP | 163.57/2,000 | | | |
| TL431CPWR | 296-12497-1-ND | Adjustable Precision Shunt Regulator | 8-TSOP | .36 | .24 | .20 | |
| TL431IDBVR | 296-10187-1-ND | Adjustable Precision Shunt Regulator | SOT-23-5 | .42 | .28 | .23 | |
| TL431IDBVR | 296-10187-2-ND | Adjustable Precision Shunt Regulator | SOT-23-5 | 287.48/3,000 | | | |
| TL431IDBZR | 296-17332-1-ND | Adjustable Precision Shunt Regulator | SOT-23 | .45 | .30 | .25 | |
| TL431IDBZR | 296-17332-2-ND | Adjustable Precision Shunt Regulator | SOT-23 | 309.79/3,000 | | | |
| TL431IDR | 296-1291-1-ND | Adjustable Precision Shunt Regulator | 8-SOIC | .78 | .47 | .38 | |
| TL431IDR | 296-1291-2-ND | Adjustable Precision Shunt Regulator | 8-SOIC | 289.14/2,500 | | | |
| TL431ILP | 296-1292-ND | Adjustable Precision Shunt Regulator | TO-92 | .47 | .32 | .26 | |
| TL431ILPR | 296-1292-1-ND | Adjustable Precision Shunt Regulator | TO-92 | 205.53/2,000 | | | |
| TL431ILPR | 296-1292-2-ND | Adjustable Precision Shunt Regulator | TO-92 | 206.53/2,000 | | | |
| TL431IP | 296-10188-5-ND | Adjustable Precision Shunt Regulator | 8-Dip | .40 | .27 | .22 | |
| TL431IPK | 296-10189-1-ND | Adjustable Precision Shunt Regulator | SOT-89 | .43 | .30 | .26 | |
| TL431IPK | 296-10189-2-ND | Adjustable Precision Shunt Regulator | SOT-89 | 132.01/1,000 | | | |
| TL431IDBVR | 296-17333-1-ND | Adjustable Precision Shunt Regulator | SOT-23-5 | .49 | .33 | .27 | |
| TL431IDBZR | 296-17334-1-ND | Adjustable Precision Shunt Regulator | SOT-23 | .53 | .35 | .29 | |
| TL431IDBZR | 296-17334-2-ND | Adjustable Precision Shunt Regulator | SOT-23 | 359.35/3,000 | | | |
| TL431IDBZT | 296-26721-1-ND | Adjustable Prec. Shunt Reg.* | SOT-23-3 | .87 | .67 | .59 | |
| TL431IDBZT | 296-26721-2-ND | Adjustable Prec. Shunt Reg.* | SOT-23-3 | 115.45/250 | | | |
| TL432ACDBZR | 296-17336-1-ND | Adjustable Precision Shunt Regulator | SOT-23 | .53 | .35 | .29 | |
| TL432ACDBZR | 296-17336-2-ND | Adjustable Precision Shunt Regulator | SOT-23 | 359.35/3,000 | | | |
| TL432AIDBZR | 296-17338-1-ND | Adjustable Precision Shunt Regulator | SOT-23 | .53 | .35 | .29 | |
| TL432AIDBZR | 296-17338-2-ND | Adjustable Precision Shunt Regulator | SOT-23 | 359.35/3,000 | | | |
| TL432BCKP | 296-18242-1-ND | Adjustable Precision Shunt Regulator | SOT-89 | .62 | .48 | .43 | |
| TL432BODBZR | 296-18880-1-ND | Adjustable Precision Shunt Regulator | SOT-23 | .68 | .53 | .47 | |
| TL432BODBZRQ1 | 296-18880-2-ND | Adjustable Precision Shunt Regulator | SOT-23 | 671.62/3,000 | | | |
| TL432IDBZR | 296-17344-1-ND | Adjustable Precision Shunt Regulator | SOT-23 | .71 | .56 | .49 | |
| TL432IDBZR | 296-17344-2-ND | Adjustable Precision Shunt Regulator | SOT-23 | 53.35 | | | |
| TL432ODBZR | 296-17346-1-ND | Adjustable Precision Shunt Regulator | SOT-23 | .53 | .35 | .29 | |
| TL497ACD | 296-10195-5-ND | 1.2V Switching Voltage Regulator | 14-SOIC | 1.50 | 1.24 | 1.12 | |
| TL497ACDR | 296-10195-1-ND | 1.2V Switching Voltage Regulator | 14-SOIC | 1.50 | 1.19 | 1.08 | |
| TL497ACDR | 296-10195-2-ND | 1.2V Switching Voltage Regulator | 14-SOIC | 1387.85/2,500 | | | |
| TL497AID | 296-10196-5-ND | 1.2V Switching Voltage Regulator | 14-Dip | 1.67 | 1.35 | 1.21 | |
| TL497AID | 296-10197-5-ND | 1.2V Switching Voltage Regulator | 14-SOIC | 1.54 | 1.24 | 1.12 | |
| TL497AIDR | 296-10197-1-ND | 1.2V Switching Voltage Regulator | 14-SOIC | 1.50 | 1.19 | 1.08 | |
| TL497AIDR | 296-10197-2-ND | 1.2V Switching Voltage Regulator | 14-SOIC | 1387.85/2,500 | | | |
| TL497AIDR | 296-10198-5-ND | 1.2V Switching Voltage Regulator | 14-Dip | 1.67 | 1.35 | 1.21 | |
| TL780-05CKTR | 296-20777-1-ND | 5.0V, 1.5A Fixed Positive Voltage Reg. | 3-D2PAK | .83 | .66 | .59 | |
| TL780-05CKTR | 296-14324-5-ND | 5.0V, 1.5A Fixed Positive Voltage Reg. | TO-220-3 | .73 | .57 | .50 | |
| TL780-12KCS | 296-14325-5-ND | 12V, Fixed Positive Volt. Regulator | TO-220-3 | .73 | .57 | .50 | |
| TL780-15KCS | 296-14326-5-ND | 15V, Fixed Positive Volt. Regulator | TO-220-3 | .73 | .57 | .50 | |
| TL783CKCSE3 | 296-20687-5-ND | High Voltage Adjustable Regulator | TO-220 | 1.67 | 1.35 | 1.21 | |
| TL783CKTTR | 296-20778-1-ND | High Voltage Adjustable Regulator | 3-D2PAK | 2.31 | 1.79 | 1.62 | |
| TL783CKTTR | 296-20778-2-ND | High Voltage Adjustable Regulator | 3-D2PAK | 578.27/500 | | | |
| TL2575H-ADJIKV | 296-21831-5-ND | Adjustable, 1A Simple Step Down Switching Voltage Regulator | TO-220-5 | 2.05 | 1.66 | 1.49 | |
| TL2575-ADJIN | 296-21832-5-ND | Adjustable, 1A Simple Step Down Switching Voltage Regulator | 16-Dip | 1.54 | 1.24 | 1.12 | |
| TL2575-05IKTTR | 296-21824-1-ND | 5V, 1A Simple Step Down Switching Voltage Regulator | 5-D2PAK | 2.17 | 1.68 | 1.52 | |
| TL2575-05IKTTR | 296-21824-2-ND | 5V, 1A Simple Step Down Switching Voltage Regulator | 5-D2PAK | 542.13/500 | | | |
| TL2575-05IKV | 296-21825-5-ND | 5V, 1A Simple Step Down Switching Voltage Regulator | TO-220-5 | 2.05 | 1.66 | 1.49 | |
| TL2575-05IN | 296-21094-5-ND | 5V, 1A Simple Step Down Switching Voltage Regulator | 16-Dip | 1.54 | 1.24 | 1.12 | |
| TL2575-12IKV | 296-21496-5-ND | 12V, 1A Simple Step Down Switching Voltage Regulator | TO-220-5 | 2.05 | 1.66 | 1.49 | |
| TL2575-12IN | 296-21826-5-ND | 12V, 1A Simple Step Down Switching Voltage Regulator | 16-Dip | 1.54 | 1.24 | 1.12 | |
| TL2575-15IKV | 296-21498-5-ND | 15V, 1A Simple Step Down Switching Voltage Regulator | TO-220-5 | 2.05 | 1.66 | 1.49 | |
| TL2575-15IN | 296-21827-5-ND | 15V, 1A Simple Step Down Switching Voltage Regulator | 16-Dip | 1.54 | 1.24 | 1.12 | |
| TL2575-33IKTTR | 296-21828-1-ND | 3.3V, 1A Simple Step Down Switching Voltage Regulator | 5-D2PAK | 2.17 | 1.68 | 1.52 | |
| TL2575-33IKTTR | 296-21828-2-ND | 3.3V, 1A Simple Step Down Switching Voltage Regulator | 5-D2PAK | 542.33/500 | | | |
| TL2575-33IKV | 296-21829-5-ND | 3.3V, 1A Simple Step Down Switching Voltage Regulator | TO-220-5 | 2.05 | 1.66 | 1.49 | |
| TL2575-33IN | 296-21095-5-ND | 3.3V, 1A Simple Step Down Switching Voltage Regulator | 16-Dip | 1.54 | 1.24 | 1.12 | |
| TL2575HV-ADJIKTTR | 296-21841-1-ND | Adjustable, 1A Simple Step Down Switching Voltage Regulator | 5-D2PAK | 2.85 | 2.33 | 2.09 | |

| TEXAS INSTRUMENTS | | Digi+Reel® (Cont.) | | POWER SUPPLY PRODUCTS | | | |
|-------------------|-------------------|---|----------|--------------------------------|------|------|--|
| | | | | RoHS Compliant Parts Available | | | |
| T.I. Part No. | Digi-Key Part No. | Description | Pkg. | Price Each* | | | |
| | | | | 1 | 25 | 100 | |
| TL2575HV-ADJIKTTR | 296-21841-2-ND | Adjustable, 1A Simple Step Down Switching Voltage Regulator | 5-D2PAK | 788.51/500 | | | |
| TL2575HV-ADJIKV | 296-21842-5-ND | Adjustable, 1A Simple Step Down Switching Voltage Regulator | TO-220-5 | 2.66 | 2.14 | 1.95 | |
| TL2575HV-ADJIN | 296-21843-5-ND | Adjustable, 1A Simple Step Down Switching Voltage Regulator | 16-Dip | 2.66 | 2.14 | 1.95 | |
| TL2575HV-05IKV | 296-21834-5-ND | 5V, 1A Simple Step Down Switching Voltage Regulator | TO-220-5 | 2.66 | 2.14 | 1.95 | |
| TL2575HV-05IN | 296-21835-5-ND | 5V, 1A Simple Step Down Switching Voltage Regulator | 16-Dip | 2.66 | 2.14 | 1.95 | |
| TL2575HV-12IKTTR | 296-21499-1-ND | 12V, 1A Simple Step Down Switching Voltage Regulator | 5-D2PAK | 2.85 | 2.33 | 2.09 | |
| TL2575HV-12IKV | 296-21500-5-ND | 12V, 1A Simple Step Down Switching Voltage Regulator | TO-220-5 | 2.66 | 2.14 | 1.95 | |
| TL2575HV-12IN | 296-21836-5-ND | 12V, 1A Simple Step Down Switching Voltage Regulator | 16-Dip | 2.66 | 2.14 | 1.95 | |
| TL2575HV-15IKV | 296-21502-5-ND | 15V, 1A Simple Step Down Switching Voltage Regulator | TO-220-5 | 2.66 | 2.14 | 1.95 | |
| TL2575HV-15IN | 296-21837-5-ND | 15V, 1A Simple Step Down Switching Voltage Regulator | 16-Dip | 2.66 | 2.14 | 1.95 | |
| TL2575HV-33IKV | 296-21839-5-ND | 3.3V, 1A Simple Step Down Switching Voltage Regulator | TO-220-5 | 2.66 | 2.14 | 1.95 | |
| TL2575HV-33IN | 296-21840-5-ND | 3.3V, 1A Simple Step Down Switching Voltage Regulator | 16-Dip | 2.66 | 2.14 | 1.95 | |
| TL3577-ADJIKTTR | 296-21852-1-ND | 100kHz Current Mode Simple Step Up/ Flyback Switching Regulator | 5-DDPAK | 6.87 | 5.71 | 5.19 | |
| TLV431ACDBVR | 296-1348-1-ND | Low Voltage Adj. Shunt Regulator | SOT-23-5 | .65 | .51 | .45 | |
| TLV431ACDBVR | 296-1348-2-ND | Low Voltage Adj. Shunt Regulator | SOT-23-5 | 646.84/3,000 | | | |
| TLV431ACDBZR | 296-18912-1-ND | Low Voltage Adj. Shunt Regulator | SOT-23 | .72 | .56 | .50 | |
| TLV431ACDBZR | 296-18912-2-ND | Low Voltage Adj. Shunt Regulator | SOT-23 | 711.27/3,000 | | | |
| TLV431AOLP | 296-10723-5-ND | Low Voltage Adj. Shunt Regulator | TO-92 | .71 | .56 | .49 | |
| TLV431AID | 296-10724-5-ND | Low Voltage Adj. Shunt Regulator | 8-SOIC | .59 | .47 | .41 | |
| TLV431AIDBVR | 296-1984-1-ND | Low Voltage Adj. Shunt Regulator | SOT-23-5 | .65 | .51 | .45 | |
| TLV431AIDBVR | 296-1984-2-ND | Low Voltage Adj. Shunt Regulator | SOT-23-5 | 646.84/3,000 | | | |
| TLV431AIDBZR | 296-18913-1-ND | Low Voltage Adj. Shunt Regulator | SOT-23 | .72 | .56 | .50 | |
| TLV431AIDBZR | 296-18913-2-ND | Low Voltage Adj. Shunt Regulator | SOT-23 | 711.27/3,000 | | | |
| TLV431AIP | 296-10725-5-ND | Low Voltage Adj. Shunt Regulator | TO-92 | .71 | .56 | .49 | |
| TLV431AIPLR | 296-24389-1-ND | Low Voltage Adj. Shunt Reg.* | TO-92-3 | .65 | .51 | .45 | |
| TLV431AIPLR | 296-24389-2-ND | Low Voltage Adj. Shunt Reg.* | TO-92-3 | 431.22/2,000 | | | |
| TLV431AODBVRQ1 | 296-24560-1-ND | Low Voltage Adj. Shunt Reg.* | SOT-23-5 | .75 | .59 | .52 | |
| TLV431AODBVRQ1 | 296-24560-2-ND | Low Voltage Adj. Shunt Reg.* | SOT-23-5 | 743.49/3,000 | | | |
| TLV431AOPK | 296-22933-5-ND | Low Voltage Adj. Shunt Regulator | SOT-89 | .59 | .47 | .41 | |
| TLV431BCDBZR | 296-17669-1-ND | Low Voltage Adj. Shunt Regulator | SOT-23-3 | .84 | .65 | .58 | |
| TLV431BCDBZR | 296-17669-2-ND | Low Voltage Adj. Shunt Regulator | SOT-23-3 | 830.23/3,000 | | | |
| TLV431BCKP | 296-22934-5-ND | Low Voltage Adj. Shunt Regulator | SOT-89 | .69 | .54 | .47 | |