

STMicroelectronics		Digi-Reel®	(Cont.)	AMPLIFIERS AND LINEAR			
		RoHS Compliant Parts Available					
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	10	100	
TL074ACD	497-2203-2-ND	Low Noise, JFET Quad Op Amp	14-SOIC	1085.08/2,500			
TL074ACN	497-7660-5-ND	Low Noise, JFET Quad Op Amp*	14-Dip	.94	.84	.66	
TL074BCN	497-7041-5-ND	Low Noise, JFET Quad Op Amp*	14-Dip	1.95	1.77	1.42	
TL074CDT	497-2204-1-ND	Low Noise, JFET Quad Op Amp	14-SOIC	.60	.49	.37	
TL074CPT	497-2204-2-ND	Low Noise, JFET Quad Op Amp	14-SOIC	424.42/2,500			
TL074CN	497-2205-5-ND	Low Noise, JFET Quad Op Amp	14-Dip	.52	.44	.33	
TL074IDT	497-4056-1-ND	Low Noise, JFET Quad Op Amp	14-SOIC	.74	.64	.51	
TL074IDT	497-4056-2-ND	Low Noise, JFET Quad Op Amp	14-SOIC	610.61/2,500			
TL074IN	497-2206-5-ND	Low Noise, JFET Quad Op Amp	14-Dip	.74	.65	.50	
TL074IYDT	497-10228-1-ND	Low Noise, JFET Quad Op Amp*	14-SOIC	.70	.63	.50	
TL074IYDT	497-10228-2-ND	Low Noise, JFET Quad Op Amp*	14-SOIC	706.71/2,500			
TL081ACDT	497-2207-1-ND	JFET Single Op Amp	8-SOIC	.80	.72	.57	
TL081ACDT	497-2207-2-ND	JFET Single Op Amp	8-SOIC	736.74/2,500			
TL081CN	497-2209-5-ND	JFET Single Op Amp	8-Dip	.46	.39	.29	
TL081IDT	497-2210-1-ND	JFET Single Op Amp	8-SOIC	.63	.55	.43	
TL081IDT	497-2210-2-ND	JFET Single Op Amp	8-SOIC	520.52/2,500			
TL081IN	497-7661-5-ND	JFET Single Op Amp*	8-Dip	.58	.51	.40	
TL082ACN	497-7662-5-ND	JFET Dual Op Amp*	8-Dip	.60	.53	.41	
TL082AIYDT	497-10229-1-ND	JFET Dual Op Amp*	8-SOIC	1.18	1.05	.83	
TL082AIYDT	497-10229-2-ND	JFET Dual Op Amp*	8-SOIC	1177.18/2,500			
TL082BIYDT	497-10230-1-ND	JFET Dual Op Amp*	8-SOIC	1.23	1.10	.87	
TL082BIYDT	497-10230-2-ND	JFET Dual Op Amp*	8-SOIC	1235.23/2,500			
TL082CDDT	497-2212-1-ND	JFET Dual Op Amp	8-SOIC	.60	.49	.37	
TL082CDDT	497-2212-2-ND	JFET Dual Op Amp	8-SOIC	424.42/2,500			
TL082CN	497-2213-5-ND	JFET Dual Op Amp	8-Dip	.52	.44	.33	
TL082CPT	497-4057-1-ND	JFET Dual Op Amp	8-TSSOP	.66	.58	.46	
TL082CPT	497-4057-2-ND	JFET Dual Op Amp	8-TSSOP	877.68/4,000			
TL082IDT	497-2214-1-ND	JFET Dual Op Amp	8-SOIC	.70	.61	.49	
TL082IDT	497-2214-2-ND	JFET Dual Op Amp	8-SOIC	580.58/2,500			
TL082IN	497-3032-5-ND	JFET Dual Op Amp	8-Dip	.65	.57	.44	
TL082IPT	497-8065-1-ND	JFET Dual Op Amp*	8-TSSOP	.80	.72	.57	
TL082IPT	497-8065-2-ND	JFET Dual Op Amp*	8-TSSOP	1178.78/4,000			
TL082IYDT	497-10231-1-ND	JFET Dual Op Amp*	8-SOIC	1.12	1.00	.79	
TL082IYDT	497-10231-2-ND	JFET Dual Op Amp*	8-SOIC	1119.12/2,500			
TL084ACDT	497-2215-1-ND	JFET Quad Op Amp	14-SOIC	.86	.78	.62	
TL084ACDT	497-2215-2-ND	JFET Quad Op Amp	14-SOIC	796.80/2,500			
TL084ACN	497-2216-5-ND	JFET Quad Op Amp	14-Dip	.79	.71	.56	
TL084AIDT	497-4752-1-ND	JFET Quad Op Amp	14-SOIC	1.01	.91	.72	
TL084AIDT	497-4752-2-ND	JFET Quad Op Amp	14-SOIC	930.93/2,500			
TL084BCDT	497-8066-1-ND	JFET Quad Op Amp*	14-SOIC	2.65	2.27	1.86	
TL084BCDT	497-8066-2-ND	JFET Quad Op Amp*	14-SOIC	2554.55/2,500			
TL084BIDT	497-7042-1-ND	JFET Quad Op Amp*	14-SOIC	1.62	1.39	1.14	
TL084BIDT	497-7042-2-ND	JFET Quad Op Amp*	14-SOIC	1561.56/2,500			
TL084BIN	497-7043-5-ND	JFET Quad Op Amp*	14-Dip	1.43	1.30	1.05	
TL084CDT	497-3033-5-ND	JFET Quad Op Amp	14-SOIC	.56	.48	.36	
TL084CDDT	497-2217-1-ND	JFET Quad Op Amp	14-SOIC	.65	.52	.39	
TL084CDDT	497-2217-2-ND	JFET Quad Op Amp	14-SOIC	456.46/2,500			
TL084CN	497-2218-5-ND	JFET Quad Op Amp	14-Dip	.58	.51	.39	
TL084CPT	497-2219-1-ND	JFET Quad Op Amp	14-TSSOP	.74	.64	.50	
TL084CPT	497-2219-2-ND	JFET Quad Op Amp	14-TSSOP	604.60/2,500			
TL084IDT	497-2220-1-ND	JFET Quad Op Amp	14-SOIC	.78	.68	.54	
TL084IDT	497-2220-2-ND	JFET Quad Op Amp	14-SOIC	640.64/2,500			
TL084IN	497-2221-5-ND	JFET Quad Op Amp	14-Dip	.74	.65	.50	
TL084IPT	497-8067-1-ND	JFET Quad Op Amp*	14-TSSOP	.99	.89	.71	
TL084IPT	497-8067-2-ND	JFET Quad Op Amp*	14-TSSOP	912.91/2,500			
TL084IYDT	497-10232-1-ND	JFET Quad Op Amp*	14-SOIC	.80	.72	.57	
TL084IYDT	497-10232-2-ND	JFET Quad Op Amp*	14-SOIC	736.74/2,500			
TS27L2ACDT	497-7673-1-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1.09	.98	.78	
TS27L2ACDT	497-7673-2-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1001.00/2,500			
TS27L2ACN	497-7674-5-ND	Precision LP, CMOS Dual Op Amp*	8-Dip	1.09	.98	1.07	
TS27L2AIDT	497-2250-5-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1.64	1.49	1.20	
TS27L2AINDT	497-7675-5-ND	Precision LP, CMOS Dual Op Amp*	8-Dip	1.70	1.54	1.24	
TS27L2BCDDT	497-8082-1-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1.07	.97	.78	
TS27L2BCDDT	497-8082-2-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1419.42/2,500			
TS27L2BIDT	497-8083-1-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	2.51	2.15	1.76	
TS27L2BIDT	497-8083-2-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	2414.41/2,500			
TS27L2CDDT	497-6774-1-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	.74	.64	.50	
TS27L2CDDT	497-6774-2-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	604.60/2,500			
TS27L2CN	497-7676-5-ND	Precision LP, CMOS Dual Op Amp*	8-Dip	1.70	1.54	1.24	
TS27L2CPT	497-8084-1-ND	Precision LP, CMOS Dual Op Amp*	8-TSSOP	1.35	1.20	.96	
TS27L2CPT	497-8084-2-ND	Precision LP, CMOS Dual Op Amp*	8-TSSOP	1976.37/4,000			
TS27L2IDT	497-2251-1-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	1.03	.92	.73	
TS27L2IDT	497-2251-2-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	940.94/2,500			
TS27L2IPT	497-8085-1-ND	Precision LP, CMOS Dual Op Amp*	8-TSSOP	1.44	1.24	1.02	
TS27L2IPT	497-8085-2-ND	Precision LP, CMOS Dual Op Amp*	8-TSSOP	2226.22/4,000			
TS27L4AIDT	497-2252-5-ND	Precision LP, CMOS Quad Op Amp	14-SOIC	1.70	1.54	1.24	
TS27L4AIN	497-2253-5-ND	Precision LP, CMOS Quad Op Amp	14-Dip	1.39	1.25	1.01	
TS27L4CDT	497-8086-1-ND	Precision LP, CMOS Quad Op Amp*	14-SOIC	1.44	1.29	1.03	
TS27L4CDT	497-8086-2-ND	Precision LP, CMOS Quad Op Amp*	14-SOIC	1325.32/2,500			
TS27L4CN	497-2254-5-ND	Precision LP, CMOS Quad Op Amp	14-Dip	.85	.76	.60	
TS27L4IDT	497-2255-1-ND	Precision LP, CMOS Quad Op Amp	14-SOIC	1.12	1.01	.80	
TS27L4IDT	497-2255-2-ND	Precision LP, CMOS Quad Op Amp	14-SOIC	1031.03/2,500			
TS27L4IN	497-2256-5-ND	Precision LP, CMOS Quad Op Amp	14-Dip	1.12	1.00	.79	
TS27L4IPT	497-8087-1-ND	Precision LP, CMOS Quad Op Amp*	14-TSSOP	1.32	1.20	.96	
TS27L4IPT	497-8087-2-ND	Precision LP, CMOS Quad Op Amp*	14-TSSOP	1759.76/2,500			
TS27M2ACDT	497-8088-1-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1.45	1.31	1.05	
TS27M2ACDT	497-8088-2-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1929.93/2,500			
TS27M2AIDT	497-2257-1-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	1.15	1.03	.82	
TS27M2AIDT	497-2257-2-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	1059.06/2,500			
TS27M2AIN	497-2258-5-ND	Precision LP, CMOS Dual Op Amp	8-Dip	1.08	.96	.76	
TS27M2BIDT	497-4445-1-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	2.51	2.15	1.76	
TS27M2BIDT	497-4445-2-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	2414.41/2,500			
TS27M2CDDT	497-8089-1-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	.82	.71	.56	
TS27M2CDDT	497-8089-2-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	670.67/2,500			
TS27M2CPT	497-7775-1-ND	Precision LP, CMOS Dual Op Amp*	8-TSSOP	1.35	1.20	.96	
TS27M2CPT	497-7775-2-ND	Precision LP, CMOS Dual Op Amp*	8-TSSOP	1976.37/4,000			
TS27M2IDT	497-2259-1-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	1.18	1.06	.84	
TS27M2IDT	497-2259-2-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	1085.08/2,500			
TS27M2IN	497-2260-5-ND	Precision LP, CMOS Dual Op Amp	8-Dip	.91	.81	.64	
TS27M4CDDT	497-8090-1-ND	Precision LP, CMOS Quad Op Amp*	14-SOIC	1.44	1.29	1.03	
TS27M4CDDT	497-8090-2-ND	Precision LP, CMOS Quad Op Amp*	14-SOIC	1325.32/2,500			
TS27M4IN	497-2263-5-ND	Precision LP, CMOS Quad Op Amp	14-Dip	1.03	.93	.75	

STMicroelectronics		Digi-Reel®	(Cont.)	AMPLIFIERS AND LINEAR			
		RoHS Compliant Parts Available					
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	10	100	
TS27M4IPT	497-8091-1-ND	Precision LP, CMOS Quad Op Amp*	14-TSSOP	1.79	1.54	1.26	
TS27M4IPT	497-8091-2-ND	Precision LP, CMOS Quad Op Amp*	14-TSSOP	1731.73/2,500			
TS271ACDT	497-2242-1-ND	CMOS Programmable LP Single Op Amp	8-SOIC	.86	.77	.62	
TS271ACDT	497-2242-2-ND	CMOS Programmable LP Single Op Amp	8-SOIC	972.97/2,500			
TS271ACN	497-2243-5-ND	CMOS Programmable LP Single Op Amp	8-Dip	.79	.71	.56	
TS271BIDT	497-8075-1-ND	CMOS Programmable LP Single Op Amp*	8-SOIC	1.27	1.16	.93	
TS271BIDT	497-8075-2-ND	CMOS Programmable LP Single Op Amp*	8-SOIC	1703.70/2,500			
TS271CDDT	497-8076-1-ND	CMOS Programmable LP Single Op Amp*	8-SOIC	.83	.75	.60	
TS271CDDT	497-8076-2-ND	CMOS Programmable LP Single Op Amp*	8-SOIC	764.76/2,500			
TS271CN	497-7670-5-ND	CMOS Programmable LP Single Op Amp*	8-Dip	.60	.54	.42	
TS271IDT	497-2244-1-ND	CMOS Programmable LP Single Op Amp	8-SOIC	.80	.72	.57	
TS271IDT	497-2244-2-ND	CMOS Programmable LP Single Op Amp	8-SOIC	736.74/2,500			
TS272ACDT	497-8077-1-ND	CMOS Dual Op Amp*	8-SOIC	1.45	1.31	1.05	
TS272ACDT	497-8077-2-ND	CMOS Dual Op Amp*	8-SOIC	1929.93/2,500			
TS272AIDT	497-2245-5-ND	CMOS Dual Op Amp	8-SOIC	1.06	.94	.75	
TS272AIN	497-2246-5-ND	CMOS Dual Op Amp	8-Dip	1.18	1.05	.83	
TS272BIDT	497-8078-1-ND	CMOS Dual Op Amp*	8-SOIC	2.51	2.15	1.76	
TS272BIDT	497-8078-2-ND	CMOS Dual Op Amp*	8-SOIC	2414.41/2,500			
TS272CD	497-3037-5-ND	CMOS Dual Op Amp	8-SOIC	1.06	.94	.75	
TS272CN	497-7671-5-ND	CMOS Dual Op Amp*	8-Dip	.86	.77	.61	
TS272CPT	497-8079-1-ND	CMOS Dual Op Amp*	8-TSSOP	.99	.89	.71	
TS272CPT	497-8079-2-ND	CMOS Dual Op Amp*	8-TSSOP	1460.66/4,000			
TS272IDT	497-2247-1-ND	CMOS Dual Op Amp	8-SOIC	1.19	1.08	.85	
TS272IDT	497-2247-2-ND	CMOS Dual Op Amp	8-SOIC	1353.35/2,500			
TS272IPT	497-8080-1-ND	CMOS Dual Op Amp*	8-TSSOP	1.47	1.32	1.05	
TS272IPT	497-8080-2-ND	CMOS Dual Op Amp*	8-TSSOP	2165.36/4,000			
TS274ACDT	497-8081-1-ND	CMOS Quad Op Amp*	14-SOIC	2.51	2.15	1.76	
TS274ACDT	497-8081-2-ND	CMOS Quad Op Amp*	14-SOIC	2414.41/2,500			
TS274CDDT	497-4060-1-ND	CMOS Quad Op Amp	14-SOIC	.90	.81	.64	
TS274CDDT	497-4060-2-ND	CMOS Quad Op Amp	14-SOIC	824.82/2,500			
TS274CN	497-7672-5-ND	CMOS Quad Op Amp*	14-Dip	1.03	.92	.73	
TS274IDT	497-2249-1-ND	CMOS Quad Op Amp	14-SOIC	1.46	1.26	1.03	
TS274IDT	497-2249-2-ND	CMOS Quad Op Amp	14-SOIC	1407.41/2,500			
TS274IN	497-5196-ND	CMOS Quad Op Amp*	14-Dip	1.43	1.30	1.05	
TS321AILT	497-8093-1-ND	Low Power Single Op Amp*	SOT-23-5	.83	.75	.60	
TS321AILT	497-8093-2-ND	Low Power Single Op Amp*	SOT-23-5	917.72/3,000			
TS321AIYLT	497-10242-1-ND	Low Power Single Op Amp*	SOT-23-5	.74	.65	.50	
TS321AIYLT	497-10242-2-ND	Low Power Single Op Amp*	SOT-23-5	804.80/3,000			
TS321IDT	497-8094-1-ND	Low Power Single Op Amp*	8-SOIC	.82	.71	.56	
TS321IDT	497-8094-2-ND	Low Power Single Op Amp*	8-SOIC	670.67/2,500			
TS321ILT	497-4061-1-ND	Low Power Single Op Amp	SOT-23-5	.60	.52	.41	
TS321ILT	497-4061-2-ND	Low Power Single Op Amp	SOT-23-5	593.39/3,000			
TS321IYLT	497-10243-1-ND	Low Power Single Op Amp*	SOT-23-5	.61	.53	.41	
TS321IYLT	497-10243-2-ND	Low Power Single Op Amp*	SOT-23-5	658.26/3,000			
TS339CDDT	497-8095-1-ND	Micropower Quad CMOS Voltage Comparator*	14-SOIC	.99	.89	.71	
TS339CDDT	497-8095-2-ND	Micropower Quad CMOS Voltage Comparator*	14-SOIC	916.92/2,500			
TS339CPT	497-4062-1-ND	Micropower Quad CMOS Voltage Comparator	14-TSSOP	.68	.59	.47	
TS339CPT	497-4062-2-ND	Micropower Quad CMOS Voltage Comparator	14-TSSOP	562.56/2,500			
TS339IDT	497-2264-1-ND	Micropower Quad CMOS Voltage Comparator	14-SOIC	.83	.75	.60	
TS339IDT	497-2264-2-ND	Micropower Quad					