

STMicroelectronics		Digi-Reel® (Cont.)		AMPLIFIERS AND LINEAR			
		RoHS Compliant Parts Available					
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	10	100	
TS393YDIT	497-10246-2-ND	Micropower Dual CMOS Voltage Comparator*	8-SOIC	626.63/2,500			
TS461CD	497-3039-5-ND	Output Rail-to-Rail Op Amp	8-SOIC	.78	.68	.53	
TS461CDT	497-2281-1-ND	Output Rail-to-Rail Op Amp	8-SOIC	.85	.74	.59	
TS461CDD	497-2281-2-ND	Output Rail-to-Rail Op Amp	8-SOIC	702.70/2,500			
TS461CLT	497-2282-1-ND	Output Rail-to-Rail Op Amp	SOT-23-5	.77	.69	.55	
TS461CLT	497-2282-2-ND	Output Rail-to-Rail Op Amp	SOT-23-5	848.05/3,000			
TS462CD	497-5431-5-ND	Output Rail-to-Rail Op Amp*	8-SOIC	.70	.63	.50	
TS462CDD	497-2283-1-ND	Output Rail-to-Rail Op Amp	8-SOIC	.77	.69	.55	
TS462CDD	497-2283-2-ND	Output Rail-to-Rail Op Amp	8-SOIC	706.71/2,500			
TS462CPT	497-4067-1-ND	Output Rail-to-Rail Op Amp	8-TSSOP	.80	.72	.57	
TS462CPT	497-4067-2-ND	Output Rail-to-Rail Op Amp	8-TSSOP	1178.78/4,000			
TS462CST	497-8109-1-ND	Output R/R Op Amp*	8-Mini SOIC	.93	.83	.66	
TS462CST	497-8109-2-ND	Output R/R Op Amp*	8-Mini SOIC	1367.77/4,000			
TS464CD	497-3040-5-ND	Output Rail-to-Rail Op Amp	14-SOIC	.67	.60	.47	
TS464CDD	497-2285-1-ND	Output Rail-to-Rail Op Amp	14-SOIC	.90	.81	.64	
TS464CDD	497-2285-2-ND	Output Rail-to-Rail Op Amp	14-SOIC	824.82/2,500			
TS464CPT	497-5432-1-ND	Output Rail-to-Rail Op Amp*	14-TSSOP	.92	.81	.64	
TS507CDD	497-5996-1-ND	High Precision R/R Op Amp*	8-SOIC	1.94	1.66	1.36	
TS507CDD	497-5996-2-ND	High Precision R/R Op Amp*	8-SOIC	1867.87/2,500			
TS507CLT	497-6944-1-ND	High Precision R/R Op Amp*	SOT-23-5	2.03	1.75	1.43	
TS507CLT	497-6944-2-ND	High Precision R/R Op Amp*	SOT-23-5	2351.95/3,000			
TS507IDT	497-5997-1-ND	High Precision R/R Op Amp*	8-SOIC	1.59	1.36	1.11	
TS507ILT	497-8118-1-ND	High Precision R/R Op Amp*	SOT-23-5	1.47	1.33	1.07	
TS507ILT	497-8118-2-ND	High Precision R/R Op Amp*	SOT-23-5	2351.95/3,000			
TS507IYLT	497-10249-1-ND	High Precision R/R Op Amp*	SOT-23-5	1.47	1.27	1.04	
TS507IYLT	497-10249-2-ND	High Precision R/R Op Amp*	SOT-23-5	1703.30/3,000			
TS512AIDT	497-2295-1-ND	Precision Dual Op Amp	8-SOIC	1.28	1.15	.91	
TS512AIDT	497-2295-2-ND	Precision Dual Op Amp	8-SOIC	1177.18/2,500			
TS512AIDYD	497-10250-1-ND	Precision Dual Op Amp*	8-SOIC	1.49	1.35	1.08	
TS512AIDYD	497-10250-2-ND	Precision Dual Op Amp*	8-SOIC	1619.62/2,500			
TS512AIDYD	497-2296-1-ND	Precision Dual Op Amp	8-SOIC	1.25	1.12	.89	
TS512IDT	497-2296-2-ND	Precision Dual Op Amp	8-SOIC	1149.15/2,500			
TS512IYD	497-10251-1-ND	Precision Dual Op Amp*	8-SOIC	1.18	1.05	.83	
TS512IYD	497-10251-2-ND	Precision Dual Op Amp*	8-SOIC	1177.18/2,500			
TS514AIDT	497-4453-1-ND	Precision Quad Op Amp	14-SOIC	1.86	1.59	1.30	
TS514AIDT	497-4453-2-ND	Precision Quad Op Amp	14-SOIC	1789.79/2,500			
TS514IDT	497-8119-1-ND	Precision Quad Op Amp*	14-SOIC	1.65	1.42	1.16	
TS514IDT	497-8119-2-ND	Precision Quad Op Amp*	14-SOIC	1589.59/2,500			
TS522IDT	497-3042-5-ND	Low Noise, Dual Op Amp	8-SOIC	1.12	1.00	.79	
TS522IDT	497-2297-1-ND	Low Noise, Dual Op Amp	8-SOIC	1.22	1.09	.87	
TS522IDT	497-2297-2-ND	Low Noise, Dual Op Amp	8-SOIC	1119.12/2,500			
TS524IDT	497-8120-1-ND	Precision LN Quad Op Amp*	14-SOIC	1.47	1.32	1.05	
TS524IDT	497-8120-2-ND	Precision LN Quad Op Amp*	14-SOIC	1353.35/2,500			
TS613ID	497-5434-5-ND	Dual Wide Band Op Amp*	8-SOIC	3.47	3.10	2.54	
TS616IDW	497-4454-5-ND	Dual Wide Band Op Amp	8-TSSOP	1.87	1.69	1.36	
TS616IDWT	497-4455-1-ND	Dual Wide Band Op Amp	8-TSSOP	2.59	2.22	1.82	
TS616IDWT	497-4455-2-ND	Dual Wide Band Op Amp	8-TSSOP	2496.49/2,500			
TS617IDT	497-8529-2-ND	Dual Wide Band Op Amp*	14-SOIC	2.35	2.12	1.71	
TS617IDT	497-8529-2-ND	Dual Wide Band Op Amp*	14-SOIC	2554.55/2,500			
TS861AIDT	497-8130-1-ND	R/R, Micropower BiCMOS Comparator*	8-SOIC	1.12	1.01	.80	
TS861AIDT	497-8130-2-ND	R/R, Micropower BiCMOS Comparator*	8-SOIC	1031.03/2,500			
TS861AILT	497-2308-1-ND	R/R, Micropower BiCMOS Comparator	SOT-23-5	1.88	1.62	1.32	
TS861AILT	497-2308-2-ND	R/R, Micropower BiCMOS Comparator	SOT-23-5	2178.98/3,000			
TS861IDT	497-4072-1-ND	R/R, Micropower BiCMOS Comparator	8-SOIC	1.16	1.00	.82	
TS861IDT	497-4072-2-ND	R/R, Micropower BiCMOS Comparator	8-SOIC	1199.20/2,500			
TS861ILT	497-6777-1-ND	R/R, Micropower BiCMOS Comparator*	SOT-23-5	1.83	1.57	1.28	
TS861ILT	497-6777-2-ND	R/R, Micropower BiCMOS Comparator*	SOT-23-5	2111.71/3,000			
TS862IDT	497-8131-1-ND	R/R, Micropower BiCMOS Comparator*	8-SOIC	1.83	1.57	1.28	
TS862IDT	497-8131-2-ND	R/R, Micropower BiCMOS Comparator*	8-SOIC	1759.76/2,500			
TS862IPT	497-8132-1-ND	R/R, Micropower BiCMOS Comparator*	8-TSSOP	1.83	1.57	1.28	
TS862IPT	497-8132-2-ND	R/R, Micropower BiCMOS Comparator*	8-TSSOP	2815.61/4,000			
TS864AIDT	497-8133-1-ND	R/R, Micropower BiCMOS Comparator	14-SOIC	2.12	1.82	1.49	
TS864AIDT	497-8133-2-ND	R/R, Micropower BiCMOS Comparator	14-SOIC	2044.04/2,500			
TS864IDT	497-8133-1-ND	R/R, Micropower BiCMOS Comparator*	14-SOIC	2.35	2.02	1.65	
TS864IDT	497-8133-2-ND	R/R, Micropower BiCMOS Comparator*	14-SOIC	2270.27/2,500			
TS864IPT	497-8134-1-ND	R/R, Micropower BiCMOS Comparator*	14-TSSOP	2.35	2.02	1.65	
TS864IPT	497-8134-2-ND	R/R, Micropower BiCMOS Comparator*	14-TSSOP	2270.27/2,500			
TS902IDT	497-8135-1-ND	R/R, CMOS Dual Op Amp*	14-SOIC	1.19	1.02	.84	
TS912AIDT	497-2310-1-ND	R/R, CMOS Dual Op Amp	8-SOIC	1.62	1.39	1.14	
TS912AIDT	497-2310-2-ND	R/R, CMOS Dual Op Amp	8-SOIC	1561.56/2,500			
TS912AIN	497-7682-5-ND	R/R, CMOS Dual Op Amp*	8-Dip	1.43	1.30	1.05	
TS912BIDT	497-6617-1-ND	R/R, CMOS Dual Op Amp*	8-SOIC	2.15	1.85	1.51	
TS912BIDT	497-6617-2-ND	R/R, CMOS Dual Op Amp*	8-SOIC	2072.07/2,500			
TS912IDT	497-6618-1-ND	R/R, CMOS Dual Op Amp*	8-SOIC	1.15	1.03	.82	
TS912IDT	497-6618-2-ND	R/R, CMOS Dual Op Amp*	8-SOIC	1059.06/2,500			
TS912IN	497-7683-5-ND	R/R, CMOS Dual Op Amp*	8-Dip	1.39	1.25	1.01	
TS912IYD	497-10252-1-ND	R/R, CMOS Dual Op Amp*	8-SOIC	1.38	1.24	.98	
TS912IYD	497-10252-2-ND	R/R, CMOS Dual Op Amp*	8-SOIC	1267.27/2,500			
TS914AIDT	497-2311-1-ND	R/R, CMOS Quad Op Amp	14-SOIC	2.03	1.75	1.43	
TS914AIDT	497-2311-2-ND	R/R, CMOS Quad Op Amp	14-SOIC	1959.96/2,500			
TS914AIYD	497-10253-1-ND	R/R, CMOS Quad Op Amp*	14-SOIC	2.08	1.89	1.52	
TS914AIYD	497-10253-2-ND	R/R, CMOS Quad Op Amp*	14-SOIC	2270.27/2,500			
TS914IDT	497-6042-1-ND	R/R, CMOS Quad Op Amp*	14-SOIC	2.00	1.72	1.41	
TS914IDT	497-6042-2-ND	R/R, CMOS Quad Op Amp*	14-SOIC	1929.93/2,500			
TS914IYD	497-10254-1-ND	R/R, CMOS Quad Op Amp*	14-SOIC	1.64	1.49	1.20	
TS914IYD	497-10254-2-ND	R/R, CMOS Quad Op Amp*	14-SOIC	1789.79/2,500			
TS921IDT	497-4074-1-ND	R/R, High Output Current Single Op Amp	8-SOIC	1.31	1.18	.94	
TS921IDT	497-4074-2-ND	R/R, High Output Current Single Op Amp	8-SOIC	1207.21/2,500			
TS921IN	497-4075-5-ND	R/R, High Output Current Single Op Amp	8-Dip	.98	.88	.69	
TS921IPT	497-8136-1-ND	R/R, High Output Curr. Single Op Amp*	8-TSSOP	1.12	1.00	.79	
TS921IPT	497-8136-2-ND	R/R, High Output Curr. Single Op Amp*	8-TSSOP	1790.59/4,000			
TS922AIDT	497-6221-1-ND	R/R, High Output Current Dual Op Amp*	8-SOIC	1.74	1.49	1.22	
TS922AIDT	497-6221-2-ND	R/R, High Output Current Dual Op Amp*	8-SOIC	1675.67/2,500			
TS922AIPYD	497-8137-1-ND	R/R, High Output Current Dual Op Amp*	8-TSSOP	1.88	1.62	1.32	
TS922AIPYD	497-8137-2-ND	R/R, High Output Current Dual Op Amp*	8-TSSOP	2905.30/4,000			
TS922AIYD	497-10255-1-ND	R/R, High Output Current Dual Op Amp*	8-SOIC	1.39	1.23	.97	
TS922AIYD	497-10255-2-ND	R/R, High Output Current Dual Op Amp*	8-SOIC	1385.38/2,500			
TS922AIYPT	497-10256-1-ND	R/R, High Output Current Dual Op Amp*	8-TSSOP	1.51	1.35	1.07	
TS922AIYPT	497-10256-2-ND	R/R, High Output Current Dual Op Amp*	8-TSSOP	2216.61/4,000			
TS922IDT	497-6035-1-ND	R/R, High Output Current Dual Op Amp*	8-SOIC	1.74	1.49	1.22	
TS922IDT	497-6035-2-ND	R/R, High Output Current Dual Op Amp*	8-SOIC	1675.67/2,500			

STMicroelectronics		Digi-Reel® (Cont.)		AMPLIFIERS AND LINEAR			
		RoHS Compliant Parts Available					
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	10	100	
TS922IN	497-3049-5-ND	R/R, High Output Current Dual Op Amp	8-Dip	1.54	1.39	1.12	
TS922IPT	497-6619-1-ND	R/R, High Output Current Dual Op Amp*	8-TSSOP	1.51	1.29	1.06	
TS922IPT	497-6619-2-ND	R/R, High Output Current Dual Op Amp*	8-TSSOP	2319.12/4,000			
TS922IYD	497-10257-1-ND	R/R, High Output Current Dual Op Amp*	8-SOIC	1.09	.97	.77	
TS922IYD	497-10257-2-ND	R/R, High Output Current Dual Op Amp*	8-SOIC	1091.09/2,500			
TS922IYPT	497-10258-1-ND	R/R, High Output Current Dual Op Amp*	8-TSSOP	1.09	.97	.77	
TS922IYPT	497-10258-2-ND	R/R, High Output Current Dual Op Amp*	8-TSSOP	1745.74/4,000			
TS924AID	497-2314-5-ND	R/R, High Output Current Quad Op Amp	14-SOIC	2.43	2.20	1.77	
TS924AIPYD	497-8138-1-ND	R/R, High Output Current Quad Op Amp*	14-TSSOP	2.47	2.23	1.82	
TS924AIPYD	497-8138-2-ND	R/R, High Output Current Quad Op Amp*	14-TSSOP	2740.74/2,500			
TS924AIYD	497-10259-1-ND	R/R, High Output Current Quad Op Amp*	14-SOIC	1.86	1.59	1.30	
TS924AIYD	497-10259-2-ND	R/R, High Output Current Quad Op Amp*	14-SOIC	1789.79/2,500			
TS924AIYPT	497-10260-1-ND	R/R, High Output Current Quad Op Amp*	14-TSSOP	1.86	1.59	1.30	
TS924AIYPT	497-10260-2-ND	R/R, High Output Current Quad Op Amp*	14-TSSOP	1789.79/2,500			
TS924ID	497-6778-5-ND	R/R I/O Quad Op Amp*	14-SOIC	2.01	1.82	1.47	
TS924IDT	497-8139-1-ND	R/R, High Output Current Quad Op Amp*	14-SOIC	2.27	1.95	1.59	
TS924IDT	497-8139-2-ND	R/R, High Output Current Quad Op Amp*	14-SOIC	2186.18/2,500			
TS924IPT	497-8140-1-ND	R/R, High Output Current Quad Op Amp*	14-TSSOP	2.44	2.10	1.72	
TS924IPT	497-8140-2-ND	R/R, High Output Current Quad Op Amp*	14-TSSOP	2356.35/2,500			
TS924IYD	497-10261-1-ND	R/R, High Output Current Quad Op Amp*	14-SOIC	1.71	1.47	1.20	
TS924IYD	497-10261-2-ND	R/R, High Output Current Quad Op Amp*	14-SOIC	1645.64/2,500			
TS924IYPT	497-10262-1-ND	R/R, High Output Current Quad Op Amp*	14-TSSOP	1.51	1.37	1.10	
TS924IYPT	497-10262-2-ND	R/R, High Output Current Quad Op Amp*	14-TSSOP	1645.64/2,500			
TS925AIPYD	497-4076-1-ND	R/R, High Output Current Quad Op Amp*	16-TSSOP	2.04	1.84	1.50	
TS925AIPYD	497-4076-2-ND	R/R, High Output Current Quad Op Amp*	16-TSSOP	2456.45/2,500			
TS925ID	497-3050-5-ND	R/R, High Output Current Quad Op Amp	16-SOIC	1.47	1.33	1.07	
TS925IDT	497-6779-1-ND	R/R I/O Quad Op Amp*	16-SOIC	2.08	1.89	1.52	
TS925IDT	497-6779-2-ND	R/R I/O Quad Op Amp*	16-SOIC	2270.27/2,500			
TS925IPT	497-8141-1-ND	R/R, High Output Current Quad Op Amp*	16-TSSOP	2.62	2.25	1.84	
TS925IPT	497-8141-2-ND	R/R, High Output Current Quad Op Amp*	16-TSSOP	2526.52/2,500			
TS931AILT	497-8142-1-ND	Output R/R Micropower Op Amp*	SOT-23-5	.65	.58	.46	
TS931AILT	497-8142-2-ND	Output R/R Micropower Op Amp*	SOT-23-5	95.16/3,000			
TS931ID	497-3051-5-ND	Output R/R Micropower Op Amp	8-SOIC	1.06	.95	.75	
TS931ILT	497-4077-1-ND	Output R/R Micropower Op Amp	SOT-23-5	1.15	1.03	.82	
TS931ILT	497-4077-2-ND	Output R/R Micropower Op Amp	SOT-23-5	1270.87/3,000			
TS932ID	497-3052-5-ND	Dual Out R/R Micropower Op Amp	8-SOIC	1.27	1.13		