

LINEAR TECHNOLOGY		DIGI+Reel® (Cont.)		POWER MANAGEMENT	
Digi-Key Part No.	Description	Pkg.	Price Each*	1	25 100
LT1587C1-3.3PBF-ND	3.3V, 3A, LDO Voltage Regulator*	T0-220	5.06	3.36	2.77
LT1610CS8PBF-ND	1.7MHz, Single Cell DC/DC Converter*	8-MSOP	3.41	2.27	1.74
LT1610CS9PBF-ND	1.7MHz, Single Cell DC/DC Converter*	8-SOIC	2.89	1.92	1.45
LT1610CS5FTRMPBFC-ND	1.4MHz, Inverting Switching Regulator*	SOT-23-5	3.51	2.34	1.86
LT1611CSS5FTRMPBFC-ND	1.4MHz, Inverting Switching Regulator*	SOT-23-5	908.71/500		
LT1613CSS5FTRMPBFC-ND	1.4MHz, Single Cell DC/DC Converter*	TSOT-23-5	3.42	3.06	2.76
LT1613CS5FTRMPBFC-ND	1.4MHz, Single Cell DC/DC Controller*	TSOT-23-5	764.14/500		
LT1614CMS8-ND	600kHz, Inverting Switching Regulator	8-MSOP	4.54	3.02	2.32
LT1614CMS9PBF-ND	600kHz, Inverting Switching Regulator*	8-MSOP	4.54	3.02	2.32
LT1614CS8PBF-ND	600kHz, Inverting Switching Regulator*	8-SOIC	4.13	2.75	2.11
LT1615ES5FTRMPBFC-ND	Micropower Step-Up DC/DC Converter*	TSOT-23-5	3.42	3.06	2.76
LT1615ES5FTRMPBFC-ND	Micropower Step-Up DC/DC Converter*	TSOT-23-5	764.14/500		
LT1615ES5-1FTR-ND	Micropower Step-Up DC/DC Converter	TSOT-23-5	3714.45/2,500		
LT1615ES5-1FTRMPBFC-ND	Micropower Step-Up DC/DC Converter*	TSOT-23-5	3.42	3.06	2.76
LT1615ES5-1FTRMPBFC-ND	Micropower Step-Up DC/DC Converter*	TSOT-23-5	764.14/500		
LT1615IS5FTRMPBFC-ND	Micropower Step-Up DC/DC Converter*	TSOT-23-5	3.88	3.47	3.13
LT1615IS5FTRMPBFC-ND	Micropower Step-Up DC/DC Converter*	TSOT-23-5	867.41/500		
LT1616ES6FTRMPBFC-ND	1.4MHz, Step-Down Switching Regulator*	SOT-23-6	3.88	3.47	3.13
LT1616ES6FTRMPBFC-ND	1.4MHz, Step-Down Switching Regulator*	SOT-23-6	867.41/500		
LT1617ES5FTRMPBFC-ND	Micropower Inverting DC/DC Converter*	TSOT-23-5	3.42	3.06	2.76
LT1617ES5FTRMPBFC-ND	Micropower Inverting DC/DC Converter*	TSOT-23-5	764.14/500		
LT1618MS8PBF-ND	1.4MHz, Step-Up DC/DC Converter*	10-MSOP	2.89	1.92	1.54
LT1619EMS8PBF-ND	300kHz, 2-Cell Current Mode PWM Controller*	8-MSOP	3.72	2.47	1.86
LT1619EMS8TR-ND	300kHz, 2-Cell Current Mode PWM Controller	8-MSOP	4904.97/2,500		
LT1619ES8PBF-ND	300kHz, 2-Cell Current Mode PWM Controller*	8-SOIC	3.51	2.34	1.76
LT1619ES8TR-ND	300kHz, 2-Cell Current Mode PWM Controller	8-SOIC	4657.74/2,500		
LT1676CS8PBF-ND	High Efficiency, Step-Down Switching Regulator*	8-SOIC	4.44	2.95	2.36
LT1676IS8PBF-ND	High Eff., Step-Down Switching Reg., Ind. Temp.*	8-SOIC	5.16	3.43	2.77
LT1680C9PBF-ND	High Power DC/DC Step-Up Controller*	16-Dip	6.61	4.39	3.52
LT1680CSW8PBF-ND	High Power DC/DC Step-Up Controller*	16-SOIC	6.92	4.60	3.68
LT1680ISW8PBF-ND	High Power DC/DC Step-Up Controller*	16-SOIC	8.26	5.49	4.42
LT1681ESW8PBF-ND	Dual Transistor Sync. Forward Controller*	20-SOIC	8.78	5.83	4.39
LT1683ES8PBF-ND	Ultra Low Noise Push-Pull DC/DC Controller*	20-SSOP	7.96	5.28	4.01
LT1725IS8PBF-ND	General Purpose Isolated Flyback Controller*	16-SOIC	5.78	3.84	2.90
LT1737IG8PBF-ND	High Power Isolated Flyback Controller*	16-SSOP	5.99	3.88	3.00
LT1738EG8PBF-ND	Ultra Low Noise DC/DC Controller*	20-SSOP	7.13	4.74	3.57
LT1761ES5-BYP#TRMPBFC-ND	Adj., 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	1.97	1.76	1.58
LT1761ES5-BYP#TRMPBFC-ND	Adj., 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	438.87/500		
LT1761ES5-1.5#TRMPBFC-ND	1.5V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	1.97	1.76	1.58
LT1761ES5-1.8#TRMPBFC-ND	1.8V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	1.97	1.76	1.58
LT1761ES5-1.8#TRMPBFC-ND	1.8V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	438.87/500		
LT1761ES5-2.5#TRMPBFC-ND	2.5V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	1.97	1.76	1.58
LT1761ES5-2.5#TRMPBFC-ND	2.5V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	438.87/500		
LT1761ES5-2.5#TRMPBFC-ND	2.5V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	1.97	1.76	1.58
LT1761ES5-2.5#TRMPBFC-ND	2.5V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	438.87/500		
LT1761ES5-3#TRMPBFC-ND	3V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	1.97	1.76	1.58
LT1761ES5-3#TRMPBFC-ND	3V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	438.87/500		
LT1761ES5-3#TRMPBFC-ND	3V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	1.97	1.76	1.58
LT1761ES5-3#TRMPBFC-ND	3V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	438.87/500		
LT1761ES5-5#TRMPBFC-ND	5V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	1.97	1.76	1.58
LT1761ES5-5#TRMPBFC-ND	5V, 100mA, Low Noise LDO MPU Regulator*	TSOT-23-5	438.87/500		
LT1761ES5-SD#TRMPBFC-ND	Adj., 100mA, Low Noise, LDO MPU Regulator*	TSOT-23-5	1.97	1.76	1.58
LT1761ES5-SD#TRMPBFC-ND	Adj., 100mA, Low Noise, LDO MPU Regulator*	TSOT-23-5	438.87/500		
LT1761ES5-1.2#TRMPBFC-ND	1.2V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	2.15	1.93	1.73
LT1761ES5-1.2#TRMPBFC-ND	1.2V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	528.70/500		
LT1761ES5-1.5#TRMPBFC-ND	1.5V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	2.15	1.93	1.73
LT1761ES5-1.5#TRMPBFC-ND	1.5V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	528.70/500		
LT1761ES5-1.8#TRMPBFC-ND	1.8V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	2.15	1.93	1.73
LT1761ES5-1.8#TRMPBFC-ND	1.8V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	528.70/500		
LT1761ES5-2.0#TRMPBFC-ND	2V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	2.15	1.93	1.73
LT1761ES5-2.0#TRMPBFC-ND	2V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	528.70/500		
LT1761ES5-2.5#TRMPBFC-ND	2.5V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	2.15	1.93	1.73
LT1761ES5-2.5#TRMPBFC-ND	2.5V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	528.70/500		
LT1761ES5-2.8#TRMPBFC-ND	2.8V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	2.15	1.93	1.73
LT1761ES5-2.8#TRMPBFC-ND	2.8V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	528.70/500		
LT1761ES5-3#TRMPBFC-ND	3V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	2.15	1.93	1.73
LT1761ES5-3#TRMPBFC-ND	3V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	528.70/500		
LT1761ES5-3#TRMPBFC-ND	3V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	2.15	1.93	1.73
LT1761ES5-3#TRMPBFC-ND	3V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	528.70/500		
LT1761ES5-5#TRMPBFC-ND	5V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	2.15	1.93	1.73
LT1761ES5-5#TRMPBFC-ND	5V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	528.70/500		
LT1761ES5-5#TRMPBFC-ND	5V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	2.15	1.93	1.73
LT1761ES5-5#TRMPBFC-ND	5V, 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	528.70/500		
LT1761ES5-SD#TRMPBFC-ND	Adj., 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	2.15	1.93	1.73
LT1761ES5-SD#TRMPBFC-ND	Adj., 100mA, Low Noise LDO MPU Reg.*	TSOT-23-5	528.70/500		
LT1762EMS8-5#PBF-ND	Adj., 150mA, Low Noise LDO MPU Regulator*	8-MSOP	1.97	1.31	99
LT1762EMS8-5#PBF-ND	Adj., 150mA, Low Noise LDO MPU Regulator*	8-MSOP	1.97	1.31	99
LT1763CS8PBF-ND	Adj., 500mA, Low Noise LDO MPU Regulator*	8-SOIC	3.41	2.27	1.71
LT1763CS8-2.5#PBF-ND	2.5V, 500mA, Low Noise, LDO MPU Regulator*	8-SOIC	3.41	2.27	1.71
LT1763CS8-3.3#PBF-ND	3.3V, 500mA, Low Noise, LDO MPU Regulator*	8-SOIC	3.41	2.27	1.71
LT1763CS8-5#PBF-ND	5V, 500mA, Low Noise, LDO MPU Regulator*	8-SOIC	3.41	2.27	1.71
LT1763D4EPBF-ND	Adj., 500mA, Low Noise, LDO MPU Reg.*	12-DFN	3.78	2.54	2.16
LT1763D1-1.8#PBF-ND	1.8V, 500mA, Low Noise, LDO MPU Reg.*	12-DFN	3.78	2.54	2.16
LT1763D1-2.5#PBF-ND	2.5V, 500mA, Low Noise, LDO MPU Reg.*	12-DFN	3.78	2.54	2.16
LT1763D1-3.3#PBF-ND	3.3V, 500mA, Low Noise, LDO MPU Reg.*	12-DFN	3.78	2.54	2.16
LT1763D1-5#PBF-ND	5V, 500mA, Low Noise, LDO MPU Reg.*	12-DFN	3.78	2.54	2.16
LT1763IS8-1.8#PBF-ND	1.8V, 500mA, Low Noise, LDO MPU Reg.*	8-SOIC	3.78	2.54	2.16
LT1764AEQ8PBF-ND	Adj., 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	6.10	4.21	3.47
LT1764AEQ-1.5-ND	1.5V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	6.10	4.21	3.47
LT1764AEQ-1.5#PBF-ND	1.5V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	6.10	4.21	3.47
LT1764AEQ-1.8#PBF-ND	1.8V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	6.10	4.21	3.47
LT1764AEQ-2.5#PBF-ND	2.5V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	6.10	4.21	3.47
LT1764AEQ-3.3#PBF-ND	3.3V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	6.10	4.21	3.47
LT1764AET-3.3#PBF-ND	Adj., 3A, Fast Transient Response, LDO Reg.*	T0-220-5	6.10	4.21	3.47
LT1764AET-3.3#PBF-ND	Adj., 3A, Fast Transient Response, LDO Reg.*	T0-220-5	6.10	4.21	3.47
LT1764EQ-2.5#PBF-ND	2.5V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	6.10	4.21	3.47
LT1764EQ-3.3#PBF-ND	3.3V, 3A, Fast Transient Response, LDO Reg.*	5-DDPAK	6.10	4.21	3.47
LT1765EFE8PBF-ND	3A Step-Down Switching Regulator*	16-TSSOP	7.97	5.70	4.70
LT1765EFE-1.8-ND	1.8V, 3A Step-Down Switching Regulator	16-TSSOP	7.97	5.70	4.70
LT1765EFE-1.8#PBF-ND	1.8V, 3A Step-Down Switching Regulator*	16-TSSOP	7.97	5.70	4.70
LT1765EFE-2.5-ND	2.5V, 3A Step-Down Switching Regulator	16-TSSOP	7.97	5.70	4.70
LT1765EFE-2.5#PBF-ND	2.5V, 3A Step-Down Switching Regulator*	16-TSSOP	7.97	5.70	4.70
LT1765EFE-3.3#PBF-ND	3.3V, 3A Step-Down Switching Regulator*	16-TSSOP	7.97	5.70	4.70
LT1765EFE-5-ND	5V, 3A Step-Down Switching Regulator	16-TSSOP	7.97	5.70	4.70

LINEAR TECHNOLOGY		DIGI+Reel® (Cont.)		POWER MANAGEMENT	
Digi-Key Part No.	Description	Pkg.	Price Each*	1	25 100
LT1765EFE-5#PBF-ND	5V, 3A Step-Down Switching Regulator*	16-TSSOP	7.97	5.70	4.70
LT1765ESE8PBF-ND	3A-Step-Down Switching Regulator*	8-SOIC	7.91	5.26	3.96
LT1766EFE#PBF-ND	1.5A, 200kHz Step-Down Switching Regulator*	16-TSSOP	6.20	4.43	3.65
LT1766EG8PBF-ND	1.5A, 200kHz Step-Down Switching Regulator*	16-SSOP	6.10	4.05	3.08
LT1766EGN-5#PBF-ND	1.5A, 200kHz Step-Down Switching Regulator*	16-SSOP	6.10	4.05	3.08
LT1766IG8PBF-ND	Adj., Mono 1.5A Step-Down Switching Regulator*	16-SSOP	7.43	4.94	3.72
LT1767EMS8PBF-ND	2.5V, Mono 1.5A Step-Down Switching Regulator*	8-MSOP	4.96	3.30	2.57
LT1767EMS-2.5-ND	2.5V, Mono 1.5A Step-Down Switching Regulator	8-MSOP	4.96	3.30	2.57
LT1767EMS-2.5#PBF-ND	2.5V, Mono 1.5A Step-Down Switching Reg.*	8-MSOP	4.96	3.30	2.57
LT1767EMS-3.3#PBF-ND	3.3V, Mono 1.5A Step-Down Switching Reg.*	8-MSOP	4.96	3.30	2.57
LT1767EMS-5#PBF-ND	5V, Mono 1.5A Step-Down Switching Regulator*	8-MSOP	4.96	3.30	2.57
LT1767EMS8EPBF-ND	Mono 1.5A Step-Down Switching Reg.*	8-MSOP	5.04	3.61	2.97
LT1767EMS8E-1.8#PBF-ND	1.8V, Mono 1.5A Step-Down Switching Reg.*	8-MSOP	5.04	3.61	2.97
LT1767EMS8E-3.3#PBF-ND	3.3V, Mono 1.5A Step-Down Switching Reg.*	8-MSOP	5.04	3.61	2.97
LT1767EMS8E-5#PBF-ND	5V, Mono 1.5A Step-Down Switching Regulator*	8-MSOP	5.04	3.61	2.97
LT1767GN8PBF-ND	High Eff., Step-Down Switching Regulator*	8-Dip	4.13	2.75	2.19
LT1767CS8PBF-ND	High Eff., Step-Down Switching Regulator*	8-SOIC	4.34	2.88	2.28
LT1767IS8#PBF-ND	High Eff., Step-Down Switching Regulator*	8-SOIC	4.96	3.30	2.61
LT1777IS#PBF-ND	Low Noise Step-Down Switching Regulator*	16-SOIC	5.16	3.43	2.77
LT1912EDD#PBF-ND	2A, 500kHz, Step-Down Switching Regulator*	10-DFN	4.87	3.48	2.87
LT1912EMSE#PBF-ND	2A, 500kHz, Step-Down Switching Regulator*	10-MSOP	5.04	3.61	2.97
LT1913EDD#PBF-ND	3.5A, 2.4MHz, Step-Down Switching Regulator*	10-DFN	6.40	4.32	3.66
LT1930AES5FTRMPBFC-ND	2.2MHz, Step-Up DC/DC Converter*	TSOT-23-5	3.88	3.47	3.13
LT1930AES5FTRMPBFC-ND	2.2MHz, Step-Up DC/DC Converter*	TSOT-23-5	867.41/500		
LT1930AES5FTRMPBFC-ND	1.2MHz, Step-Up DC/DC Converter*	TSOT-23-5	3.88	3.47	3.13
LT1930AES5FTRMPBFC-ND	1.2MHz, Step-Up DC/DC Converter*	TSOT-23-5	867.41/500		
LT1931AES5FTRMPBFC-ND	2.2MHz, Inverting DC/DC Converter*	TSOT-23-5	4.11	3.68	3.31
LT1931AES5FTRMPBFC-ND	2.2MHz, Inverting DC/DC Converter*	TSOT-23-5	919.04/500		
LT1931ES5FTRMPBFC-ND	1.2MHz, Inverting DC/DC Converter*	TSOT-23-5	4.11	3.68	3.31
LT1931ES5FTRMPBFC-ND	1.2MHz, Inverting DC/DC Converter*	TSOT-23-5	919.04/500		
LT1932ES6FTRMPBFC-ND	Constant-Current DC/DC LED Driver*	SOT-23-6	3.44	3.08	2.77
LT1932ES6FTRMPBFC-ND	Constant-Current DC/DC LED Driver*	SOT-23-6	769.31/500		
LT1933ES6FTRMPB					