

Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25	100
LTC1278-5CSW#PBF-ND	12-Bit Sampling ADC with Shutdown*	24-SOIC	21.17	14.13	12.11
LTC1279CG-ND	12-Bit Sampling ADC with Shutdown	24-SSOP	21.38	14.20	11.74
LTC1282BCSW-ND	12-Bit 3V, Sampling ADC with Reference	24-SOIC	23.24	15.49	12.19
LTC1285CN#PBF-ND	12-Bit 3V, Micropower Sampling ADC*	8-Dip	10.49	6.97	5.37
LTC1286CN#PBF-ND	12-Bit Micropower Sampling ADC*	8-Dip	8.16	5.46	4.34
LTC1286CS#PBF-ND	12-Bit Micropower Sampling ADC*	8-SOIC	8.78	5.87	4.67
LTC1286IS#PBF-ND	12-Bit Micropower Sampling ADC*	8-SOIC	10.95	7.32	5.83
LTC1288CN#PBF-ND	12-Bit 3V, Serial In/Out Sampling ADC*	8-Dip	10.49	6.97	5.37
LTC1288CS#PBF-ND	12-Bit 3V, Serial In/Out Sampling ADC*	8-SOIC	11.15	7.41	5.75
LTC1290CCN#PBF-ND	12-Bit Data Acquisition System*	20-Dip	26.10	17.34	13.18
LTC1290CCSW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	31.31	20.79	15.82
LTC1290CIN#PBF-ND	12-Bit Data Acquisition System*	20-Dip	37.34	24.80	19.29
LTC1290CISW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	37.34	24.80	19.29
LTC1290DCN#PBF-ND	12-Bit Data Acquisition System*	20-Dip	10.90	7.25	5.54
LTC1290DCSW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	18.42	12.24	9.38
LTC1291CCN8-ND	12-Bit Data Acquisition System	8-Dip	23.24	15.49	12.40
LTC1291CCN8#PBF-ND	12-Bit Data Acquisition System*	8-Dip	23.24	15.49	12.40
LTC1291DCN8#PBF-ND	12-Bit Data Acquisition System*	8-Dip	14.98	10.00	7.85
LTC1292CCN8#PBF-ND	12-Bit Data Acquisition System*	8-Dip	23.24	15.49	12.40
LTC1292DCN8#PBF-ND	12-Bit Data Acquisition System*	8-Dip	14.98	10.00	7.85
LTC1293CCN#PBF-ND	12-Bit Data Acquisition System*	16-Dip	37.18	24.78	19.80
LTC1293CCN#PBF-ND	12-Bit Data Acquisition System*	16-Dip	24.78	15.52	13.18
LTC1293DCN#PBF-ND	12-Bit Data Acquisition System*	16-Dip	14.98	10.00	7.85
LTC1293DCN#PBF-ND	12-Bit Data Acquisition System*	16-SOIC	17.97	11.98	9.38
LTC1294BCSW-ND	12-Bit Data Acquisition System	20-SOIC	37.18	24.78	19.80
LTC1294CCSW-ND	12-Bit Data Acquisition System*	20-SOIC	29.74	19.83	15.82
LTC1294DCN#PBF-ND	12-Bit Data Acquisition System*	20-Dip	14.98	10.00	7.85
LTC1294DCSW-ND	12-Bit Data Acquisition System	20-SOIC	17.97	11.98	9.38
LTC1294DCSW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	17.97	11.98	9.38
LTC1296BCN#PBF-ND	12-Bit Data Acquisition System*	20-Dip	20.14	13.43	10.74
LTC1296BCSW-ND	12-Bit Data Acquisition System*	20-SOIC	20.65	13.76	11.03
LTC1296BCSW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	20.65	13.76	11.03
LTC1296CCSW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	14.77	9.84	7.85
LTC1296DCN#PBF-ND	12-Bit Data Acquisition System*	20-Dip	13.12	8.76	6.99
LTC1296DCSW#PBF-ND	12-Bit Data Acquisition System*	20-SOIC	13.42	8.97	7.15
LTC1297DCN8-ND	12-Bit Data Acquisition System	8-Dip	17.97	11.98	9.42
LTC1297DCN8#PBF-ND	12-Bit Data Acquisition System*	8-Dip	17.97	11.98	9.42
LTC1298CN8#PBF-ND	12-Bit Sampling ADC*	8-Dip	8.16	5.46	4.34
LTC1298CS8#PBF-ND	12-Bit Sampling ADC*	8-SOIC	8.78	5.87	4.67
LTC1298IS8#PBF-ND	12-Bit Sampling ADC, Ind. Temp*	8-SOIC	10.95	7.32	5.83
LTC1392CN8#PBF-ND	10-Bit Micropwr. Data Acquisition System*	8-Dip	6.20	4.14	3.39
LTC1400CS8#PBF-ND	12-Bit 400kSPS ADC with Shutdown*	8-SOIC	8.26	5.49	4.34
LTC1400IS8-ND	12-Bit 400kSPS ADC with Shutdown*	8-SOIC	9.19	6.11	4.84
LTC1400IS8#PBF-ND	12-Bit 400kSPS ADC with Shutdown*	8-SOIC	9.19	6.11	4.84
LTC1401IS8#PBF-ND	12-Bit 200kSPS ADC with Shutdown*	8-SOIC	6.40	4.26	3.35
LTC1403ACMSE#PBF-ND	14-Bit 2.8MSPS Sampling ADC*	10-MSPOP	11.57	8.27	6.81
LTC1403AIMSE-1#PBF-ND	14-Bit 2.8MSPS Sampling ADC*	10-MSPOP	11.57	8.27	6.81
LTC1403AIMSE#PBF-ND	14-Bit 2.8MSPS Sampling ADC*	10-MSPOP	13.22	9.45	7.78
LTC1403AIMSE-1#PBF-ND	14-Bit 2.8MSPS Sampling ADC*	10-MSPOP	13.22	9.45	7.78
LTC1403CMSE#PBF-ND	12-Bit 2.8MSPS Sampling ADC*	10-MSPOP	6.61	4.72	3.90
LTC1403CMSE-1#PBF-ND	12-Bit 2.8MSPS Sampling ADC*	10-MSPOP	6.61	4.72	3.90
LTC1403IMSE#PBF-ND	12-Bit 2.8MSPS Sampling ADC*	10-MSPOP	7.54	5.39	4.44
LTC1403IMSE-1#PBF-ND	12-Bit 2.8MSPS Sampling ADC*	10-MSPOP	7.54	5.39	4.44
LTC1404CS8#PBF-ND	12-Bit 600kSPS ADC with Shutdown*	8-SOIC	8.67	5.76	4.55
LTC1404IS8#PBF-ND	12-Bit 600kSPS ADC with Shutdown*	8-SOIC	9.50	6.31	5.00
LTC1407AHMSE#PBF-ND	14-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	16.96	11.40	9.70
LTC1407ACMSE#PBF-ND	14-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	11.57	8.27	6.81
LTC1407ACMSE-1#PBF-ND	14-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	11.57	8.27	6.81
LTC1407AIMSE#PBF-ND	14-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	13.22	9.45	7.78
LTC1407AIMSE-1#PBF-ND	14-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	13.22	9.45	7.78
LTC1407CMSE#PBF-ND	12-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	6.61	4.72	3.90
LTC1407CMSE-1#PBF-ND	12-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	6.61	4.72	3.90
LTC1407IMSE-1#PBF-ND	12-Bit 3MSPS Simultaneous Sampling ADC*	10-MSPOP	7.54	5.39	4.44
LTC1408CUH#PBF-ND	14-Bit 600kSPS ADC with Shutdown*	32-QFN	15.16	10.83	8.92
LTC1408CUH-12#PBF-ND	12-Bit 600kSPS ADC with Shutdown*	32-QFN	9.57	6.84	5.63
LTC1408IUH#PBF-ND	14-Bit 600kSPS ADC w/Shutdown*	32-QFN	18.20	13.00	10.71
LTC1408IUH-12#PBF-ND	12-Bit 600kSPS ADC w/Shutdown*	32-QFN	11.48	8.21	6.76
LTC1410CSW#PBF-ND	12-Bit 1.25MSPS Sampling ADC*	28-SSOP	17.55	11.66	8.90
LTC1412CG#PBF-ND	12-Bit 2MSPS Sampling ADC*	28-SSOP	17.66	11.73	8.83
LTC1414CG#PBF-ND	14-Bit 2MSPS Sampling ADC*	28-SSOP	28.09	18.72	15.00
LTC1415CG#PBF-ND	12-Bit 1.25MSPS Sampling ADC*	28-SSOP	18.38	12.21	9.22
LTC1415CSW#PBF-ND	12-Bit 1.25MSPS Sampling ADC*	28-SOIC	17.55	11.66	8.90
LTC1415IG#PBF-ND	12-Bit 1.25MSPS Sampling ADC*	28-SSOP	20.03	13.31	10.04
LTC1416CG#PBF-ND	14-Bit 400kSPS Sampling ADC, Ind. Temp*	28-SSOP	12.18	8.10	6.12
LTC1416IG#PBF-ND	14-Bit 400kSPS Sampling ADC, Ind. Temp*	28-SSOP	13.01	8.64	6.51
LTC1417ACGN#PBF-ND	14-Bit 400kSPS Sampling ADC*	16-SSOP	16.52	10.98	8.27
LTC1417CGN#PBF-ND	14-Bit 400kSPS Sampling ADC*	16-SSOP	13.42	8.92	6.74
LTC1417IGN#PBF-ND	14-Bit 400kSPS Sampling ADC*	16-SSOP	14.77	9.81	7.40
LTC1418ACG#PBF-ND	14-Bit 200kSPS ADC, Serial/Parallel I/O*	28-SSOP	18.38	12.21	9.22
LTC1418AIG-ND	14-Bit 200kSPS ADC, S/P I/O, Ind. Temp.	28-SSOP	19.73	13.10	9.88
LTC1418CG-ND	14-Bit 200kSPS ADC, S/P I/O, Ind. Temp.	28-SSOP	14.25	9.47	7.15
LTC1418CG#PBF-ND	14-Bit 200kSPS ADC, S/P I/O, Ind. Temp.*	28-SSOP	14.25	9.47	7.15
LTC1418CN-ND	14-Bit 200kSPS ADC, Serial/Parallel I/O*	28-Dip	13.84	9.19	6.94
LTC1418CN#PBF-ND	14-Bit 200kSPS ADC, Serial/Parallel I/O*	28-Dip	13.84	9.19	6.94
LTC1419ACSW#PBF-ND	14-Bit 800kSPS Sampling ADC*	28-SOIC	44.20	29.35	22.10
LTC1419CG-ND	14-Bit 800kSPS Sampling ADC	28-SSOP	26.85	17.83	13.40
LTC1419CSW#PBF-ND	14-Bit 800kSPS Sampling ADC*	28-SOIC	26.84	17.69	13.33
LTC1419IG#PBF-ND	14-Bit 800kSPS Sampling ADC, Ind. Temp*	28-SSOP	29.95	19.89	15.06
LTC1594CS#PBF-ND	4-Channel, 12-Bit SV, Sampling Serial ADC*	16-SOIC	9.29	6.18	4.96
LTC1594IS#PBF-ND	4-Channel, 12-Bit SV, Sampling Serial ADC*	16-SOIC	10.74	7.14	5.75
LTC1598CG-ND	8-Channel, 12-Bit SV, Sampling Serial ADC*	24-SSOP	9.50	6.31	5.13
LTC1598CG#PBF-ND	8-Channel, 12-Bit SV, Sampling Serial ADC*	24-SSOP	9.50	6.31	5.13
LTC1598LCG#PBF-ND	8-Channel, 12-Bit SV, Sampling Serial ADC*	24-SSOP	9.61	6.41	5.33
LTC1603CG#PBF-ND	16-Bit Sampling ADC with Shutdown*	36-SSOP	16.84	11.24	9.34
LTC1604AIG#PBF-ND	16-Bit Sampling ADC with Shutdown*	36-SSOP	52.15	34.63	26.08
LTC1604CG#PBF-ND	16-Bit Sampling ADC with Shutdown*	36-SSOP	36.76	24.41	18.39
LTC1605ACC#PBF-ND	16-Bit, 100kSPS Sampling ADC*	28-SSOP	41.00	27.23	20.53
LTC1605AISW#PBF-ND	16-Bit, 100kSPS Sampling ADC, Ind. Temp*	28-SOIC	42.13	27.98	21.07
LTC1605CN#PBF-ND	16-Bit, 100kSPS Sampling ADC*	28-Dip	29.85	19.82	14.93
LTC1605CSW#PBF-ND	16-Bit, 100kSPS Sampling ADC*	28-SOIC	29.85	19.82	14.93
LTC1605IN#PBF-ND	16-Bit, 100kSPS Sampling ADC, Ind. Temp*	28-Dip	31.60	20.99	15.82
LTC1605ISW#PBF-ND	16-Bit, 100kSPS Sampling ADC, Ind. Temp*	28-SOIC	31.60	20.99	15.82
LTC1605-1CG#PBF-ND	16-Bit, 100kSPS Sampling ADC*	28-SSOP	30.47	20.23	15.45
LTC1605-2CG#PBF-ND	16-Bit, 100kSPS Sampling ADC*	28-SSOP	30.47	20.23	15.45

* RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

(Continued)

Free shipping on orders over €65! All prices in euro and include duties. (EU2011-EN) 1139

C