

DIGI KEY PART NO.		DESCRIPTION		Pkg.		PRICE EACH*		
				1	25	100		
<b>Delta Sigma ADC</b>								
LTC2400CS8#PBF-ND	24-Bit Microprocessor ADC*	8-SOIC	8.78	5.87	5.00			
LTC2400IS8#PBF-ND	24-Bit Microprocessor ADC, Ind. Temp.*	8-SOIC	10.02	6.70	5.75			
LTC2401CMS#PBF-ND	24-Bit, 1-Channel uPwr Delta Sigma ADC*	10-MSPOP	8.47	5.63	4.67			
LTC2402CMS#PBF-ND	24-Bit, 2-Channel uPwr Delta Sigma ADC*	10-MSPOP	8.99	5.97	4.92			
LTC2408CG#PBF-ND	24-Bit, 8-Channel uPwr ADC*	28-SSOP	10.02	6.70	5.75			
LTC2410CG#PBF-ND	24-Bit, No Latency Delta Sigma ADC*	16-SSOP	8.78	5.87	5.00			
LTC2411CMS#PBF-ND	24-Bit, No Latency Delta Sigma ADC*	10-MSPOP	8.78	5.87	5.00			
LTC2411CMSTR-ND	24-Bit, No Latency Delta Sigma ADC*	10-MSPOP	12788	76/2,500				
LTC2411IMS#PBF-ND	24-Bit, No Latency Delta Sigma ADC*	10-MSPOP	10.02	6.70	5.75			
LTC2411IMSTR-ND	24-Bit, No Latency Delta Sigma ADC*	10-MSPOP	14649	44/2,500				
LTC2412CGN-ND	24-Bit, No Latency Delta Sigma ADC	16-SSOP	7.85	5.22	4.18			
LTC2412CGN#PBF-ND	24-Bit, No Latency Delta Sigma ADC*	16-SSOP	7.85	5.22	4.18			
LTC2413CGN#PBF-ND	24-Bit, Microprocessor ADC*	16-SSOP	8.78	5.87	5.00			
LTC2413IGN#PBF-ND	24-Bit, Microprocessor ADC*	16-SSOP	10.02	6.70	5.75			
LTC2414CGN#PBF-ND	24-Bit, 8-Ch. No Latency Delta Sigma ADC*	28-SSOP	10.02	6.70	5.75			
LTC2415CGN#PBF-ND	24-Bit No Latency Delta Sigma ADC*	16-SSOP	8.78	5.87	5.00			
LTC241510GN#PBF-ND	24-Bit No Latency Delta Sigma ADC*	16-SSOP	8.78	5.87	5.00			
LTC241515GN#PBF-ND	24-Bit No Latency Delta Sigma ADC*	16-SSOP	10.02	6.70	5.75			
LTC2418CGN#PBF-ND	24-Bit, 16-Ch. No Latency Delta Sigma ADC*	28-SSOP	11.15	7.44	6.31			
LTC2418IGN#PBF-ND	24-Bit, 16-Ch. No Latency Delta Sigma ADC*	28-SSOP	12.29	8.18	7.03			
LTC2420CS8#PBF-ND	20-Bit, uPwr No Latency Delta Sigma ADC*	8-SOIC	6.82	4.53	3.72			
LTC2420IS8#PBF-ND	20-Bit, uPwr No Latency Delta Sigma ADC*	8-SOIC	7.54	5.01	4.14			
LTC2421IMS#PBF-ND	20-Bit, 1-Channel uPwr Delta Sigma ADC*	10-MSPOP	7.85	5.22	4.34			
LTC2422CMS#PBF-ND	20-Bit, 2-Channel uPwr Delta Sigma ADC*	10-MSPOP	7.23	4.80	3.97			
LTC2422IMS#PBF-ND	20-Bit, 2-Channel uPwr Delta Sigma ADC*	10-MSPOP	8.05	5.35	4.47			
LTC2424CG#PBF-ND	20-Bit, 4-Channel uPwr Delta Sigma ADC*	28-SSOP	7.64	5.08	4.22			
LTC2428CG#PBF-ND	20-Bit, 8-Channel uPwr Delta Sigma ADC*	28-SSOP	8.37	5.56	4.63			
LTC2431CMS#PBF-ND	20-Bit Delta Sigma ADC*	10-MSPOP	6.10	4.05	3.27			
LTC24331CMS#PBF-ND	16-Bit No Latency Delta Sigma ADC*	10-MSPOP	3.21	2.15	1.82			
LTC24361CGN#PBF-ND	16-Bit No Latency Delta Sigma ADC*	16-SSOP	4.03	2.68	2.15			
LTC2440CGN#PBF-ND	24-Bit, Differential Delta Sigma ADC*	16-SSOP	9.19	6.11	5.13			
LTC2440IGN#PBF-ND	24-Bit, Differential Delta Sigma ADC*	16-SSOP	10.43	6.93	5.75			
LTC2442CG#PBF-ND	24-Bit, 4-Channel Delta Sigma ADC*	36-SSOP	12.61	8.79	7.24			
LTC2442IG#PBF-ND	24-Bit, 4-Channel Delta Sigma ADC*	36-SSOP	14.71	10.55	8.69			
LTC2444CUHF#PBF-ND	24-Bit, 8-Ch./16-Ch. Delta Sigma ADC*	38-DFN	10.64	7.07	5.66			
LTC2445CUHF#PBF-ND	24-Bit, 8-Ch./16-Ch. Delta Sigma ADC*	38-DFN	10.64	7.07	5.66			
LTC2445IUHF#PBF-ND	24-Bit, 8-Ch. Delta Sigma ADC*	38-DFN	12.29	8.16	6.57			
LTC2446IUHF#PBF-ND	24-Bit, 8-Channel Delta Sigma ADC*	38-DFN	13.63	9.06	7.27			
LTC2447IUHF#PBF-ND	24-Bit, 8-Channel Delta Sigma ADC*	38-DFN	13.63	9.06	7.27			
LTC2448CUHF#PBF-ND	24-Bit, 8-Ch./16-Ch. Delta Sigma ADC*	38-DFN	11.77	7.82	6.28			
LTC2449CUHF#PBF-ND	24-Bit, 8-Ch./16-Ch. Delta Sigma ADC*	38-DFN	11.77	7.82	6.28			
LTC2450CDD#TRMPBFCT-ND	16-Bit Delta Sigma ADC*	6-DFN	2.26	2.03	1.83			
LTC2450CDD#TRMPBFTR-ND	16-Bit Delta Sigma ADC*	6-DFN	178.71	500				
LTC2450CDDC-1#TRMPBFCT-ND	16-Bit Delta Sigma ADC*	6-DFN	2.26	2.03	1.83			
LTC2450CDDC-1#TRMPBFTR-ND	16-Bit Delta Sigma ADC*	6-DFN	178.71	500				
LTC2450IDD#TRMPBFCT-ND	16-Bit Delta Sigma ADC*	6-DFN	2.71	2.42	2.18			
LTC2450IDD#TRMPBFTR-ND	16-Bit Delta Sigma ADC*	6-DFN	859.14	500				
LTC2450IDD1#TRMPBFCT-ND	16-Bit Delta Sigma ADC*	6-DFN	2.71	2.42	2.18			
LTC2450IDD1#TRMPBFTR-ND	16-Bit Delta Sigma ADC*	6-DFN	859.14	500				
LTC2451CDD#TRMPBFCT-ND	16-Bit Delta Sigma ADC with I <sup>2</sup> C Interface*	8-DFN	2.36	2.11	1.90			
LTC2451CDD#TRMPBFTR-ND	16-Bit Delta Sigma ADC with I <sup>2</sup> C Interface*	8-DFN	726.97	500				
LTC2451CTS8#TRMPBFCT-ND	16-Bit Delta Sigma ADC with I <sup>2</sup> C Interface*	TSOT-23-8	2.36	2.11	1.90			
LTC2451CTS8#TRMPBFTR-ND	16-Bit Delta Sigma ADC with I <sup>2</sup> C Interface*	TSOT-23-8	726.97	500				
LTC2451IDD#TRMPBFCT-ND	16-Bit Delta Sigma ADC with I <sup>2</sup> C Interface*	8-DFN	2.80	2.50	2.25			
LTC2451IDD#TRMPBFTR-ND	16-Bit Delta Sigma ADC with I <sup>2</sup> C Interface*	8-DFN	2.80	2.50	2.25			
LTC2451ITS8#TRMPBFCT-ND	16-Bit Delta Sigma ADC with I <sup>2</sup> C Interface*	TSOT-23-8	2.80	2.50	2.25			
LTC2451ITS8#TRMPBFTR-ND	16-Bit Delta Sigma ADC with I <sup>2</sup> C Interface*	TSOT-23-8	867.41	500				
LTC2452CDD#TRMPBFCT-ND	16-Bit Delta Sigma ADC with SPI Interface*	8-DFN	2.54	2.28	2.05			
LTC2452CDD#TRMPBFTR-ND	16-Bit Delta Sigma ADC with SPI Interface*	8-DFN	2.54	2.28	2.05			
LTC2452CTS8#TRMPBFCT-ND	16-Bit Delta Sigma ADC with SPI Interface*	TSOT-23-8	788.93	500				
LTC2452CTS8#TRMPBFTR-ND	16-Bit Delta Sigma ADC with SPI Interface*	8-DFN	3.06	2.73	2.46			
LTC2452IDD#TRMPBFCT-ND	16-Bit Delta Sigma ADC with SPI Interface*	TSOT-23-8	3.06	2.73	2.46			
LTC2452IDD#TRMPBFTR-ND	16-Bit Delta Sigma ADC with SPI Interface*	TSOT-23-8	941.75	500				
LTC2453CDD#TRMPBFCT-ND	16-Bit Differential Delta Sigma ADC*	8-DFN	2.48	2.21	1.99			
LTC2453CDD#TRMPBFTR-ND	16-Bit Differential Delta Sigma ADC*	8-DFN	2.48	2.21	1.99			
LTC2453CTS8#TRMPBFCT-ND	16-Bit Differential Delta Sigma ADC*	TSOT-23-8	788.93	500				
LTC2453CTS8#TRMPBFTR-ND	16-Bit Differential Delta Sigma ADC*	8-DFN	2.94	2.63	2.37			
LTC2453IDD#TRMPBFCT-ND	16-Bit Differential Delta Sigma ADC*	TSOT-23-8	2.94	2.63	2.37			
LTC2453IDD#TRMPBFTR-ND	16-Bit Differential Delta Sigma ADC*	TSOT-23-8	941.75	500				
LTC2460CDD#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-DFN	2.89	1.95	1.66			
LTC2460CMS#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-MSPOP	2.89	1.95	1.66			
LTC2460IDD#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-DFN	3.35	2.24	1.91			
LTC2460IMS#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-MSPOP	3.35	2.24	1.91			
LTC2461CDD#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-DFN	2.89	1.95	1.66			
LTC2461CMS#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-MSPOP	2.89	1.95	1.66			
LTC2461IDD#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-DFN	3.35	2.24	1.91			
LTC2461IMS#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-MSPOP	3.35	2.24	1.91			
LTC2462CDD#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-DFN	2.89	1.95	1.66			
LTC2462CMS#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-MSPOP	2.89	1.95	1.66			
LTC2462IDD#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-DFN	3.35	2.24	1.91			
LTC2462IMS#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-MSPOP	3.35	2.24	1.91			
LTC2463CDD#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-DFN	3.35	2.24	1.91			
LTC2463CMS#PBF-ND	16-Bit Delta Sigma ADC with Ref.*	12-MSPOP	3.35	2.24	1.91			
LTC2470CDD#PBF-ND	16-Bit Delta Sigma ADC*	12-DFN	3.00	2.01	1.71			
LTC2470CMS#PBF-ND	16-Bit Delta Sigma ADC*	12-MSPOP	3.00	2.01	1.71			
LTC2470IDD#PBF-ND	16-Bit Delta Sigma ADC*	12-DFN	3.43	2.31	1.96			
LTC2470IMS#PBF-ND	16-Bit Delta Sigma ADC*	12-MSPOP	3.43	2.31	1.96			
LTC2472CDD#PBF-ND	16-Bit Delta Sigma ADC*	12-DFN	3.00	2.01	1.71			
LTC2472CMS#PBF-ND	16-Bit Delta Sigma ADC*	12-MSPOP	3.00	2.01	1.71			
LTC2472IDD#PBF-ND	16-Bit Delta Sigma ADC*	12-DFN	3.43	2.31	1.96			
LTC2472IMS#PBF-ND	16-Bit Delta Sigma ADC*	12-MSPOP	3.43	2.31	1.96			
LTC2473CDD#PBF-ND	16-Bit Delta Sigma ADC*	12-DFN	3.00	2.01	1.71			
LTC2473CMS#PBF-ND	16-Bit Delta Sigma ADC*	12-MSPOP	3.00	2.01	1.71			
LTC2473IDD#PBF-ND	16-Bit Delta Sigma ADC*	12-DFN	3.43	2.31	1.96			
LTC2473IMS#PBF-ND	16-Bit Delta Sigma ADC*	12-MSPOP	3.43	2.31	1.96			
LTC2480CDD#PBF-ND	16-Bit Delta Sigma ADC with Easy Drive*	10-DFN	3.06	2.19	1.81			
LTC2480IDD#PBF-ND	16-Bit Delta Sigma ADC with Easy Drive*	10-DFN	3.68	2.63	2.17			
LTC2481CDD#PBF-ND	16-Bit Delta Sigma ADC with Easy Drive*	10-DFN	3.06	2.19	1.81			
LTC2481IDD#PBF-ND	16-Bit Delta Sigma ADC with Easy Drive*	10-DFN	3.68	2.63	2.17			
LTC2482CDD#PBF-ND	16-Bit Delta Sigma ADC with Easy Drive*	10-DFN	2.73	1.95	1.61			
LTC2482IDD#PBF-ND	16-Bit Delta Sigma ADC with Easy Drive*	10-DFN	3.26	2.33	1.92			
LTC2483CDD#PBF-ND	16-Bit Delta Sigma ADC with Easy Drive*	10-DFN	2.73	1.95	1.61			
LTC2483IDD#PBF-ND	16-Bit Delta Sigma ADC with Easy Drive*	10-DFN	3.26	2.33	1.92			
LTC2484CDD#PBF-ND	24-Bit, Delta Sigma ADC with Easy Drive*	10-DFN	4.05	2.90	2.38			
LTC2484IDD#PBF-ND	24-Bit, Delta Sigma ADC with Easy Drive*	10-DFN	4.86	3.47	2.86			
LTC2485CDD#PBF-ND	24-Bit, Delta Sigma ADC with Easy Drive*	10-DFN	4.05	2.90	2.38			
LTC2485IDD#PBF-ND	24-Bit, Delta Sigma ADC with Easy Drive*	10-DFN	4.86	3.47	2.86			

DIGI KEY PART NO.		DESCRIPTION		Pkg.		PRICE EACH*		
				1	25	100		
LTC2486CDE#PBF-ND	16-Bit, 2/4-Ch. Delta Sigma ADC with PGA*	14-DFN	3.99	2.85	2.34			
LTC2486IDE#PBF-ND	16-Bit, 2/4-Ch. Delta Sigma ADC with PGA*	14-DFN	4.77	3.42	2.81			
LTC2487IDE#PBF-ND	16-Bit, 2/4-Ch. Delta Sigma ADC with PGA*	14-DFN	4.77	3.42	2.81			
LTC2488IDE#PBF-ND	16-Bit, 2/4-Channel Delta Sigma ADC*	14-DFN	4.38	3.13	2.57			
LTC2489IDE#PBF-ND	16-Bit, 2/4-Channel Delta Sigma ADC*	14-DFN	4.38	3.13	2.57			
LTC2492CDE#PBF-ND	24-Bit, 2/4-Channel Delta Sigma ADC*	14-DFN	5.00	3.57	2.95			
LTC2493IDE#PBF-ND	24-Bit, 2/4-Channel Delta Sigma ADC*	14-DFN	5.99	4.28	3.52			
LTC2494IUHF#PBF-ND	16-Bit, 8/16-Channel Delta Sigma ADC*	38-DFN	5.78	4.14	3.41			
LTC2495IUHF#PBF-ND	16-Bit, 8/16-Channel Delta Sigma ADC*	38-DFN	5.78	4.14	3.41			
LTC2496CUHF#PBF-ND	16-Bit, 8/16-Channel Delta Sigma ADC*	38-DFN	4.49	3.21	2.64			
LTC2496IUHF#PBF-ND	16-Bit, 8/16-Channel Delta Sigma ADC*	38-DFN	5.39	3.85	3.18			
LTC2497CUHF#PBF-ND	16-Bit, 8/16-Channel Delta Sigma ADC*	38-DFN	4.49	3.21	2.64			
LTC2498CUHF#PBF-ND	24-Bit, 8/16-Channel Delta Sigma ADC*	38-DFN	5.85	4.18	3.44			
LTC2498IUHF#PBF-ND	24-Bit, 8/16-Channel Delta Sigma ADC*	38-DFN	7.01	5.00	4.13			
LTC2499CUHF#PBF-ND	24-Bit, 8/16-Ch. Delta Sigma ADC*	38-DFN	5.85	4.18	3.44			
LTC2499IUHF#PBF-ND	24-Bit, 8/16-Ch. Delta Sigma ADC*	38-DFN	7.01	5.00	4.13			
<b>High Speed ADC</b>								
LTC1402CGN#PBF-ND	12-Bit, 2.2MSPS Sampling ADC*	16-SSOP	12.18	8.10	6.12			
LTC1405IGN#PBF-ND	12-Bit, 5MSPS Sampling ADC*	28-SSOP	11.36	7.55	5.71			
LTC1406IGN#PBF-ND	8-Bit, 20MSPS Sampling ADC	24-SSOP	5.78	3.84	3.06			
LTC1407IGN#PBF-ND	8-Bit, 20MSPS Sampling ADC*	24-SSOP	5.78	3.84	3.06			
LTC1420CGN#PBF-ND	12-Bit, 10MSPS Sampling ADC*	28-SSOP	10.33	6.86	5.17			
LTC1420IGN#PBF-ND	12-Bit, 10MSPS Sampling ADC*	28-SSOP	11.36	7.55	5.71			
LTC1740CG-ND	14-Bit, 6MSPS Sampling ADC	36-SSOP	28.40	18.86	15.16			
LTC1741CFW-ND	12-Bit, 65MSPS Low Noise ADC	48-TSSOP	22.41	14.88	11.21			