

Panasonic DigiReel		VOLTAGE REGULATORS		
		RoHS Compliant		
Digi-Key Part No.	Description	Pkg.	Price Each*	
			1	25 100
AN77L03M-ND	3V, 100mA, Positive LDO Voltage Regulator	TO-243	1.15	.93 .81
AN77L03ME1TR-ND	3V, 100mA, Positive LDO Voltage Regulator	TO-243	493.18/1,000	
AN77L035M-ND	3.5V, 100mA, Positive LDO Voltage Regulator	TO-243	1.15	.93 .81
AN77L035ME1TR-ND	3.5V, 100mA, Positive LDO Voltage Regulator	TO-243	493.18/1,000	
AN77L04M-ND	5V, 100mA, Positive LDO Voltage Regulator	TO-243	1.15	.93 .81
AN77L04ME1TR-ND	5V, 100mA, Positive LDO Voltage Regulator	TO-243	493.18/1,000	
AN77L06M-ND	6V, 100mA, Positive LDO Voltage Regulator	TO-92	1.15	.93 .81
AN77L06ME1TR-ND	6V, 100mA, Positive LDO Voltage Regulator	TO-243	536.97/1,000	
AN77L07M-ND	7V, 100mA, Positive LDO Voltage Regulator	TO-92	1.15	.93 .81
AN77L07ME1TR-ND	7V, 100mA, Positive LDO Voltage Regulator	TO-243	493.18/1,000	
AN77L08M-ND	8V, 100mA, Positive LDO Voltage Regulator	TO-92	1.15	.93 .81
AN77L08ME1TR-ND	8V, 100mA, Positive LDO Voltage Regulator	TO-243	1.15	.93 .81
AN77L09M-ND	9V, 100mA, Positive LDO Voltage Regulator	TO-92	1.15	.93 .81
AN77L09ME1TR-ND	9V, 100mA, Positive LDO Voltage Regulator	TO-243	1.15	.93 .81
AN77L10M-ND	10V, 100mA, Positive LDO Voltage Regulator	TO-243	1.21	1.01 .81
AN78L09M-ND	9V, 100mA, Positive General Purpose Voltage Regulator	TO-243	.42	.32 .27
AN78L15ME1TR-ND	15V, 100mA, Positive General Purpose Voltage Regulator	TO-243	146.22/1,000	
AN78M08NSPE1TR-ND	8V, 0.5A, Positive Output Voltage Regulator	SPSSU	1040.89/3,000	
AN79L10ME1TR-ND	10V, 100mA, Negative General Purpose Voltage Regulator	TO-243	142.09/1,000	
AN79L18M-ND	18V, 100mA, Negative General Purpose Voltage Regulator	TO-243	.38	.29 .25
AN79L18ME1TR-ND	18V, 100mA, Negative General Purpose Voltage Regulator	TO-243	136.31/1,000	
AN79L20M-ND	20V, 100mA, Negative General Purpose Voltage Regulator	TO-92	.41	.31 .26
AN79L20M-ND	20V, 100mA, Negative General Purpose Voltage Regulator	TO-243	.38	.29 .25
AN79L20ME1TR-ND	20V, 100mA, Negative General Purpose Voltage Regulator	TO-243	136.31/1,000	
AN79L24M-ND	24V, 100mA, Negative General Purpose Voltage Regulator	TO-243	.39	.29 .25
AN79L24ME1TR-ND	24V, 100mA, Negative General Purpose Voltage Regulator	TO-243	136.31/1,000	
AN80L20RMS-ND	2V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L21RMS-ND	2.1V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L21RMSXTXTR-ND	2.1V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1429.98/3,000	
AN80L25RMS-ND	2.5V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L25RMSXTXTR-ND	2.5V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1429.98/3,000	
AN80L28RMS-ND	2.8V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L28RMSXTXTR-ND	2.8V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1429.98/3,000	
AN80L29RMS-ND	2.9V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L29RMSXTXTR-ND	2.9V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1429.98/3,000	
AN80L30RMS-ND	3V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L30RMSXTXTR-ND	3V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1429.98/3,000	
AN80L31RMS-ND	3.1V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L31RMSXTXTR-ND	3.1V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1429.98/3,000	
AN80L33RMS-ND	3.3V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L33RMSXTXTR-ND	3.3V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1429.98/3,000	
AN80L34RMS-ND	3.4V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L34RMSXTXTR-ND	3.4V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1429.98/3,000	
AN80L36RMS-ND	3.6V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.21	1.01 .81
AN80L36RMSXTXTR-ND	3.6V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1429.98/3,000	
AN80L48RMS-ND	4.8V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L48RMSXTXTR-ND	4.8V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1429.98/3,000	
AN80L49RMS-ND	4.9V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L49RMSXTXTR-ND	4.9V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1429.98/3,000	
AN80L50RMS-ND	5V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L50RMSXTXTR-ND	5V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1429.98/3,000	
AN80L51RMS-ND	5.1V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L52RMS-ND	5.2V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1.15	.93 .81
AN80L52RMSXTXTR-ND	5.2V, 150mA, with Reset, Positive LDO Voltage Regulator	MINISD	1429.98/3,000	
AN80M27RSP-ND	2.7V, 500mA, with On-Off, LP Loss, Positive Voltage Reg.	SPSSU	1.95	1.58 1.42
AN80M27RSPXTXTR-ND	2.7V, 500mA, with On-Off, LP Loss, Positive Voltage Reg.	SPSSU	2726.13/3,000	
AN80T05-ND	Voltage Supply for Car Audio	12-SIL	2.66	2.14 1.95
AN80T05LF-ND	Voltage Supply for Car Audio	12-SIL	2.71	2.18 1.99
AN80T32-ND	Multi-Voltage Regulator	TO-2207	1.69	1.37 1.23
AN80T53-ND	Multi-Voltage Regulator	TO-2207	1.77	1.43 1.29
AN1433SMTXCLCT-ND	7V-14V, Positive, Variable Output Shunt Regulator	SSMINISD	.92	.73 .65
AN1433SMTXLTR-ND	7V-14V, Positive, Variable Output Shunt Regulator	SSMINISD	1045.84/3,000	
AN7705SP-ND	5V, 1.2A, Positive Low Power Loss Voltage Regulator	SPSSU	1.90	1.53 1.19
AN7705SPE1TR-ND	5V, 1.2A, Positive Low Power Loss Voltage Regulator	SPSSU	3197.01/3,000	
AN7706SPE1TR-ND	6V, 1.2A, Positive Low Power Loss Voltage Regulator	SPSSU	2993.79/3,000	
AN7707SPE1TR-ND	7V, 1.2A, Positive Low Power Loss Voltage Regulator	SPSSU	2993.79/3,000	
AN7708SPE1TR-ND	8V, 1.2A, Positive Low Power Loss Voltage Regulator	SPSSU	1.94	1.56 1.42
AN7709SPE1TR-ND	9V, 1.2A, Positive Low Power Loss Voltage Regulator	SPSSU	2993.79/3,000	
AN7710SPE1TR-ND	10V, 1.2A, Positive Low Power Loss Voltage Regulator	SPSSU	2993.79/3,000	
AN7712SP-ND	12V, 1.2A, Positive Low Power Loss Voltage Regulator	SPSSU	1.94	1.56 1.42
AN7715SP-ND	15V, 1.2A, Positive Low Power Loss Voltage Regulator	SPSSU	1.94	1.56 1.42
AN8002M-ND	2V, 50mA, Positive LDO Voltage Regulator	TO-243	.83	.67 .58
AN8003M-E1TR-ND	3V, 50mA, Positive LDO Voltage Regulator	TO-243	355.22/1,000	
AN8004M-ND	4V, 50mA, Positive LDO Voltage Regulator	TO-243	.83	.67 .58
AN8006M-ND	6V, 50mA, Positive LDO Voltage Regulator	TO-243	.83	.67 .58
AN8006M-E1TR-ND	6V, 50mA, Positive LDO Voltage Regulator	TO-243	355.22/1,000	
AN8007M-ND	7V, 50mA, Positive LDO Voltage Regulator	TO-243	.83	.67 .58
AN8007M-E1TR-ND	7V, 50mA, Positive LDO Voltage Regulator	TO-243	355.22/1,000	
AN8008M-ND	8V, 50mA, Positive LDO Voltage Regulator	TO-243	.83	.67 .58
AN8008M-E1TR-ND	8V, 50mA, Positive LDO Voltage Regulator	TO-243	355.22/1,000	
AN8009M-E1TR-ND	9V, 50mA, Positive LDO Voltage Regulator	TO-243	355.22/1,000	
AN8010-ND	10V, 50mA, Positive LDO Voltage Regulator	TO-92	.75	.61 .53
AN8025M-ND	2.5V, 50mA, Positive LDO Voltage Regulator	TO-243	.83	.67 .58
AN8025M-E1TR-ND	2.5V, 50mA, Positive LDO Voltage Regulator	TO-243	355.22/1,000	
AN8045M-ND	4.5V, 50mA, Positive LDO Voltage Regulator	TO-243	.83	.67 .58
AN8045M-E1TR-ND	4.5V, 50mA, Positive LDO Voltage Regulator	TO-243	355.22/1,000	
AN8085M-ND	8.5V, 50mA, Positive LDO Voltage Regulator	TO-243	.83	.67 .58
AN8085M-E1TR-ND	8.5V, 50mA, Positive LDO Voltage Regulator	TO-243	355.22/1,000	
AN84001A-LC-ND	Nine-Output Linear Voltage Regulator	16-ZIP	2.86	2.30 2.10
AN8400A-ND	Multi-Voltage Regulator	TO-2207	1.97	1.59 1.44
AN8406A-ND	Multi-Voltage Regulator	TO-2207	2.03	1.64 1.49
AN7703SPE1TR-ND	3.5V, 1.2A, Positive Low Power Loss Voltage Regulator	SPSSU	3197.01/3,000	

JRC / NJR Corporation DigiReel		AMPLIFIERS		
		RoHS Compliant		
Digi-Key Part No.	Description	Pkg.	Price Each*	
			1	25 100
NJG1101F-TE1CT-ND	Wideband AGC Amp, GaAs MMIC	6-MTP	1.91	1.60 1.28
NJG1101F-TE1TR-ND	Wideband AGC Amp, GaAs MMIC	6-MTP	3339.51/3,000	
NJG1103F1-TE1CT-ND	1.5/1.9GHz Low Noise Amp, GaAs MMIC	6-MTP	.77	.65 .52
NJG1103F1-TE1TR-ND	1.5/1.9GHz Low Noise Amp, GaAs MMIC	6-MTP	1344.48/3,000	

JRC / NJR Corporation DigiReel (Cont.)		AMPLIFIERS		
		RoHS Compliant		
Digi-Key Part No.	Description	Pkg.	Price Each*	
			1	25 100
NJG1105F-TE1CT-ND	1.8/1.9/2.1GHz Band Low Noise Amp, GaAs MMIC	6-MTP	2.26	1.88 1.51
NJG1105F-TE1TR-ND	1.8/1.9/2.1GHz Band Low Noise Amp, GaAs MMIC	6-MTP	3946.69/3,000	
NJG1302V-TE1CT-ND	Medium Power Amp, GaAs MMIC	14-SSOP	5.20	4.34 3.47
NJG1302V-TE1TR-ND	Medium Power Amp, GaAs MMIC	14-SSOP	6071.84/2,000	
NJG1307R-TE1CT-ND	Driver Amp, GaAs MMIC	8-VSP	2.43	2.03 1.62
NJG1307R-TE1TR-ND	Driver Amp, GaAs MMIC	8-VSP	2833.52/2,000	
NJM064D-ND	J-Fet Input Op Amp	14-Dip	.77	.65 .52
NJM074M-ND	Quad J-Fet Input Op Amp	14-DMP	.87	.73 .58
NJM082D-ND	Dual J-Fet Input Op Amp	8-Dip	40	34 .27
NJM084D-ND	Quad J-Fet Input Op Amp	14-Dip	.97	.81 .65
NJM319M#-ND	Precision, High Speed, Dual Voltage Comparator*	14-DMP	1.18	.99 .79
NJM2060D-ND	High-Gain, Wide-Bandwidth, Quad Op Amp	14-Dip	50	42 .34
NJM2073M#-ND	Dual Low Voltage Power Amp*	8-DMP	.97	.81 .65
NJM2076D-ND	Dual Low Voltage Power Amp	8-Dip	1.14	.95 .76
NJM2076M#-ND	Dual Low Voltage Power Amp	8-DMP	1.14	.95 .76
NJM2082D#-ND	Dual J-Fet Input Op Amp*	8-Dip	.78	.66 .53
NJM2113M#-ND	Low Voltage Audio Power Amp*	8-DMP	.68	.57 .46
NJM2119M#-ND	Dual Single Supply Op Amp*	8-DMP	2.92	2.44 1.96
NJM2120M-ND	Op Amp, 2-Input/1-Output Analog Switch	8-DMP	.55	.46 .37
NJM2121M-ND	Dual Op Amp, 2-Input/1-Output Analog Switch	8-DMP	.45	.38 .30
NJM2122D-ND	Ultra Low Noise Dual Op Amp	8-Dip	.97	.81 .65
NJM2125F-TE1#CT-ND	Single Supply Op Amp*	5-MTP	.52	.44 .35
NJM2135M-TE2CT-ND	Low Voltage Audio Power Amp	8-DMP	.52	.44 .35
NJM2137M-ND	Ultra Wideband, High Slew Rate, Single Op Amp	8-DMP	1.24	1.04 .83
NJM2138M-ND	Ultra Wideband, High Slew Rate, Dual Op Amp	8-DMP	1.04	.87 .70
NJM2140R-TE1#CT-ND	Low Saturation Dual Op Amp*	8-VSP	2.08	1.74 1.39
NJM2140R-TE1#TR-ND	Low Saturation Dual Op Amp*	8-VSP	.71	.60 .48
NJM2143R-TE1#CT-ND	Single Supply Dual Op Amp*	8-VSP	.46	.39 .31
NJM2143R-TE1#TR-ND	Single Supply Dual Op Amp*	8-VSP	540.68/2,000	
NJM2171AR-TE1CT-ND	Low Voltage Headphone Amp for Portable Audio	10-VSP	.74	.62 .50
NJM2171AR-TE1TR-ND	Low Voltage Headphone Amp for Portable Audio	10-VSP	867.41/2,000	
NJM2172V-TE1#CT-ND	Op Amp with Electric Variable Resistor*	14-SSOP	1.78	1.49 1.19
NJM2172V-TE1#TR-ND	Op Amp with Electric Variable Resistor*	14-SSOP	2081.77/2,000	
NJM2174V-TE2CT-ND	Audio Line Amp with Mute Function	14-SSOP	1.21	1.02 .81
NJM2174V-TE2TR-ND	Audio Line Amp with Mute Function	14-SSOP	1416.76/2,000	
NJM2267M#-ND	Dual Video 6dB Amp with 75-Ohm Driver*	8-DMP	.86	.72 .58
NJM2268M-ND	Dual Video 6dB Amplifier	8-DMP	.47	.40 .32
NJM2403D-ND	Single Supply Dual Comparator	8-Dip	.45	.38 .30
NJM2407R-TE1#CT-ND	Single Supply Dual Comparator*	8-VSP	.47	.40 .32
NJM2407R-TE1#TR-ND	Single Supply Dual Comparator*	8-VSP	549.36/2,000	
NJM2538V-TE1#CT-ND	Video Amp with 75-Ohm Driver	20-SSOP	2.43	2.03 1.62
NJM2538V-TE1#TR-ND	Video Amp with 75-Ohm Driver	20-SSOP	2833.52/2,000	
NJM2574RBI-TE1#CT-ND	Low Voltage Video Amp with LPF*	8-TVSP	1.02	.85 .68
NJM2574RBI-TE1#TR-ND	Low Voltage Video Amp with LPF*	8-TVSP	1185.45/2,000	
NJM2575F1-TE1#CT-ND	Low Voltage Video Amp with LPF*	6-MTP	.86	.72 .58
NJM2576RBI-TE1#CT-ND	Low Voltage Video Amp with LPF*	8-TVSP	1.18	.99 .79
NJM2576RBI-TE1#TR-ND	Low Voltage Video Amp with LPF*	8-TVSP	1373.39/2,000	
NJM2580D-ND	Single Supply Wideband 3-Channel Video Amp	14-Dip	2.08	1.74 1.39
NJM2580M-ND	Single Supply Wideband 3-Channel Video Amp	14-DMP	1.73	1.45 1.16
NJM2710V-TE1CT-ND	Ultra High Speed Hex Op Amp	20-SSOP	2.01	1.68 1.34
NJM2710V-TE1TR-ND	Ultra High Speed Hex Op Amp	20-SSOP	2341.99/2,000	
NJM2711F-TE1#CT-ND	Ultra High Speed Single Op Amp*	5-MTP	2.46	2.06 1.65
NJM2716F-TE1CT-ND	Single Supply High-Slew Rate Single Op Amp	5-MTP	1.04	.87 .70
NJM2716F-TE1TR-ND	Single Supply High-Slew Rate Single Op Amp	5-MTP	1821.55/3,000	
NJM2729E-TE1#CT-ND	Precision Op Amp*	8-EMP	2.30	1.93 1.54
NJM2732RBI-TE1#CT-ND	Full-Swing Input and Output Type Dual Op Amp*	8-TVSP	2.14	1.79 1.43
NJM2732RBI-TE1#TR-ND	Low Noise, Low Supply Voltage Dual Op Amp*	8-TVSP	1.91	1.60 1.28
NJM2737RBI-TE1CT-ND	Low Noise, Low Supply Voltage Dual Op Amp*	8-TVSP	2226.34/2,000	
NJM2737RBI-TE1#CT-ND	Low Noise, Low Supply Voltage Dual Op Amp*	8-TVSP	1.96	1.64 1.31
NJM2737RBI-TE1#TR-ND	Low Noise, Low Supply Voltage Dual Op Amp*	8-TVSP	2040.46/2,000	
NJM2770RBI-TE1CT-ND	High Power and Low Voltage Audio Power Amp	8-TVSP	.99	.83 .67
NJM2770RBI-TE1TR-ND	High Power and Low Voltage Audio Power Amp	8-TVSP	1156.54/2,000	
NJM2772V-TE1CT-ND	Low Voltage Headphone Amp for Portable Audio	14-SSOP	1.12	.93 .75
NJM2772V-TE1TR-ND	Low Voltage Headphone Amp for Portable Audio	14-SSOP	1301.11/2,000	
NJM4558D#-ND	Dual Op Amp*	8-Dip	.43	.36 .29
NJM4562M-ND	High Gain, Wide-Bandwidth, Low Noise, Dual Op Amp	8-DMP	.42	.36 .29
NJM4565D#-ND	High Gain, Wide-Bandwidth, Low Noise, Dual Op Amp*	8-Dip	.46	.39 .31
NJM4714M#-ND	General Purpose Quad Op Amp*	14-DMP	1.43	1.19 .96
NJM5532M#-ND	High Performance Low Noise Dual Op Amp*	8-DMP	.97	.81 .65
NJM5534M#-ND	High Performance Low Noise Op Amp*	8-DMP	.68	.57 .46
NJM12901M-ND	Single Supply Quad Comparator	14-DMP	.62	.52 .42
NJM12902M-ND	Single Supply Quad Op Amp	14-DMP	.67	.56 .45
NJM12904M-TE1#CT-ND	Single Supply Dual Op Amp*	8-DMP	.32	.27 .22
NJM13404D-ND	Single Supply Dual Op Amp	8-Dip	.55	.46 .37
NJM13404M-ND	Single Supply Dual Op Amp	8-DMP	.55	.46 .37
NJM14558D#-ND	Dual Op Amp*	8-Dip	.50	.42 .34
NJM14558M-ND	Dual Op Amp	8-DMP	.42	.36 .29
NJU7001M-ND	Low Voltage CMOS Op Amp	8-DMP	.57	.48 .38
NJU7004D-ND	Quad Low Voltage CMOS Op Amp	14-Dip	1.66	1.39 1.11
NJU7004M-ND	Quad Low Voltage CMOS Op Amp	14-DMP	1.66	1.39 1.11