

DIGI-KEY Part No.	Description	Pkg.	PRICE EACH*		
			1	25	100
MAX240CMH+-ND	+5V Multichannel RS-232 Driver/Receiver w/ Shutdown*	44-MQFP	10.24	7.74	4.96
MAX241CAI+-ND	+5V Multich. RS-232 Driver/Receiver w/ Shutdown*	28-SSOP	7.66	5.11	3.71
MAX241CWI+-ND	+5V Multichannel RS-232 Driver/Receiver w/ Shutdown*	28-SOIC	7.28	4.85	3.52
MAX241EAI+-ND	+5V Multich. RS-232 Driver/Receiver w/ Shutdown*	28-SSOP	9.11	6.08	4.41
MAX241ECI+-ND	+5V Multich. RS-232 Driver/Receiver w/ Shutdown, ESD Prot.*	28-SSOP	8.83	5.89	4.27
MAX241ECWI+-ND	+5V Multichannel RS-232 Driver/Receiver w/ Shutdown*	28-SOIC	8.43	5.62	4.07
MAX241EAI+-ND	+5V Multich. RS-232 Driver/Rcvr w/ Shutdown, ESD Prot.*	28-SSOP	11.03	7.36	5.33
MAX241EEWI+-ND	+5V Multich. RS-232 Driver/Rcvr w/ Shutdown, ESD Prot.*	28-SOIC	10.52	7.02	5.09
MAX241EWI+-ND	+5V Multich. RS-232 Driver/Receiver w/ Shutdown*	28-SOIC	8.73	5.83	4.22
MAX242CAP+-ND	+5V Multich. RS-232 Driver/Receiver w/ Shutdown*	20-SSOP	5.31	3.54	2.57
MAX242CPN+-ND	+5V Multichannel RS-232 Driver/Receiver w/ Shutdown*	18-Dip	4.70	3.14	2.27
MAX242CWN+-ND	+5V Multichannel RS-232 Driver/Receiver w/ Shutdown*	18-SOIC	4.70	3.14	2.27
MAX242EPN+-ND	+5V Multichannel RS-232 Driver/Receiver w/ Shutdown*	18-Dip	5.62	3.75	2.72
MAX242EWN+-ND	+5V Multichannel RS-232 Driver/Receiver w/ Shutdown*	18-SOIC	5.62	3.75	2.72
MAX243CPE+-ND	+5V Multichannel RS-232 Driver/Receiver*	16-Dip	5.31	3.54	2.57
MAX243CSE+-ND	+5V Multichannel RS-232 Driver/Receiver*	16-SOIC	5.31	3.54	2.57
MAX243CWE+-ND	+5V Multichannel RS-232 Driver/Receiver*	16-SOIC	5.31	3.54	2.57
MAX243PE+-ND	+5V Multichannel RS-232 Driver/Receiver*	16-Dip	6.35	4.24	3.08
MAX243ESE+-ND	+5V Multichannel RS-232 Driver/Receiver*	16-SOIC	6.35	4.24	3.08
MAX248EQH-D-ND	+5V Multichannel RS-232 Driver/Receiver w/ Shutdown*	44-PLCC	21.78	16.44	9.67
MAX248EQH-D-ND	+5V Multichannel RS-232 Driver/Receiver w/ Shutdown*	44-PLCC	25.40	16.94	12.27
MAX249CQH-D-ND	+5V Multichannel RS-232 Driver/Receiver w/ Shutdown*	44-PLCC	19.53	13.02	9.44
MAX250CPD+-ND	+5V Isolated RS-232 Driver/Receiver*	14-Dip	7.38	4.92	3.57
MAX250CSD+-ND	+5V Isolated RS-232 Driver/Receiver*	14-SOIC	8.12	5.42	3.93
MAX250EPD+-ND	+5V Isolated RS-232 Driver/Receiver*	14-Dip	10.54	7.03	5.09
MAX250ESD+-ND	+5V Isolated RS-232 Driver/Receiver*	14-SOIC	10.14	7.66	6.70
MAX250ESD+-ND	+5V Isolated RS-232 Driver/Receiver*	14-SOIC	11.59	7.73	5.61
MAX251CPD+-ND	+5V Isolated RS-232 Driver/Receiver*	14-Dip	7.38	4.92	3.57
MAX251CSD+-ND	+5V Isolated RS-232 Driver/Receiver*	14-SOIC	8.12	5.42	3.93
MAX251EPD+-ND	+5V Isolated RS-232 Driver/Receiver*	14-Dip	10.54	7.03	5.09
MAX251ESD+-ND	+5V Isolated RS-232 Driver/Receiver*	14-SOIC	11.59	7.73	5.61
MAX253CPA+-ND	Transformer Driver for Isolated RS-485 Interface*	8-Dip	2.71	1.81	1.31
MAX253CSA+-ND	Transformer Driver for Isolated RS-485 Interface*	8-SOIC	2.71	1.81	1.31
MAX253CUA+-ND	Transformer Driver for Isolated RS-485 Interface*	8-µMAX	2.96	1.98	1.43
MAX253EPA+-ND	Transformer Driver for Isolated RS-485 Interface*	8-Dip	3.83	2.56	1.86
MAX253ESA+-ND	Transformer Driver for Isolated RS-485 Interface*	8-SOIC	3.52	2.35	1.71
MAX256ASA+-ND	3W Primary Side Controller/Half-Bridge Driver*	8-SOIC	6.02	4.02	2.91
MAX481CPA+-ND	Low Power, RS-485/RS-422 Transceiver*	8-Dip	2.65	1.77	1.29
MAX481CSA+-ND	Low Power, RS-485/RS-422 Transceiver*	8-SOIC	2.65	1.77	1.29
MAX481ECPA+-ND	Low Power, RS-485/RS-422 Transceiver, ESD Prot.*	8-Dip	3.30	2.20	1.60
MAX481ECSA+-ND	Low Power, RS-485/RS-422 Transceiver, ESD Prot.*	8-SOIC	3.30	2.20	1.60
MAX481ECPA+-ND	Low Power, RS-485/RS-422 Transceiver, ESD Prot.*	8-Dip	5.18	3.46	2.51
MAX481EESA+-ND	Low Power, RS-485/RS-422 Transceiver, ESD Prot.*	8-SOIC	5.18	3.46	2.51
MAX481EPA+-ND	Low Power, RS-485/RS-422 Transceiver*	8-Dip	3.32	2.22	1.61
MAX481ESA+-ND	Low Power, RS-485/RS-422 Transceiver*	8-SOIC	3.32	2.22	1.61
MAX483CPA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-Dip	2.65	1.77	1.29
MAX483CSA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-SOIC	2.65	1.77	1.29
MAX483CUA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-µMAX	2.65	1.77	1.29
MAX483ECPA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transcvr., ESD Prot.*	8-Dip	3.30	2.20	1.60
MAX483ECSA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transcvr., ESD Prot.*	8-SOIC	3.30	2.20	1.60
MAX483ECPA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transcvr., ESD Prot.*	8-Dip	4.75	3.17	2.29
MAX483EESA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transcvr., ESD Prot.*	8-SOIC	4.75	3.17	2.29
MAX483EPA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transceiver*	8-Dip	3.32	2.22	1.61
MAX483ESA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transceiver*	8-SOIC	3.32	2.22	1.61
MAX485CPA+-ND	Low Power, RS-485/RS-422 Transceiver*	8-Dip	2.65	1.77	1.29
MAX485CSA+-ND	Low Power, RS-485/RS-422 Transceiver*	8-SOIC	2.65	1.77	1.29
MAX485CUA+-ND	Low Power, RS-485/RS-422 Transceiver*	8-µMAX	2.65	1.77	1.29
MAX485ECPA+-ND	Low Power, RS-485/RS-422 Transcvr., ESD Protected*	8-Dip	3.30	2.20	1.60
MAX485ECSA+-ND	Low Power, RS-485/RS-422 Transcvr., ESD Protected*	8-SOIC	3.30	2.20	1.60
MAX485ECPA+-ND	Low Power, RS-485/RS-422 Transcvr., ESD Prot.*	8-Dip	4.75	3.17	2.29
MAX485EESA+-ND	Low Power, RS-485/RS-422 Transcvr., ESD Prot.*	8-SOIC	4.75	3.17	2.29
MAX485EPA+-ND	Low Power, RS-485/RS-422 Transceiver*	8-Dip	3.32	2.22	1.61
MAX485ESA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-SOIC	3.32	2.22	1.61
MAX487CPA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-Dip	2.71	1.81	1.31
MAX487CSA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-SOIC	2.71	1.81	1.31
MAX487CUA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-µMAX	2.71	1.81	1.31
MAX487ECPA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transcvr., ESD Prot.*	8-Dip	3.30	2.20	1.60
MAX487ECSA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transcvr., ESD Prot.*	8-SOIC	3.30	2.20	1.60
MAX487ECPA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transcvr., ESD Prot.*	8-Dip	4.75	3.17	2.29
MAX487EESA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transcvr., ESD Prot.*	8-SOIC	4.75	3.17	2.29
MAX487EPA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-Dip	3.40	2.27	1.64
MAX487ESA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-SOIC	3.40	2.27	1.64
MAX488CPA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-Dip	2.71	1.81	1.31
MAX488CSA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-SOIC	2.71	1.81	1.31
MAX488CUA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-µMAX	2.96	1.98	1.43
MAX488ECPA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transcvr., ESD Prot.*	8-Dip	3.30	2.20	1.60
MAX488ECSA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transcvr., ESD Prot.*	8-SOIC	3.30	2.20	1.60
MAX488ECPA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transcvr., ESD Prot.*	8-Dip	4.75	3.17	2.29
MAX488EESA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transcvr., ESD Prot.*	8-SOIC	4.75	3.17	2.29
MAX488EPA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-Dip	4.70	3.27	1.64

DIGI-KEY Part No.	Description	Pkg.	PRICE EACH*		
			1	25	100
MAX488ESA+-ND	Slew-Rate-Limited, RS-485/RS-422 Transceiver*	8-SOIC	3.40	2.27	1.64
MAX489CPD+-ND	Slew-Rate-Ltd., RS-485/RS-422 TxRx w/ Drive Enable*	14-Dip	2.71	1.81	1.31
MAX489CSD+-ND	Slew-Rate-Ltd., RS-485/RS-422 TxRx w/ Drive Enable*	14-SOIC	2.71	1.81	1.31
MAX489ECPD+-ND	Slew-Rate-Ltd., RS-485/RS-422 TxRx w/ Drive Enable, ESD Protected*	14-Dip	3.30	2.20	1.60
MAX489EESD+-ND	Slew-Rate-Ltd., RS-485/RS-422 TxRx w/ Drive Enable, ESD Protected*	14-SOIC	3.30	2.20	1.60
MAX489EPD+-ND	Slew-Rate-Ltd., RS-485/RS-422 TxRx w/ Drive Enable, ESD Protected*	14-Dip	4.75	3.17	2.29
MAX489EESD+-ND	Slew-Rate-Ltd., RS-485/RS-422 TxRx w/ Drive Enable, ESD Protected*	14-SOIC	4.75	3.17	2.29
MAX489EPD+-ND	Slew-Rate-Ltd., RS-485/RS-422 TxRx w/ Drive Enable*	14-Dip	3.40	2.27	1.64
MAX490CPA+-ND	RS-485/RS-422 Transceiver with Full Duplex*	8-Dip	2.71	1.81	1.31
MAX490CSA+-ND	RS-485/RS-422 Transceiver with Full Duplex*	8-SOIC	2.71	1.81	1.31
MAX490CUA+-ND	Slew-Rate-Ltd., RS-485/RS-422 Transceiver*	8-µMAX	2.71	1.81	1.31
MAX490ECPA+-ND	RS-485/RS-422 Transceiver w/ Full Duplex, ESD Prot.*	8-Dip	3.30	2.20	1.60
MAX490ECSA+-ND	RS-485/RS-422 Transceiver w/ Full Duplex, ESD Prot.*	8-SOIC	3.30	2.20	1.60
MAX490EPA+-ND	RS-485/RS-422 Transceiver w/ Full Duplex, ESD Prot.*	8-Dip	4.75	3.17	2.29
MAX490ESA+-ND	RS-485/RS-422 Transceiver with Full Duplex*	8-SOIC	3.40	2.27	1.64
MAX491CPD+-ND	RS-485/RS-422 Transceiver, Low Power*	14-Dip	2.71	1.81	1.31
MAX491CSD+-ND	RS-485/RS-422 Transceiver, Low Power*	14-SOIC	2.71	1.81	1.31
MAX491ECPD+-ND	RS-485/RS-422 Transceiver, Low Power, ESD Prot.*	14-Dip	3.30	2.20	1.60
MAX491EESD+-ND	RS-485/RS-422 Transceiver, Low Power, ESD Prot.*	14-SOIC	3.30	2.20	1.60
MAX491EPD+-ND	RS-485/RS-422 Transceiver, Low Power, ESD Prot.*	14-Dip	4.75	3.17	2.29
MAX491ESD+-ND	RS-485/RS-422 Transceiver, Low Power*	14-SOIC	3.40	2.27	1.64
MAX560CAI+-ND	3.3V Transceiver with Receivers Active in Shutdown*	28-SSOP	8.34	5.57	4.04
MAX560CWI+-ND	3.3V Transceiver w/ Receivers Active in Shutdown*	28-SOIC	7.94	5.30	3.84
MAX561CAI+-ND	3.3V Transceiver w/ Receivers Active in Shutdown*	28-SSOP	8.34	5.57	4.04
MAX562CAI+-ND	2.7V-5.25V, 230Kbps Serial Interface*	28-SSOP	7.53	5.03	3.64
MAX562CWI+-ND	2.7V-5.25V, 230Kbps Serial Interface*	28-SOIC	6.91	4.61	3.34
MAX562EAI+-ND	2.7V-5.25V, 230Kbps Serial Interface*	28-SSOP	10.77	7.18	5.20
MAX562EWI+-ND	2.7V-5.25V, 230Kbps Serial Interface*	28-SOIC	10.77	7.18	5.20
MAX563CWI+-ND	3.3V, EIA/TIA-562 Dual Transceiver*	18-SOIC	5.31	3.54	2.57
MAX1406CAE+-ND	RS-232 Transceiver, ESD-Protected*	16-SSOP	2.96	1.98	1.43
MAX1406EAE+-ND	RS-232 Transceiver, ESD-Protected*	16-SSOP	4.24	2.83	2.05
MAX1406EPE+-ND	RS-232 Transceiver, ESD-Protected*	16-Dip	4.24	2.83	2.05
MAX1406EWE+-ND	RS-232 Transceiver, ESD-Protected*	16-SOIC	4.24	2.83	2.05
MAX1480ACPI+-ND	Isolated RS-485/RS-422 Data Interface*	28-Dip	25.22	16.82	12.19
MAX1480AEP+-ND	Isolated RS-485/RS-422 Data Interface*	28-Dip	17.33	14.68	13.61
MAX1480BCPI+-ND	Isolated RS-485/RS-422 Data Interface*	28-Dip	24.10	16.07	11.64
MAX1480BEP+-ND	Isolated RS-485/RS-422 Data Interface*	28-Dip	16.97	14.38	13.31
MAX1480CCPI+-ND	Isolated RS-485/RS-422 Data Interface*	28-Dip	25.22	16.82	12.19
MAX1480EACPI+-ND	Isolated RS-485/RS-422 Data Interface*	28-Dip	24.40	16.27	11.80
MAX1480EAEPI+-ND	Isolated RS-485/RS-422 Data Interface*	28-Dip	21.10	17.88	14.90
MAX1480ECCPI+-ND	Isolated RS-485/RS-422 Data Interface*	28-Dip	24.40	16.27	11.80
MAX1480ECCPI+-ND	Isolated RS-485/RS-422 Data Interface*	28-Dip	21.10	17.88	14.90
MAX1481CUB+-ND	Full Duplex, Slew Rate Ltd, LP RS-422 Transceiver*	10-µMAX	2.65	1.77	1.29
MAX1481EUB+-ND	Full Duplex, Slew Rate Ltd, LP RS-422 Transceiver*	10-µMAX	3.30	2.20	1.60
MAX1482CPD+-ND	Full Duplex, Slew Rate Ltd, LP RS-485 Transceiver*	14-Dip	2.71	1.81	1.31
MAX1482CSD+-ND	Full Duplex, Slew Rate Ltd, LP RS-485 Transceiver*	14-SOIC	2.71	1.81	1.31
MAX1482EPP+-ND	Full Duplex, Slew Rate Ltd, LP RS-485 Transceiver*	14-PDIP	3.40	2.27	1.64
MAX1482ESD+-ND	Full Duplex, Slew Rate Ltd, LP RS-485 Transceiver*	14-SOIC	3.40	2.27	1.64
MAX1483CPA+-ND	Half Duplex, Slew-Rate Ltd, RS485 Transceiver*	8-Dip	2.71	1.81	1.31
MAX1483CSA+-ND	Half Duplex, Slew-Rate Ltd, RS485 Transceiver*	8-SOIC	2.71	1.81	1.31
MAX1483CUA+-ND	Half Duplex, Slew Rate Ltd, LP RS-485 Transceiver*	8-µMAX	2.71	1.81	1.31
MAX1483EPA+-ND	Half Duplex, Slew Rate Ltd, LP RS-485 Transceiver*	8-PDIP	3.40	2.27	1.64
MAX1483ESA+-ND	Half Duplex, Slew-Rate Ltd, RS485 Transceiver*	8-SOIC	3.40	2.27	1.64
MAX1484CUB+-ND	Full Duplex, LP RS-422/RS-485 Transceiver*	10-µMAX	2.65	1.77	1.29
MAX1484EUB+-ND	Full Duplex, LP RS-422/RS-485 Transceiver*	10-µMAX	3.30	2.20	1.60
MAX1485CUB+-ND	Half/Full Duplex, Slew-Rate Ltd, RS-422/RS-485 Transcvr.*	10-µMAX	2.65	1.77	1.29
MAX1485EUB+-ND	Half/Full Duplex, Slew-Rate Ltd, RS-422/RS-485 Transcvr.*	10-µMAX	3.30	2.20	1.60
MAX1486CUB+-ND	Half/Full Duplex, RS-422/RS-485 Transceiver*	10-µMAX	2.65	1.77	1.29
MAX1486EUB+-ND	Half/Full Duplex, RS-422/RS-485 Transceiver*	10-µMAX	3.30	2.20	1.60
MAX1487CPA+-ND	2.5Mbps RS-485/RS-422 Transceiver*	8-Dip	2.71	1.81	1.31
MAX1487CSA+-ND	2.5Mbps RS-485/RS-422 Transceiver*	8-SO			