



Surface Mount, 5% Thick-Film Chip Resistors
CRCW Series 0201 / 0402 / 0603 / 0805 / 1206 / 1210 / 2010 / 2512 (Cont.)



CRCW 5% 1/10W — 0603 Series
Resistor Values

Table with 17 columns: Resistance values from 0.0 to 10M. Row 1: 0.0, 2.4, 6.2, 16, 43, 110, 300, 750, 2.0K, 5.1K, 13K, 36K, 91K, 240K, 620K, 1.6M, 4.3M. Row 2: 1.0, 2.7, 6.8, 18, 47, 120, 330, 820, 2.2K, 5.6K, 15K, 39K, 100K, 270K, 680K, 1.8M, 4.7M.

Table with 13 columns: Description, Value Range, TCR, Rated Voltage, Rated Power, Dimensions (W, L, T, tb), Digi-Key Part No., Cut Tape Pricing (10, 50, 200), Digi-Key Part No., Tape & Reel Pricing (5,000), Vishay Part No.

CRCW 5% 1/8W — 0805 Series
Resistor Values

Table with 20 columns: Resistance values from 0.0 to 9.1M. Row 1: 0.0, 1.6, 3.0, 5.1, 9.1, 16, 30, 51, 91, 160, 300, 510, 910, 1.6K, 3.0K, 5.1K, 9.1K, 16K, 30K, 51K, 91K, 160K, 300K, 510K, 910K, 1.6M, 3.0M, 5.1M, 9.1M.

Table with 13 columns: Description, Value Range, TCR, Rated Voltage, Rated Power, Dimensions (W, L, T, tb), Digi-Key Part No., Cut Tape Pricing (10, 50, 200), Digi-Key Part No., Tape & Reel Pricing (5,000), Vishay Part No.

CRCW 5% 1/4W — 1206 Series
Resistor Values

Table with 21 columns: Resistance values from 0.0 to 9.1M. Row 1: 0.0, 1.6, 3.0, 5.1, 9.1, 16, 30, 51, 91, 160, 300, 510, 910, 1.6K, 3.0K, 5.1K, 9.1K, 16K, 30K, 51K, 91K, 160K, 300K, 510K, 910K, 1.6M, 3.0M, 5.1M, 9.1M.

Table with 13 columns: Description, Value Range, TCR, Rated Voltage, Rated Power, Dimensions (W, L, T, tb), Digi-Key Part No., Cut Tape Pricing (10, 50, 200), Digi-Key Part No., Tape & Reel Pricing (5,000), Vishay Part No.

CRCW 5% 1/2W — 1210 Series
Resistor Values

Table with 21 columns: Resistance values from 0.0 to 910K. Row 1: 0.0, 1.6, 3.0, 5.1, 9.1, 16, 30, 51, 91, 160, 300, 510, 910, 1.6K, 3.0K, 5.1K, 9.1K, 16K, 30K, 51K, 91K, 160K, 300K, 510K, 910K.

Table with 13 columns: Description, Value Range, TCR, Rated Voltage, Rated Power, Dimensions (W, L, T, tb), Digi-Key Part No., Cut Tape Pricing (10, 50, 200), Digi-Key Part No., Tape & Reel Pricing (5,000), Vishay Part No.

CRCW 5% 3/4W — 2010 Series
Resistor Values

Table with 21 columns: Resistance values from 0.0 to 910K. Row 1: 0.0, 1.6, 3.0, 5.1, 9.1, 16.0, 30.0, 51.0, 91.0, 160, 300, 510, 910, 1.6K, 3.0K, 5.1K, 9.1K, 16K, 30K, 51K, 91K, 160K, 300K, 510K, 910K.

Table with 13 columns: Description, Value Range, TCR, Rated Voltage, Rated Power, Dimensions (W, L, T, tb), Digi-Key Part No., Cut Tape Pricing (10, 50, 200), Digi-Key Part No., Tape & Reel Pricing (4,000), Vishay Part No.

CRCW 5% 1W — 2512 Series
Resistor Values

Table with 21 columns: Resistance values from 0.0 to 910K. Row 1: 0.0, 1.6, 3.0, 5.1, 9.1, 16, 30, 51, 91, 160, 300, 510, 910, 1.6K, 3.0K, 5.1K, 9.1K, 16K, 30K, 51K, 91K, 160K, 300K, 510K, 910K.

Table with 13 columns: Description, Value Range, TCR, Rated Voltage, Rated Power, Dimensions (W, L, T, tb), Digi-Key Part No., Cut Tape Pricing (10, 50, 200), Digi-Key Part No., Tape & Reel Pricing (2,000), Vishay Part No.

Digi-Reel Most SMT cutdown parts are available on a Digi-Reel. For Digi-Reel part number, change 1-ND to 6-ND or CT-ND to DKR-ND. See Digi-Key Services on page 2 for additional information.

1962 (EU2011-EN) Free shipping on orders over €65! All prices in euro and include duties.