

Input Voltage Range (VDC)	Output Voltage @ Maximum Current (VDC @ A)		Output Power Maximum (W)	Mounting Type	Modular Orientation	Digi-Key Part No.	Price Each			Texas Instruments Part No.
	Output #1	Output #2					1	25	100	
7.0 - 15.0	3.3 @ 2.0	—	6.6	TH	Horizontal	78HT233HC-ND◆	32.87	28.44	26.66	78HT233HC
7.0 - 15.0	3.3 @ 2.0	—	6.6	TH	Vertical	78HT233VC-ND◆	32.87	28.44	26.66	78HT233VC
7.0 - 30.0	5.0 @ 1.5	—	7.5	TH	Horizontal	78SR105HC-ND	22.82	19.40	17.97	78SR105HC
7.0 - 30.0	5.0 @ 1.5	—	7.5	SMT	Horizontal	78SR105SC-ND	22.82	19.40	17.97	78SR105SC
7.0 - 30.0	5.0 @ 1.5	—	7.5	TH	Vertical	78SR105VC-ND◆	22.82	19.40	17.97	78SR105VC
14.5 - 30.0	6.0 @ 1.5	—	9.0	TH	Horizontal	78SR108HC-ND◆	29.71	25.26	23.40	78SR108HC
14.5 - 30.0	8.0 @ 1.5	—	12.0	TH	Horizontal	78SR108HC-ND◆	29.71	25.26	23.40	78SR108HC
14.5 - 30.0	12.0 @ 1.5	—	18.0	TH	Horizontal	78SR112HC-ND◆	29.71	25.26	23.40	78SR112HC
14.5 - 30.0	12.0 @ 1.5	—	18.0	SMT	Horizontal	78SR112SC-ND◆	29.71	25.26	23.40	78SR112SC
14.5 - 30.0	12.0 @ 1.5	—	18.0	TH	Vertical	78SR112VC-ND◆	29.71	25.26	23.40	78SR112VC
14.5 - 30.0	15.0 @ 1.5	—	22.5	TH	Horizontal	78SR115HC-ND◆	29.71	25.26	23.40	78SR115HC
14.5 - 30.0	15.0 @ 1.5	—	22.5	TH	Vertical	78SR115VC-ND◆	29.71	25.26	23.40	78SR115VC
7.0 - 30.0	5.0 @ 1.5	—	7.5	TH	Horizontal	78ST105HC-ND◆	29.71	25.26	23.40	78ST105HC
7.0 - 30.0	5.0 @ 1.5	—	7.5	TH	Vertical	78ST105VC-ND◆	29.71	25.26	23.40	78ST105VC
14.5 - 30.0	12.0 @ 1.5	—	18.0	TH	Horizontal	78ST112HC-ND◆	29.71	25.26	23.40	78ST112HC
14.5 - 30.0	12.0 @ 1.5	—	18.0	SMT	Horizontal	78ST112SC-ND◆	25.78	21.92	20.31	78ST112SC
14.5 - 30.0	12.0 @ 1.5	—	18.0	TH	Vertical	78ST112VC-ND◆	29.71	25.26	23.40	78ST112VC
7.0 - 26.0	3.3 @ 1.5	—	5.0	TH	Horizontal	78ST133HC-ND◆	29.71	25.26	23.40	78ST133HC
7.0 - 26.0	3.3 @ 1.5	—	5.0	SMT	Horizontal	78ST133SC-ND◆	29.71	25.26	23.40	78ST133SC
7.0 - 26.0	3.3 @ 1.5	—	5.0	TH	Vertical	78ST133VC-ND◆	29.71	25.26	23.40	78ST133VC
8.0 - 20.0	5.0 @ 2.0	—	10.0	TH	Horizontal	78ST205HC-ND◆	32.87	28.44	26.66	78ST205HC
8.0 - 20.0	5.0 @ 2.0	—	10.0	TH	Vertical	78ST205VC-ND◆	32.87	28.44	26.66	78ST205VC
14.5 - 28.0	12.0 @ 2.0	—	24.0	TH	Horizontal	78ST212HC-ND	42.35	36.63	34.34	78ST212HC
14.5 - 28.0	12.0 @ 2.0	—	24.0	TH	Vertical	78ST212VC-ND	42.35	36.63	34.34	78ST212VC
9.0 - 28.0	5.0 @ 2.0	—	10.0	TH	Horizontal	PT78HT205H-ND◆	17.84	15.17	14.06	PT78HT205H
9.0 - 28.0	5.0 @ 2.0	—	10.0	SMT	Horizontal	PT78HT205S-ND◆	17.84	15.17	14.06	PT78HT205S
9.0 - 28.0	5.0 @ 2.0	—	10.0	TH	Vertical	PT78HT205V-ND◆	17.84	15.17	14.06	PT78HT205V
12.0 - 28.0	8.0 @ 2.0	—	16.0	TH	Horizontal	296-20250-ND◆	17.84	15.17	14.06	PT78HT208H
12.0 - 28.0	8.0 @ 2.0	—	16.0	SMT	Horizontal	296-20251-ND◆	17.84	15.17	14.06	PT78HT208S
9.0 - 15.0	3.3 @ 2.0	—	6.6	TH	Horizontal	PT78HT233H-ND◆	17.84	15.17	14.06	PT78HT233H
9.0 - 15.0	3.3 @ 2.0	—	6.6	SMT	Horizontal	PT78HT233S-ND◆	17.84	15.17	14.06	PT78HT233S
9.0 - 28.0	5.25 @ 2.0	—	10.5	TH	Horizontal	296-20252-ND◆	17.84	15.17	14.06	PT78HT253H
9.0 - 28.0	5.25 @ 2.0	—	10.5	SMT	Horizontal	296-20253-ND◆	17.84	15.17	14.06	PT78HT253S
9.0 - 28.0	5.25 @ 2.0	—	10.5	TH	Vertical	296-20254-ND◆	17.84	15.17	14.06	PT78HT253V
10.5 - 28.0	6.5 @ 2.0	—	13.0	SMT	Horizontal	296-20255-ND◆	17.84	15.17	14.06	PT78HT265S
10.5 - 28.0	6.5 @ 2.0	—	13.0	TH	Vertical	296-20256-ND◆	17.84	15.17	14.06	PT78HT265V
7.0 - 25.0	-3.0 @ 1.0	—	3.0	TH	Horizontal	296-20257-ND	15.72	13.22	12.15	PT78NR103H
7.0 - 25.0	-3.0 @ 1.0	—	3.0	SMT	Horizontal	296-20258-ND◆	15.72	13.22	12.15	PT78NR103S
7.0 - 25.0	-3.0 @ 1.0	—	3.0	TH	Vertical	296-20259-ND	15.72	13.22	12.15	PT78NR103V
7.0 - 25.0	-5.0 @ 1.0	—	5.0	TH	Horizontal	PT78NR105H-ND◆	15.72	13.22	12.15	PT78NR105H
7.0 - 25.0	-5.0 @ 1.0	—	5.0	SMT	Horizontal	PT78NR105S-ND◆	15.72	13.22	12.15	PT78NR105S
7.0 - 25.0	-5.0 @ 1.0	—	5.0	TH	Vertical	PT78NR105V-ND◆	15.72	13.22	12.15	PT78NR105V
7.0 - 21.0	-6.0 @ 0.8	—	4.8	TH	Horizontal	296-20260-ND	15.72	13.22	12.15	PT78NR106V
7.0 - 21.0	-9.0 @ 0.55	—	5.0	TH	Horizontal	296-20261-ND◆	15.72	13.22	12.15	PT78NR109H
7.0 - 21.0	-9.0 @ 0.55	—	5.0	SMT	Horizontal	296-20262-ND◆	15.72	13.22	12.15	PT78NR109S
7.0 - 18.0	-12.0 @ 0.4	—	4.8	TH	Horizontal	PT78NR112H-ND◆	17.84	15.17	14.06	PT78NR112H
7.0 - 18.0	-12.0 @ 0.4	—	4.8	SMT	Horizontal	PT78NR112S-ND◆	17.84	15.17	14.06	PT78NR112S
7.0 - 18.0	-12.0 @ 0.4	—	4.8	TH	Vertical	PT78NR112V-ND◆	17.84	15.17	14.06	PT78NR112V
7.0 - 15.0	-15.0 @ 0.3	—	4.5	TH	Horizontal	296-20263-ND◆	15.72	13.22	12.15	PT78NR115H
7.0 - 15.0	-15.0 @ 0.3	—	4.5	SMT	Horizontal	296-20264-ND◆	15.72	13.22	12.15	PT78NR115S
7.0 - 15.0	-15.0 @ 0.3	—	4.5	TH	Vertical	296-20265-ND◆	15.72	13.22	12.15	PT78NR115V
7.0 - 25.0	-5.2 @ 1.0	—	5.2	TH	Horizontal	296-20266-ND◆	15.72	13.22	12.15	PT78NR152H
7.0 - 25.0	-5.2 @ 1.0	—	5.2	SMT	Horizontal	296-20267-ND◆	15.72	13.22	12.15	PT78NR152S
7.0 - 25.0	-5.2 @ 1.0	—	5.2	TH	Vertical	296-20268-ND	15.72	13.22	12.15	PT78NR152V
9.0 - 38.0	5.0 @ 1.5	—	7.5	TH	Horizontal	PT78ST105H-ND◆	15.72	13.22	12.15	PT78ST105H
9.0 - 38.0	5.0 @ 1.5	—	7.5	SMT	Horizontal	PT78ST105S-ND◆	15.72	13.22	12.15	PT78ST105S
9.0 - 38.0	5.0 @ 1.5	—	7.5	TH	Vertical	PT78ST105V-ND◆	15.72	13.22	12.15	PT78ST105V
10.0 - 38.0	6.0 @ 1.5	—	9.0	SMT	Horizontal	296-20277-ND◆	17.84	15.17	14.06	PT78ST106S
10.0 - 38.0	6.0 @ 1.5	—	9.0	TH	Vertical	PT78ST106V-ND◆	17.84	15.17	14.06	PT78ST106V
11.0 - 38.0	7.0 @ 1.5	—	10.5	TH	Horizontal	296-20278-ND◆	17.84	15.17	14.06	PT78ST107H
11.0 - 38.0	7.0 @ 1.5	—	10.5	SMT	Horizontal	296-20279-ND◆	17.84	15.17	14.06	PT78ST107S
12.0 - 38.0	8.0 @ 1.5	—	12.0	TH	Horizontal	296-20280-ND◆	15.72	13.22	12.15	PT78ST108H
12.0 - 38.0	8.0 @ 1.5	—	12.0	SMT	Horizontal	296-20281-ND◆	15.72	13.22	12.15	PT78ST108S
12.0 - 38.0	8.0 @ 1.5	—	12.0	TH	Vertical	296-20282-ND◆	15.72	13.22	12.15	PT78ST108V
13.0 - 38.0	9.0 @ 1.5	—	13.5	TH	Horizontal	PT78ST109H-ND	15.72	13.22	12.15	PT78ST109H
13.0 - 38.0	9.0 @ 1.5	—	13.5	SMT	Horizontal	296-20283-ND	15.72	13.22	12.15	PT78ST109S
13.0 - 38.0	9.0 @ 1.5	—	13.5	TH	Vertical	296-20284-ND	15.72	13.22	12.15	PT78ST109V
14.0 - 38.0	10.0 @ 1.5	—	15.0	SMT	Horizontal	296-20285-ND◆	15.72	13.22	12.15	PT78ST110S
14.0 - 38.0	10.0 @ 1.5	—	15.0	TH	Vertical	296-20286-ND	15.72	13.22	12.15	PT78ST110V
16.0 - 38.0	12.0 @ 1.5	—	18.0	TH	Horizontal	PT78ST112H-ND◆	17.84	15.17	14.06	PT78ST112H
16.0 - 38.0	12.0 @ 1.5	—	18.0	SMT	Horizontal	PT78ST112S-ND◆	17.84	15.17	14.06	PT78ST112S
16.0 - 38.0	12.0 @ 1.5	—	18.0	TH	Vertical	PT78ST112V-ND◆	17.84	15.17	14.06	PT78ST112V
17.9 - 38.0	13.9 @ 1.5	—	20.9	SMT	Horizontal	296-20288-ND	17.84	15.17	14.06	PT78ST114S
17.9 - 38.0	13.9 @ 1.5	—	20.9	TH	Vertical	296-20289-ND◆	17.84	15.17	14.06	PT78ST114V
19.0 - 38.0	15.0 @ 1.5	—	22.5	TH	Horizontal	PT78ST115H-ND◆	17.84	15.17	14.06	PT78ST115H
19.0 - 38.0	15.0 @ 1.5	—	22.5	SMT	Horizontal	296-20290-ND◆	17.84	15.17	14.06	PT78ST115S
9.0 - 26.0	3.3 @ 1.5	—	5.0	TH	Horizontal	PT78ST133H-ND◆	15.72	13.22	12.15	PT78ST133H
9.0 - 26.0	3.3 @ 1.5	—	5.0	SMT	Horizontal	PT78ST133S-ND	15.72	13.22	12.15	PT78ST133S
9.0 - 26.0	3.3 @ 1.5	—	5.0	TH	Vertical	PT78ST133V-ND◆	15.72	13.22	12.15	PT78ST133V
9.25 - 38.0	5.25 @ 1.5	—	7.9	SMT	Horizontal	296-20291-ND◆	15.72	13.22	12.15	PT78ST153S
9.25 - 38.0	5.25 @ 1.5	—	7.9	TH	Vertical	296-20292-ND◆	15.72	13.22	12.15	PT78ST153V
10.5 - 38.0	6.5 @ 1.5	—	9.8	SMT	Horizontal	296-20293-ND	15.72	13.22	12.15	PT78ST165S
10.5 - 38.0	6.5 @ 1.5	—	9.8	TH	Vertical	296-20294-ND	15.72	13.22	12.15	PT78ST165V
16.0 - 28.0	12.0 @ 2.0	—	24.0	TH	Vertical	PT78ST212V-ND◆	26.93	22.90	21.21	PT78ST212V
-9.0 - -30.0	-5.0 @ 1.5	—	7.5	TH	Horizontal	PT79SR105H-ND◆	23.13	19.67	18.22	PT79SR105H
-9.0 - -30.0	-5.0 @ 1.5	—	7.5	SMT	Horizontal	PT79SR105S-ND	23.13	19.67	18.22	PT79SR105S
-9.0 - -30.0	-5.0 @ 1.5	—	7.5	TH	Vertical	PT79SR105V-ND	22.30	18.96	17.57	PT79SR105V
-13.0 - -30.0	-9.0 @ 1.5	—	13.5	TH	Horizontal	296-20295-ND	18.67	15.87	14.71	PT79SR109H
-13.0 - -30.0	-9.0 @ 1.5	—	13.5	SMT	Horizontal	296-20296-ND	18.67	15.87	14.71	PT79SR109S
-16.0 - -30.0	-12.0 @ 1.5	—	18.0	TH	Horizontal	PT79SR112H-ND	23.13	19.67	18.22	PT79SR112H
-16.0 - -30.0	-12.0 @ 1.5	—	18.0	SMT	Horizontal	296-20297-ND	23.13	19.67	18.22	PT79SR112S
-16.0 - -30.0	-12.0 @ 1.5	—	18.0	TH	Vertical	PT79SR112V-ND	22.30	18.96	17.57	PT79SR112V
-19.0 - -30.0	-15.0 @ 1.5	—	22.5	TH	Horizontal	296-20298-ND◆	23.13	19.67	18.22	PT79SR115H
-19.0 - -30.0	-15.0 @ 1.5	—	22.5	SMT	Horizontal	296-20299-ND	23.13	19.67	18.22	PT79SR115S
-19.0 - -30.0	-15.0 @ 1.5	—	22.5	TH	Vertical	296-20300-ND◆	22.30	18.96	17.57	PT79SR115V
-9.2 - -30.0	-5.2 @ 1.5	—	7.8	TH	Horizontal	296-20301-ND	23.13	19.67	18.22	PT79SR152H
-9.2 - -30.0	-5.2 @ 1.5	—	7.8	SMT	Horizontal	296-20302-ND◆	23.13	19.67	18.22	PT79SR152S
-9.2 - -30.0	-5.2 @ 1.5	—	7.8	TH	Vertical	296-20303-ND◆	22.30	18.96	17.57	PT79SR152V
4.75 - 14.0	0.7 - 3.6 @ 20.0	—	72.0	TH	Horizontal	296-23227-ND◆	21.31	18.12	16.79	PTD08A020WAD

◆ RoHS Compliant † Cut Tape ‡ Tape and Reel

 Most SMT cutdown parts are available on a Digi-Reel®. For Digi-Reel part number, change 1-ND to 6-ND or CT-ND to DKR-ND. See Digi-Key® Services on page 2 for additional information.

Free shipping on orders over €65! All prices