



Fig.	Mounting Type	Input Voltage (V)	Output Voltage (V)	Output Current (mA)	Digi-Key Part No.	Tube Price Each			Murata Power Solutions Part No.
						1	5	10	
1	DIP 15	±5	±100	811-1460-5-ND	7.66	7.43	7.32	NMA1505DC	
	DIP 15	±12	+42	811-1462-5-ND	7.66	7.43	7.32	NMA1512DC	
	DIP 15	±15	+33	811-1464-5-ND	7.66	7.43	7.32	NMA1515DC	
4	SIP 5	±5	±100	811-1448-5-ND	7.28	7.07	6.96	NMA0505SC	
	SIP 5	±9	+55	811-1449-5-ND	7.28	7.07	6.96	NMA0509SC	
	SIP 5	±12	+42	811-1451-5-ND	7.28	7.07	6.96	NMA0512SC	
	SIP 5	±15	+33	811-1453-5-ND	7.28	7.07	6.96	NMA0515SC	
	SIP 12	±5	±100	811-1454-5-ND	7.28	7.07	6.96	NMA1205SC	
	SIP 12	±9	+55	811-1455-5-ND	7.28	7.07	6.96	NMA1209SC	
	SIP 12	±12	+42	811-1457-5-ND	7.28	7.07	6.96	NMA1212SC	
	SIP 12	±15	+33	811-1459-5-ND	7.28	7.07	6.96	NMA1215SC	
	SIP 15	±5	±100	811-1461-5-ND	7.28	7.07	6.96	NMA1505SC	
	SIP 15	±12	+42	811-1463-5-ND	7.28	7.07	6.96	NMA1512SC	
	SIP 15	±15	+33	811-1465-5-ND	7.28	7.07	6.96	NMA1515SC	
	SIP 24	±5	±100	811-1467-5-ND	8.38	8.14	8.02	NMA2405SC	
SIP 24	±12	+42	811-1468-5-ND	8.38	8.14	8.02	NMA2412SC		
SIP 24	±15	+33	811-1470-5-ND	8.38	8.14	8.02	NMA2415SC		
NMD Series									
4	SIP 5	5/5	100/100	811-1471-5-ND	8.73	8.48	8.35	NMD050505SC	
	SIP 5	5/5	100/34	811-1472-5-ND	8.73	8.48	8.35	NMD050515SC	
NME Series									
1	DIP 5	5	200	811-1473-5-ND	7.66	7.43	7.32	NME0505DC	
	DIP 5	9	111	811-1475-5-ND	7.66	7.43	7.32	NME0509DC	
	DIP 5	12	83	811-1477-5-ND	7.66	7.43	7.32	NME0512DC	
	DIP 5	15	66	811-1479-5-ND	7.66	7.43	7.32	NME0515DC	
	DIP 12	5	200	811-1482-5-ND	7.66	7.43	7.32	NME1205DC	
	DIP 12	12	83	811-1484-5-ND	7.66	7.43	7.32	NME1212DC	
	DIP 24	5	200	811-1488-5-ND	8.78	8.52	8.39	NME2405DC	
	DIP 24	12	83	811-1491-5-ND	8.78	8.52	8.39	NME2412DC	
	DIP 24	15	66	811-1493-5-ND	8.78	8.52	8.39	NME2415DC	
	SIP 5	5	200	811-1474-5-ND	7.28	7.07	6.96	NME0505SC	
	SIP 5	9	111	811-1476-5-ND	7.28	7.07	6.96	NME0509SC	
	SIP 5	12	83	811-1478-5-ND	7.28	7.07	6.96	NME0512SC	
SIP 5	15	66	811-1480-5-ND	7.28	7.07	6.96	NME0515SC		
SIP 5	24	42	811-1481-5-ND	8.38	8.14	8.02	NME0524SC		
4	SIP 12	5	200	811-1483-5-ND	7.28	7.07	6.96	NME1205SC	
	SIP 12	12	83	811-1485-5-ND	7.28	7.07	6.96	NME1212SC	
	SIP 12	15	66	811-1486-5-ND	7.28	7.07	6.96	NME1215SC	
	SIP 15	5	200	811-1487-5-ND	7.28	7.07	6.96	NME1505SC	
	SIP 24	5	200	811-1489-5-ND	8.38	8.14	8.02	NME2405SC	
	SIP 24	9	111	811-1490-5-ND	8.38	8.14	8.02	NME2409SC	
SIP 24	12	83	811-1492-5-ND	8.38	8.14	8.02	NME2412SC		
SIP 24	15	66	811-1494-5-ND	8.38	8.14	8.02	NME2415SC		
NMF Series									
1	DIP 5	5	100	811-1495-5-ND	7.18	6.97	6.86	NMF0505DC	
	SIP 5	5	100	811-1496-5-ND	6.82	6.63	6.53	NMF0505SC	
	SIP 5	12	83	811-1497-5-ND	6.82	6.63	6.53	NMF0512SC	
	SIP 5	15	67	811-1498-5-ND	6.82	6.63	6.53	NMF0515SC	
	SIP 12	5	100	811-1499-5-ND	6.82	6.63	6.53	NMF1205SC	
	SIP 12	12	83	811-1500-5-ND	6.82	6.63	6.53	NMF1212SC	
	SIP 12	15	67	811-1501-5-ND	6.82	6.63	6.53	NMF1215SC	
	SIP 24	5	100	811-1502-5-ND	7.86	7.64	7.52	NMF2405SC	
	SIP 24	15	67	811-1503-5-ND	7.86	7.64	7.52	NMF2415SC	
NMG Series									
4	SIP 5	5	400	811-1702-5-ND	9.83	9.55	9.40	NMG0505SC	
	SIP 5	9	222	811-1703-5-ND	9.83	9.55	9.40	NMG0509SC	
	SIP 5	12	167	811-1704-5-ND	9.83	9.55	9.40	NMG0512SC	
	SIP 5	15	133	811-1705-5-ND	9.83	9.55	9.40	NMG0515SC	
	SIP 12	5	400	811-1706-5-ND	9.83	9.55	9.40	NMG1205SC	
	SIP 12	9	222	811-1707-5-ND	9.83	9.55	9.40	NMG1209SC	
SIP 12	12	167	811-1708-5-ND	9.83	9.55	9.40	NMG1212SC		
SIP 12	15	133	811-1709-5-ND	9.83	9.55	9.40	NMG1215SC		
NMH Series									
1	DIP 5	±5	±200	811-1504-5-ND	12.23	11.88	11.70	NMH0505DC	
	DIP 5	±9	+111	811-1506-5-ND	12.23	11.88	11.70	NMH0509DC	
	DIP 5	±12	+83	811-1508-5-ND	12.23	11.88	11.70	NMH0512DC	
	DIP 5	±15	+67	811-1510-5-ND	12.23	11.88	11.70	NMH0515DC	
	DIP 5	±24	+42	811-1512-5-ND	14.09	13.68	13.47	NMH0524DC	
	DIP 12	±5	±200	811-1513-5-ND	12.23	11.88	11.70	NMH1205DC	
	DIP 12	±9	+111	811-1515-5-ND	12.23	11.88	11.70	NMH1209DC	
	DIP 12	±12	+83	811-1517-5-ND	12.23	11.88	11.70	NMH1212DC	
	DIP 12	±15	+67	811-1519-5-ND	12.23	11.88	11.70	NMH1215DC	
	DIP 24	±5	±200	811-1521-5-ND	14.09	13.68	13.47	NMH2405DC	
	DIP 24	±12	+83	811-1524-5-ND	14.09	13.68	13.47	NMH2412DC	
	DIP 24	±15	+67	811-1526-5-ND	14.09	13.68	13.47	NMH2415DC	
4	SIP 5	±5	±200	811-1505-5-ND	11.66	11.32	11.15	NMH0505SC	
	SIP 5	±9	+111	811-1507-5-ND	11.66	11.32	11.15	NMH0509SC	
	SIP 5	±12	+83	811-1509-5-ND	11.66	11.32	11.15	NMH0512SC	
	SIP 5	±15	+67	811-1511-5-ND	11.66	11.32	11.15	NMH0515SC	
	SIP 12	±5	±200	811-1514-5-ND	11.66	11.32	11.15	NMH1205SC	
	SIP 12	±9	+111	811-1516-5-ND	11.66	11.32	11.15	NMH1209SC	
	SIP 12	±12	+83	811-1518-5-ND	11.66	11.32	11.15	NMH1212SC	
	SIP 12	±15	+67	811-1520-5-ND	11.66	11.32	11.15	NMH1215SC	
	SIP 24	±5	±200	811-1522-5-ND	13.42	13.02	12.82	NMH2405SC	
	SIP 24	±9	+111	811-1523-5-ND	13.42	13.02	12.82	NMH2409SC	
	SIP 24	±12	+83	811-1525-5-ND	13.42	13.02	12.82	NMH2412SC	
	SIP 24	±15	+67	811-1527-5-ND	13.42	13.02	12.82	NMH2415SC	

Fig.	Mounting Type	Input Voltage (V)	Output Voltage (V)	Output Current (mA)	Digi-Key Part No.	Tube Price Each			Murata Power Solutions Part No.
						1	5	10	
NMJ Series									
4	SIP 3.3	3.3	303	811-1528-5-ND	11.66	11.32	11.15	NMJ0303SAC	
	SIP 5	3.3	303	811-1529-5-ND	11.66	11.32	11.15	NMJ0503SAC	
	SIP 5	+5	±100	811-1531-5-ND	11.66	11.32	11.15	NMJ0505SAC	
	SIP 5	5	200	811-1530-5-ND	11.66	11.32	11.15	NMJ0505SAC	
	SIP 5	+9	+55	811-1533-5-ND	11.66	11.32	11.15	NMJ0509SAC	
	SIP 5	9	111	811-1532-5-ND	11.66	11.32	11.15	NMJ0509SAC	
	SIP 5	±12	+42	811-1535-5-ND	11.66	11.32	11.15	NMJ0512SAC	
	SIP 5	12	83	811-1534-5-ND	11.66	11.32	11.15	NMJ0512SAC	
	SIP 5	±15	+33	811-1537-5-ND	11.66	11.32	11.15	NMJ0515SAC	
	SIP 5	15	66	811-1536-5-ND	11.66	11.32	11.15	NMJ0515SAC	
	SIP 12	+5	±100	811-1539-5-ND	11.66	11.32	11.15	NMJ1205SAC	
	SIP 12	5	200	811-1538-5-ND	11.66	11.32	11.15	NMJ1205SAC	
SIP 12	+9	+55	811-1541-5-ND	11.66	11.32	11.15	NMJ1209SAC		
SIP 12	9	111	811-1540-5-ND	11.66	11.32	11.15	NMJ1209SAC		
SIP 12	±12	+42	811-1543-5-ND	11.66	11.32	11.15	NMJ1212SAC		
SIP 12	12	83	811-1542-5-ND	11.66	11.32	11.15	NMJ1212SAC		
SIP 12	±15	+33	811-1545-5-ND	11.66	11.32	11.15	NMJ1215SAC		
SIP 12	15	66	811-1544-5-ND	11.66	11.32	11.15	NMJ1215SAC		
NMK Series									
4	SIP 5	5	400	811-1546-5-ND	10.53	10.23	10.07	NMK0505SAC	
	SIP 5	9	222	811-1547-5-ND	10.53	10.23	10.07	NMK0509SAC	
	SIP 5	12	167	811-1548-5-ND	10.53	10.23	10.07	NMK0512SAC	
	SIP 5	15	133	811-1549-5-ND	10.53	10.23	10.07	NMK0515SAC	
	SIP 12	5	400	811-1550-5-ND	10.53	10.23	10.07	NMK1205SAC	
	SIP 12	9	222	811-1551-5-ND	10.53	10.23	10.07	NMK1209SAC	
SIP 12	12	167	811-1552-5-ND	10.53	10.23	10.07	NMK1212SAC		
SIP 12	15	133	811-1553-5-ND	10.53	10.23	10.07	NMK1215SAC		
NML Series									
4	SIP 5	5	400	811-1554-5-ND	11.66	11.32	11.15	NML0505SC	
	SIP 5	9	222	811-1555-5-ND	11.66	11.32	11.15	NML0509SC	
	SIP 5	12	167	811-1556-5-ND	11.66	11.32	11.15	NML0512SC	
	SIP 5	15	133	811-1557-5-ND	11.66	11.32	11.15	NML0515SC	
	SIP 12	5	400	811-1558-5-ND	11.66	11.32	11.15	NML1205SC	
	SIP 12	9	222	811-1559-5-ND	11.66	11.32	11.15	NML1209SC	
SIP 12	12	167	811-1560-5-ND	11.66	11.32	11.15	NML1212SC		
SIP 12	15	133	811-1561-5-ND	11.66	11.32	11.15	NML1215SC		
NMR Series									
4	SIP 5	5	200	811-1566-5-ND	7.28	7.07	6.96	NMR100C	
	SIP 5	12	83	811-1567-5-ND	7.28	7.07	6.96	NMR101C	
	SIP 5	15	67	811-1568-5-ND	7.28	7.07	6.96	NMR102C	
	SIP 12	5	200	811-1569-5-ND	7.28	7.07	6.96	NMR106C	
	SIP 12	12	83	811-1570-5-ND	7.28	7.07	6.96	NMR107C	
	SIP 12								