

A

Fig.	Nb. de positions	Dimension - Pouces (mm)		N° de référence Digi-Key	Prix de bande coupée			N° de référence Digi-Key	Bande et bobine		N° de référence FCI	
		A	B		1	25	100		Qté	Prix		
6	10	0.646 (16.40)	0.354 (9.00)	609-1140-1-ND	.70	8.63	29.28	609-1140-2-ND	2,000	295.57/M	SFW10S-2STE1LF	
	11	0.685 (17.40)	0.394 (10.00)	609-1142-1-ND	.72	9.02	30.60	609-1142-2-ND	1,000	251.12	SFW11S-2STE1LF	
	12	0.724 (18.40)	0.433 (11.00)	609-1144-1-ND	.73	9.29	31.50	609-1144-2-ND	1,000	258.44	SFW12S-2STE1LF	
	15	0.843 (21.40)	0.551 (14.00)	609-1148-1-ND	.86	10.93	37.10	609-1148-2-ND	1,000	304.38	SFW15S-2STE1LF	
	16	0.882 (22.40)	0.591 (15.00)	609-1150-1-ND	.95	12.15	41.19	609-1150-2-ND	1,000	337.99	SFW16S-2STE1LF	
	18	0.961 (24.40)	0.670 (17.00)	609-1154-1-ND	.92	11.75	39.83	609-1154-2-ND	1,000	316.66	SFW18S-2STE1LF	
	20	1.040 (26.40)	0.748 (19.00)	609-1156-1-ND	.58	6.89	22.95	609-1156-2-ND	1,000	357.30	SFW20S-2STE1LF	
	24	1.197 (30.40)	0.906 (23.00)	609-1162-1-ND	1.20	16.56	55.71	609-1162-2-ND	1,000	460.70	SFW24S-2STE1LF	
	26	1.276 (32.40)	0.984 (25.00)	609-1164-1-ND	1.01	13.15	44.42	609-1164-2-ND	1,000	362.35	SFW26S-2STE1LF	
	30	1.354 (34.40)	1.063 (27.00)	609-1166-1-ND	1.19	16.75	54.83	609-1166-2-ND	1,000	456.87	SFW28S-2STE1LF	
		1.433 (36.40)	1.142 (29.00)	609-1168-1-ND	1.09	14.27	49.31	609-1168-2-ND	1,000	402.26	SFW30S-2STE1LF	
Série SFW — Entrée supérieure CMS, ZIF avec plaque de montage												
6	4	0.409 (10.40)	0.118 (3.00)	609-1133-1-ND	.78	9.76	33.10	609-1133-2-ND	1,000	271.58	SFW4S-2STME1LF	
	5	0.449 (11.40)	0.157 (4.00)	609-1135-1-ND	.79	9.67	32.80	609-1135-2-ND	1,000	269.14	SFW5S-2STME1LF	
	8	0.567 (14.40)	0.276 (7.00)	609-1138-1-ND	.91	11.13	37.76	609-1138-2-ND	1,000	309.80	SFW8S-2STME1LF	
	10	0.646 (16.40)	0.354 (9.00)	609-1141-1-ND	.72	8.76	29.71	609-1141-2-ND	1,000	319.96	SFW10S-2STME1LF	
	11	0.685 (17.40)	0.394 (10.00)	609-1143-1-ND	.76	9.50	32.09	609-1143-2-ND	1,000	261.78	SFW11S-2STME1LF	
	12	0.724 (18.40)	0.433 (11.00)	609-1145-1-ND	.74	9.44	31.91	609-1145-2-ND	1,000	260.34	SFW12S-2STME1LF	
	20	1.040 (26.40)	0.748 (19.00)	609-1157-1-ND	1.07	13.94	47.08	609-1157-2-ND	1,000	384.14	SFW20S-2STME1LF	
	24	1.197 (30.40)	0.906 (23.00)	609-1163-1-ND	.78	10.27	34.68	609-1163-2-ND	1,000	282.92	SFW24S-2STME1LF	
	30	1.433 (36.40)	1.142 (29.00)	609-1169-1-ND	1.25	17.24	57.99	609-1169-2-ND	1,000	479.61	SFW30S-2STME1LF	
	Série HFW — Entrée latérale CMS, LIF, type de contact inférieur											
7	4	0.260 (6.60)	0.118 (3.00)	609-1782-1-ND	.58	7.18	22.97	609-1782-2-ND	2,000	175.73/M	HFW4R-1STE1LF	
	5	0.300 (7.60)	0.157 (4.00)	609-1784-1-ND	.42	4.95	16.01	609-1784-2-ND	2,000	121.97/M	HFW5R-1STE1LF	
	6	0.339 (8.60)	0.197 (5.00)	609-1786-1-ND	.30	3.58	11.56	609-1786-2-ND	4,000	88.09/M	HFW6R-1STE1LF	
	8	0.417 (10.60)	0.276 (7.00)	609-1788-1-ND	.66	8.39	27.26	609-1788-2-ND	2,000	206.82/M	HFW8R-1STE1LF	
	10	0.496 (12.60)	0.354 (9.00)	609-1790-1-ND	.67	8.46	27.50	609-1790-2-ND	2,000	211.54/M	HFW10R-1STE1LF	
	12	0.575 (14.60)	0.433 (11.00)	609-1792-1-ND	.42	5.23	16.74	609-1792-2-ND	2,000	129.71/M	HFW12R-1STE1LF	
	14	0.654 (16.60)	0.512 (13.00)	609-1794-1-ND	.75	9.66	32.77	609-1794-2-ND	2,000	252.07/M	HFW14R-1STE1LF	
	18	0.811 (20.60)	0.670 (17.00)	609-1800-1-ND	.75	9.41	31.92	609-1800-2-ND	2,000	245.59/M	HFW18R-1STE1LF	
	20	0.890 (22.60)	0.748 (19.00)	609-1802-1-ND	.49	5.88	19.58	609-1802-2-ND	2,000	149.81/M	HFW20R-1STE1LF	
	Série HFW — Entrée latérale CMS, LIF, type de contact supérieur											
7	4	0.260 (6.60)	0.118 (3.00)	609-1783-1-ND	.65	8.14	26.44	609-1783-2-ND	2,000	203.41/M	HFW4R-2STE1LF	
	5	0.300 (7.60)	0.157 (4.00)	609-1785-1-ND	.43	5.20	16.81	609-1785-2-ND	2,000	128.07/M	HFW5R-2STE1LF	
	6	0.339 (8.60)	0.197 (5.00)	609-1787-1-ND	.30	3.58	11.56	609-1787-2-ND	2,000	84.24/M	HFW6R-2STE1LF	
	8	0.417 (10.60)	0.276 (7.00)	609-1789-1-ND	.84	10.35	33.44	609-1789-2-ND	2,000	226.91/M	HFW8R-2STE1LF	
	10	0.496 (12.60)	0.354 (9.00)	609-1791-1-ND	.62	7.78	25.28	609-1791-2-ND	2,000	194.52/M	HFW10R-2STE1LF	
	12	0.575 (14.60)	0.433 (11.00)	609-1793-1-ND	.78	9.54	30.51	609-1793-2-ND	2,000	221.19/M	HFW12R-2STE1LF	
	16	0.732 (18.60)	0.591 (15.00)	609-1799-1-ND	.45	5.45	17.47	609-1799-2-ND	2,000	135.36/M	HFW16R-2STE1LF	
	20	0.890 (22.60)	0.748 (19.00)	609-1803-1-ND	1.11	13.35	44.48	609-1803-2-ND	2,000	340.31/M	HFW20R-2STE1LF	
	22	0.969 (24.60)	0.827 (21.00)	609-1805-1-ND	.58	7.22	23.11	609-1805-2-ND	2,000	176.76/M	HFW22R-2STE1LF	
	24	1.047 (26.60)	0.906 (23.00)	609-1807-1-ND	1.01	12.37	41.22	609-1807-2-ND	2,000	315.30/M	HFW24R-2STE1LF	
Série SFW — Entrée latérale CMS, ZIF, type de contact inférieur												
8	4	0.386 (9.80)	0.118 (3.00)	609-1883-1-ND	.77	9.62	32.63	609-1883-2-ND	2,000	251.05/M	SFW4R-1STE1LF	
	5	0.425 (10.80)	0.157 (4.00)	609-1887-1-ND	.77	9.82	33.30	609-1887-2-ND	2,000	256.14/M	SFW5R-1STE1LF	
	6	0.465 (11.80)	0.197 (5.00)	609-1889-1-ND	1.05	12.93	41.35	609-1889-2-ND	2,000	320.47/M	SFW6R-1STE1LF	
	8	0.543 (13.80)	0.276 (7.00)	609-1893-1-ND	.67	8.44	27.45	609-1893-2-ND	2,000	211.16/M	SFW8R-1STE1LF	
	10	0.622 (15.80)	0.354 (9.00)	609-1897-1-ND	.85	11.12	37.56	609-1897-2-ND	2,000	296.54/M	SFW10R-1STE1LF	
	12	0.701 (17.80)	0.433 (11.00)	609-1900-1-ND	.75	9.41	31.91	609-1900-2-ND	2,000	245.46/M	SFW12R-1STE1LF	
	14	0.780 (19.80)	0.512 (13.00)	609-1902-1-ND	.76	9.76	33.10	609-1902-2-ND	2,000	254.61/M	SFW14R-1STE1LF	
	15	0.819 (20.80)	0.551 (14.00)	609-1905-1-ND	.82	10.46	35.33	609-1905-2-ND	2,000	264.94/M	SFW15R-1STE1LF	
	16	0.858 (21.80)	0.591 (15.00)	609-1907-1-ND	.97	13.34	44.87	609-1907-2-ND	2,000	339.62/M	SFW16R-1STE1LF	
	18	0.937 (23.80)	0.670 (17.00)	609-1911-1-ND	.82	10.77	36.35	609-1911-2-ND	2,000	287.01/M	SFW18R-1STE1LF	
8	20	1.016 (25.80)	0.748 (19.00)	609-1913-1-ND	1.19	16.48	56.52	609-1913-2-ND	2,000	455.28/M	SFW20R-1STE1LF	
	22	1.094 (27.80)	0.827 (21.00)	609-1916-1-ND	.87	11.42	39.43	609-1916-2-ND	2,000	311.28/M	SFW22R-1STE1LF	
	24	1.173 (29.80)	0.906 (23.00)	609-1919-1-ND	.87	11.98	40.28	609-1919-2-ND	2,000	315.76/M	SFW24R-1STE1LF	
	26	1.252 (31.80)	0.984 (25.00)	609-1921-1-ND	1.30	17.63	61.70	609-1921-2-ND	2,000	502.47/M	SFW26R-1STE1LF	
	28	1.331 (33.80)	1.063 (27.00)	609-1924-1-ND	.76	9.53	32.19	609-1924-2-ND	2,000	355.74/M	SFW28R-1STE1LF	
	30	1.409 (35.80)	1.142 (29.00)	609-1926-1-ND	1.06	14.97	49.00	609-1926-2-ND	2,000	394.73/M	SFW30R-1STE1LF	
	Série SFW — Entrée latérale CMS, ZIF, type de contact supérieur											
	8	4	0.386 (9.80)	0.118 (3.00)	609-1884-1-ND	.75	9.30	31.53	609-1884-2-ND	2,000	242.54/M	SFW4R-2STE1LF
		5	0.425 (10.80)	0.157 (4.00)	609-1888-1-ND	.75	9.30	31.53	609-1888-2-ND	2,000	242.54/M	SFW5R-2STE1LF
		6	0.465 (11.80)	0.197 (5.00)	609-1890-1-ND	.86	11.41	38.53	609-1890-2-ND	2,000	304.16/M	SFW6R-2STE1LF
8		0.543 (13.80)	0.276 (7.00)	609-1894-1-ND	.66	8.25	26.81	609-1894-2-ND	2,000	206.20/M	SFW8R-2STE1LF	
10		0.622 (15.80)	0.354 (9.00)	609-1898-1-ND	1.01	12.60	40.32	609-1898-2-ND	2,000	308.43/M	SFW10R-2STE1LF	
12		0.701 (17.80)	0.433 (11.00)	609-1901-1-ND	.90	12.36	41.55	609-1901-2-ND	2,000	325.71/M	SFW12R-2STE1LF	
14		0.780 (19.80)	0.512 (13.00)	609-1903-1-ND	1.01	13.85	46.59	609-1903-2-ND	2,000	365.13/M	SFW14R-2STE1LF	
15		0.819 (20.80)	0.551 (14.00)	609-1906-1-ND	.79	9.82	33.15	609-1906-2-ND	2,000	248.64/M	SFW15R-2STE1LF	
16		0.858 (21.80)	0.591 (15.00)	609-1908-1-ND	.80	10.11	34.15	609-1908-2-ND	2,000	256.12/M	SFW16R-2STE1LF	
18		0.937 (23.80)	0.670 (17.00)	609-1912-1-ND	1.01	13.84	46.54	609-1912-2-ND	2,000	364.76/M	SFW18R-2STE1LF	
8	20	1.016 (25.80)	0.748 (19.00)	609-1914-1-ND	.91	11.86	40.97	609-1914-2-ND	2,000	323.47/M	SFW20R-2STE1LF	
	22	1.094 (27.80)	0.827 (21.00)	609-1917-1-ND	.87	11.45	39.55	609-1917-2-ND	2,000	312.29/M	SFW22R-2STE1LF	
	24	1.173 (29.80)	0.906 (23.00)	609-1920-1-ND	1.24	17.30	59.32	609-1920-2-ND	2,000	469.64/M	SFW24R-2STE1LF	
	26	1.252 (31.80)	0.984 (25.00)	609-1922-1-ND	1.13	15.28	52.40	609-1922-2-ND	2,000	422.12/M	SFW26R-2STE1LF	
	28	1.331 (33.80)	1.063 (27.00)	609-1924-1-ND	1.39	18.74	65.59	609-1924-2-ND	2,000	534.09/M	SFW28R-2STE1LF	
	30	1.409 (35.80)	1.142 (29.00)	609-1927-1-ND	1.39	18.74	65.59	609-1927-2-ND	2,000	534.09/M	SFW30R-2STE1LF	
	Série SFW — Entrée latérale CMS, ZIF, type de contact inférieur avec mécanisme de verrouillage de câble											
	8	4	0.386 (9.80)	0.118 (3.00)	609-1885-1-ND	.74	9.01	30.56	609-1885-2-ND	2,000	235.05/M	SFW4R-3STE1LF
		6	0.465 (11.80)	0.197 (5.00)	609-1891-1-ND	.64	8.09	26.27	609-1891-2-ND	2,000	202.14/M	SFW6R-3STE1LF
		8	0.543 (13.80)	0.276 (7.00)	609-1895-1-ND	.80	10.01	33.81	609-1895-2-ND	2,000	253.59/M	SFW8R-3STE1LF
14		0.780 (19.80)	0.512 (13.00)	609-1904-1-ND	.97	13.43	45.19	609-1904-2-ND	2,000	341.99/M	SFW14R-3STE1LF	
16		0.858 (21.80)	0.591 (15.00)	609-1909-1-ND	.96	11.75</						