



MOSFET (續)



C

圖	封裝	VDS (V)	ID (A)	最大 RDS (開) (mΩ)	Digi-Key 零件編號	絕緣帶包裝 定價			Digi-Key 零件編號	編帶和捲軸封裝		Alpha & Omega Semiconductor 零件編號
						1	25	100		數量	定價	
8	8-DFN	30	20	10	785-1139-1-ND	8.93	168.42	594.29	—	—	—	AON7702
	TO-220	105	40	28	785-1144-5-ND†	9.69	194.61	681.18	—	—	—	AOT404
		75	80	11.5	785-1145-5-ND†	11.05	220.20	770.71	—	—	—	AOT430
		60	85	7.5	785-1146-5-ND†	13.18	263.05	920.68	—	—	—	AOT460
	TO-220	60	70	18	785-1147-5-ND†	8.59	171.40	599.90	—	—	—	AOT462
<b>P-通道</b>												
1	SOT-23	30	4.3	44	785-1001-1-ND	3.83	62.57	205.58	785-1001-2-ND	3,000	867.21/M	AO3401A
	SOT-23	30	2.6	130	785-1003-1-ND	3.74	60.62	198.95	785-1003-2-ND	3,000	841.70/M	AO3403
	SOT-23	30	4.3	48	785-1006-1-ND	4.42	72.69	238.74	785-1006-2-ND	3,000	1011.74/M	AO3407A
	SOT-23	30	2.6	130	785-1007-1-ND	4.85	71.16	229.55	785-1007-2-ND	3,000	824.70/M	AO3409
	SOT-23	20	3	97	785-1008-1-ND	4.76	69.89	225.30	785-1008-2-ND	3,000	807.69/M	AO3413
	SOT-23	20	4	43	785-1010-1-ND	4.34	71.42	235.85	785-1010-2-ND	3,000	1055.10/M	AO3415
	SOT-23	20	3.5	75	785-1013-1-ND	4.51	65.89	212.55	785-1013-2-ND	3,000	765.18/M	AO3419
2	SOT-23	20	2	92	785-1016-1-ND	4.17	60.62	195.55	785-1016-2-ND	3,000	705.67/M	AO3423
	8-SOIC	30	6.1	46	785-1019-1-ND	6.21	105.85	367.54	—	—	—	AO4403
	8-SOIC	30	12	11	785-1022-1-ND	5.61	108.40	382.59	785-1022-2-ND	3,000	1853.44/M	AO4407A
	8-SOIC	30	15	7.5	785-1023-1-ND	9.35	184.92	665.71	785-1023-2-ND	3,000	3451.82/M	AO4409
	8-SOIC	30	9.7	20	785-1024-1-ND	6.97	121.92	418.04	785-1024-2-ND	3,000	1963.97/M	AO4419
	8-SOIC	60	6.2	40	785-1025-1-ND	6.63	128.64	454.01	785-1025-2-ND	3,000	2193.52/M	AO4421
	8-SOIC	38	14	10	785-1026-1-ND	9.44	185.60	668.00	785-1026-2-ND	3,000	3460.32/M	AO4425
	8-SOIC	30	11	14	785-1029-1-ND	6.12	114.95	405.55	785-1029-2-ND	3,000	1853.44/M	AO4433
3	8-SOIC	30	10.5	18	785-1030-1-ND	6.38	112.14	384.38	785-1030-2-ND	3,000	1802.43/M	AO4435
	8-SOIC	30	6.5	46	785-1036-1-ND	6.12	107.21	367.54	785-1036-2-ND	3,000	1725.91/M	AO4459
	6-TSOP	30	3.7	44	785-1068-1-ND	4.51	73.37	242.31	—	—	—	AO6401A
	6-TSOP	30	6	35	785-1070-1-ND	4.68	79.15	274.95	785-1070-2-ND	3,000	1292.31/M	AO6403
	6-TSOP	30	5	52	785-1072-1-ND	4.85	79.75	261.95	785-1072-2-ND	3,000	1105.26/M	AO6405
	6-TSOP	20	5	45	785-1074-1-ND	4.68	77.28	255.23	785-1074-2-ND	3,000	1141.82/M	AO6409
	SC70-3	30	1.2	150	785-1085-1-ND	4.59	75.75	248.68	785-1085-2-ND	3,000	1054.25/M	AO7401
	SC70-3	20	1.4	113	785-1091-1-ND	4.42	72.35	239.08	—	—	—	AO7413
	SC70-6	30	1.6	150	785-1087-1-ND	4.42	72.35	239.08	—	—	—	AO7405
	SC70-6	20	2	100	785-1092-1-ND	5.10	84.08	277.85	—	—	—	AO7415
	6	TO-252 (D-PAK)	30	85	6	785-1101-1-ND	9.69	191.30	688.66	785-1101-2-ND	2,500	3570.84/M
TO-252 (D-PAK)		60	12	115	785-1102-1-ND	6.21	120.73	425.95	785-1102-2-ND	2,500	2057.49/M	AOD407
TO-252 (D-PAK)		60	26	40	785-1103-1-ND	8.25	159.75	563.68	785-1103-2-ND	2,500	2720.64/M	AOD409
TO-252 (D-PAK)		30	25	34	785-1106-1-ND	5.02	88.42	303.01	785-1106-2-ND	2,500	1419.84/M	AOD417
<b>雙N通道</b>												
2	8-SOIC	30	6.9	27	785-1053-1-ND	6.72	116.99	401.21	785-1053-2-ND	3,000	1887.45/M	AO4800B
	8-SOIC	20	9.4	14	785-1056-1-ND	8.08	151.76	535.63	—	—	—	AO4806
	8-SOIC	30	8.5	16	785-1059-1-ND	6.46	124.30	438.70	785-1059-2-ND	3,000	2117.00/M	AO4818B
	8-SOIC	30	6.8	16	785-1060-1-ND	6.63	125.06	441.25	785-1060-2-ND	3,000	2134.01/M	AO4822A
	8-SOIC	60	4.5	56	785-1062-1-ND	6.55	114.61	392.79	785-1062-2-ND	3,000	1844.94/M	AO4828
	8-SOIC	40	6	31	785-1063-1-ND	5.61	108.40	382.59	785-1063-2-ND	3,000	1853.44/M	AO4840
	8-SOIC	30	7.5	22	785-1064-1-ND	6.12	106.36	364.74	785-1064-2-ND	3,000	1717.41/M	AO4842
3	8-SOIC	30	9	15.8	785-1065-1-ND	8.25	158.99	561.13	785-1065-2-ND	3,000	2712.14/M	AO4932
	6-TSOP	30	3.4	60	785-1081-1-ND	5.10	87.23	303.01	—	—	—	AO6800
	6-TSOP	30	3.1	75	785-1082-1-ND	5.10	87.23	303.01	785-1082-2-ND	3,000	1190.28/M	AO6802
10	8-TSSOP	20	7	21	785-1097-1-ND	5.78	109.85	387.69	785-1097-2-ND	3,000	1887.45/M	AO8820
	8-TSSOP	20	6	27	785-1099-1-ND	6.97	118.77	412.43	—	—	—	AO8830
11	6-DFN	30	7.2	20	785-1134-1-ND	7.82	148.19	522.87	—	—	—	AON5802A
<b>雙P通道</b>												
2	8-SOIC	30	8	19	785-1055-1-ND	10.20	200.90	723.10	785-1055-2-ND	3,000	3749.39/M	AO4805
	8-SOIC	30	6	35	785-1057-1-ND	6.97	135.18	476.96	785-1057-2-ND	3,000	2304.05/M	AO4807
	8-SOIC	30	7.1	25	785-1058-1-ND	8.93	172.00	607.04	785-1058-2-ND	3,000	2933.19/M	AO4813
	8-TSSOP	12	7	18	785-1095-1-ND	9.95	190.10	668.17	785-1095-2-ND	3,000	3110.46/M	AO8803
<b>NIP通道</b>												
2	8-SOIC	60	4.5/3.2	56	785-1041-1-ND	7.06	135.86	479.51	785-1041-2-ND	3,000	2321.05/M	AO4612
	8-SOIC	30	8.1/7.1	20	785-1043-1-ND	7.31	140.96	497.37	785-1043-2-ND	3,000	2406.07/M	AO4616
	8-SOIC	20	7.3/5	23	785-1046-1-ND	6.72	116.99	401.21	785-1046-2-ND	3,000	1887.45/M	AO4622
3	6-TSOP	30	3.4/2.3	60	785-1076-1-ND	5.19	85.11	281.08	—	—	—	AO6601
	6-TSOP	30	3.1/2.7	75	785-1077-1-ND	4.42	76.94	263.73	785-1077-2-ND	3,000	1241.30/M	AO6602
	6-TSOP	20	3.4/2.5	60	785-1078-1-ND	4.42	77.71	266.54	785-1078-2-ND	3,000	1249.80/M	AO6604
5	SC70-6	20	0.9/0.6	300	785-1093-1-ND	5.36	87.83	288.47	785-1093-2-ND	3,000	1224.29/M	AO7600
12	TO-252-5	40	8/8	33	785-1117-1-ND	8.25	162.64	585.36	785-1117-2-ND	2,500	3035.22/M	AOD604
13	8-PDIP	30	7.5/6.6	28	785-1140-5-ND†	7.40	143.68	500.43	—	—	—	AOP605
	8-PDIP	60	4.7/3.4	56	785-1141-5-ND†	7.14	138.41	482.06	—	—	—	AOP607
	8-PDIP	60	4.7/3.5	60	785-1142-5-ND†	7.14	137.73	479.77	—	—	—	AOP609
	8-PDIP	30	7.7/6.2	24	785-1143-5-ND†	7.31	142.32	495.84	—	—	—	AOP610

† 散裝

Digi-Reel® 大多數SMT削減零件都可以在Digi-Reel®上獲得。要獲得Digi-Reel零件編號，請將1-ND更改為6-ND或將CT-ND更改為DKR-ND。詳情請參閱第2頁的Digi-Key®服務。

對金額超過HK\$750的訂單提供免費送貨服務！全部價格均以港幣計算。

1698 (HK2011-ZH)

www.digikey.hk — 電話：(852) 3104 0500 — 傳真：(852) 3104 0686