

STMicroelectronics		Digi-Reel® (Cont.)		AMPLIFIERS AND LINEAR RoHS Compliant Parts Available		
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
TSH3441DT	497-4988-1-ND	340MHz Single Supply Triple Video Buffer	8-SOIC	2.37	2.04	1.66
TSH3441DT	497-4988-2-ND	340MHz Single Supply Triple Video Buffer	8-SOIC	2286.28/2,500		
TSH3451DT	497-8530-1-ND	36MHz Single Supply Triple Video Buffer*	14-SOIC	1.35	1.20	.96
TSH3451DT	497-8530-2-ND	36MHz Single Supply Triple Video Buffer*	14-SOIC	1235.23/2,500		
TSH3501DT	497-4465-1-ND	550MHz LM Current Feedback Amp	8-SOIC	2.26	1.94	1.59
TSH3501DT	497-4465-2-ND	550MHz LM Current Feedback Amp	8-SOIC	2332.33/2,500		
TSH3501LT	497-4466-1-ND	550MHz LM Current Feedback Amp	SOT-23-5	2.26	1.94	1.59
TSH3501LT	497-4466-2-ND	550MHz LM Current Feedback Amp	SOT-23-5	2798.80/3,000		
TSV321RAILT	497-7687-1-ND	In/Out, R/R, Low Power Op Amp*	SOT-23-5	.62	.54	.43
TSV321RAILT	497-7687-2-ND	In/Out, R/R, Low Power Op Amp*	SOT-23-5	617.42/3,000		
TSV321RIILT	497-8164-1-ND	In/Out, R/R, Low Power Op Amp*	SOT-23-5	.74	.65	.51
TSV321RIILT	497-8164-2-ND	In/Out, R/R, Low Power Op Amp*	SOT-23-5	737.54/3,000		
TSV321RIYLT	497-10277-1-ND	In/Out, R/R, Low Power Op Amp*	SOT-23-5	.58	.51	.39
TSV321RIYLT	497-10277-2-ND	In/Out, R/R, Low Power Op Amp*	SOT-23-5	624.62/3,000		
TSV3241DT	497-8198-1-ND	GP, In/Out, R/R, Low Power Op Amp*	14-SOIC	.77	.69	.55
TSV3241DT	497-8198-2-ND	GP, In/Out, R/R, Low Power Op Amp*	14-SOIC	706.71/2,500		
TSV3241PT	497-5201-1-ND	GP, In/Out, R/R, Low Power Op Amp*	14-TSSOP	.77	.67	.53
TSV3241PT	497-5201-2-ND	GP, In/Out, R/R, Low Power Op Amp*	14-TSSOP	632.63/2,500		
TSV3241YDT	497-10278-1-ND	GP, In/Out, R/R, Low Power Op Amp*	14-SOIC	.78	.68	.54
TSV3241YDT	497-10278-2-ND	GP, In/Out, R/R, Low Power Op Amp*	14-SOIC	640.64/2,500		
TSV3241YPT	497-10279-1-ND	GP, In/Out, R/R, Low Power Op Amp*	14-TSSOP	.70	.62	.48
TSV3241YPT	497-10279-2-ND	GP, In/Out, R/R, Low Power Op Amp*	14-TSSOP	640.64/2,500		
TSV358A1DT	497-5827-1-ND	GP, In/Out, R/R, Low Power Op Amp*	8-SOIC	1.18	1.06	.84
TSV358A1DT	497-5827-2-ND	GP, In/Out, R/R, Low Power Op Amp*	8-SOIC	1087.09/2,500		
TSV3581DT	497-4772-1-ND	GP, In/Out, R/R, Low Power Op Amp	8-SOIC	.77	.67	.53
TSV3581DT	497-4772-2-ND	GP, In/Out, R/R, Low Power Op Amp	8-SOIC	632.63/2,500		
TSV3581PT	497-4771-1-ND	GP, In/Out, R/R, Low Power Op Amp	8-TSSOP	.62	.54	.43
TSV3581YDT	497-10182-1-ND	GP, In/Out, R/R, Low Power Op Amp	8-SOIC	.59	.52	.41
TSV3581YDT	497-10182-2-ND	GP, In/Out, R/R, Low Power Op Amp	8-SOIC	488.49/2,500		
TSV3581YPT	497-10280-1-ND	GP, In/Out, R/R, Low Power Op Amp	8-TSSOP	.59	.52	.41
TSV3581YPT	497-10280-2-ND	GP, In/Out, R/R, Low Power Op Amp	8-TSSOP	781.58/4,000		
TSV6111CT	497-10351-1-ND	Single, I/O, R/R, 120kHz Op Amp*	SC70-5	.74	.65	.50
TSV6111CT	497-10351-2-ND	Single, I/O, R/R, 120kHz Op Amp*	SC70-5	804.80/3,000		
TSV6111LT	497-10350-1-ND	Single, I/O, R/R, 120kHz Op Amp*	SOT23-5	.74	.64	.51
TSV6111LT	497-10350-2-ND	Single, I/O, R/R, 120kHz Op Amp*	SOT23-5	732.73/3,000		
TSV6121DT	497-10349-1-ND	Dual, I/O, R/R, 120kHz Op Amp*	8-SOIC	.94	.84	.66
TSV6121DT	497-10349-2-ND	Dual, I/O, R/R, 120kHz Op Amp*	8-SOIC	940.94/2,500		
TSV6121ST	497-10348-1-ND	Dual, I/O, R/R, 120kHz Op Amp*	8-MSOP	1.03	.92	.73
TSV6121ST	497-10348-2-ND	Dual, I/O, R/R, 120kHz Op Amp*	8-MSOP	1649.65/4,000		
TSV620A1CT	497-10157-1-ND	Single, I/O, R/R, 420kHz Op Amp*	SC70-6	1.03	.92	.73
TSV620A1CT	497-10157-2-ND	Single, I/O, R/R, 420kHz Op Amp*	SC70-6	1237.24/3,000		
TSV620A1ILT	497-10158-1-ND	Single, I/O, R/R, 420kHz Op Amp*	SOT23-6	1.03	.92	.73
TSV620A1ILT	497-10158-2-ND	Single, I/O, R/R, 420kHz Op Amp*	SOT23-6	1237.24/3,000		
TSV620A1LT	497-10159-1-ND	Single, I/O, R/R, 420kHz Op Amp*	SC70-6	.77	.68	.54
TSV620A1LT	497-10159-2-ND	Single, I/O, R/R, 420kHz Op Amp*	SC70-6	917.72/3,000		
TSV620A1LT	497-10160-1-ND	Single, I/O, R/R, 420kHz Op Amp*	SOT23-6	.77	.68	.54
TSV620A1LT	497-10160-2-ND	Single, I/O, R/R, 420kHz Op Amp*	SOT23-6	917.72/3,000		
TSV621A1CT	497-8533-1-ND	Single, I/O, R/R, 420kHz Op Amp*	SC70-5	1.12	1.01	.80
TSV621A1CT	497-8533-2-ND	Single, I/O, R/R, 420kHz Op Amp*	SC70-5	1237.24/3,000		
TSV621A1ILT	497-8534-1-ND	Single, I/O, R/R, 420kHz Op Amp*	SOT-23-5	1.12	1.01	.80
TSV621A1ILT	497-8534-2-ND	Single, I/O, R/R, 420kHz Op Amp*	SOT-23-5	1237.24/3,000		
TSV621A1LT	497-8535-1-ND	Single, I/O, R/R, 420kHz Op Amp*	SC70-5	.77	.69	.55
TSV621A1LT	497-8535-2-ND	Single, I/O, R/R, 420kHz Op Amp*	SC70-5	848.05/3,000		
TSV6211LT	497-8536-1-ND	Single, I/O, R/R, 420kHz Op Amp*	SOT-23-5	.77	.69	.55
TSV6211LT	497-8536-2-ND	Single, I/O, R/R, 420kHz Op Amp*	SOT-23-5	848.05/3,000		
TSV6221LT	497-10059-1-ND	Dual, I/O, R/R, 420kHz Op Amp*	SOT-23-8	.91	.81	.64
TSV6221LT	497-10059-2-ND	Dual, I/O, R/R, 420kHz Op Amp*	SOT-23-8	1095.49/3,000		
TSV625A1PT	497-10161-1-ND	Quad, I/O, R/R, 420kHz Op Amp*	16-TSSOP	1.80	1.63	1.31
TSV625A1PT	497-10161-2-ND	Quad, I/O, R/R, 420kHz Op Amp*	16-TSSOP	1959.96/2,500		
TSV6251PT	497-10162-1-ND	Quad, I/O, R/R, 420kHz Op Amp*	16-TSSOP	1.28	1.16	.93
TSV6251PT	497-10162-2-ND	Quad, I/O, R/R, 420kHz Op Amp*	16-TSSOP	1391.39/2,500		
TSV630A1CT	497-8537-1-ND	Single, I/O, R/R, 880kHz Op Amp*	SC70-6	1.12	1.01	.80
TSV630A1CT	497-8537-2-ND	Single, I/O, R/R, 880kHz Op Amp*	SC70-6	1237.24/3,000		
TSV630A1ILT	497-8538-1-ND	Single, I/O, R/R, 880kHz Op Amp*	SOT-23-6	.96	.86	.69
TSV630A1ILT	497-8538-2-ND	Single, I/O, R/R, 880kHz Op Amp*	SOT-23-6	1059.46/3,000		
TSV6311LT	497-8544-1-ND	Single, I/O, R/R, 880kHz Op Amp*	SOT-23-5	.70	.63	.50
TSV6311LT	497-8544-2-ND	Single, I/O, R/R, 880kHz Op Amp*	SOT-23-5	848.05/3,000		
TSV632A1LT	497-10060-1-ND	Dual, I/O, R/R, 420kHz Op Amp*	SOT-23-8	1.23	1.10	.87
TSV632A1LT	497-10060-2-ND	Dual, I/O, R/R, 420kHz Op Amp*	SOT-23-8	1482.28/3,000		
TSV6321LT	497-10061-1-ND	Dual, I/O, R/R, 420kHz Op Amp*	SOT-23-8	.91	.81	.64
TSV6321LT	497-10061-2-ND	Dual, I/O, R/R, 420kHz Op Amp*	SOT-23-8	1095.49/3,000		
TSV91A1AIDT	497-5828-1-ND	Single, I/O, R/R, 8MHz Op Amp*	8-SOIC	1.32	1.14	.93
TSV91A1AIDT	497-5828-2-ND	Single, I/O, R/R, 8MHz Op Amp*	8-SOIC	1365.36/2,500		
TSV91A1AILT	497-5998-1-ND	Single, I/O, R/R, 8MHz Op Amp*	SOT-23-5	1.51	1.35	1.08
TSV91A1AILT	497-5998-2-ND	Single, I/O, R/R, 8MHz Op Amp*	8-SOIC	1.04 .94 .74		
TSV9111DT	497-5999-1-ND	Single, I/O, R/R, 8MHz Op Amp*	8-SOIC	992.99/2,500		
TSV9111DT	497-6000-1-ND	Single, I/O, R/R, 20MHz Op Amp*	SOT-23-5	1.28	1.15	.91
TSV9111DT	497-6000-2-ND	Single, I/O, R/R, 20MHz Op Amp*	SOT-23-5	1412.61/3,000		
TSV912A1DT	497-5829-1-ND	Dual, I/O, R/R, 8MHz Op Amp*	8-SOIC	1.86	1.59	1.30
TSV912A1DT	497-5829-2-ND	Dual, I/O, R/R, 8MHz Op Amp*	8-SOIC	1789.79/2,500		
TSV912A1ST	497-5830-1-ND	Dual, I/O, R/R, 8MHz Op Amp*	8-MSOP	1.51	1.30	1.06
TSV912A1ST	497-5830-2-ND	Dual, I/O, R/R, 8MHz Op Amp*	8-MSOP	2501.70/4,000		
TSV9121DT	497-8165-1-ND	Dual, I/O, R/R, 8MHz Op Amp*	8-SOIC	1.69	1.46	1.19
TSV9121DT	497-8165-2-ND	Dual, I/O, R/R, 8MHz Op Amp*	8-SOIC	1631.63/2,500		
TSV9121ST	497-5771-1-ND	Dual, I/O, R/R, 8MHz Op Amp*	8-MSOP	1.68	1.45	1.18
TSV9121ST	497-5771-2-ND	Dual, I/O, R/R, 8MHz Op Amp*	8-MSOP	2777.17/4,000		
TSV9121YST	497-10385-1-ND	Quad, I/O, R/R, 8MHz Op Amp*	8-MSOP	.97	.87	.69
TSV9121YST	497-10385-2-ND	Quad, I/O, R/R, 8MHz Op Amp*	8-MSOP	1556.76/4,000		
TSV914A1DT	497-6127-1-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-SOIC	1.72	1.48	1.21
TSV914A1DT	497-6127-2-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-SOIC	1661.66/2,500		
TSV914A1PT	497-5831-1-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-TSSOP	2.21	1.90	1.55
TSV914A1PT	497-5831-2-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-TSSOP	2130.13/2,500		
TSV914A1YDT	497-10384-1-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-SOIC	1.28	1.16	.93
TSV914A1YDT	497-10384-2-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-SOIC	1391.39/2,500		
TSV914A1YPT	497-10383-1-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-TSSOP	1.28	1.16	.93
TSV914A1YPT	497-10383-2-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-TSSOP	1391.39/2,500		
TSV9141DT	497-6128-1-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-SOIC	1.71	1.47	1.20
TSV9141DT	497-6128-2-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-SOIC	1645.84/2,500		

STMicroelectronics		Digi-Reel® (Cont.)		AMPLIFIERS AND LINEAR RoHS Compliant Parts Available		
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
TSV9141PT	497-5832-1-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-TSSOP	2.03	1.75	1.43
TSV9141PT	497-5832-2-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-TSSOP	1959.96/2,500		
TSV9141YPT	497-10382-1-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-TSSOP	1.44	1.29	1.03
TSV9141YPT	497-10382-2-ND	Quad, I/O, R/R, 8MHz Op Amp*	14-TSSOP	1325.32/2,500		
TSV991A1ILT	497-5833-1-ND	Single, I/O, R/R, 20MHz Op Amp*	SOT-23-5	1.32	1.14	.93
TSV991A1ILT	497-5833-2-ND	Single, I/O, R/R, 20MHz Op Amp*	SOT-23-5	1638.44/3,000		
TSV9911LT	497-6001-1-ND	Single, I/O, R/R, 20MHz Op Amp*	SOT-23-5	1.28	1.09	.93
TSV9911YDT	497-10347-1-ND	Single, I/O, R/R, 20MHz Op Amp*	8-SOIC	.78	.68	.53
TSV9911YDT	497-10347-2-ND	Single, I/O, R/R, 20MHz Op Amp*	8-SOIC	702.70/2,500		
TSV9911YLT	497-10281-1-ND	Single, I/O, R/R, 20MHz Op Amp*	SOT-23-5	.72	.64	.49
TSV9911YLT	497-10281-2-ND	Single, I/O, R/R, 20MHz Op Amp*	SOT-23-5	787.99/3,000		
TSV992A1DT	497-5834-1-ND	Dual, I/O, R/R, 20MHz Op Amp*	8-SOIC	1.86	1.59	1.30
TSV992A1DT	497-5834-2-ND	Dual, I/O, R/R, 20MHz Op Amp*	8-SOIC	1789.79/2,500		
TSV992A1ST	497-5835-1-ND	Dual, I/O, R/R, 20MHz Op Amp*	8-MSOP	1.51	1.30	1.06
TSV992A1ST	497-5835-2-ND	Dual, I/O, R/R, 20MHz Op Amp*	8-MSOP	2501.70/4,000		
TSV9921DT	497-6002-1-ND	Dual, I/O, R/R, 20MHz Op Amp*	8-SOIC	1.49	1.28	1.05
TSV9921DT	497-6002-2-ND	Dual, I/O, R/R, 20MHz Op Amp*	8-SOIC	1759.76/2,500		
TSV9921ST	497-5836-1-ND	Dual, I/O, R/R, 20MHz Op Amp*	8-MSOP	1.71	1.47	1.20
TSV9921ST	497-5836-2-ND	Dual, I/O, R/R, 20MHz Op Amp*	8-MSOP	2633.03/4,000		
TSV9921YDT	497-10359-1-ND	Dual, I/O, R/R, 20MHz Op Amp*	8-SOIC	.74	.66	.52
TSV9921YDT	497-10359-2-ND	Dual, I/O, R/R, 20MHz Op Amp*	8-SOIC	736.74/2,500		
TSV994A1DT	497-6125-1-ND	Quad, I/O, R/R, 20MHz Op Amp*	14-SOIC	1.63	1.40	1.15
TSV994A1DT	497-6125-2-ND	Quad, I/O, R/R, 20MHz Op Amp*	14-SOIC	1687.69/2,500		
TSV994A1PT	497-5837-1-ND	Quad, I/O, R/R, 20MHz Op Amp*	14-TSSOP	1.99	1.71	1.40
TSV994A1PT	497-5837-2-ND	Quad, I/O, R/R, 20MHz Op Amp*	14-TSSOP	186 .59 1.30		
TSV994A1YPT	497-6126-1-ND	Quad, I/O, R/R, 20MHz Op Amp*	14-SOIC	1.79	1.59	1.30
TSV994A1YPT	497-6126-2-ND	Quad, I/O, R/R, 20MHz Op Amp*	14-SOIC	1789.79/2,500		
TSV9941DT	497-6003-1-ND	Quad, I/O, R/R, 20MHz Op Amp*	SOT-23-5	2.25	1.99	1.69
TSV9941DT	497-6003-2-ND	Quad, I/O, R/R, 20MHz Op Amp*	14-SOIC	121 .107 .85		
TSV9941YDT	4					