



C

図	V <sub>oss</sub> (V)	ID (A)	R <sub>ds(on)</sub> (Ω)	Digi-Key 品番	価格 1 10 100	テープおよび リール毎 価格	STMicro 品番
<b>Nチャンネル</b>							
<b>TO-220</b>							
24	120	.0022	497-7519-5-ND	370 3304 27092	—	STP300NH02L	
25	80	.0049	497-9093-5-ND	150 1355 10885	—	STP95N2LH5	
30	22	.05	497-7516-5-ND	99 882 6966	—	STP22NF03L	
30	27	.020	497-9095-5-ND	87 764 6037	—	STP27N3LH5	
30	40	.022	497-3187-5-ND	130 1147 9066	—	STP40NF03L	
30	80	.0054	497-8451-5-ND	162 1460 11738	—	STP85N3LH5	
30	80	.0028	497-9097-5-ND	261 2327 19076	—	STP150N3LLH6	
30	80	.0042	497-10307-5-ND	153 1380 11088	—	STP95N3LLH6	
30	90	.0065	497-7535-5-ND	262 2363 18988	—	STP90NF03L	
30	120	.0037	497-6738-5-ND	260 2318 19002	—	STP200NF03	
40	80	.0065	497-7534-5-ND	134 1209 9711	—	STP90N4F3	
40	80	.0065	497-7536-5-ND	211 1911 15352	—	STP95N4F3	
40	80	.0070	497-10075-5-ND	287 2563 21019	—	STP150NF04	
40	120	.0037	497-3524-5-ND	319 2843 23313	—	STP200NF04	
40	120	.0038	497-4819-5-ND	263 2347 19242	—	STP200NF04L	
40	120	.0044	497-8789-5-ND	398 3554 29142	—	STP200N4F3	
40	120	.0046	497-7497-5-ND	292 2607 21371	—	STP100NF04	
55	80	.005	497-5898-5-ND	260 2318 19002	—	STP80NF5L-06	
55	80	.0065	497-2774-5-ND	236 2138 17180	—	STP80NF55-06	
55	80	.008	497-3202-5-ND	220 1991 16002	—	STP80NF55-08	
55	80	.008	497-4370-5-ND	230 2078 16693	—	STP140NF55	
55	80	.008	497-6744-5-ND	220 1991 16002	—	STP85NF55	
55	80	.008	497-7023-5-ND	292 2607 21371	—	STP141NF55	
55	80	.008	497-7532-5-ND	265 2369 19427	—	STP85NF55L	
55	80	8.5	497-7528-5-ND	191 1732 13919	—	STP60NF55F3	
55	120	.0037	497-8810-5-ND	610 5450 44683	—	STP190NF55F3	
55	120	.0038	497-7512-5-ND	451 4028 33027	—	STP180NF55F3	
55	120	.0038	497-7513-5-ND	477 4264 34961	—	STP185NF55F3	
55	120	.005	497-6117-5-ND	358 3200 26236	—	STP150NF55	
60	16	.1	497-2766-5-ND	76 663 5117	—	STP16NF06	
60	16	.09	497-2765-5-ND	83 736 5816	—	STP16NF06L	
60	20	.07	497-4374-5-ND	105 929 7341	—	STP20NF06	
60	20	.07	497-4375-5-ND	105 929 7341	—	STP20NF06L	
60	30	.04	497-3186-5-ND	99 882 6966	—	STP36NF06	
60	30	.04	497-7522-5-ND	133 1175 9287	—	STP36NF06L	
60	38	.028	497-3189-5-ND	107 949 7497	—	STP45NF06	
60	50	.018	497-2777-5-ND	115 1015 8027	—	STP55NF06	
60	55	.018	497-6742-5-ND	134 1186 9376	—	STP55NF06L	
60	60	.016	497-2779-5-ND	145 1314 10560	—	STP60NF06	
60	60	.014	497-5895-5-ND	146 1317 10581	—	STP60NF06L	
60	60	.014	497-7529-5-ND	142 1254 9906	—	STP65NF06	
60	80	.010	497-3201-5-ND	254 2292 18419	—	STP80NF06	
60	120	.0039	497-9096-5-ND	432 3861 31658	—	STP200NF63	
75	80	.011	497-2788-5-ND	206 1857 14926	—	STP75NF75	
75	120	.004	497-7508-5-ND	412 3673 30122	—	STP160NF75F3	
75	120	.0065	497-5894-5-ND	264 2388 19191	—	STP140NF75	

図	V <sub>oss</sub> (V)	ID (A)	R <sub>ds(on)</sub> (Ω)	Digi-Key 品番	価格 1 10 100	テープおよび リール毎 価格	STMicro 品番
100	15	.13	497-7506-5-ND	79 705 5572	—	STP14NF10	
100	26	.060	497-3185-5-ND	122 1083 8558	—	STP24NF10	
100	35	.045	497-7520-5-ND	122 1083 8558	—	STP30NF10	
100	40	.033	497-6741-5-ND	206 1857 14926	—	STP40NF10L	
100	40	.035	497-2645-5-ND	136 1206 9531	—	STP35NF10	
100	50	.028	497-3188-5-ND	185 1673 13443	—	STP40NF10	
100	65	.0195	497-8812-5-ND	153 1380 11088	—	STP70N10F4	
100	80	.023	497-4384-5-ND	252 2272 18257	—	STP80NF10	
100	80	.015	497-2642-5-ND	262 2363 18988	—	STP80NF10	
100	110	.0105	497-4118-5-ND	255 2274 18650	—	STP120NF10	
120	40	.032	497-4381-5-ND	169 1526 12266	—	STP40NF12	
120	80	.018	497-6743-5-ND	267 2413 19394	—	STP80NF12	
200	9	.40	497-2757-5-ND	99 882 6966	—	IRF630	
200	15	.16	497-7514-5-ND	162 1460 11738	—	STP19NF20	
200	18	.125	497-5812-5-ND	180 1620 13017	—	STP20NF20	
200	30	.075	497-5825-5-ND	238 2151 17282	—	STP30NF20	
200	40	.045	497-5806-5-ND	293 2617 21463	—	STP40NF20	
200	75	.034	497-5958-5-ND	336 2999 24590	—	STP75NF20	
250	13	.235	497-7509-5-ND	150 1355 10885	—	STP16NF25	
250	17	.165	497-7511-5-ND	191 1726 13870	—	STP17NF25	
250	22	.15	497-6740-5-ND	180 1625 13058	—	STP22NS25Z	
250	45	.069	497-7526-5-ND	358 3200 26236	—	STP50NF25	
300	9	.4	497-7502-5-ND	176 1592 12794	—	STP12NK30Z	
300	30	.090	497-7521-5-ND	569 5117 42077	—	STP30NM30N	
400	5.4	1	497-3200-5-ND	141 1274 10235	—	STP7NK40Z	
400	10	.55	497-7500-5-ND	144 1299 10440	—	STP11NK40Z	
500	3	2.7	497-3190-5-ND	71 635 5022	—	STP4NK50Z	
500	3	2.7	497-5131-5-ND	122 1078 8514	—	STP4NK50ZD	
500	4.4	1.5	497-3195-5-ND	107 949 7497	—	STP5NK50Z	
500	5.6	1.2	497-4385-5-ND	107 940 7430	—	STP6NK50Z	
500	7.2	.85	497-3203-5-ND	206 1857 14926	—	STP9NK50Z	
500	11	.48	497-7504-5-ND	227 2031 16648	—	STP13NK50Z	
500	12	.35	497-2666-5-ND	372 3317 27198	—	STP12NM50	
500	14	.38	497-4526-5-ND	319 2843 23313	—	STP14NK50Z	
500	17	.27	497-7515-5-ND	424 3791 31084	—	STP20NK50Z	
500	20	.25	497-2663-5-ND	491 4385 35950	—	STP20NM50	
500	20	.25	497-6739-5-ND	584 5212 42740	—	STP20NM50FD	
500	22	.14	497-4672-5-ND	628 5652 46469	—	STP25NM50N	
520	4.4	1.22	497-5953-5-ND	100 886 7002	—	STP5NK52ZD	
525	6.2	.98	497-9094-5-ND	211 1911 15352	—	STP7NS2K3	
550	5	.78	497-7531-5-ND	208 1885 15149	—	STP7NM50N	
550	7.5	.56	497-7537-5-ND	181 1629 13091	—	STP9NM50N	
550	12	.32	497-7505-5-ND	256 2289 18768	—	STP13NM50N	
550	15	.26	497-7510-5-ND	310 2769 22703	—	STP16NM50N	
550	27	.115	497-8790-5-ND	924 8316 68375	—	STP30NM50N	

◆RoHS準拠 †リール毎の品番は、「1-ND」を「2-ND」に変更してください。‡カットテープ (続き)

Digi-Reel® たいていのSMTカットダウン部品はDigi-Reel®でご利用いただけます。Digi-Reelの品番は、1-NDを6-NDに、またはCT-NDをDKR-NDに変更してください。追加情報は、2ページのDigi-Key® サービスをご覧ください。

7,500円以上のご注文の送料は無料! (日本円でのご注文に限りです。) 価格は全て日本円で関税込み

www.digikey.jp — 電話: 0120-855-960 — Fax: 0120-855-961

(JP2011-JA) 1575