

最大 ESR (Ω)	負荷 キャパシタンス	周波数 (MHz)	Digi-Key 品番	カットテープ 単価				Digi-Key 品番	リール毎 価格 1,000個	ECS 品番
				1	10	100	500			
80	9pF	16.000000	XC1611CT-ND	149	134	112	89	XC1611TR-ND	82764	ECS-160-9-42-CKM-TR
60	13pF	24.000000	XC1613CT-ND	149	134	112	89	XC1613TR-ND	82764	ECS-240-13-42-CKM-TR
60	13pF	26.000000	XC1614CT-ND	149	134	112	89	XC1614TR-ND	82764	ECS-260-13-42-CKM-TR
60	13pF	32.000000	XC1615CT-ND	157	141	118	94	XC1615TR-ND	87277	ECS-320-13-42-CKM-TR
ECX-32. -20°C~70°C. ±50ppm. 3.2 x 2.5 x 0.70mm										
100	20pF	16.000000	XC1137CT-ND	322	290	242	193	XC1137TR-ND	179042	ECS-160-20-33-TR
100	20pF	18.432000	XC1138CT-ND	322	290	242	193	XC1138TR-ND	179042	ECS-184-20-33-TR
100	20pF	19.660800	XC1139CT-ND	322	290	242	193	XC1139TR-ND	179042	ECS-196-20-33-TR
100	20pF	20.000000	XC1140CT-ND	322	290	242	193	XC1140TR-ND	179042	ECS-200-20-33-TR
100	20pF	24.000000	XC1141CT-ND	322	290	242	193	XC1141TR-ND	179042	ECS-240-20-33-TR
100	20pF	25.000000	XC1142CT-ND	322	290	242	193	XC1142TR-ND	179042	ECS-250-20-33-TR
100	20pF	27.000000	XC1143CT-ND	322	290	242	193	XC1143TR-ND	179042	ECS-270-20-33-TR
50	シリーズ	30.000000	XC1145CT-ND	322	290	242	193	XC1145TR-ND	179042	ECS-300-S-33-TR
50	20pF	30.000000	XC1144CT-ND	322	290	242	193	XC1144TR-ND	179042	ECS-300-20-33-TR
50	シリーズ	32.000000	XC1147CT-ND	322	290	242	193	XC1147TR-ND	179042	ECS-320-S-33-TR
50	20pF	32.000000	XC1146CT-ND	322	290	242	193	XC1146TR-ND	179042	ECS-320-20-33-TR
50	20pF	36.000000	XC1148CT-ND	322	290	242	193	XC1148TR-ND	179042	ECS-360-20-33-TR
50	20pF	40.000000	XC1150CT-ND	322	290	242	193	XC1150TR-ND	179042	ECS-400-20-33-TR
ECX-2236. Bluetooth™およびZigbeeアプリケーション用. ±10±10. -20°C~70°C. 2.5 x 2.0 x 0.55mm										
100	8pF	16.000000	XC1552CT-ND	311	280	234	187	XC1552TR-ND	173019	ECS-160-8-36CKM
100	8pF	18.432000	XC1553CT-ND	311	280	234	187	XC1553TR-ND	173019	ECS-184-8-36CKM
100	8pF	19.200000	XC1554CT-ND	311	280	234	187	XC1554TR-ND	173019	ECS-192-8-36CKM
100	8pF	20.000000	XC1556CT-ND	311	280	234	187	XC1556TR-ND	173019	ECS-200-8-36CKM
100	8pF	24.000000	XC1557CT-ND	311	280	234	187	XC1557TR-ND	173019	ECS-240-8-36CKM
100	8pF	25.000000	XC1559CT-ND	311	280	234	187	XC1559TR-ND	173019	ECS-250-8-36CKM
100	8pF	26.000000	XC1560CT-ND	311	280	234	187	XC1560TR-ND	173019	ECS-260-8-36CKM
100	8pF	27.000000	XC1561CT-ND	311	280	234	187	XC1561TR-ND	173019	ECS-270-8-36CKM
100	8pF	30.000000	XC1562CT-ND	311	280	234	187	XC1562TR-ND	173019	ECS-300-8-36CKM
100	8pF	32.000000	XC1563CT-ND	311	280	234	187	XC1563TR-ND	173019	ECS-320-8-36CKM
100	8pF	48.000000	XC1566CT-ND	311	280	234	187	XC1566TR-ND	173019	ECS-480-8-36CKM
100	8pF	80.000000	XC1567CT-ND	485	436	364	291	XC1567TR-ND	269321	ECS-800-8-36CKM
ECX-1637. Bluetooth™およびZigbeeアプリケーション用. ±10±10. -20°C~70°C. 2.0 x 1.6 x 0.45mm										
100	8pF	24.000000	XC1543CT-ND	349	314	262	210	XC1543TR-ND	194048	ECS-240-8-37CKM
100	8pF	26.000000	XC1545CT-ND	349	314	262	210	XC1545TR-ND	194048	ECS-260-8-37CKM
100	8pF	27.000000	XC1546CT-ND	349	314	262	210	XC1546TR-ND	194048	ECS-270-8-37CKM
100	8pF	32.000000	XC1547CT-ND	349	314	262	210	XC1547TR-ND	194048	ECS-320-8-37CKM

D

32.768kHz水晶発振子および発振器

図1: 32.768kHz水晶発振子 (Top View, Side View, Bottom View)

図2: 32.768kHz水晶発振子 (Top View, Side View, Bottom View)

図3: 32.768kHz水晶発振子 (Top View, Side View, Bottom View)

図4: 32.768kHz水晶発振子 (Top View, Side View, Bottom View)

図5: 32.768kHz水晶発振子 (Top View, Side View, Bottom View)

図6: 32.768kHz水晶発振子 (Top View, Side View, Bottom View)

メーカー 品番	L	D	LS
ECS-3X8	8.2	3.1	1.1
ECS-3X8X	8.2	3.1	1.1
ECS-327-12.5-13	6.2	2.1	0.7
ECS-327-12.5-13X	6.2	2.1	0.7
ECS-327-8-14	5.1	1.5	0.45
ECS-327-8-14X	5.1	1.5	0.45

図	ESR 最大 (Ω)	負荷容量 (pF)	Digi-Key 品番	カットテープ 単価				リール毎		ECS 品番
				1	10	100	Digi-Key 品番	数量	価格	
面実装水晶振動子										
1	50k	6.0	XC746CT-ND	97	81	65	XC746TR-ND	3,000	60182/M	ECS-.327-6-17-TR
	50k	6.0	XC1307CT-ND◆	118	103	71	XC1307TR-ND◆	3,000	52659/M	ECS-.327-6-17X-TR
	50k	12.5	XC488CT-ND	97	81	65	XC488TR-ND	3,000	60182/M	ECS-.327-12.5-17-TR
	50k	12.5	XC1195CT-ND◆	118	103	71	XC1195TR-ND◆	3,000	52659/M	ECS-.327-12.5-17X-TR
	65k	7.0	XC1657CT-ND◆	81	73	61	XC1657TR-ND◆	3,000	45128/M	ECS-.327-7-38-TR
2	65k	12.5	XC1616CT-ND◆	81	73	61	XC1616TR-ND◆	3,000	45128/M	ECS-.327-12.5-38
	70k	12.5	XC1658CT-ND◆	87	78	65	XC1658TR-ND◆	3,000	48106/M	ECS-.327-12.5-39-TR
3	70k	7.0	XC1656CT-ND◆	114	102	85	XC1656TR-ND◆	3,000	63179/M	ECS-.327-7-34B-TR
	70k	12.5	XC1617CT-ND◆	114	102	85	XC1617TR-ND◆	3,000	63179/M	ECS-.327-12.5-34B
面実装発振器 — RoHS準拠										
5	—	—	XC777CT-ND	608	498	442	XC777TR-ND	2,000	368615/M	ECS-327SMO-TR
	—	—	XC1489CT-ND	647	582	485	XC1489TR-ND	1,000	359576	ECS-327KO-TR
シリンダタイプ水晶振動子										
6	35k	12.5	X801-ND†	27	24	20	—	—	—	ECS-3X8
	35k	12.5	X1123-ND†◆	27	24	20	—	—	—	ECS-3X8X
	35k	12.5	X802-ND†	27	24	20	—	—	—	ECS-.327-12.5-13
	35k	12.5	X1124-ND†◆	27	24	20	—	—	—	ECS-.327-12.5-13X
	40k	8.0	X803-ND†	237	213	171	—	—	—	ECS-.327-8-14
	40k	8.0	X1125-ND†◆	57	51	41	—	—	—	ECS-.327-8-14X

◆ RoHS準拠 † ハルク

Digi-Reel® たいていのSMTカットダウン部品は Digi-Reel® でご利用いただけます。Digi-Reelの品番は、1-NDを6-NDに、またはCT-NDをDKR-NDに変更してください。追加情報は、2ページの Digi-Key® サービスをご覧ください。

7,500円以上のご注文の送料は無料! (日本円でのご注文に限ります。) 価格は全て日本円で関税込み

www.digikey.jp — 電話: 0120-855-960 — Fax: 0120-855-961

(JP2011-JA) 1713