



图	V _{DSS} (V)	I _D (A)	R _{DS(on)} (Ω)	Digi-Key 零件编号	价格	1	10	100	带卷† 价格	STMicro. 零件编号
200	75	0.034	497-5320-5-ND	5.78	50.31	374.61	—	—	—	STW75M20
200	75	0.034	497-5959-5-ND	6.11	56.92	442.73	—	—	—	STW75M20
250	52	0.045	497-4428-5-ND	7.70	71.73	557.87	—	—	—	STW52M25Z
500	14	0.34	497-3260-5-ND	6.70	62.37	485.10	—	—	—	STW15MKS0Z
500	14	0.38	497-3258-5-ND	4.47	41.58	323.40	—	—	—	STW14MKS0Z
500	17	0.27	497-3261-5-ND	4.53	42.50	340.03	—	—	—	STW20MKS0Z
500	18	0.19	497-4806-5-ND	5.83	50.67	377.31	—	—	—	STW18MKS0Z
500	20	0.25	497-2717-5-ND	10.01	96.25	731.50	—	—	—	STW20MKS0Z
500	22	0.14	497-4675-5-ND	11.61	111.65	848.54	—	—	—	STW25MKS0Z
500	29	0.13	497-5768-ND	15.22	146.30	1111.88	—	—	—	STW29MKS0Z
500	30	0.120	497-3264-5-ND	16.02	154.00	1170.40	—	—	—	STW26MKS0Z
500	31	0.13	497-4425-5-ND	12.01	115.50	877.80	—	—	—	STW29MKS0Z
500	45	0.1	497-2760-5-ND	19.82	190.58	1448.37	—	—	—	STW45MKS0Z
500	45	0.1	497-2718-5-ND	20.33	194.81	1482.25	—	—	—	STW45MKS0Z
550	14	0.35	497-3259-5-ND	8.04	74.84	582.12	—	—	—	STW14MKS0Z
550	20	0.25	497-3262-5-ND	8.93	83.16	646.80	—	—	—	STW20MKS0Z
600	10	0.75	497-3253-5-ND	4.82	44.91	349.27	—	—	—	STW10MKS0Z
600	13	0.55	497-3257-5-ND	7.81	64.07	540.54	—	—	—	STW13MKS0Z
600	14	0.42	497-3558-5-ND	4.53	42.50	340.03	—	—	—	STW14MKS0Z
600	16	0.36	497-4422-5-ND	11.21	107.80	819.28	—	—	—	STW16MKS0Z
600	17	0.24	497-5024-5-ND	10.01	96.25	731.50	—	—	—	STW17MKS0Z
600	20	0.29	497-5415-5-ND	9.83	91.48	711.48	—	—	—	STW20MKS0Z
600	20	0.17	497-5025-5-ND	12.01	115.50	877.80	—	—	—	STW20MKS0Z
600	27	0.185	497-4424-5-ND	14.01	134.75	1024.10	—	—	—	STW27MKS0Z
600	30	0.135	497-3265-5-ND	14.00	102.39	900.90	—	—	—	STW30MKS0Z
600	30	0.145	497-4426-5-ND	18.48	177.10	1347.50	—	—	—	STW30MKS0Z
600	45	0.11	497-2768-5-ND	18.48	177.10	1347.50	—	—	—	STW45MKS0Z
600	20	0.29	497-3263-5-ND	8.93	83.16	646.80	—	—	—	STW20MKS0Z
700	7.5	1	497-5899-5-ND	3.16	29.57	236.54	—	—	—	STW9MKS0Z
700	20	0.285	497-3559-5-ND	8.12	70.58	525.53	—	—	—	STW20MKS0Z
800	9	0.90	497-3254-5-ND	4.88	45.74	365.90	—	—	—	STW10MKS0Z
800	10.5	0.75	497-3256-5-ND	7.15	66.53	517.44	—	—	—	STW12MKS0Z
800	11	0.4	497-4420-5-ND	10.72	99.79	776.16	—	—	—	STW11MKS0Z
800	19	0.38	497-4423-5-ND	7.65	52.36	420.79	—	—	—	STW19MKS0Z
900	8	1.3	497-2784-5-ND	4.44	41.58	332.64	—	—	—	STW9MKS0Z
900	9.2	0.82	497-6198-5-ND	7.38	68.61	533.61	—	—	—	STW11MKS0Z
900	11	0.88	497-4421-5-ND	6.96	64.86	504.50	—	—	—	STW12MKS0Z
900	15	0.55	497-3557-5-ND	8.93	83.16	646.80	—	—	—	STW15MKS0Z
950	10	0.9	497-5167-5-ND	6.48	60.29	468.93	—	—	—	STW12MKS0Z
1000	8.3	1.38	497-3255-5-ND	9.38	87.32	679.14	—	—	—	STW11MKS0Z
1000	13	0.70	497-3556-5-ND	13.48	119.35	962.50	—	—	—	STW13MKS0Z
1500	2.5	6	497-6332-5-ND	11.97	115.12	874.87	—	—	—	STW3N150
1500	4	7	497-5092-5-ND	10.61	102.03	775.39	—	—	—	STW4N150

图	V _{DSS} (V)	I _D (A)	R _{DS(on)} (Ω)	Digi-Key 零件编号	价格	1	10	100	带卷† 价格	STMicro. 零件编号
40	80	0.0065	497-5106-1-ND	5.21	45.74	388.08	4504.50/2,500	—	—	STD95N04
60	12	0.1	497-2487-1-ND	1.25	9.70	83.16	970.20/2,500	—	—	STD12NF06L74
60	12	0.1	497-3154-1-ND	1.25	9.70	83.16	970.20/2,500	—	—	STD12NF06T4
60	24	0.07	497-4329-1-ND	1.69	14.45	123.26	1434.51/2,500	—	—	STD16NF06L74
60	24	0.032	497-5888-1-ND	1.54	13.09	111.65	1299.38/2,500	—	—	STD20NF06L74
60	28	0.028	497-5734-1-ND	2.83	18.37	140.59	2910.60/2,500	—	—	STD30NF06
60	35	0.028	497-4101-1-ND	2.16	18.33	156.31	1819.13/2,500	—	—	STD30NF06L74
60	35	0.024	497-3159-1-ND	2.34	19.90	169.71	1975.05/2,500	—	—	STD35NF06T4
60	60	0.014	497-6195-1-ND	2.77	23.56	200.97	2338.88/2,500	—	—	STD60NF06T4
75	40	0.024	497-4334-1-ND	2.59	21.99	187.57	2182.95/2,500	—	—	STD45NF75T4
100	13	0.13	497-3153-1-ND	1.46	11.32	97.02	1131.90/2,500	—	—	STD10NF10T4
100	25	0.035	497-3156-1-ND	2.16	18.33	156.31	1819.13/2,500	—	—	STD25NF10L74
200	5	0.7	497-4335-1-ND	1.72	14.66	125.05	1455.30/2,500	—	—	STD5N20L74
200	18	0.125	497-4330-1-ND	2.68	16.52	120.89	—	—	—	STD20N20T4
200	22	0.105	497-4653-1-ND	3.47	28.88	242.55	3753.75/2,500	—	—	STD22NM20NT4
400	3	1.8	497-2477-1-ND	1.54	13.09	111.65	1299.38/2,500	—	—	STD5N40ZT4
500	2.3	3.3	497-4333-1-ND	2.70	22.88	195.16	2271.32/2,500	—	—	STD3NKS0ZT4
500	3	2.7	497-4103-1-ND	1.60	13.61	116.12	1351.35/2,500	—	—	STD4NKS0ZT4
500	3	0.7	497-5105-1-ND	1.54	13.09	111.65	1299.38/2,500	—	—	STD4NKS0ZD
500	4	1.5	497-3520-1-ND	2.46	20.94	178.64	2079.00/2,500	—	—	STD5NKS0ZT4
500	7.5	0.8	497-3162-1-ND	3.82	33.54	284.59	3303.30/2,500	—	—	STD5NM50T4
500	11	0.38	497-5784-1-ND	4.47	57.29	443.52	5913.60/2,500	—	—	STD12NM50N
520	4	1.5	497-5735-1-ND	1.79	15.11	129.51	1507.28/2,500	—	—	STD5NKS2ZD
600	1	8.5	497-2483-1-ND	1.54	13.09	111.65	1299.38/2,500	—	—	STD1NKG0T4
600	2	4.4	497-6192-1-ND	1.60	12.40	106.26	1239.70/2,500	—	—	STD2NKG0Z
600	2.4	3.6	497-4102-1-ND	1.60	13.61	116.12	1351.35/2,500	—	—	STD3NKG0ZT4
600	3	1.5	497-3161-1-ND	3.00	26.43	224.22	2602.60/2,500	—	—	STD3NM60T4
600	4	1.76	497-5889-1-ND	1.91	16.23	138.45	1611.23/2,500	—	—	STD4NKG0ZT4
600	5	1	497-3163-1-ND	3.76	33.03	280.28	3253.25/2,500	—	—	STD5NM60T4
600	10	0.45	497-5733-1-ND	5.39	47.74	369.60	4928.00/2,500	—	—	STD11NM60N
650	5	1.2	497-5890-1-ND	2.28	19.37	165.24	1923.08/2,500	—	—	STD5NKG0ZT4
700	1.6	7	497-4331-1-ND	2.23	13.78	100.87	2442.83/2,500	—	—	STD2NKG0ZT4
800	1.0	16	497-4751-1-ND	1.52	11.86	101.64	1185.80/2,500	—	—	STD1NKG0ZT4
900	2.1	6.5	497-4332-1-ND	2.48	21.10	179.98	2094.60/2,500	—	—	STD2NKG0ZT4

C

Digi-Reel® Digi-Reel® 中含有大多数的 SMT 切割零件。将 1-ND 改为 6-ND 或将 CT-ND 改为 DKR-ND, 即为 Digi-Reel 零件编号。请参阅第 2 页上的 Digi-Key® 服务以获得更多信息。

若订单金额超过 \$135, 可提供免费送货! 全部产品均以新加坡元计价。

www.digikey.sg — 免费电话: 800-1011-692 — 电话: (852) 3104 0500 — 传真: (852) 3104 0686 (SG092-10) 1441