

D

图	系列	频率	Digi-Key 零件编号	剪切带 单价			Digi-Key 零件编号	带卷		Epson 零件编号		
				1	50	10		数量	价格			
1	MA-506	18.00000 MHz	SE2632CT-ND	1.72	1.48	1.24	SE2632TR-ND	1,000	689.92	MA-506 18.0000M-C0		
		18.43200 MHz	SE2633CT-ND	1.72	1.48	1.24	SE2633TR-ND	1,000	689.92	MA-506 18.4320M-C0		
		19.66080 MHz	SE2635CT-ND	1.72	1.48	1.24	SE2635TR-ND	1,000	689.92	MA-506 19.6608M-C0		
		20.00000 MHz	SE2609CT-ND	1.72	1.48	1.24	SE2609TR-ND	1,000	689.92	MA-506 20.0000M-C0		
		20.48000 MHz	SE2636CT-ND	1.72	1.48	1.24	SE2636TR-ND	1,000	689.92	MA-506 20.4800M-C0		
		22.11840 MHz	SE2637CT-ND	1.72	1.48	1.24	SE2637TR-ND	1,000	689.92	MA-506 22.1184M-C0		
		24.00000 MHz	SE2610CT-ND	1.72	1.48	1.24	SE2610TR-ND	1,000	689.92	MA-506 24.0000M-C0		
		24.57600 MHz	SE2638CT-ND	1.72	1.48	1.24	SE2638TR-ND	1,000	689.92	MA-506 24.5760M-C0		
		25.00000 MHz	SE2639CT-ND	1.72	1.48	1.24	SE2639TR-ND	1,000	689.92	MA-506 25.0000M-C0		
		27.00000 MHz	SE2641CT-ND	1.72	1.48	1.24	SE2641TR-ND	1,000	689.92	MA-506 27.0000M-C0:(FUND)		
		28.63600 MHz	SE2642CT-ND	1.72	1.48	1.24	SE2642TR-ND	1,000	689.92	MA-506 28.6360M-C0:(30T)		
		33.00000 MHz	SE2647CT-ND	1.72	1.48	1.24	SE2647TR-ND	1,000	689.92	MA-506 33.0000M-C0		
		40.00000 MHz	SE2615CT-ND	1.72	1.48	1.24	SE2615TR-ND	1,000	689.92	MA-506 40.0000M-C0		
		48.00000 MHz	SE2651CT-ND	1.72	1.48	1.24	SE2651TR-ND	1,000	689.92	MA-506 48.0000M-C0		
		50.00000 MHz	SE2616CT-ND	1.72	1.48	1.24	SE2616TR-ND	1,000	689.92	MA-506 50.0000M-C0		
		64.00000 MHz	SE2653CT-ND	1.89	1.62	1.35	SE2653TR-ND	1,000	754.60	MA-506 64.0000M-C0		
		2	MC-146	32.76800 kHz	SE2416CT-ND	2.16	1.85	1.54	SE2416TR-ND	250	308.00	MC-146 32.768KA-AC3
		3	MC-156	32.76800 kHz	SE2412CT-ND	2.00	1.71	1.43	SE2412TR-ND	1,000	797.72	MC-156 32.7680KA-A0
		4	MC-306	32.76800 kHz	SE2407CT-ND	1.46	1.25	1.04	SE2407TR-ND	1,000	582.12	MC-306 32.7680K-A0
				32.76800 kHz	SE2417CT-ND	1.46	1.25	1.04	SE2417TR-ND	250	207.90	MC-306 32.768K-E3
		5	MC-405	32.76800 kHz	SE2405CT-ND	1.46	1.25	1.04	SE2405TR-ND	1,000	582.12	MC-405 32.7680K-A0
		6	MC-406	32.76800 kHz	SE2418CT-ND	1.46	1.25	1.04	SE2418TR-ND	250	207.90	MC-406 32.768K-A3
		符合 RoHS 规范要求										
		7	FC-135	32.76800 kHz	SE2413CT-ND	4.59	3.93	3.28	SE2413TR-ND	250	654.50	FC-135 32.7680KA-A3
8	FC-255	32.76800 kHz	SE2415CT-ND	2.86	2.45	2.05	SE2415TR-ND	250	408.10	FC-255 32.7680K-A3		
9	MA-406	10.00000 MHz	SER3646CT-ND	1.72	1.48	1.24	SER3646TR-ND	250	246.40	MA-406 10.0000M-C3:ROHS		
		12.00000 MHz	SER3643CT-ND	1.72	1.48	1.24	SER3643TR-ND	250	246.40	MA-406 12.0000M-C3:ROHS		
		14.31818 MHz	SER3647CT-ND	1.72	1.48	1.24	SER3647TR-ND	250	246.40	MA-406 14.31818M-C3:ROHS		
		16.00000 MHz	SER3645CT-ND	1.72	1.48	1.24	SER3645TR-ND	250	246.40	MA-406 16.0000M-C3:ROHS		
		25.00000 MHz	SER3644CT-ND	1.72	1.48	1.24	SER3644TR-ND	250	246.40	MA-406 25.0000M-C3:ROHS		
		25.00000 MHz	SER3642CT-ND	1.72	1.48	1.24	SER3642TR-ND	250	246.40	MA-406 25.0000M-C3:ROHS		
1	MA-505	4.00000 MHz	SER2518CT-ND	4.31	3.70	3.08	SER2518TR-ND	1,000	1724.80	MA-505 4.0000M-C0:ROHS		
		4.09600 MHz	SER2519CT-ND	4.31	3.70	3.08	SER2519TR-ND	1,000	1724.80	MA-505 4.0960M-C0:ROHS		
		4.91520 MHz	SER2520CT-ND	4.31	3.70	3.08	SER2520TR-ND	1,000	1724.80	MA-505 4.9152M-C0:ROHS		
		6.00000 MHz	SER2501CT-ND	1.72	1.48	1.24	SER2501TR-ND	1,000	689.92	MA-505 6.0000M-C0:ROHS		
		7.37280 MHz	SER2503CT-ND	1.72	1.48	1.24	SER2503TR-ND	1,000	689.92	MA-505 7.3728M-C0:ROHS		
		8.00000 MHz	SER2504CT-ND	1.72	1.48	1.24	SER2504TR-ND	1,000	689.92	MA-505 8.0000M-C0:ROHS		
		9.83040 MHz	SER2524CT-ND	1.72	1.48	1.24	SER2524TR-ND	1,000	689.92	MA-505 9.8304M-C0:ROHS		
		10.00000 MHz	SER2505CT-ND	1.72	1.48	1.24	SER2505TR-ND	1,000	689.92	MA-505 10.0000M-C0:ROHS		
		11.05920 MHz	SER2506CT-ND	1.72	1.48	1.24	SER2506TR-ND	1,000	689.92	MA-505 11.0592M-C0:ROHS		
		12.00000 MHz	SER2507CT-ND	1.72	1.48	1.24	SER2507TR-ND	1,000	689.92	MA-505 12.0000M-C0:ROHS		
		14.31800 MHz	SER2528CT-ND	1.72	1.48	1.24	SER2528TR-ND	1,000	689.92	MA-505 14.3180M-C0:ROHS		
		14.74560 MHz	SER2529CT-ND	1.72	1.48	1.24	SER2529TR-ND	1,000	689.92	MA-505 14.7456M-C0:ROHS		
		16.00000 MHz	SER2508CT-ND	1.72	1.48	1.24	SER2508TR-ND	1,000	689.92	MA-505 16.0000M-C0:ROHS		
		18.43200 MHz	SER2533CT-ND	1.72	1.48	1.24	SER2533TR-ND	1,000	689.92	MA-505 18.4320M-C0:ROHS		
		19.66000 MHz	SER2535CT-ND	1.72	1.48	1.24	SER2535TR-ND	1,000	689.92	MA-505 19.6600M-C0:ROHS		
		20.00000 MHz	SER2509CT-ND	1.72	1.48	1.24	SER2509TR-ND	1,000	689.92	MA-505 20.0000M-C0:ROHS		
		24.00000 MHz	SER2510CT-ND	1.72	1.48	1.24	SER2510TR-ND	1,000	689.92	MA-505 24.0000M-C0:ROHS		
		24.57600 MHz	SER2538CT-ND	1.72	1.48	1.24	SER2538TR-ND	1,000	689.92	MA-505 24.5760M-C0:ROHS		
		25.00000 MHz	SER2539CT-ND	1.72	1.48	1.24	SER2539TR-ND	1,000	689.92	MA-505 25.0000M-C0:ROHS		
		29.49120 MHz	SER2543CT-ND	1.72	1.48	1.24	SER2543TR-ND	1,000	689.92	MA-505 29.4912M-C0:(30T):ROHS		
		30.00000 MHz	SER2544CT-ND	1.72	1.48	1.24	SER2544TR-ND	1,000	689.92	MA-505 30.0000M-C0:ROHS		
		40.00000 MHz	SER2515CT-ND	1.72	1.48	1.24	SER2515TR-ND	1,000	689.92	MA-505 40.0000M-C0:ROHS		
		1	MA-506	4.00000 MHz	SER2618CT-ND	4.31	3.70	3.08	SER2618TR-ND	1,000	1724.80	MA-506 4.0000M-C0:ROHS
				4.09600 MHz	SER2619CT-ND	4.31	3.70	3.08	SER2619TR-ND	1,000	1724.80	MA-506 4.0960M-C0:ROHS
4.91520 MHz	SER2620CT-ND			4.31	3.70	3.08	SER2620TR-ND	1,000	1724.80	MA-506 4.9152M-C0:ROHS		
6.00000 MHz	SER2601CT-ND			1.72	1.48	1.24	SER2601TR-ND	1,000	689.92	MA-506 6.0000M-C0:ROHS		
6.14400 MHz	SER2602CT-ND			1.72	1.48	1.24	SER2602TR-ND	1,000	689.92	MA-506 6.1440M-C0:ROHS		
7.37280 MHz	SER2603CT-ND			1.72	1.48	1.24	SER2603TR-ND	1,000	689.92	MA-506 7.3728M-C0:ROHS		
8.00000 MHz	SER2604CT-ND			1.72	1.48	1.24	SER2604TR-ND	1,000	689.92	MA-506 8.0000M-C0:ROHS		
9.83000 MHz	SER2624CT-ND			1.72	1.48	1.24	SER2624TR-ND	1,000	689.92	MA-506 9.8300M-C0:ROHS		
10.00000 MHz	SER2605CT-ND			1.72	1.48	1.24	SER2605TR-ND	1,000	689.92	MA-506 10.0000M-C0:ROHS		
11.05920 MHz	SER2606CT-ND			1.72	1.48	1.24	SER2606TR-ND	1,000	689.92	MA-506 11.0592M-C0:ROHS		
12.00000 MHz	SER2607CT-ND			1.72	1.48	1.24	SER2607TR-ND	1,000	689.92	MA-506 12.0000M-C0:ROHS		
12.28800 MHz	SER2627CT-ND			1.72	1.48	1.24	SER2627TR-ND	1,000	689.92	MA-506 12.2880M-C0:ROHS		
14.31818 MHz	SER2628CT-ND	1.72	1.48	1.24	SER2628TR-ND	1,000	689.92	MA-506 14.31818M-C0:ROHS				
14.74560 MHz	SER2629CT-ND	1.72	1.48	1.24	SER2629TR-ND	1,000	689.92	MA-506 14.7456M-C0:ROHS				
16.00000 MHz	SER2608CT-ND	1.72	1.48	1.24	SER2608TR-ND	1,000	689.92	MA-506 16.0000M-C0:ROHS				
18.00000 MHz	SER2632CT-ND	1.72	1.48	1.24	SER2632TR-ND	1,000	689.92	MA-506 18.0000M-C0:ROHS				
18.43200 MHz	SER2633CT-ND	1.72	1.48	1.24	SER2633TR-ND	1,000	689.92	MA-506 18.4320M-C0:ROHS				
20.00000 MHz	SER2609CT-ND	1.72	1.48	1.24	SER2609TR-ND	1,000	689.92	MA-506 20.0000M-C0:ROHS				
22.11840 MHz	SER2637CT-ND	1.72	1.48	1.24	SER2637TR-ND	1,000	689.92	MA-506 22.1184M-C0:ROHS				
24.00000 MHz	SER2610CT-ND	1.72	1.48	1.24	SER2610TR-ND	1,000	689.92	MA-506 24.0000M-C0:ROHS				
24.57600 MHz	SER2638CT-ND	1.72	1.48	1.24	SER2638TR-ND	1,000	689.92	MA-506 24.5760M-C0:ROHS				
25.00000 MHz	SER2639CT-ND	1.72	1.48	1.24	SER2639TR-ND	1,000	689.92	MA-506 25.0000M-C0:ROHS				
27.00000 MHz	SER2641CT-ND	1.72	1.48	1.24	SER2641TR-ND	1,000	689.92	MA-506 27.0000M-C0:(FUND):ROHS				
28.63600 MHz	SER2642CT-ND	1.72	1.48	1.24	SER2642TR-ND	1,000	689.92	MA-506 28.6360M-C0:(30T):ROHS				
32.76800 MHz	SER2646CT-ND	1.72	1.48	1.24	SER2646TR-ND	1,000	689.92	MA-506 32.7680M-C0:ROHS				
48.00000 MHz	SER2651CT-ND	1.72	1.48	1.24	SER2651TR-ND	1,000	689.92	MA-506 48.0000M-C0:ROHS				
64.00000 MHz	SER2653CT-ND	1.89	1.62	1.35	SER2653TR-ND	1,000	754.60	MA-506 64.0000M-C0:ROHS				
2	MC-146	32.76800 kHz	SE2416CT-ND	2.16	1.85	1.54	SE2416TR-ND	250	308.00	MC-146 32.768KA-AC3:ROHS		
3	MC-156	32.76800 kHz	SE2412CT-ND	2.00	1.71	1.43	SE2412TR-ND	1,000	797.72	MC-156 32.7680KA-A0:ROHS		
4	MC-306	32.76800 kHz	SE2407CT-ND	1.46	1.25	1.04	SE2407TR-ND	1,000	582.12	MC-306 32.7680K-A0:ROHS		
		32.76800 kHz	SE2417CT-ND	1.46	1.25	1.04	SE2417TR-ND	250	207.90	MC-306 32.768K-E3:ROHS		
6	MC-406	32.76800 kHz	SER2405CT-ND	1.46	1.25	1.04	SER2405TR-ND	1,000	582.12	MC-406 32.7680K-A0:ROHS		
		32.76800 kHz	SER2418CT-ND	1.46	1.25	1.04	SER2418TR-ND	250	207.90	MC-406 32.768K-A3:ROHS		

Digi-Reel® Digi-Reel® 中含有大多数的 SMT 切割零件。将 1-ND 改为 6-ND 或将 CT-ND 改为 DKR-ND, 即为 Digi-Reel 零件编号。请参阅第 2 页上的 Digi-Key® 服务以获得更多信息。

若订单金额超过 \$135, 可提供免费送货! 全部产品均以新加坡元计价。

1588 (SG092-10) www.digikey.sg - 免费电话: 800-1011-692 - 电话: (852) 3104 0500 - 传真: (852) 3104 0686