





Wire Ferrules – Insulated

Material: Copper/Plastic. Surface: Tin-plated.



Twin-Wire Ferrules for Two Wires

Material: Copper/Plastic
Surface: Tin-plated



A

Size (mm ²)	AWG	Type	Color Code	Dimensions (mm)				Digi-Key Part No.	Pricing			AE Part No.
				A	B	C	D		10	50	100	
0.14	26	DIN	Gray	10.5	6	0.8	2.0	288-1001-ND*	2.32	10.15	17.40	1161014
				12.5	8	0.8	2.0	288-1002-ND*	2.48	10.85	18.60	1181014
		W	Gray	10.5	6	0.8	2.0	288-1039-ND*	2.32	10.15	17.40	1162014
0.25	24	DIN	Yellow	10.5	6	0.8	2.0	288-1003-ND*	2.32	10.15	17.40	11610025
				12.5	8	0.8	2.0	288-1004-ND*	2.48	10.85	18.60	11810025
		W	Blue	10.5	6	0.8	2.0	288-1041-ND*	2.32	10.15	17.40	11620025
				12.5	8	0.8	2.0	288-1042-ND*	2.48	10.85	18.60	11820025
0.34	24	DIN	Turquoise	10.5	6	0.8	2.0	288-1005-ND*	2.32	10.15	17.40	1161034
				12.5	8	0.8	2.0	288-1006-ND*	2.48	10.85	18.60	1181034
		W	Turquoise	10.5	6	0.8	2.0	288-1043-ND*	2.32	10.15	17.40	1162034
				12.5	8	0.8	2.0	288-1044-ND*	2.48	10.85	18.60	1182034
0.50	20	DIN	White	11.5	6	1.1	2.5	288-1007-ND	1.68	7.35	12.60	1161050
				13.5	8	1.1	2.5	288-1008-ND	1.20	5.25	9.00	1181050
		W	Orange	11.5	6	1.1	2.5	288-1045-ND	1.68	7.35	12.60	1162050
				13.5	8	1.1	2.5	288-1046-ND	1.20	5.25	9.00	1182050
				15.5	10	1.1	2.5	288-1047-ND	1.68	7.35	12.60	11102050
0.75	20	DIN	Gray	12.0	6	1.3	2.8	288-1010-ND	1.76	7.70	13.20	1161075
				14.0	8	1.3	2.8	288-1011-ND	1.20	5.25	9.00	1181075
		W	White	12.0	6	1.3	2.8	288-1048-ND	1.76	7.70	13.20	1162075
				14.0	8	1.3	2.8	288-1049-ND	1.20	5.25	9.00	1182075
1.00	18	DIN	Red	12.5	6	1.5	3.0	288-1014-ND	2.00	8.75	15.00	1161010
				14.5	8	1.5	3.0	288-1015-ND	1.28	5.60	9.60	1181010
		W	Yellow	12.5	6	1.5	3.0	288-1052-ND	2.00	8.75	15.00	1162010
				14.5	8	1.5	3.0	288-1053-ND	1.28	5.60	9.60	1182010
				16.5	10	1.5	3.0	288-1054-ND	2.00	8.75	15.00	11102010
				18.5	12	1.5	3.0	288-1055-ND	2.00	8.75	15.00	11122010
1.50	16	DIN	Black	12.5	6	1.8	3.4	288-1018-ND*	2.80	12.25	21.00	1161015
				14.5	8	1.8	3.4	288-1019-ND	1.76	7.70	13.20	1181015
		W	Red	12.5	6	1.8	3.4	288-1056-ND*	2.80	12.25	21.00	1162015
				14.5	8	1.8	3.4	288-1057-ND	1.76	7.70	13.20	1182015
				16.5	10	1.8	3.4	288-1058-ND	2.80	12.25	21.00	11102015
2.08	14	DIN	Yellow	14.5	8	2.05	3.6	288-1023-ND*	2.20	9.63	16.50	1181208
2.50	14	DIN	Blue	15.0	8	2.3	4.2	288-1024-ND	1.76	7.70	13.20	1181025
				19.0	12	2.3	4.2	288-1025-ND	2.40	10.50	18.00	11121025
		W	Blue	15.0	8	2.3	4.2	288-1062-ND	1.76	7.70	13.20	1182025
				19.0	12	2.3	4.2	288-1063-ND	2.40	10.50	18.00	11122025
4.00	12	DIN	Gray	17.5	10	2.9	4.8	288-1027-ND	2.88	12.60	21.60	11101040
				20.0	12	2.9	4.8	288-1028-ND	2.88	12.60	21.60	11121040
		W	Gray	17.5	10	2.9	4.8	288-1065-ND	2.88	10.80	14.40	11102040
				20.0	12	2.9	4.8	288-1066-ND	2.88	10.80	14.40	11122040
6.00	10	DIN	Yellow	20.0	12	3.6	6.2	288-1030-ND	3.80	14.25	19.00	11121060
				20.0	12	3.6	6.2	288-1068-ND	3.80	14.25	19.00	11122060
		W	Black	20.0	12	3.6	6.2	288-1032-ND	3.80	14.25	19.00	11121100
10.00	8	DIN	Red	21.0	12	4.6	7.5	288-1034-ND	5.20	19.50	26.00	11121160
16.00	6	DIN	Blue	23.0	12	6.0	8.8	288-1034-ND	5.20	19.50	26.00	11121160
25.00	4	DIN	Yellow	29.0	16	7.5	11.0	288-1036-ND	13.20	49.50	66.00	11161250

* Does not conform to DIN 46228 Part 4
Note: For additional sizes, please visit our web site.

Size (mm ²)	AWG	Color	Dimensions (mm)				Digi-Key Part No.	Pricing			AE Part No.
			A	B	C	D		10	50	100	
2 x 0.50	2 x 20	White	15.0	8.0	1.5	2.3 / 4.5	288-1124-ND	1.60	7.00	12.00	1381050
2 x 0.75	2 x 20	Gray	15.0	8.0	1.8	2.6 / 5.1	288-1125-ND	1.60	7.00	12.00	1381075
2 x 0.75	2 x 20	Gray	17.0	10.0	1.8	2.6 / 5.1	288-1126-ND	2.04	8.93	15.30	13101075
2 x 1.00	2 x 18	Red	15.0	8.0	2.05	3.2 / 5.1	288-1127-ND	1.88	8.23	14.00	1381010
2 x 1.00	2 x 18	Red	17.0	10.0	2.05	3.2 / 5.1	288-1128-ND	2.60	11.38	19.50	13101010
2 x 1.50	2 x 16	Black	16.0	8.0	2.3	3.5 / 6.4	288-1129-ND	2.24	9.80	16.80	1381015
2 x 1.50	2 x 16	Black	20.0	12.0	2.3	3.5 / 6.4	288-1130-ND	3.20	14.00	24.00	13121015
2 x 2.50	2 x 14	Blue	18.5	10.0	2.9	4.0 / 7.5	288-1131-ND	3.20	14.00	24.00	13101025
2 x 2.50	2 x 14	Blue	21.5	13.0	2.9	4.0 / 7.5	288-1132-ND	3.20	14.00	24.00	13131025
2 x 4.00	2 x 12	Gray	23.0	12.0	3.8	4.9 / 8.6	288-1133-ND	5.80	21.75	29.00	13121040
2 x 6.00	2 x 10	Yellow	25.0	14.0	4.9	5.8 / 9.6	288-1134-ND	6.20	23.25	31.00	13141060
2 x 10.00	2 x 8	Red	26.0	14.0	6.5	7.0 / 12.6	288-1135-ND	7.60	28.50	38.00	13141100
2 x 16.00	2 x 6	Blue	31.0	16.0	8.5	8.8 / 16.6	288-1136-ND	20.00	87.50	150.00	13161160

Wire Ferrules – Non-Insulated

Material: Copper
Surface: Tin-plated



Size (mm ²)	AWG	Dimensions (mm)				Digi-Key Part No.	Pricing			AE Part No.
		A	B	C	D		10	50	100	
0.25	24	5	0.8	1.7	288-1077-ND*	.60	2.63	4.50	12510025	
		7	0.8	1.7	288-1078-ND*	.60	2.63	4.50	12710025	
0.34	22	5	0.9	1.8	288-1079-ND*	.64	2.80	4.80	12510034	
		7	0.9	1.8	288-1080-ND*	.64	2.80	4.80	12710034	
0.50	20	6	1.0	2.1	288-1081-ND	.68	2.98	5.10	12610050	
		8	1.0	2.1	288-1082-ND*	.72	3.15	5.40	12810050	
		10	1.0	2.1	288-1083-ND	.72	3.15	5.40	121010050	
0.75	20	6	1.2	2.3	288-1084-ND	.84	3.68	6.30	12610075	
		8	1.2	2.3	288-1085-ND*	.84	3.68	6.30	12810075	
		10	1.2	2.3	288-1086-ND	.88	3.85	6.60	121010075	
		12	1.2	2.3	288-1087-ND	.96	4.20	7.20	121210075	
1.00	18	6	1.4	2.5	288-1088-ND	.88	3.85	6.60	12610100	
		7	1.4	2.5	288-1089-ND	.88	3.85	6.60	12710100	
		8	1.4	2.5	288-1090-ND*	.88	3.85	6.60	12810100	
		10	1.4	2.5	288-1091-ND	.88	3.85	6.60	121010100	
		12	1.4	2.5	288-1092-ND*	1.00	4.38	7.50	121210100	
1.50	16	7	1.7	2.8	288-1093-ND	.92	4.03	6.90	12710150	
		8	1.7	2.8	288-1094-ND	.92	4.03	6.90	12810150	
		10	1.7	2.8	288-1095-ND	.96	4.20	7.20	121010150	
		12	1.7	2.8	288-1096-ND	1.08	4.73	8.10	121210150	
		15	1.7	2.8	288-1097-ND*	1.08	4.73	8.10	121510150	
2.50	14	7	2.2	3.4	288-1099-ND	1.16	5.08	8.70	12710250	
		8	2.2	3.4	288-1100-ND	1.16	5.08	8.70	12810250	
		10	2.2	3.4	288-1101-ND	1.16	5.08	8.70	121010250	
		12	2.2	3.4	288-1102-ND	1.16	5.08	8.70	121210250	
4.00	12	9	2.8	4.0	288-1105-ND	1.12	4.90	8.40	12910400	
		10	2.8	4.0	288-1106-ND	1.12	4.90	8.40	121010400	
		12	2.8	4.0	288-1107-ND	1.00	4.38	7.50	121210400	
6	10	10	3.5	4.7	288-1110-ND	2.24	9.80	16.80	121010600	
		12	3.5	4.7	288-1111-ND	2.24	9.80	16.80	121210600	
10.00	8	12	4.5	5.8	288-1114-ND	2.00	8.75	15.00	1212110	
25.00	4	12	7.3	9.5	288-1121-ND*	10.40	45.50	78.00	1212125	

* Does not conform to DIN 46228 Part 1

Assortment Boxes

288-1147-ND	Assortment Box 1 — 150 pieces DIN Type (30 pieces each of sizes 0.25, 0.34, 0.50, 0.75, and 1.00)	\$50.00
288-1153-ND	Assortment Box 1 — 150 pieces W Type (30 pieces each of sizes 0.25, 0.34, 0.50, 0.75, and 1.00)	\$50.00
288-1148-ND	Assortment Box 2 — 400 pieces DIN Type (50 pieces each of sizes 0.50 and 2.50; 100 pieces each of sizes 0.75, 1.00, and 1.50)	\$75.00
288-1154-ND	Assortment Box 2 — 400 pieces W Type (50 pieces each of sizes 0.50 and 2.50; 100 pieces each of sizes 0.75, 1.00, and 1.50)	\$75.00
288-1149-ND	Assortment Box 3 — 100 pieces DIN Type (50 pieces each of size 4.00; 20 pieces each of sizes 6.00 and 10.00, 10 pieces of size 16.00)	