


A


BNC PC Board/Panel Mount Jack Connectors with Mounting Flanges 50 Ohm



Hardware Sold Separately

Description	Center Contact	Mount. Height Inch (mm)	Body Material	Digi-Key Part No.	Price Each 1 25	AMP Part No.
Right Angle	Tin	.625 (15.88)	VALOX, White	A32242-ND	9.40 8.09	5226978-1
Right Angle	Gold	.625 (15.88)	VALOX, White	A32252-ND	9.40 8.09	5226978-3

BNC PC Board/Panel Mount Right Angle Jack Connectors 50 Ohm



Hardware Sold Separately


Description	Center Contact	Mount. Height A Inch (mm)	Body Material	Digi-Key Part No.	Price Each 1 25	AMP Part No.
Without Mounting Posts	Tin	.625 (15.88)	VALOX, White	A32253-ND	3.30 2.84	5226990-1
With Mounting Posts	Tin	.625 (15.88)	VALOX, White	A32244-ND	2.43 2.10	5227161-1
Without Mounting Posts	Gold	.625 (15.88)	VALOX, White	A32254-ND	2.83 2.44	5226990-3
With Mounting Posts	Gold	.625 (15.88)	VALOX, White	A32258-ND	2.43 2.10	5227161-3
With Mounting Posts	Gold	.519 (13.18)	VALOX, White	A32260-ND	2.43 2.10	5227161-7
With Mounting Posts	Tin	.625 (15.88)	VALOX, Black	A32245-ND	2.43 2.10	5227161-2
Without Mounting Posts	Gold	.625 (15.88)	VALOX, Black	A32255-ND	2.83 2.44	5226990-6
With Mounting Posts	Gold	.625 (15.88)	VALOX, Black	A32259-ND	2.43 2.10	5227161-6
With Mounting Posts	Gold	.519 (13.18)	VALOX, Black	A32261-ND	2.43 2.10	5227161-9
Without Mounting Posts	Tin	.625 (15.88)	Metal	A32264-ND	9.43 8.11	5227433-1
With Mounting Posts	Tin	.625 (15.88)	Metal	A32248-ND	3.28 2.83	5227661-1
Without Mounting Posts	Gold	.625 (15.88)	Metal	A32267-ND	3.37 2.90	5227676-1
With Mounting Posts	Gold	.625 (15.88)	Metal	A24499-ND	3.48 2.99	227677-1
With Mounting Posts	Gold	.625 (15.88)	Metal	A32268-ND	3.28 2.83	5227677-1
With Mounting Posts	Gold	.500 (12.70)	Metal	A32273-ND	5.83 5.01	5413879-1

Zinc Die Cast — RoHS Compliant

With Mounting Posts	Gold	.518 (13.16)	Zinc, White	A97552-ND	2.43 2.09	1-1337542-0
With Mounting Posts	Gold	.622 (15.80)	Zinc, White	A97553-ND	2.43 2.09	1-1337543-0
With Mounting Posts	Gold	.518 (13.16)	Zinc, Black	A97554-ND	2.43 2.09	1-1634613-0
With Mounting Posts	Gold	.622 (15.80)	Zinc, Black	A97555-ND	2.43 2.09	1-1634612-0
With Mounting Posts	Gold	.598 (15.20)	Zinc	A97556-ND	3.80 3.27	1-1337494-0

◆ RoHS Compliant

BNC PC Board/Panel Mount Vertical Jack Connectors 50 Ohm



Hardware Sold Separately

Description	Center Contact	Body Material	Digi-Key Part No.	Price Each 1 25	AMP Part No.
Without Mounting Posts	Tin-Lead	VALOX, White	A24501-ND	8.85 7.62	226993-1
Without Mounting Posts	Tin	VALOX, White	A32256-ND	7.98 6.86	5226993-1
With Mounting Posts	Tin	VALOX, White	A32246-ND	2.43 2.10	5227222-1
Without Mounting Posts	Gold	VALOX, White	A32257-ND	7.98 6.86	5226993-3
With Mounting Posts	Gold	VALOX, White	A32262-ND	2.43 2.10	5227222-3
Without Mounting Posts	Tin	VALOX, Black	A32243-ND	9.20 7.92	5226993-2
With Mounting Posts	Tin	VALOX, Black	A32247-ND	4.03 3.47	5227222-2
With Mounting Posts	Gold	VALOX, Black	A32263-ND	4.03 3.47	5227222-6
With Mounting Posts	Tin	Metal	A32265-ND	3.90 3.36	5227671-1
With Mounting Posts	Gold	Metal	A32266-ND	2.80 2.41	5227673-1

Zinc Die Cast — RoHS Compliant

With Mounting Posts	Gold	Zinc, White	A97557-ND	2.53 2.18	1-1337541-0
With Mounting Posts	Gold	Zinc, Black	A97558-ND	2.53 2.18	1-1634505-0

◆ RoHS Compliant

Jack Accessories 50 and 75 Ohm

Description	Digi-Key Part No.	Price Each 1 25	AMP Part No.
Insulating Bushing for Mounting Jacks, Nylon	A24532-ND	.43 .37	222163-1
Insulating Bushing for Bulkhead Solder Jacks	A24533-ND	.23 .20	227223-1

Description	Digi-Key Part No.	Price Each 1 25	AMP Part No.
Screw for panel thickness of 3/32 (2.38mm) or greater	A24534-ND	.35 .31	221108-2
Screw for panel thickness of less than 3/32 (2.38mm)	A24535-ND	.35 .31	221108-4
Lockwasher	A1129-ND	.29 .27	1-329632-2
Hex Nut	A1128-ND	.31 .28	1-329631-2

Zinc Die Cast — RoHS Compliant

BNC/TNC Hexagonal Nut	A97566-ND	.24 .21	1-1634816-0
BNC/TNC Lockwasher	A97567-ND	.18 .16	1-1634817-0

◆ RoHS Compliant

BNC Vertical Metallized PC Board Mount Jack Connectors 50 Ohm





Fig.	Body Plating	Center Contact	Body Material	Digi-Key Part No.	Price Each 1 25	AMP Part No.
1	Nickel	Silver	VALOX	A24512-ND	4.28 3.69	227699-1
	Nickel	Silver	VALOX	A33798-ND	3.94 3.39	5227699-1
	Gold	VALOX	A32269-ND	3.94 3.39	5227699-2	
	Nickel	Tin	VALOX	A32249-ND	3.94 3.39	5227699-3
2	Nickel	Gold	VALOX	A24515-ND	6.05 5.21	221123-2
	Nickel	Gold	VALOX	A32241-ND	3.83 3.29	5221123-2
3	Nickel	Silver	VALOX	A24516-ND	5.65 4.86	222420-1
	Nickel	Silver	VALOX	A32251-ND	6.23 5.36	5222420-1
	Tin-Lead	Silver	VALOX	A24517-ND	5.23 4.50	414305-1
	Tin	Silver	VALOX	A32493-ND	4.80 4.13	5414305-1

Zinc Die Cast — RoHS Compliant

3	Nickel	Gold	Zinc	A97581-ND	1.80 1.55	5-1634503-1
	Nickel	Gold	Zinc	A97583-ND	1.78 1.53	5-1634506-1

◆ RoHS Compliant

BNC Press-Fit Terminal Jack Connectors 50 Ohm



Body Plating	Center Contact	Body Material	Digi-Key Part No.	Price Each 1 25	AMP Part No.
Nickel	Gold	TEFLON	A32250-ND	5.00 4.30	5222006-1

BNC Right-Angle PC Board Mount Jack Connectors





Fig.	Body Plating	Center Contact Length - In (mm)	Digi-Key Part No.	Price Each 1 25	AMP Part No.
1	Nickel	.171 (4.34)	A32270-ND	6.60 5.68	5413631-1
	Tin	.171 (4.34)	A32271-ND	6.55 5.64	5413631-2
	Nickel	.131 (3.33)	A32272-ND	8.03 6.91	5413631-3
	Nickel	.131 (3.33)	A97570-ND	3.43 2.95	5-1634556-0
2	Nickel	—	A24539-ND	3.15 2.71	414373-1
	Nickel	—	A32274-ND	2.66 2.29	5414373-1

◆ RoHS Compliant † Zinc Die Cast

BNC Twist-On Connectors 50 Ohm



Center Contact: Gold Body Plating: Nickel

Description	Dielectric	Cable Group RG/U	Digi-Key Part No.	Price Each 1 25	AMP Part No.
Plug	Polymethylpentene	59, 59A, 59B	A24483-ND	5.23 4.50	414265-3
			A33797-ND	4.50 3.87	5414265-3

◆ RoHS Compliant

More Product Available Online: www.digikey.com