

3M Zero Insertion Force (ZIF) I.C. Sockets (Cont.)



A

No. of Pins	Contact Plating	Dimensions — Inch (mm)				Digi-Key Part No.	Pricing		3M Part No.
		A	B	C	D		1	10	
24	Gold	.96 (24.4)	.56 (14.2)	1.77 (45.0)	.300 (7.62)	3M5022-ND	14.86	118.88	224-5248-19-0602J
28		1.26 (32.0)	.86 (21.8)	1.98 (50.3)	.600 (15.24)	3M5023-ND	13.56	108.48	228-1277-19-0602J
28		1.06 (26.9)	.66 (16.8)	1.98 (50.3)	.400 (10.16)	3M5029-ND	16.66	133.28	228-4817-19-0602J
32		1.25 (32.0)	.86 (21.9)	2.17 (55.2)	.600 (15.24)	3M5031-ND	14.96	119.68	232-1285-19-0602J
40		1.27 (32.3)	.86 (21.8)	2.58 (65.5)	.600 (15.24)	3M5034-ND	17.50	140.00	240-1280-19-0602J
40	Gold	1.66 (42.2)	1.26 (32.0)	2.58 (65.5)	1.000 (25.4)	3M5038-ND	21.36	170.88	240-3639-19-0602J
42		1.26 (32.0)	.86 (21.8)	2.68 (68.1)	.600 (15.24)	3M5040-ND	17.90	143.20	242-1281-19-0602J
48		1.25 (31.8)	.86 (21.8)	2.98 (75.8)	.600 (15.24)	3M5046-ND	20.14	161.12	248-1282-19-0602J
64		1.70 (43.2)	1.30 (33.0)	3.95 (100.3)	.900 (22.86)	3M5051-ND	29.34	234.72	264-4493-19-0602J
ZIP DIP Receptacles — Solder Tail without Flanges									
24	Gold	1.26 (32.0)	.86 (21.8)	1.77 (45.0)	.600 (15.24)	3M5019-ND	9.64	77.12	224-1275-29-0602J
28		1.26 (32.0)	.86 (21.8)	1.98 (50.3)	.600 (15.24)	3M5024-ND	10.66	85.28	228-1277-29-0602J
28		1.09 (27.9)	.70 (17.8)	1.59 (40.5)	.400 (10.16)	3M5027-ND	10.60	84.80	228-1290-29-0602J
32		1.25 (32.0)	.86 (21.9)	2.17 (55.2)	.600 (15.24)	3M5032-ND	11.66	93.28	232-1285-29-0602J
40		1.27 (32.3)	.86 (21.8)	2.58 (65.5)	.600 (15.24)	3M5035-ND	13.36	106.88	240-1280-29-0602J
42	Gold	1.26 (32.0)	.86 (21.8)	2.68 (68.1)	.600 (15.24)	3M5041-ND	13.52	108.16	242-1281-29-0602J
42		1.30 (33.0)	.90 (22.9)	2.08 (52.9)	.600 (15.24)	3M5044-ND	14.08	112.64	242-1293-29-0602J
48		1.25 (31.8)	.86 (21.8)	2.98 (75.8)	.600 (15.24)	3M5047-ND	15.14	121.12	248-1282-29-0602J
64		1.52 (38.5)	1.11 (28.3)	2.85 (72.5)	.800 (20.32)	3M5050-ND	19.16	153.28	264-1300-29-0602J
90		1.61 (40.8)	1.19 (30.2)	3.77 (95.7)	.900 (22.86)	3M5053-ND	28.22	225.76	290-1294-29-0602J
ZIP DIP Receptacles — Wire Wrap without Flanges									
24	Gold	1.26 (32.0)	.86 (21.8)	1.77 (45.0)	.600 (15.24)	3M5020-ND	12.10	96.80	224-1275-39-0602J
28		1.26 (32.0)	.86 (21.8)	1.98 (50.3)	.600 (15.24)	3M5025-ND	13.56	108.48	228-1277-39-0602J
32		1.25 (32.0)	.86 (21.9)	2.17 (55.2)	.600 (15.24)	3M5033-ND	14.96	119.68	232-1285-39-0602J
40		1.27 (32.3)	.86 (21.8)	2.58 (65.5)	.600 (15.24)	3M5036-ND	17.50	140.00	240-1280-39-0602J
42		1.26 (32.0)	.86 (21.8)	2.68 (68.1)	.600 (15.24)	3M5042-ND	17.90	143.20	242-1281-39-0602J
48	1.25 (31.8)	.86 (21.8)	2.98 (75.8)	.600 (15.24)	3M5048-ND	19.00	152.00	248-1282-39-0602J	
Universal DIP Sockets									
24	Gold	1.77 (45.0)	—	1.10 (27.94)	—	3M2406-ND	13.06	103.64	224-1286-00-0602J
28		1.99 (50.5)	—	1.30 (33.02)	—	3M2806-ND	15.66	124.29	228-1371-00-0602J
32		2.19 (56.6)	—	1.50 (38.10)	—	3M5005-ND	20.78	166.24	232-1287-00-0602J
40		2.59 (65.8)	—	1.90 (48.26)	—	3M4006-ND	20.44	162.20	240-1288-00-0602J
42		2.69 (68.2)	—	2.00 (50.80)	—	3M5006-ND	26.04	208.32	242-1289-00-0602J
Shrink DIP Sockets — .070" Pin to Pin Pitch									
28	Gold	1.60 (40.5)	1.42 (36.1)	.70 (17.8)	.40 (10.16)	3M5007-ND	13.12	104.96	228-1290-00-0602J
32		1.73 (44.0)	1.56 (39.6)	.70 (17.8)	.40 (10.16)	3M5008-ND	18.44	147.52	232-1291-00-0602J
42		2.10 (52.9)	1.90 (48.5)	.90 (22.9)	.60 (15.24)	3M5009-ND	17.98	143.84	242-1293-00-0602J
56		2.57 (65.4)	2.40 (61.0)	.90 (22.9)	.60 (15.24)	3M5010-ND	25.90	207.20	256-1292-00-0602J
64		2.90 (72.5)	2.68 (68.0)	1.10 (28.3)	.80 (20.70)	3M5011-ND	25.18	201.44	264-1300-00-0602J
90		3.77 (95.7)	3.59 (91.3)	1.23 (31.3)	.90 (22.86)	3M5012-ND	40.26	322.08	290-1294-00-3302J
SOIC Lidded Sockets									
8	Gold	1.45 (36.8)	.47 (11.9)	—	—	3M5054-ND	17.94	143.52	208-7391-55-1902
14		1.45 (36.8)	.47 (11.9)	—	—	3M5055-ND	20.24	161.92	214-7390-55-1902
16		1.59 (40.4)	.57 (14.5)	—	—	3M5077-ND	21.48	171.84	216-7224-55-1902
16		1.45 (36.8)	.47 (11.9)	—	—	3M5078-ND	21.48	171.84	216-7383-55-1902
18		1.59 (40.4)	.57 (14.5)	—	—	3M5056-ND	22.04	176.32	218-7223-55-1902
20	Gold	1.59 (40.4)	.57 (14.5)	—	—	3M5057-ND	23.28	186.24	220-7201-55-1902
24		1.69 (42.9)	.80 (20.3)	—	—	3M5058-ND	25.72	205.76	224-7397-55-1902
28		1.69 (42.9)	.80 (20.3)	—	—	3M5059-ND	28.12	224.96	228-7396-55-1902
28		1.69 (42.9)	.80 (20.3)	—	—	3M5060-ND	28.12	224.96	228-7474-55-1902
In-Line ZIP Strip Sockets									
10	Gold	1.77 (45.0)	1.60 (40.8)	—	—	3M5061-ND	26.10	208.80	210-2599-00-0602
20		2.77 (70.4)	2.57 (65.3)	—	—	3M5062-ND	29.44	235.52	220-2600-00-0602
24		3.15 (80.0)	2.97 (75.4)	—	—	3M5063-ND	30.50	244.00	224-5809-00-0602
32		3.97 (100.8)	3.81 (96.8)	—	—	3M5064-ND	32.64	261.12	232-2601-00-0602
36		4.35 (110.5)	4.17 (105.9)	—	—	3M5065-ND	33.64	269.12	236-6225-00-0602

Matrix Size	Description	Digi-Key Part No.	Pricing		3M Part No.
			1	10	
PGA ZIP Sockets					
10 x 10	Socket Kit without Contacts	3M5066-ND	29.12	232.96	200-6310-9UN-1900
11 x 11	Socket Kit without Contacts	3M5067-ND	29.20	233.60	200-6311-9UN-1900
13 x 13	Socket Kit without Contacts	3M5068-ND	29.54	236.32	200-6313-9UN-1900
15 x 15	Socket Kit without Contacts	3M5069-ND	50.06	400.48	200-6315-9UN-1900
17 x 17	Socket Kit without Contacts	3M5070-ND	45.28	362.24	200-6317-9UN-1900
19 x 19	Socket Kit without Contacts	3M5071-ND	53.84	430.72	200-6319-9UN-1900
21 x 21	Socket Kit without Contacts	3M5072-ND	64.74	517.92	200-6321-9UN-1900
25 x 25	Socket Kit without Contacts	3M5073-ND	86.20	689.60	200-6325-9UN-1900
—	Socket Contact - BeCu/Au Plated	3M5074-ND	.22	1.76	300-6300-CNA-0002B
—	Extra Hole Plugs - Set of 10	3M5075-ND	1.50	12.00	200-4660-14-1900


DIP Sockets

Features:

- Dual leaf, high compression contact provides reliable termination
- Side and end stackable

Specifications:

- Insulation Material: Polyester glass filled
- Flammability: UL 94V-0
- Color: Black
- Underplating: 35µ" min. Nickel overall
- Surface Plating: 135µ" min. Matte Tin overall
- Current Rating: 1 Amp
- Temperature Rating: -25°C - 85°C



No. of Contact	Dimensions — Inch (mm)			Digi-Key Part No.	Pricing			3M Part No.
	A	B	C		1	10	100	
Straight Tail								
8	.395 (10.03)	.300 (7.62)	.400 (10.16)	3M5461-ND	.18	1.56	12.60	4808-3000-CP
14	.695 (17.65)	.300 (7.62)	.400 (10.16)	3M5462-ND	.15	1.30	10.50	4814-3000-CP
16	.795 (20.19)	.300 (7.62)	.400 (10.16)	3M5463-ND	.15	1.30	10.50	4816-3000-CP
18	.895 (22.73)	.300 (7.62)	.400 (10.16)	3M5464-ND	.21	1.82	14.70	4818-3000-CP
20	.995 (25.27)	.300 (7.62)	.400 (10.16)	3M5465-ND	.21	1.82	14.70	4820-3000-CP
24	1.195 (30.35)	.300 (7.62)	.400 (10.16)	3M5466-ND	.24	2.08	16.80	4824-3000-CP
24	1.195 (30.35)	.600 (15.24)	.700 (17.78)	3M5467-ND	.24	2.08	16.80	4824-6000-CP
28	1.395 (35.43)	.600 (15.24)	.700 (17.78)	3M5469-ND	.27	2.34	18.90	4828-6000-CP
32	1.595 (40.51)	.600 (15.24)	.700 (17.78)	3M5470-ND	.30	2.60	21.00	4832-6000-CP
40	1.995 (50.67)	.600 (15.24)	.700 (17.78)	3M5471-ND	.39	3.38	27.30	4840-6000-CP
48	2.395 (60.83)	.600 (15.24)	.700 (17.78)	3M5472-ND	.48	4.16	33.60	4848-6000-CP

No. of Contact	Dimensions — Inch (mm)			Digi-Key Part No.	Pricing			3M Part No.
	A	B	C		1	10	100	
Kinked Tail								
8	.395 (10.03)	.300 (7.62)	.400 (10.16)	3M5473-ND	.18	1.56	12.60	4808-3004-CP
14	.695 (17.65)	.300 (7.62)	.400 (10.16)	3M5474-ND	.18	1.56	12.60	4814-3004-CP
16	.795 (20.19)	.300 (7.62)	.400 (10.16)	3M5475-ND	.18	1.56	12.60	4816-3004-CP
18	.895 (22.73)	.300 (7.62)	.400 (10.16)	3M5476-ND	.24	2.08	16.80	4818-3004-CP
20	.995 (25.27)	.300 (7.62)	.400 (10.16)	3M5477-ND	.24	2.08	16.80	4820-3004-CP
24	1.195 (30.35)	.300 (7.62)	.400 (10.16)	3M5478-ND	.30	2.60	21.00	4824-3004-CP
28	1.395 (35.43)	.300 (7.62)	.400 (10.16)	3M5480-ND	.30	2.60	21.00	4828-3004-CP
24	1.195 (30.35)	.600 (15.24)	.700 (17.78)	3M5479-ND	.30	2.60	21.00	4824-6004-CP
28	1.395 (35.43)	.600 (15.24)	.700 (17.78)	3M5481-ND	.33	2.86	23.10	4828-6004-CP
32	1.595 (40.51)	.600 (15.24)	.700 (17.78)	3M5482-ND	.39	3.38	27.30	4832-6004-CP
40	1.995 (50.67)	.600 (15.24)	.700 (17.78)	3M5483-ND	.48	4.16	33.60	4840-6004-CP
48	2.395 (60.83)	.600 (15.24)	.700 (17.78)	3M5484-ND	.57	4.94	39.90	4848-6004-CP

More Product Available Online: www.digkey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380