

Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25	100
NJG1101F-TE1CT-ND	Wideband AGC Amp, GaAs MMIC	6-MTP	2.31	1.93	1.54
NJG1101F-TE1TR-ND	Wideband AGC Amp, GaAs MMIC	6-MTP	4042.50/3,000		
NJG1103F1-TE1CT-ND	1.5/1.9GHz Low Noise Amp, GaAs MMIC	6-MTP	.93	.78	.62
NJG1103F1-TE1TR-ND	1.5/1.9GHz Low Noise Amp, GaAs MMIC	6-MTP	1627.50/3,000		
NJG1105F-TE1CT-ND	1.8/1.9/2.1GHz Band Low Noise Amp, GaAs MMIC	6-MTP	2.73	2.28	1.82
NJG1105F-TE1TR-ND	1.8/1.9/2.1GHz Band Low Noise Amp, GaAs MMIC	6-MTP	4777.50/3,000		
NJG1302V-TE1CT-ND	Medium Power Amp, GaAs MMIC	14-SSOP	6.30	5.25	4.20
NJG1302V-TE1TR-ND	Medium Power Amp, GaAs MMIC	14-SSOP	7350.00/2,000		
NJG1307R-TE1CT-ND	Driver Amp, GaAs MMIC	8-VSP	2.94	2.45	1.96
NJG1307R-TE1TR-ND	Driver Amp, GaAs MMIC	8-VSP	3430.00/2,000		
NJM0640-ND	J-Fet Input Op Amp	14-Dip	.93	.78	.62
NJM072D-ND	Dual J-Fet Input Op Amp*	8-Dip	.45	.38	.30
NJM072M-ND	Dual J-Fet Input Op Amp	8-DMP	.54	.45	.36
NJM074M-ND	Quad J-Fet Input Op Amp	14-DMP	1.05	.88	.70
NJM082D-ND	Quad J-Fet Input Op Amp	8-Dip	1.48	.40	.32
NJM084D-ND	Quad J-Fet Input Op Amp	14-Dip	1.17	.98	.78
NJM0319M-ND	Precision, High Speed, Dual Voltage Comparator*	14-DMP	1.08	.90	.72
NJM2060D-ND	High-Gain, Wide-Bandwidth, Quad Op Amp	14-Dip	60	50	40
NJM2068D-ND	Dual Noise Dual Op Amp*	8-Dip	.39	.33	.26
NJM2070D-ND	Low Voltage Power Amp	8-Dip	.84	.70	.56
NJM2073D-ND	Dual Low Voltage Power Amp*	8-Dip	.87	.73	.58
NJM2073M-ND	Dual Low Voltage Power Amp*	8-DMP	.87	.73	.58
NJM2076D-ND	Dual Low Voltage Power Amp*	8-Dip	1.38	1.15	.92
NJM2076M-ND	Dual Low Voltage Power Amp*	8-DMP	1.38	1.15	.92
NJM2082D-ND	Dual J-Fet Input Op Amp*	8-Dip	60	50	40
NJM2082M-ND	Dual J-Fet Input Op Amp	8-DMP	51	43	34
NJM2100D-ND	Dual Op Amp*	8-Dip	60	50	40
NJM2113M-ND	Low Voltage Audio Power Amp*	8-DMP	57	48	38
NJM2119M-ND	Dual Single Supply Op Amp*	8-DMP	1.17	.98	.78
NJM2120M-ND	Op Amp, 2-Input/1-Output Analog Switch	8-DMP	66	55	44
NJM2121M-ND	Dual Op Amp, 2-Input/1-Output Analog Switch	8-DMP	54	45	36
NJM2122D-ND	Ultra Low Noise Dual Op Amp	8-Dip	1.17	.98	.78
NJM2125F-TE1CT-ND	Single Supply Op Amp*	5-MTP	63	53	42
NJM2125F-TE1TR-ND	Single Supply Op Amp*	5-MTP	1102.50/3,000		
NJM2135M-TE2CT-ND	Low Voltage Audio Power Amp	8-DMP	63	53	42
NJM2135M-TE2TR-ND	Low Voltage Audio Power Amp	8-DMP	735.00/2,000		
NJM2136M-ND	Ultra Wideband, High Slew Rate, Single Op Amp	8-DMP	1.50	1.25	1.00
NJM2137M-ND	Ultra Wideband, High Slew Rate, Dual Op Amp	8-DMP	1.26	1.05	.84
NJM2138M-ND	Ultra Wideband, High Slew Rate, Quad Op Amp	14-DMP	2.52	2.10	1.68
NJM2140R-TE1CT-ND	Low Saturation Dual Op Amp*	8-VSP	.63	.53	.42
NJM2140R-TE1TR-ND	Low Saturation Dual Op Amp*	8-VSP	735.00/2,000		
NJM2143R-TE1CT-ND	Single Supply Dual Op Amp*	8-VSP	.45	.38	.30
NJM2143R-TE1TR-ND	Single Supply Dual Op Amp*	8-VSP	560.00/2,000		
NJM2149M-ND	Low Voltage Audio Power Amp*	8-DMP	90	75	60
NJM2171AR-TE1CT-ND	Low Voltage Headphone Amp for Portable Audio	10-VSP	90	75	60
NJM2171AR-TE1TR-ND	Low Voltage Headphone Amp for Portable Audio	10-VSP	1050.00/2,000		
NJM2172V-TE1CT-ND	Op Amp with Electric Variable Resistor*	14-SSOP	1.86	1.55	1.24
NJM2172V-TE1TR-ND	Op Amp with Electric Variable Resistor*	14-SSOP	2206.00/2,000		
NJM2174V-TE2CT-ND	Audio Line Amp with Mute Function	14-SSOP	1.47	1.23	.98
NJM2174V-TE2TR-ND	Audio Line Amp with Mute Function	14-SSOP	1715.00/2,000		
NJM2204AD-ND	Integrated IF Limiting Amp	16-Dip	2.52	2.10	1.68
NJM2267M-ND	Dual Video 6dB Amp with 75-Ohm Driver*	8-DMP	.72	.60	.48
NJM2268M-ND	Dual Video 6dB Amplifier	8-DMP	.57	.48	.38
NJM2403D-ND	Single Supply Dual Comparator	8-Dip	54	45	36
NJM2406F-TE1CT-ND	Single Comparator*	5-MTP	42	35	28
NJM2406F-TE1TR-ND	Single Comparator*	5-MTP	735.00/3,000		
NJM2407R-TE1CT-ND	Single Supply Dual Comparator*	8-VSP	.45	.38	.30
NJM2407R-TE1TR-ND	Single Supply Dual Comparator*	8-VSP	560.00/2,000		
NJM2538V-TE1CT-ND	Video Amp with 75-Ohm Driver	20-SSOP	2.94	2.45	1.96
NJM2538V-TE1TR-ND	Video Amp with 75-Ohm Driver	20-SSOP	3430.00/2,000		
NJM2547R1-TE1CT-ND	Low Voltage Video Amp with LPF*	8-TVSP	.99	.83	.66
NJM2547R1-TE1TR-ND	Low Voltage Video Amp with LPF*	8-TVSP	1156.00/2,000		
NJM2575F1-TE1CT-ND	Low Voltage Video Amp with LPF*	6-MTP	.84	.70	.56
NJM2575F1-TE1TR-ND	Low Voltage Video Amp with LPF*	6-MTP	1524.00/3,000		
NJM2576R1-TE1CT-ND	Low Voltage Video Amp with LPF*	8-TVSP	1.17	.98	.78
NJM2576R1-TE1TR-ND	Low Voltage Video Amp with LPF*	8-TVSP	1400.00/2,000		
NJM2580D-ND	Single Supply Wideband 3-Channel Video Amp	14-Dip	2.52	2.10	1.68
NJM2580M-ND	Single Supply Wideband 3-Channel Video Amp	14-DMP	2.10	1.75	1.40
NJM2710V-TE1CT-ND	Ultra High Speed Hex Op Amp	20-SSOP	2.43	2.03	1.62
NJM2710V-TE1TR-ND	Ultra High Speed Hex Op Amp	20-SSOP	2835.00/2,000		
NJM2711F-TE1CT-ND	Ultra High Speed Single Op Amp*	5-MTP	2.43	2.03	1.62
NJM2711F-TE1TR-ND	Ultra High Speed Single Op Amp*	5-MTP	4359.00/3,000		
NJM2716F-TE1CT-ND	Single Supply High-Slew Rate Single Op Amp	5-MTP	1.26	1.05	.84
NJM2716F-TE1TR-ND	Single Supply High-Slew Rate Single Op Amp	5-MTP	2205.00/3,000		
NJM2730F-TE1CT-ND	Low Supply Voltage Single Op Amp*	5-MTP	.84	.70	.56
NJM2730F-TE1TR-ND	Low Supply Voltage Single Op Amp*	5-MTP	2.10	1.75	1.40
NJM2732R1-TE1CT-ND	Full-Swing Input and Output Type Dual Op Amp*	8-TVSP	2486.00/2,000		
NJM2732R1-TE1TR-ND	Full-Swing Input and Output Type Dual Op Amp*	8-TVSP	2.31	1.93	1.54
NJM2737R1-TE1CT-ND	Low Noise, Low Supply Voltage Dual Op Amp	8-TVSP	2695.00/2,000		
NJM2737R1-TE1TR-ND	Low Noise, Low Supply Voltage Dual Op Amp	8-TVSP	2.37	1.98	1.58
NJM2737R1-TE1TR-ND	Low Noise, Low Supply Voltage Dual Op Amp*	8-TVSP	2766.00/2,000		
NJM2770R1-TE1CT-ND	High Power and Low Voltage Audio Power Amp	8-TVSP	1.20	1.00	.80
NJM2770R1-TE1TR-ND	High Power and Low Voltage Audio Power Amp	8-TVSP	1400.00/2,000		
NJM2772V-TE1CT-ND	Low Voltage Headphone Amp for Portable Audio	14-SSOP	1.35	1.13	.90
NJM2772V-TE1TR-ND	Low Voltage Headphone Amp for Portable Audio	14-SSOP	1575.00/2,000		
NJM4558D-ND	Dual Op Amp*	8-Dip	.42	.35	.28
NJM4558M-ND	Dual Op Amp*	8-DMP	.42	.35	.28
NJM4559M-ND	Dual High Gain Op Amp	8-DMP	.42	.35	.28
NJM4560D-ND	High Gain, Wide-Bandwidth, Dual Op Amp*	8-Dip	.42	.35	.28
NJM4562M-ND	High Gain, Wide-Bandwidth, Low Noise, Dual Op Amp	8-DMP	51	43	34
NJM4565D-ND	High Gain, Wide-Bandwidth, Low Noise, Dual Op Amp*	8-Dip	.48	.40	.32
NJM4741M-ND	General Purpose Quad Op Amp*	14-DMP	1.47	1.23	.98
NJM5532M-ND	High Performance Low Noise Dual Op Amp*	8-DMP	.99	.83	.66
NJM5534M-ND	High Performance Low Noise Op Amp*	8-DMP	.69	.58	.46
NJM12901M-ND	Single Supply Quad Comparator	14-DMP	.75	.63	.50
NJM12902M-ND	Single Supply Quad Op Amp	14-DMP	81	68	54
NJM12904M-TE1CT-ND	Single Supply Dual Op Amp*	8-DMP	.39	.33	.26
NJM12904M-TE1TR-ND	Single Supply Dual Op Amp*	8-DMP	490.00/2,000		
NJM13403M-ND	Single Supply Quad Op Amp*	14-DMP	.99	.83	.66
NJM13404D-ND	Single Supply Dual Op Amp	8-Dip	.66	.55	.44

Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25	100
NJM13404M-ND	Single Supply Dual Op Amp	8-DMP	.66	.55	.44
NJM13700D-ND	Dual Op Transconductance Amp	16-Dip	.99	.83	.66
NJM14558D-ND	Dual Op Amp*	8-Dip	.51	.43	.34
NJM14558M-ND	Dual Op Amp	8-DMP	.51	.43	.34
NJMF0P7D-ND	Low Offset Voltage, Low Drift Op Amp*	8-Dip	1.02	.85	.68
NJU7001M-ND	Low Voltage CMOS Op Amp	8-DMP	.69	.58	.46
NJU7004D-ND	Quad Low Voltage CMOS Op Amp	14-Dip	2.01	1.68	1.34
NJU7004M-ND	Quad Low Voltage CMOS Op Amp	14-DMP	2.01	1.68	1.34
NJU7006F-TE1CT-ND	Super Low Operating Current and Low Offset Voltage, Tiny Single CMOS Op Amp	5-MTP	1.86	1.55	1.24
NJU7006F-TE1TR-ND	Super Low Operating Current and Low Offset Voltage, Tiny Single CMOS Op Amp	5-MTP	3255.00/3,000		
NJU7007F3-TE1CT-ND	Low Power, Low Offset Voltage Super Small Sized Single CMOS Op Amp	SC88A	.84	.70	.56
NJU7007F3-TE1TR-ND	Low Power, Low Offset Voltage Super Small Sized Single CMOS Op Amp	SC88A	1470.00/3,000		
NJU7008F3-TE1CT-ND	Low Power, Low Offset Voltage Super Small Sized Single CMOS Op Amp	SC88A	.84	.70	.56
NJU7008F3-TE1TR-ND	Low Power, Low Offset Voltage Super Small Sized Single CMOS Op Amp	SC88A	1470.00/3,000		
NJU7011F-TE1CT-ND	Low Power Tiny Single CMOS Op Amp	5-MTP	.54	.45	.36
NJU7014D-ND	Low Power Dual CMOS Op Amp	8-Dip	1.17	.98	.78
NJU7015D-ND	Low Power Dual CMOS Op Amp	8-Dip	1.17	.98	.78
NJU7016D-ND	Low Power Dual CMOS Op Amp	8-Dip	1.20	1.00	.80
NJU7021D-ND	Single Low Voltage CMOS Op Amp	8-Dip	1.38	1.15	.92
NJU7022M-ND	Dual Low Voltage CMOS Op Amp	8-DMP	.87	.73	.58
NJU7024D-ND	Quad Low Voltage CMOS Op Amp	14-Dip	2.13	1.78	1.42
NJU7024M-ND	Quad Low Voltage CMOS Op Amp	14-DMP	2.25	1.88	1.50
NJU7031D-ND	Low Voltage CMOS Op Amp	8-Dip	.75	.63	.50
NJU7031M-ND	Low Voltage CMOS Op Amp	8-DMP	.75	.63	.50
NJU7032M-ND	Dual Low Voltage CMOS Op Amp*	8-DMP	.99	.83	.66
NJU7034D-ND	Quad Low Voltage CMOS Op Amp	14-Dip	1.71	1.43	1.14
NJU7051D-ND	Low Input Offset Voltage CMOS Op Amp	8-Dip	1.38	1.15	.92
NJU7051M-ND	Low Input Offset Voltage CMOS Op Amp	8-DMP	1.05	.88	.70
NJU7054D-ND	Low Input Offset Voltage CMOS Op Amp	14-Dip	1.53	1.28	1.02
NJU7054M-ND	Quad Low Input Offset Voltage CMOS Op Amp	14-DMP	1.47	1.23	.98
NJU7061D-ND	Single Low Input Offset Voltage CMOS Op Amp	8-Dip	1.02	.85	.68
NJU7062D-ND	Dual Low Input Offset Voltage CMOS Op Amp	8-Dip	.99	.83	.66
NJU7072M-ND	Dual Low Input Offset Voltage CMOS Op Amp	8-DMP	1.68	1.40	1.12
NJU7074D-ND	Quad Low Input Offset Voltage CMOS Op Amp	14-Dip	2.73	2.28	1.82
NJU7074M-ND	Quad Low Input Offset Voltage CMOS Op Amp	14-DMP	2.10	1.75	1.40
NJU7081R-TE1CT-ND	Single Low Voltage CMOS Power Amp	8-VSP	.63	.53	.42
NJU7081R-TE1TR-ND	Single Low Voltage CMOS Power Amp	8-VSP	735.00/2,000		
NJU7082V-TE1CT-ND	Dual Low Voltage CMOS Power Amp	8-SSOP	.72	.60	.48
NJU7091AF-TE1CT-ND	Low Power/Low Offset Voltage Tiny Single CMOS Op Amp	5-MTP	.51	.43	.34
NJU7091AF-TE1TR-ND	Low Power/Low Offset Voltage Tiny Single CMOS Op Amp	5-MTP	892.50/3,000		
NJU7092AF-TE1CT-ND	Low Power/Low Offset Voltage Tiny Single CMOS Op Amp	5-MTP	.39	.33	.26
NJU7092AF-TE1TR-ND	Low Power/Low Offset Voltage Tiny Single CMOS Op Amp	5-MTP	682.50/3,000		
NJU7093AF-TE1CT-ND	Low Power/Low Offset Voltage Tiny Single CMOS Op Amp*	5-MTP	.63	.53	.42
NJU7093AF-TE1TR-ND	Low Power/Low Offset Voltage Tiny Single CMOS Op Amp*	5-MTP	1104.00/3,000		
NJU7094D-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-Dip	1.32	1.10	.88
NJU7094M-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-DMP	1.32	1.10	.88
NJU7094R-TE1CT-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-VSP	2.73	2.28	1.82
NJU7094R-TE1TR-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-VSP	3185.00/3,000		
NJU7094R1-TE1CT-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp*	8-TVSP	2.73	2.28	1.82
NJU7094R1-TE1TR-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp*	8-TVSP	3256.00/2,000		
NJU7094V-TE1CT-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-SSOP	1.47	1.23	.98
NJU7094V-TE1TR-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-SSOP	1715.00/2,000		
NJU7095D-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-Dip	1.26	1.05	.84
NJU7095M-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-DMP	1.26	1.05	.84
NJU7095R-TE1CT-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-VSP	2.73	2.28	1.82
NJU7095R-TE1TR-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-VSP	3185.00/3,000		
NJU7095R1-TE1CT-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-TVSP	2.73	2.28	1.82
NJU7095R1-TE1TR-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-TVSP	3185.00/3,000		
NJU7095V-TE1CT-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-SSOP	2.73	2.28	1.82
NJU7095V-TE1TR-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-SSOP	3185.00/3,000		
NJU7096M-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-DMP	.96	.80	.64
NJU7096R-TE1CT-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp*	8-VSP	2.73	2.28	1.82
NJU7096R-TE1TR-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp*	8-VSP	3256.00/2,000		
NJU7096R1-TE1CT-ND	Low Power/Low Offset Voltage Dual CMOS Op Amp	8-TV			