

<b>JRC / NJR Corporation DRIVERS (Continued)</b>			
Digi-Key Part No.	Description	Pkg.	Price Each★ 1 25 100
NJM#3777E3-ND	Dual Stepper Motor Driver*	24-EMP	5.13 4.28 3.42
NJM#3777E3-ND	Stepper Motor Driver	24-EMP	5.04 4.20 3.36
NJU6048F-TE1CT-ND	High Efficiency White LED Driver	SOT-23-5	1.68 1.40 1.12
NJU6048F-TE1TR-ND	High Efficiency White LED Driver	SOT-23-5	2940.00/3,000
NJU#6050F-TE2CT-ND	High Efficiency White LED Driver*	SOT-23-5	1.50 1.25 1.00
NJU#6050F-TE2TR-ND	High Efficiency White LED Driver*	SOT-23-5	2625.00/3,000
NJU#6060V-TE1CT-ND	Full Color LED Controller Driver with PWM Control*	10-SSOP	1.47 1.23 .98
NJU#6060V-TE1TR-ND	Full Color LED Controller Driver with PWM Control*	10-SSOP	1750.00/2,000
NJU7325R-TE1CT-ND	Single-Phase DC Brushless Motor Driver	8-VSP	1.05 .88 .70
NJU7325R-TE1TR-ND	Single-Phase DC Brushless Motor Driver	8-VSP	1225.00/2,000
NJU#8711V-TE2CT-ND	3V Operation Switching Driver for Class D Amp*	10-SSOP	2.52 2.10 1.68
NJU#8711V-TE2TR-ND	3V Operation Switching Driver for Class D Amp*	10-SSOP	3256.00/2,000
NJU#8713V-TE1CT-ND	2V Operation Switching Driver for Class D Amp*	14-SSOP	2.73 2.28 1.82
NJU#8713V-TE1TR-ND	2V Operation Switching Driver for Class D Amp*	14-SSOP	2766.00/2,000
NJW4301D-ND	2-Channel Bridge Driver	16-Dip	3.48 2.90 2.32
NJW4301M-ND	2-Channel Bridge Driver	30-SDMP	3.48 2.90 2.32

<b>JRC / NJR Corporation MULTIPLEXER</b>			
Digi-Key Part No.	Description	Pkg.	Price Each★ 1 25 100
NJU40518M-ND	Single 8-Channel Mux	16-DMP	93 .78 .62
NJU40538D-ND	Triple 2-Channel Mux	16-Dip	96 .80 .64

<b>JRC / NJR Corporation POWER MANAGEMENT</b>			
Digi-Key Part No.	Description	Pkg.	Price Each★ 1 25 100
NJM#78L12L2A-ND	12V, 100mA, Positive Voltage Regulator*	TO-92	.36 .30 .24
NJM#78L805BD-ND	Series Regulator with Reset Function	8-Dip	.72 .60 .48
NJM#78L805BM-ND	Series Regulator with Reset Function	8-DMP	.45 .38 .30
NJM#78L805UA-ND	5V, 100mA, Positive Voltage Regulator*	SOT-89	.39 .33 .26
NJM#78L806UA-ND	6V, 100mA, Positive Voltage Regulator*	SOT-89	.39 .33 .26
NJM#78L808UA-ND	8V, 100mA, Positive Voltage Regulator*	SOT-89	.39 .33 .26
NJM#78L809UA-ND	9V, 100mA, Positive Voltage Regulator*	SOT-89	.39 .33 .26
NJM#78L12UA-ND	12V, 100mA, Positive Voltage Regulator*	SOT-89	.39 .33 .26
NJM#78L15UA-ND	15V, 100mA, Positive Voltage Regulator*	SOT-89	.39 .33 .26
NJM#78L20UA-ND	20V, 100mA, Positive Voltage Regulator*	SOT-89	.39 .33 .26
NJM#78LR05BUTE1CT-ND	Series Regulator with Reset Function*	SOT-89-5	.63 .53 .42
NJM#78LR05BUTE1TR-ND	Series Regulator with Reset Function*	SOT-89-5	367.50/1,000
NJM#78LR05DD-ND	Series Regulator with Reset Function	8-Dip	.72 .60 .48
NJM#78LR05DU-TE1CT-ND	Series Regulator with Reset Function	SOT-89-5	.60 .50 .40
NJM#78LR05DU-TE1TR-ND	Series Regulator with Reset Function	SOT-89-5	350.00/1,000
NJM#78M05FA-ND	5V, 500mA, Positive Voltage Reg. with Isolated Tab*	TO-220F	.57 .48 .38
NJM#78M09FA-ND	9V, 500mA, Positive Voltage Reg. with Isolated Tab*	TO-220F	.57 .48 .38
NJM#78M12FA-ND	12V, 500mA, Positive Voltage Reg. with Isolated Tab*	TO-220F	.57 .48 .38
NJM#78M15FA-ND	15V, 500mA, Positive Voltage Reg. with Isolated Tab*	TO-220F	.57 .48 .38
NJM#78M24FA-ND	24V, 500mA, Positive Voltage Reg. with Isolated Tab*	TO-220F	.57 .48 .38
NJM#79L05UA-ND	5V, 100mA, Negative Voltage Regulator*	SOT-89	.45 .38 .30
NJM#79L08UA-ND	8V, 100mA, Negative Voltage Regulator*	SOT-89	.45 .38 .30
NJM#79L09UA-TE1CT-ND	9V, 100mA, Negative Voltage Regulator*	SOT-89	.45 .38 .30
NJM#79L12L2A-ND	12V, 100mA, Negative Voltage Regulator*	TO-92	.42 .35 .28
NJM#79L12UA-ND	12V, 100mA, Negative Voltage Regulator*	SOT-89	.45 .38 .30
NJM#79L15UA-ND	15V, 100mA, Negative Voltage Regulator*	SOT-89	.45 .38 .30
NJM#79L15UA-ND	15V, 100mA, Negative Voltage Regulator*	SOT-89	.45 .38 .30
NJM#79L24UA-ND	24V, 100mA, Negative Voltage Regulator*	SOT-89	.45 .38 .30
NJM#79M05FA-ND	5V, 500mA, Negative Voltage Regulator with Isolated Tab*	TO-220F	.63 .53 .42
NJM#79M08FA-ND	8V, 500mA, Negative Voltage Regulator with Isolated Tab*	TO-220F	.69 .58 .46
NJM#79M15FA-ND	15V, 500mA, Negative Voltage Regulator with Isolated Tab	TO-220F	.69 .58 .46
NJM#79M18FA-ND	18V, 500mA, Negative Voltage Regulator with Isolated Tab	TO-220F	.69 .58 .46
NJM#79M24FA-ND	24V, 500mA, Negative Voltage Regulator with Isolated Tab	TO-220F	.69 .58 .46
NJM3170L1-TE1CT-ND	Adjustable 3-Terminal Positive Voltage Regulator	TO-252	.90 .75 .60
NJM3170L1-TE1TR-ND	Adjustable 3-Terminal Positive Voltage Regulator	TO-252	1575.00/3,000
NJM3170L1-TE1CT-ND	Adjustable 3-Terminal Positive Voltage Regulator*	TO-252	.87 .73 .58
NJM3170L1-TE1TR-ND	Adjustable 3-Terminal Positive Voltage Regulator*	TO-252	1524.00/3,000
NJM#317F-ND	Adjustable 1.5A Voltage Regulator with Isolated Tab*	TO-220F	.87 .73 .58
NJM#431D-ND	Adjustable Precision Shunt Regulator	8-Dip	.48 .40 .32
NJM#431E-ND	Adjustable Precision Shunt Regulator	8-SOIC	.42 .35 .28
NJM#431L-ND	Adjustable Precision Shunt Regulator	TO-92	.42 .35 .28
NJM#431M-ND	Adjustable Precision Shunt Regulator	8-DMP	.54 .45 .36
NJM#723M-ND	Precision Voltage Regulator	14-DMP	.54 .45 .36
NJM#723M-ND	Precision Voltage Regulator*	14-DMP	.72 .60 .48
NJM#72355D-ND	2-Output High Voltage Switching Regulator*	18-Dip	2.58 2.15 1.72
NJM#72360D-ND	DC/DC Converter Control IC*	8-Dip	.84 .70 .56
NJM#72370R2-TE1CT-ND	2.0V, Low Dropout Voltage Regulator with On/Off Control	8-VSP	.60 .50 .40
NJM#72370R2-TE1TR-ND	2.0V, Low Dropout Voltage Regulator with On/Off Control	8-VSP	700.00/2,000
NJM#72370R3-TE1CT-ND	3.0V, Low Dropout Voltage Regulator with On/Off Control	8-VSP	.60 .50 .40
NJM#72370R3-TE1TR-ND	3.0V, Low Dropout Voltage Regulator with On/Off Control	8-VSP	700.00/2,000
NJM#72370R3-TE1CT-ND	3.7V, Low Dropout Voltage Regulator with On/Off Control	8-VSP	.60 .50 .40
NJM#72370R3-TE1TR-ND	3.7V, Low Dropout Voltage Regulator with On/Off Control	8-VSP	700.00/2,000
NJM#72370U3-TE1CT-ND	3.0V, Low Dropout Voltage Regulator with On/Off Control	SOT-89-5	.60 .50 .40
NJM#72373AF-TE1CT-ND	Adjustable High Precision Shunt Regulator	5-MTP	.66 .55 .44
NJM#72373AF-TE1TR-ND	Adjustable High Precision Shunt Regulator	5-MTP	1155.00/3,000
NJM#72373AU-TE1CT-ND	Adjustable High Precision Shunt Regulator	SOT-89	.84 .70 .56
NJM#72373AU-TE1TR-ND	Adjustable High Precision Shunt Regulator	SOT-89	490.00/1,000
NJM#2384D-ND	DC/DC Converter Control	14-Dip	2.10 1.75 1.40
NJM#2391D1.03TE1CT-ND	3V, Low Dropout Voltage Regulator	TO-252	.84 .70 .56
NJM#2391D1.03TE1TR-ND	3V, Low Dropout Voltage Regulator	TO-252	1524.00/3,000
NJM#2396F05-ND	Low Dropout Voltage Regulator	TO-220F-4	1.14 .95 .76
NJM#2396F63-ND	Low Dropout Voltage Regulator	TO-220F-4	1.05 .88 .70
NJM#2397F-ND	Adjustable Low Dropout Voltage Regulator	TO-220F-4	1.14 .95 .76
NJM#2800F3342TE1CT-ND	3.3V, Low Dropout Voltage Regulator with Reset	5-MTP	1.05 .88 .70
NJM#2800F3342TE1TR-ND	3.3V, Low Dropout Voltage Regulator with Reset	5-MTP	1837.50/3,000
NJM#2800U3342TE1CT-ND	3.3V, Low Dropout Voltage Regulator with Reset	SOT-89-5	1.05 .88 .70
NJM#2800U3342TE1TR-ND	3.3V, Low Dropout Voltage Regulator with Reset	SOT-89-5	630.00/1,000
NJM#2845DL118TE1CT-ND	1.8V, Low Dropout Voltage Regulator	TO-252	.63 .53 .42
NJM#2845DL118TE1TR-ND	1.8V, Low Dropout Voltage Regulator	TO-252	1102.50/3,000

Digi-Key Part No.	Description	Pkg.	Price Each★ 1 25 100
NJM#2845DL123TE1CT-ND	2.3V, Low Dropout Voltage Regulator	TO-252	.63 .53 .42
NJM#2845DL123TE1TR-ND	2.3V, Low Dropout Voltage Regulator	TO-252	1102.50/3,000
NJM#2845DL125TE1CT-ND	2.5V, Low Dropout Voltage Regulator	TO-252	.63 .53 .42
NJM#2845DL103TE1CT-ND	3V, Low Dropout Voltage Regulator	TO-252	.63 .53 .42
NJM#2845DL103TE1TR-ND	3V, Low Dropout Voltage Regulator	TO-252	1102.50/3,000
NJM#2846DL303TE1CT-ND	3V, Low Dropout Voltage Regulator	TO-252-5	.81 .68 .54
NJM#2846DL303TE1TR-ND	3V, Low Dropout Voltage Regulator	TO-252-5	1417.50/3,000
NJM#2846DL305TE1CT-ND	5V, Low Dropout Voltage Regulator	TO-252-5	.81 .68 .54
NJM#2846DL305TE1TR-ND	5V, Low Dropout Voltage Regulator	TO-252-5	1417.50/3,000
NJM#2846DL318TE1CT-ND	1.8V, Low Dropout Voltage Regulator	TO-252-5	.81 .68 .54
NJM#2846DL318TE1TR-ND	1.8V, Low Dropout Voltage Regulator	TO-252-5	1417.50/3,000
NJM#2846DL323TE1CT-ND	2.3V, Low Dropout Voltage Regulator	TO-252-5	.81 .68 .54
NJM#2846DL323TE1TR-ND	2.3V, Low Dropout Voltage Regulator	TO-252-5	1417.50/3,000
NJM#2860F3-25TE1CT-ND	Low Dropout Voltage Regulator	SC-88A	.45 .38 .30
NJM#2860F3-25TE1TR-ND	Low Dropout Voltage Regulator	SC-88A	787.50/3,000
NJM#2860F3-33TE1CT-ND	Low Dropout Voltage Regulator	SC-88A	.45 .38 .30
NJM#2860F3-33TE1TR-ND	Low Dropout Voltage Regulator	SC-88A	787.50/3,000
NJM#2860F3-47TE1CT-ND	Low Dropout Voltage Regulator	SC-88A	.45 .38 .30
NJM#2860F3-47TE1TR-ND	Low Dropout Voltage Regulator	SC-88A	787.50/3,000
NJM#2863F03-TE1CT-ND	3V, Ultra Low Noise Low Dropout Voltage Regulator	5-MTP	.45 .38 .30
NJM#2863F03-TE1TR-ND	3V, Ultra Low Noise Low Dropout Voltage Regulator	5-MTP	787.50/3,000
NJM#2863F28-TE1CT-ND	2.8V, Ultra Low Noise Low Dropout Voltage Regulator	5-MTP	.45 .38 .30
NJM#2863F28-TE1TR-ND	2.8V, Ultra Low Noise Low Dropout Voltage Regulator	5-MTP	787.50/3,000
NJM#2863F29-TE1CT-ND	2.9V, Ultra Low Noise Low Dropout Voltage Regulator	5-MTP	.45 .38 .30
NJM#2863F29-TE1TR-ND	2.9V, Ultra Low Noise Low Dropout Voltage Regulator	5-MTP	787.50/3,000
NJM#2864F03-TE1CT-ND	3V, Ultra Low Noise Low Dropout Voltage Regulator	5-MTP	.45 .38 .30
NJM#2864F03-TE1TR-ND	3V, Ultra Low Noise Low Dropout Voltage Regulator	5-MTP	787.50/3,000
NJM#2865F33TE1CT-ND	3.3V, Low Dropout Voltage Regulator*	SC88A	.48 .40 .32
NJM#2865F33TE1TR-ND	3.3V, Low Dropout Voltage Regulator*	SC88A	840.00/3,000
NJM#2870F21-TE1CT-ND	2.1V, Low Dropout Voltage Regulator	5-MTP	.42 .35 .28
NJM#2870F21-TE1TR-ND	2.1V, Low Dropout Voltage Regulator	5-MTP	735.00/3,000
NJM#2870F33-TE1CT-ND	3.3V, Low Dropout Voltage Regulator*	5-MTP	.39 .33 .26
NJM#2870F33-TE1TR-ND	3.3V, Low Dropout Voltage Regulator*	5-MTP	682.50/3,000
NJM#2870F48-TE1CT-ND	4.8V, Low Dropout Voltage Regulator	5-MTP	.42 .35 .28
NJM#2870F48-TE1TR-ND	4.8V, Low Dropout Voltage Regulator	5-MTP	735.00/3,000
NJM#2871AF25TE1CT-ND	2.5V, Low Dropout Voltage Regulator*	5-MTP	.48 .40 .32
NJM#2871AF25TE1TR-ND	2.5V, Low Dropout Voltage Regulator*	5-MTP	840.00/3,000
NJM#2880U21-TE1CT-ND	2.1V, Low Dropout Voltage Regulator	SOT-89-5	.75 .63 .50
NJM#2880U21-TE1TR-ND	2.1V, Low Dropout Voltage Regulator	SOT-89-5	437.50/1,000
NJM#2881F28-TE1CT-ND	2.8V, Low Dropout Voltage Regulator*	SOT-23-5	.54 .45 .36
NJM#2881F28-TE1TR-ND	2.8V, Low Dropout Voltage Regulator*	SOT-23-5	999.00/3,000
NJM#2886DL233TE1CT-ND	3.3V, Low Dropout Voltage Regulator	TO-252-5	.96 .80 .64
NJM#2886DL233TE1TR-ND	3.3V, Low Dropout Voltage Regulator	TO-252-5	1680.00/3,000
NJM#2930F05-ND	5V, Low Dropout Voltage Regulator	TO-220F	.72 .60 .48
NJM#2930F85-ND	8.5V, Low Dropout Voltage Regulator	TO-220F	.72 .60 .48
NJM#2930L85-ND	8.5V, Low Dropout Voltage Regulator	TO-92	.54 .45 .36
NJM#7905FA-ND	5V, 1.5A, Negative Voltage Regulator with Isolated Tab	TO-220F	.93 .78 .62
NJM#7905FA-ND	5V, 1.5A, Negative Voltage Regulator with Isolated Tab*	TO-220F	.78 .65 .52
NJM#7908FA-ND	8V, 1.5A, Negative Voltage Regulator with Isolated Tab*	TO-220F	.78 .65 .52
NJM#7909FA-ND	9V, 1.5A, Negative Voltage Regulator with Isolated Tab*	TO-220F	.78 .65 .52
NJM#7912FA-ND	12V, 1.5A, Negative Voltage Regulator with Isolated Tab*	TO-220F	.78 .65 .52
NJM#7915FA-ND	15V, 1.5A, Negative Voltage Regulator with Isolated Tab*	TO-220F	.78 .65 .52
NJM#7918FA-ND	18V, 1.5A, Negative Voltage Regulator with Isolated Tab*	TO-220F	.93 .78 .62
NJM#7918FA-ND	18V, 1.5A, Negative Voltage Regulator with Isolated Tab*	TO-220F	.78 .65 .52
NJM#7924FA-ND	24V, 1.5A, Negative Voltage Regulator with Isolated Tab	TO-220F	.93 .78 .62
NJM#7924FA-ND	24V, 1.5A, Negative Voltage Regulator with Isolated Tab*	TO-220F	.78 .65 .52
NJU#7201L12-ND	1.2V, CMOS 3-Terminal Positive Voltage Regulator	TO-92	.60 .50 .40
NJU#7201L232-ND	3.2V, CMOS 3-Terminal Positive Voltage Regulator*	TO-92	.60 .50 .40
NJU#7201L55-ND	5.5V, CMOS 3-Terminal Positive Voltage Regulator	TO-92	.63 .53 .42
NJU#7201U32-ND	3.2V, CMOS 3-Terminal Positive Voltage Regulator*	SOT-89	.63 .53 .42
NJU#7211L50-ND	-5.0V, CMOS 3-Terminal Negative Voltage Regulator	TO-92	.72 .60 .48
NJU#7222L50-ND	5V, High Prec./Output Current CMOS 3-Terminal Voltage Reg.	TO-92	.84 .70 .56
NJU#7222U30-ND	3V, High Prec./Output Current CMOS 3-Terminal Voltage Reg.	SOT-89	.66 .55 .44
NJU#7223U50-ND	5V, High Prec./Output Current CMOS 3-Terminal Voltage Reg.	SOT-89	.66 .55 .44
NJU#7223F18-ND	1.8V, 500mA Low Dropout Voltage Regulator	TO-220F	.93 .78 .62
NJU#7223F50-ND	5V, 500mA Low Dropout Voltage Regulator*	TO-220F	.93 .78 .62
NJU#7231F12-TE1CT-ND	1.2V, High Precision CMOS 3-Terminal Voltage Regulator	5-MTP	.60 .50 .40
NJU#7231F12-TE1TR-ND	1.2V, High Precision CMOS 3-Terminal Voltage Regulator	5-MTP	1050.00/3,000
NJU#7231F28-TE1CT-ND	2.8V, High Precision CMOS 3-Terminal Voltage Regulator	5-MTP	.60 .50 .40
NJU#7231F28-TE1TR-ND	2.8V, High Precision CMOS 3-Terminal Voltage Regulator	5-MTP	1050.00/3,000
NJU#7231L12-ND	1.2V, High Precision CMOS 3-Terminal Voltage Regulator	TO-92	.75 .63 .50
NJU#7231L28-ND	2.8V, High Precision CMOS 3-Terminal Voltage Regulator	TO-92	.75 .63 .50
NJU#7231L52-ND	5.2V, High Precision CMOS 3-Terminal Voltage Regulator	TO-92	.75 .63 .50
NJU#7231U18-TE1CT-ND	1.8V, High Precision CMOS 3-Terminal Voltage Regulator	SOT-89	.60 .50 .40
NJU#7231U18-TE1TR-ND	1.8V, High Precision CMOS 3-Terminal Voltage Regulator	SOT-89	350.00/1,000
NJU#7231U30-TE1CT-ND	3V, High Precision CMOS 3-Terminal Voltage Regulator	SOT-89	.60 .50 .40
NJU#7231U30-TE1TR-ND	3V, High Precision CMOS 3-Terminal Voltage Regulator	SOT-89	350.00/1,000
NJU#7231U50-TE1CT-ND	5V, High Precision CMOS 3-Terminal Voltage Regulator	SOT-89	.60 .50 .40
NJU#7231U50-TE1TR-ND	5V, High Precision CMOS 3-Terminal Voltage Regulator	SOT-89	350.00/1,000
NJU#7241F18-TE1CT-ND	1.8V, High Precision LDO 60mA CMOS Voltage Regulator	5-MTP	.69 .58 .46
NJU#7241F18-TE1TR-ND	1.8V, High Precision LDO 60mA CMOS Voltage Regulator	5-MTP	1207.50/3,000
NJU#7241F28-TE1CT-ND	2.8V, High Precision LDO 60mA CMOS Voltage Regulator	5-MTP	.69 .58 .46
NJU#7241F28-TE1TR-ND	2.8V, High Precision LDO 60mA CMOS Voltage Regulator	5-MTP	1207.50/3,000
NJU#7241F40-TE1CT-ND	4V, High Precision LDO 60mA CMOS Voltage Regulator	5-MTP	.69 .58 .46
NJU#7241F40-TE1TR-ND	4V,		